

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192086

Luminaire Tested: **LDA6A25940D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A25940D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2660.1 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192086

CATALOG NUMBER: LDA6A25940D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P1192086

CATALOG NUMBER: LDA6A25940D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	85		90	87	85		89
6	97	90	86	83	96	90	86	83	88	85	82		87	84	82		86
7	94	87	83	80	93	87	82	79	85	82	79		84	81	79		83
8	91	84	80	77	90	84	79	77	83	79	76		82	78	76		81
9	88	81	77	74	87	81	77	74	80	76	74		79	76	73		79
10	86	79	74	72	85	78	74	71	78	74	71		77	74	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	428540
5°	408952
10°	349381
15°	286040
20°	183072
25°	70528
30°	14464
35°	3841
40°	1209
45°	380
50°	162
55°	105
60°	121
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P1192086
 CATALOG NUMBER: LDA6A25940D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	669.3	25.2
10°-20°	1345.4	50.6
20°-30°	589.7	22.2
30°-40°	49.3	1.9
40°-50°	4.9	0.2
50°-60°	1.1	0.0
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2604.4	97.9
0°-40°	2653.7	99.8
0°-60°	2659.7	100.0
0°-90°	2660.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2660.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7817	
5°	7432	669
15°	5040	1345
25°	1166	590
35°	57	49
45°	5	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1192086

CATALOG NUMBER: LDA6A25940D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7817.2
1°	7779.7
2°	7718.3
3°	7648.1
4°	7559.1
5°	7431.5
6°	7249.6
7°	7014.2
8°	6756.0
9°	6510.7
10°	6276.4
11°	6041.0
12°	5811.5
13°	5573.1
14°	5319.9
15°	5040.0
17.5°	4179.6
20°	3138.1
22.5°	2049.3
25°	1166.0
27.5°	542.9
30°	228.5
32.5°	118.7
35°	57.4
37.5°	30.6
40°	16.9
42.5°	9.0
45°	4.9
47.5°	3.0
50°	1.9
52.5°	1.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1192086
CATALOG NUMBER: LDA6A25940D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	0.0
87.5°	0.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)