

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192142

Luminaire Tested: **LDA6A35930D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A35930D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3445.9 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192142

CATALOG NUMBER: LDA6A35930D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot



TEST NUMBER: P1192142

CATALOG NUMBER: LDA6A35930D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83		
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	81	78	77		
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75		
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72		
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555164
5°	529792
10°	452608
15°	370558
20°	237163
25°	91372
30°	18731
35°	4966
40°	1553
45°	496
50°	213
55°	115
60°	132
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P1192142

CATALOG NUMBER: LDA6A35930D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	867.1	25.2
10°-20°	1743.0	50.6
20°-30°	763.9	22.2
30°-40°	63.9	1.9
40°-50°	6.4	0.2
50°-60°	1.2	0.0
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3374.0	97.9
0°-40°	3437.8	99.8
0°-60°	3445.4	100.0
0°-90°	3445.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10127	
5°	9627	867
15°	6529	1743
25°	1511	764
35°	74	64
45°	6	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1192142

CATALOG NUMBER: LDA6A35930D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	10127.0
1°	10078.4
2°	9998.8
3°	9908.0
4°	9792.6
5°	9627.4
6°	9391.7
7°	9086.6
8°	8752.3
9°	8434.4
10°	8130.8
11°	7825.8
12°	7528.7
13°	7219.9
14°	6892.0
15°	6529.2
17.5°	5414.6
20°	4065.3
22.5°	2654.8
25°	1510.6
27.5°	703.5
30°	295.9
32.5°	153.9
35°	74.2
37.5°	39.7
40°	21.7
42.5°	11.6
45°	6.4
47.5°	3.9
50°	2.5
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192142

CATALOG NUMBER: LDA6A35930D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	0.0
87.5°	0.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)