

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192507

Luminaire Tested: **LDA6A55950D010TE LARH40FL 6LFC1H**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26683)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH40FL 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5708.8 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192507

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LFC1H

Luminous Intensity Polar Plot





TEST NUMBER: P1192507

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	104		103	101	100		99
2	110	107	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	97	94	98	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	88	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	92	85	81	77	91	85	80	77	83	80	77		82	79	76		81
8	89	82	77	74	88	81	77	74	80	77	74		80	76	73		79
9	86	79	74	71	85	78	74	71	78	74	71		77	73	71		76
10	84	76	72	69	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	779093
5°	703443
10°	640146
15°	585179
20°	427078
25°	210339
30°	45577
35°	8660
40°	2311
45°	1023
50°	606
55°	487
60°	450
65°	389
70°	321
75°	212
80°	0
85°	0



TEST NUMBER: P1192507

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1182.3	20.7
10°-20°	2769.7	48.5
20°-30°	1597.8	28.0
30°-40°	138.9	2.4
40°-50°	11.6	0.2
50°-60°	4.6	0.1
60°-70°	2.7	0.0
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5549.8	97.2
0°-40°	5688.7	99.6
0°-60°	5705.0	99.9
0°-90°	5708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5708.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14212	
5°	12783	###
15°	10311	2770
25°	3477	1598
35°	129	139
45°	13	12
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1192507

CATALOG NUMBER: LDA6A55950D010TE LARH40FL 6LFC1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	14211.8
2.5°	13498.9
5°	12783.0
7.5°	12113.6
10°	11499.8
12.5°	10971.0
15°	10310.8
17.5°	9191.3
20°	7320.7
22.5°	5299.4
25°	3477.4
27.5°	1801.8
30°	720.0
32.5°	378.1
35°	129.4
37.5°	53.6
40°	32.3
42.5°	20.3
45°	13.2
47.5°	8.1
50°	7.1
52.5°	6.0
55°	5.1
57.5°	4.1
60°	4.1
62.5°	3.0
65°	3.0
67.5°	2.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)