

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192663

Luminaire Tested: **LDA6A65950D010TE LARH20SP 6LA1LI**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26676)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH20SP 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5640.8 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192663

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LA1LI

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192663

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96		
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93		
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	90		
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	87		
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84		
6	98	91	87	84	96	91	87	84	89	86	83	88	85	83	87	84	82	81		
7	95	88	84	81	94	87	83	81	86	83	80	85	82	80	84	82	79	78		
8	92	85	81	78	91	85	81	78	84	80	78	83	80	77	82	79	77	76		
9	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74		
10	87	80	76	73	86	80	76	73	79	75	73	78	75	73	78	75	72	71		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1248436
5°	1085359
10°	735413
15°	509793
20°	355263
25°	204429
30°	16034
35°	1318
40°	658
45°	442
50°	401
55°	325
60°	373
65°	441
70°	369
75°	233
80°	347
85°	0



TEST NUMBER: P1192663

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1678.5	29.8
10°-20°	2528.2	44.8
20°-30°	1392.8	24.7
30°-40°	28.8	0.5
40°-50°	4.7	0.1
50°-60°	3.5	0.1
60°-70°	3.0	0.1
70°-80°	1.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5599.5	99.3
0°-40°	5628.3	99.8
0°-60°	5636.4	99.9
0°-90°	5640.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5640.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22773	
5°	19723	###
15°	8982	2528
25°	3380	1393
35°	20	29
45°	6	5
55°	3	3
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1192663

CATALOG NUMBER: LDA6A65950D010TE LARH20SP 6LA1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	22773.3
2.5°	22092.1
5°	19723.2
7.5°	16764.5
10°	13211.2
12.5°	10879.4
15°	8982.5
17.5°	7572.7
20°	6089.7
22.5°	4763.1
25°	3379.7
27.5°	1442.4
30°	253.3
32.5°	32.3
35°	19.7
37.5°	12.8
40°	9.2
42.5°	7.0
45°	5.7
47.5°	4.7
50°	4.7
52.5°	4.7
55°	3.4
57.5°	3.4
60°	3.4
62.5°	3.4
65°	3.4
67.5°	2.3
70°	2.3
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)