

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192728

Luminaire Tested: **LDA6A70935D010TE LARH40FL 6LFC1H**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26683)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH40FL 6LFC1H
Description: PORTFOLIO 6" Flat Cone, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6941.1 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192728

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LFC1H

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192728

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LFC1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96		
2	110	107	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	88	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	92	85	81	77	91	85	80	77	83	80	77	82	79	76	81	78	76	75		
8	89	82	77	74	88	81	77	74	80	77	74	80	76	73	79	76	73	72		
9	86	79	74	71	85	78	74	71	78	74	71	77	73	71	76	73	70	69		
10	84	76	72	69	83	76	71	68	75	71	68	74	71	68	74	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	947260
5°	855281
10°	778331
15°	711485
20°	519270
25°	255735
30°	55407
35°	10527
40°	2820
45°	1240
50°	733
55°	593
60°	537
65°	480
70°	385
75°	275
80°	0
85°	0



TEST NUMBER: P1192728

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LFC1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1437.5	20.7
10°-20°	3367.6	48.5
20°-30°	1942.6	28.0
30°-40°	168.9	2.4
40°-50°	14.1	0.2
50°-60°	5.6	0.1
60°-70°	3.3	0.0
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6747.8	97.2
0°-40°	6916.7	99.6
0°-60°	6936.4	99.9
0°-90°	6941.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6941.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17279	
5°	15542	###
15°	12536	3368
25°	4228	1943
35°	157	169
45°	16	14
55°	6	6
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1192728

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LFC1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	17279.4
2.5°	16412.6
5°	15542.2
7.5°	14728.3
10°	13982.2
12.5°	13339.1
15°	12536.3
17.5°	11175.4
20°	8901.0
22.5°	6443.4
25°	4227.9
27.5°	2190.9
30°	875.3
32.5°	459.9
35°	157.3
37.5°	65.1
40°	39.4
42.5°	24.6
45°	16.0
47.5°	9.8
50°	8.6
52.5°	7.3
55°	6.2
57.5°	4.9
60°	4.9
62.5°	3.7
65°	3.7
67.5°	2.4
70°	2.4
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)