

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192795

Luminaire Tested: **LDA6A75930D010TE LARH40FL 6LAL1LI**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26680)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH40FL 6LAL1LI
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6409.7 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192795

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LAL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1192795

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LAL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	112	110	108		112	110	108	107		106	105	103			103	101	100			96
2	110	107	103	101		108	105	102	99		102	99	97			99	97	95			92
3	106	101	97	94		105	100	96	94		98	95	92			95	93	91			88
4	103	97	92	89		101	96	92	89		94	90	88			92	89	87			84
5	99	93	88	85		98	92	87	84		90	86	84			88	85	83			81
6	96	89	84	81		94	88	84	80		87	83	80			85	82	79			78
7	92	85	80	77		91	85	80	77		83	79	77			82	79	76			75
8	89	82	77	74		88	81	77	74		80	76	74			79	76	73			72
9	86	79	74	71		85	78	74	71		78	74	71			77	73	71			69
10	83	76	71	68		83	76	71	68		75	71	68			74	71	68			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1030438
5°	804532
10°	705542
15°	644816
20°	470995
25°	229828
30°	56091
35°	12822
40°	2755
45°	1256
50°	640
55°	946
60°	954
65°	804
70°	593
75°	530
80°	379
85°	0



TEST NUMBER: P1192795

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LAL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1354.5	21.1
10°-20°	3051.1	47.6
20°-30°	1797.3	28.0
30°-40°	175.4	2.7
40°-50°	14.0	0.2
50°-60°	7.9	0.1
60°-70°	6.1	0.1
70°-80°	2.9	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6202.8	96.8
0°-40°	6378.2	99.5
0°-60°	6400.2	99.9
0°-90°	6409.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6409.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18797	
5°	14620	###
15°	11362	3051
25°	3800	1797
35°	192	175
45°	16	14
55°	10	8
65°	6	6
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P1192795

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LAL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	18796.7
2.5°	16824.0
5°	14620.0
7.5°	13519.7
10°	12674.6
12.5°	12059.9
15°	11361.6
17.5°	10133.2
20°	8073.5
22.5°	5823.2
25°	3799.6
27.5°	2267.6
30°	886.1
32.5°	464.2
35°	191.6
37.5°	63.4
40°	38.5
42.5°	24.9
45°	16.2
47.5°	9.9
50°	7.5
52.5°	8.7
55°	9.9
57.5°	8.7
60°	8.7
62.5°	7.5
65°	6.2
67.5°	5.0
70°	3.7
72.5°	3.7
75°	2.5
77.5°	2.5
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)