

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212649

Luminaire Tested: **LDSQA6A60930D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60930D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5590.6 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212649

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P1212649

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	109		112	110	108	107		106	105	104		103	101	100		99	98	98
2	110	107	103	101		108	105	102	100		102	99	97		99	97	95		96	95	93
3	107	101	98	94		105	100	97	94		98	95	92		95	93	91		93	91	89
4	103	97	93	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	88	84		90	87	84		89	85	83		87	85	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	92	85	81	77		91	85	80	77		84	80	77		82	79	76		81	78	76
8	89	82	77	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	86	79	74	71		85	79	74	71		78	74	71		77	73	71		76	73	71
10	84	76	72	69		83	76	71	69		75	71	68		74	71	68		74	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	623015
5°	542391
10°	490069
15°	447791
20°	327898
25°	161803
30°	35925
35°	7280
40°	1214
45°	359
50°	60
55°	68
60°	78
65°	92
70°	113
75°	0
80°	0
85°	0



TEST NUMBER: P1212649

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1163.3	20.8
10°-20°	2699.3	48.3
20°-30°	1583.3	28.3
30°-40°	137.0	2.5
40°-50°	5.9	0.1
50°-60°	0.8	0.0
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5445.9	97.4
0°-40°	5582.9	99.9
0°-60°	5589.6	100.0
0°-90°	5590.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5590.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14470	
5°	12550	###
15°	10046	2699
25°	3406	1583
35°	138	137
45°	6	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1212649

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	14470.0
2.5°	13597.1
5°	12549.5
7.5°	11852.4
10°	11209.3
12.5°	10674.3
15°	10045.9
17.5°	8960.0
20°	7156.4
22.5°	5175.2
25°	3405.9
27.5°	1919.4
30°	722.6
32.5°	373.0
35°	138.5
37.5°	42.2
40°	21.6
42.5°	11.7
45°	5.9
47.5°	2.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)