

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219660

Luminaire Tested: **LDSQA6A70950D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70950D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6251.3 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219660

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P1219660

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	115	112	110	109	112	110	108	107		106	105	104			103	101	100			99
2	110	107	103	101	108	105	102	100		102	99	97			99	97	95			96
3	107	101	98	94	105	100	97	94		98	95	92			95	93	91			93
4	103	97	93	89	101	96	92	89		94	90	88			92	89	87			90
5	99	93	88	85	98	92	88	84		90	87	84			89	85	83			87
6	96	89	84	81	94	88	84	81		87	83	80			85	82	80			84
7	92	85	81	77	91	85	80	77		84	80	77			82	79	76			81
8	89	82	77	74	88	82	77	74		81	77	74			80	76	74			79
9	86	79	74	71	85	79	74	71		78	74	71			77	73	71			76
10	84	76	72	69	83	76	71	69		75	71	68			74	71	68			74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	696628
5°	606478
10°	547980
15°	500701
20°	366643
25°	180920
30°	40171
35°	8136
40°	1360
45°	408
50°	67
55°	75
60°	86
65°	102
70°	126
75°	0
80°	0
85°	0



TEST NUMBER: P1219660

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1300.8	20.8
10°-20°	3018.2	48.3
20°-30°	1770.4	28.3
30°-40°	153.2	2.5
40°-50°	6.7	0.1
50°-60°	0.9	0.0
60°-70°	1.0	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6089.4	97.4
0°-40°	6242.6	99.9
0°-60°	6250.1	100.0
0°-90°	6251.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6251.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16180	
5°	14032	###
15°	11233	3018
25°	3808	1770
35°	155	153
45°	7	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1219660

CATALOG NUMBER: LDSQA6A70950D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	16179.7
2.5°	15203.7
5°	14032.3
7.5°	13252.8
10°	12533.9
12.5°	11935.5
15°	11232.9
17.5°	10018.7
20°	8002.0
22.5°	5786.6
25°	3808.3
27.5°	2146.4
30°	808.0
32.5°	417.2
35°	154.8
37.5°	47.2
40°	24.2
42.5°	13.1
45°	6.7
47.5°	3.2
50°	1.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)