

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P400656

Luminaire Tested: **TT-D4-840-U-DL**

Issue Date: 6/3/2020

Test Information

Test Method: LM-79-08
Report Number: P400656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1908-473-26)
Test Lab: INNOVATION CENTER
Issue Date: 6/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: TT-D4-840-U-DL
Description: TOPTIER LED PARKING GARAGE LUMINAIRE
4000K, 80 CRI LEDS AND DRIVE LANE DISTRIBUTION
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5968 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type IV - Short - Non-Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 59.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P400656

CATALOG NUMBER: TT-D4-840-U-DL

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.6 fc
 Type IV - Short - Non-Cutoff

REPORT NUMBER: P400656

CATALOG NUMBER: TT-D4-840-U-DL

Luminous Intensity Polar Plot



REPORT NUMBER: P400656

CATALOG NUMBER: TT-D4-840-U-DL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1739.1	0.0	1739.1
	% Fixture	29.1	0.0	29.1
Street Side	Lumens	4228.9	0.0	4228.9
	% Fixture	70.9	0.0	70.9
Total	Lumens	5968.0	0.0	5968.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.3	0.2
10°-20°	49.5	0.8
20°-30°	117.1	2.0
30°-40°	265.0	4.4
40°-50°	590.7	9.9
50°-60°	1187.5	19.9
60°-70°	1744.2	29.2
70°-80°	1533.7	25.7
80°-90°	466.9	7.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5968.0	100.0
0°-180°	5968.0	100.0

Coefficient of Utilization



REPORT NUMBER: P400656


CATALOG NUMBER: TT-D4-840-U-DL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	104.2	1.7			
FM	(30°-60°)	1397.6	23.4			
FH	(60°-80°)	2381.1	39.9			G2/5000
FVH	(80°-90°)	346.0	5.8			G3/500
BL	(0°-30°)	75.7	1.3	B0/110		
BM	(30°-60°)	645.6	10.8	B1/1000		
BH	(60°-80°)	896.8	15.0	B2/1000		G2/1000
BVH	(80°-90°)	120.9	2.0			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P400656

CATALOG NUMBER: TT-D4-840-U-DL

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	42.5°	45°	55°	65°	75°	85°
0°	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5
2.5°	135.0	133.9	133.9	133.9	132.8	132.8	132.8	132.8	131.7	131.7	131.7
5°	142.8	141.7	142.8	140.6	139.5	139.5	138.4	138.4	137.3	136.1	135.0
7.5°	154.0	152.9	152.9	150.7	149.5	148.4	148.4	146.2	145.1	142.8	140.6
10°	166.3	166.3	165.2	164.0	161.8	159.6	159.6	156.2	155.1	151.8	148.4
12.5°	180.8	180.8	180.8	178.6	176.3	175.2	173.0	170.7	167.4	161.8	158.5
15°	198.6	198.6	198.6	196.4	194.2	191.9	190.8	186.4	180.8	175.2	168.5
17.5°	221.0	218.7	218.7	216.5	214.3	213.1	210.9	206.5	198.6	191.9	183.0
20°	245.5	244.4	243.3	243.3	241.0	238.8	237.7	231.0	222.1	209.8	198.6
22.5°	273.4	272.3	272.3	274.5	273.4	270.1	270.1	260.0	247.7	233.2	216.5
25°	308.0	306.9	309.1	313.6	313.6	311.4	308.0	298.0	280.1	260.0	239.9
27.5°	345.9	344.8	349.3	357.1	359.3	356.0	353.8	342.6	322.5	295.7	266.7
30°	391.7	392.8	405.1	414.0	419.6	417.4	416.3	404.0	371.6	340.4	302.4
32.5°	447.5	444.2	459.8	474.3	484.3	489.9	486.6	472.1	444.2	395.1	347.1
35°	506.6	507.8	526.7	547.9	571.4	573.6	580.3	565.8	527.8	469.8	402.9
37.5°	583.6	574.7	599.3	639.4	667.3	691.9	687.4	678.5	633.9	556.9	465.4
40°	652.8	650.6	685.2	741.0	792.3	828.0	832.5	821.3	762.2	652.8	532.3
42.5°	732.1	738.8	786.8	863.8	941.9	993.2	980.9	975.3	906.2	766.7	623.8
45°	812.4	834.7	896.1	1007.7	1099.2	1172.9	1194.1	1175.1	1090.3	946.3	739.9
47.5°	909.5	939.6	1015.5	1166.2	1315.7	1401.6	1406.1	1463.0	1334.7	1119.3	860.4
50°	1037.8	1051.2	1157.3	1341.4	1546.7	1667.2	1701.8	1703.0	1574.6	1293.4	996.6
52.5°	1163.9	1174.0	1313.5	1551.2	1830.2	1967.4	1975.3	2018.8	1843.6	1574.6	1191.8
55°	1315.7	1311.3	1503.2	1788.9	2118.1	2317.9	2375.9	2435.0	2211.8	1796.7	1303.4
57.5°	1463.0	1456.3	1687.3	2062.3	2512.0	2710.7	2758.7	2716.2	2384.8	1889.3	1358.1
60°	1599.2	1622.6	1903.8	2364.7	2816.7	3006.4	3038.8	2923.8	2496.4	1960.7	1392.7
62.5°	1740.9	1787.8	2128.1	2616.9	3049.9	3186.1	3188.3	3053.3	2682.8	2099.1	1505.4
65°	1873.7	1948.5	2302.2	2832.3	3212.9	3349.0	3364.6	3243.0	2865.8	2219.6	1524.4
67.5°	1990.9	2090.2	2422.8	2948.4	3323.3	3411.5	3419.3	3244.1	2822.3	2170.5	1472.0
70°	2085.7	2166.1	2497.5	2950.6	3246.3	3270.9	3265.3	3078.9	2701.7	2073.5	1383.8
72.5°	2122.6	2188.4	2461.8	2812.2	3019.8	3014.2	3009.7	2837.9	2503.1	1911.6	1256.6
75°	2070.1	2089.1	2266.5	2516.5	2648.2	2679.4	2683.9	2528.8	2196.2	1671.7	1078.0
77.5°	1853.6	1843.6	1979.7	2144.9	2244.2	2266.5	2262.1	2132.6	1841.3	1389.4	903.9
80°	1469.7	1490.9	1575.7	1685.1	1784.4	1809.0	1793.3	1695.1	1432.9	1083.6	694.1
82.5°	1027.8	1053.5	1124.9	1207.5	1282.2	1282.2	1296.7	1201.9	1015.5	777.8	485.4
85°	554.6	540.1	618.2	712.0	765.5	775.6	781.2	749.9	628.3	469.8	287.9
87.5°	91.5	98.2	121.6	186.4	212.0	245.5	261.1	204.2	123.9	79.2	58.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P400656

CATALOG NUMBER: TT-D4-840-U-DL

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5	129.5
2.5°	131.7	130.6	129.5	128.3	128.3	127.2	127.2	127.2	128.3	128.3	128.3
5°	135.0	133.9	132.8	131.7	129.5	129.5	129.5	129.5	129.5	129.5	129.5
7.5°	140.6	138.4	137.3	135.0	132.8	132.8	131.7	131.7	131.7	132.8	131.7
10°	147.3	145.1	142.8	139.5	138.4	137.3	136.1	136.1	137.3	137.3	136.1
12.5°	155.1	154.0	149.5	146.2	144.0	142.8	141.7	142.8	141.7	142.8	142.8
15°	166.3	162.9	157.4	154.0	150.7	149.5	148.4	149.5	149.5	150.7	149.5
17.5°	178.6	174.1	168.5	162.9	158.5	157.4	157.4	157.4	158.5	159.6	158.5
20°	193.1	187.5	179.7	173.0	168.5	167.4	167.4	168.5	169.6	170.7	170.7
22.5°	207.6	203.1	191.9	183.0	180.8	179.7	178.6	180.8	183.0	184.1	185.2
25°	229.9	221.0	207.6	197.5	193.1	193.1	194.2	196.4	197.5	199.8	198.6
27.5°	253.3	243.3	226.5	213.1	209.8	208.7	210.9	213.1	217.6	217.6	216.5
30°	285.7	268.9	247.7	235.5	226.5	227.7	231.0	234.4	238.8	241.0	241.0
32.5°	322.5	304.7	275.6	256.7	252.2	253.3	254.4	260.0	264.5	268.9	265.6
35°	370.5	348.2	312.5	291.3	280.1	279.0	283.5	290.1	294.6	296.8	296.8
37.5°	422.9	393.9	349.3	331.4	318.0	316.9	318.0	323.6	329.2	331.4	335.9
40°	486.6	450.8	398.4	369.4	359.3	357.1	361.6	369.4	369.4	372.7	373.8
42.5°	564.7	518.9	460.9	422.9	410.7	410.7	409.6	416.3	416.3	416.3	414.0
45°	664.0	612.7	536.8	497.7	476.5	465.4	468.7	464.2	463.1	466.5	456.4
47.5°	760.0	695.2	606.0	563.6	542.4	535.7	523.4	520.0	514.5	514.5	500.0
50°	871.6	791.2	705.3	645.0	624.9	606.0	595.9	580.3	563.6	560.2	554.6
52.5°	1057.9	957.5	822.5	757.7	706.4	687.4	664.0	643.9	623.8	608.2	617.1
55°	1133.8	1031.1	902.8	840.3	804.6	786.8	743.2	716.4	686.3	664.0	676.3
57.5°	1171.8	1060.2	940.8	893.9	883.8	867.1	834.7	789.0	754.4	726.5	728.7
60°	1193.0	1075.8	960.8	918.4	912.9	924.0	907.3	876.0	822.5	794.6	791.2
62.5°	1274.4	1151.7	1017.8	957.5	945.2	953.0	957.5	938.5	893.9	857.1	847.0
65°	1291.2	1160.6	1028.9	989.9	991.0	993.2	996.6	976.5	954.1	908.4	899.5
67.5°	1240.9	1112.6	995.4	963.1	965.3	991.0	1011.1	1009.9	985.4	946.3	943.0
70°	1165.1	1040.1	931.8	902.8	908.4	931.8	975.3	997.7	993.2	967.5	973.1
72.5°	1046.8	935.2	840.3	818.0	831.4	853.7	895.0	935.2	958.6	964.2	976.5
75°	908.4	819.1	729.8	716.4	726.5	752.2	790.1	837.0	888.3	916.2	924.0
77.5°	749.9	668.5	602.6	593.7	608.2	631.6	669.6	706.4	764.4	813.5	824.7
80°	587.0	516.7	469.8	462.0	470.9	491.0	520.0	550.2	606.0	643.9	649.5
82.5°	407.3	364.9	334.8	330.3	335.9	343.7	367.2	395.1	426.3	456.4	459.8
85°	236.6	209.8	202.0	195.3	207.6	207.6	213.1	228.8	244.4	246.6	253.3
87.5°	43.5	41.3	42.4	31.2	39.1	27.9	27.9	35.7	26.8	31.2	25.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)