

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P981591

Luminaire Tested: **FFX-CLB-40-AMB-U-VM9-T5**

Issue Date: 04/15/2025

Test Information

Test Method: LM-79-08
Report Number: P981591
Test Lab: INNOVATION CENTER(G3)
Issue Date: 04/15/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: FFX-CLB-40-AMB-U-VM9-T5
Description: FAIRFAX POST TOP FIXTURE w/ ULA ACORN 9 INCH NECK
Light Source: (6) 1500K CCT, 0 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1114.5 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Luminous Opening: Vertical Cylinder (Dia: 1.33' x H: 2.08')
IES Classification: Type V - Short
BUG Rating: B1 - U3 - G1


Input Watts (W): 41.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 16.5%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P981591
 CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 0.2 fc
 Type V - Short - N/A

REPORT NUMBER: P981591
CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5

Luminous Intensity Polar Plot



REPORT NUMBER: P981591

CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	326.7	230.6	557.2
	% Fixture	29.3	20.7	50.0
Street Side	Lumens	326.7	230.6	557.2
	% Fixture	29.3	20.7	50.0
Total	Lumens	653.3	461.1	1114.5
	% Fixture	58.6	41.4	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.2	0.1
10°-20°	8.5	0.8
20°-30°	25.4	2.3
30°-40°	52.2	4.7
40°-50°	81.4	7.3
50°-60°	105.4	9.5
60°-70°	121.5	10.9
70°-80°	129.2	11.6
80°-90°	128.6	11.5
90°-100°	120.1	10.8
100°-110°	105.3	9.4
110°-120°	86.6	7.8
120°-130°	64.7	5.8
130°-140°	42.2	3.8
140°-150°	23.9	2.1
150°-160°	11.8	1.1
160°-170°	5.1	0.5
170°-180°	1.4	0.1
0°-90°	653.3	58.6
0°-180°	1114.5	100.0



REPORT NUMBER: P981591


CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	17.5	1.6			
FM	(30°-60°)	119.5	10.7			
FH	(60°-80°)	125.3	11.2			G0/660
FVH	(80°-90°)	64.3	5.8			G1/100
BL	(0°-30°)	17.5	1.6	B0/110		
BM	(30°-60°)	119.5	10.7	B0/220		
BH	(60°-80°)	125.3	11.2	B1/500		G0/660
BVH	(80°-90°)	64.3	5.8			G1/100
UL	(90°-100°)	120.1	10.8		U3/500	
UH	(100°-180°)	341.0	30.6		U3/500	

BUG Rating: B1-U3-G1

Type V Short





REPORT NUMBER: P981591
CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5

CANDELA DISTRIBUTION (FULL):

0°	
0°	8.0
2.5°	8.1
5°	9.9
7.5°	13.6
10°	18.0
12.5°	23.0
15°	28.7
17.5°	34.2
20°	40.2
22.5°	46.8
25°	54.0
27.5°	61.2
30°	68.5
32.5°	75.8
35°	82.9
37.5°	89.5
40°	95.5
42.5°	100.9
45°	105.4
47.5°	109.3
50°	112.7
52.5°	115.4
55°	117.8
57.5°	119.5
60°	120.9
62.5°	122.0
65°	122.6
67.5°	122.9
70°	122.9
72.5°	122.8
75°	122.3
77.5°	121.6
80°	120.6
82.5°	119.5
85°	118.0
87.5°	116.4
90°	114.5
92.5°	112.5
95°	110.2
97.5°	107.8
100°	105.1
102.5°	102.4
105°	99.5
107.5°	96.6
110°	93.5

REPORT NUMBER: P981591
CATALOG NUMBER: FFX-CLB-40-AMB-U-VM9-T5

CANDELA DISTRIBUTION (continued):

	0°
112.5°	90.4
115°	87.2
117.5°	83.9
120°	80.2
122.5°	76.3
125°	72.0
127.5°	67.6
130°	63.2
132.5°	58.8
135°	54.2
137.5°	49.8
140°	45.5
142.5°	41.5
145°	37.7
147.5°	34.0
150°	30.7
152.5°	27.7
155°	25.0
157.5°	22.6
160°	20.7
162.5°	19.0
165°	17.6
167.5°	16.6
170°	15.8
172.5°	15.1
175°	14.6
177.5°	14.3
180°	14.2

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2501-332-6

Test Date: 03/28/2025

Luminaire Tested: FFX-CLB-AMB-U-FR-T5


Data in this report applies to families of products including FFX-CLB-AMB-U-FR-T5

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2501-332-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 03/31/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **FFX-CLB-AMB-U-FR-T5**
 Description: FAIRFAX ACORN W/ FAIRFAX REFRACTOR AMBER T5

Spectral Parameters

CCT (K):	1477	CRI (Ra):	-16.4		
CIE u':	0.3612	R1:	-26.9	R9:	-362.0
CIE v':	0.5457	R2:	55.7	R10:	34.1
Duv:	0.0143	R3:	19.5	R11:	-85.9
CIE x:	0.5980	R4:	-61.2	R12:	-0.3
CIE y:	0.4014	R5:	-34.3	R13:	-8.9
CIE z:	0.0006	R6:	47.8	R14:	48.3
Peak Wavelength (nm):	599	R7:	-4.8	R15:	-60.0
Dominant Wavelength (nm):	594	R8:	-127.3		
Purity:	99.99006				
Rf:	1.7				
Rg:	0.1				



Test Conditions


Stabilization Time: 152M
 Operation Time: 3H 32M
 Sphere Temperature (°C): 24.9

REPORT NUMBER: SP1-2501-332-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	12/16/2024	6/16/2025
Power Meter	INXT2011004	1/21/2025	1/21/2026
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2501-332-6

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2501-332-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	52	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	23	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	11	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	13	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	23	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	40	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	69	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	118	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	201	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	337	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	566	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	880	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	982	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	633	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	302	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	123	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.21

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	52	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	23	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	11	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	13	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	23	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	40	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	69	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	118	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	201	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	337	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	566	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	880	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	982	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	633	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	302	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	123	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-6

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 0.11


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	52	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	23	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	11	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	0	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	0	NR	810	0	NR	940	0	NR
425	0	NR	555	13	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	23	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	40	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	69	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	118	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	201	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	337	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	566	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	880	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	982	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	633	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	302	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	123	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2501-332-6





TM-30-18

Summary

$R_f = 1.7$
 $R_g = 0.1$
 $CIE R_a = -16.4$
 $R_g = -362.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 90	CES26 = 0	CES51 = 20	CES76 = 0
CES02 = 70	CES27 = 35	CES52 = 3	CES77 = 0
CES03 = 31	CES28 = 28	CES53 = 0	CES78 = 0
CES04 = 77	CES29 = 1	CES54 = 15	CES79 = 3
CES05 = 52	CES30 = 35	CES55 = 8	CES80 = 1
CES06 = 56	CES31 = 1	CES56 = 0	CES81 = 0
CES07 = 42	CES32 = 0	CES57 = 0	CES82 = 52
CES08 = 39	CES33 = 25	CES58 = 0	CES83 = 23
CES09 = 30	CES34 = 1	CES59 = 11	CES84 = 56
CES10 = 88	CES35 = 27	CES60 = 62	CES85 = 10
CES11 = 70	CES36 = 79	CES61 = 15	CES86 = 0
CES12 = 76	CES37 = 8	CES62 = 53	CES87 = 4
CES13 = 48	CES38 = 46	CES63 = 68	CES88 = 2
CES14 = 77	CES39 = 77	CES64 = 0	CES89 = 0
CES15 = 75	CES40 = 53	CES65 = 0	CES90 = 3
CES16 = 50	CES41 = 77	CES66 = 0	CES91 = 57
CES17 = 56	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 60	CES43 = 0	CES68 = 0	CES93 = 3
CES19 = 80	CES44 = 96	CES69 = 30	CES94 = 0
CES20 = 72	CES45 = 2	CES70 = 0	CES95 = 0
CES21 = 94	CES46 = 7	CES71 = 0	CES96 = 3
CES22 = 87	CES47 = 73	CES72 = 44	CES97 = 1
CES23 = 94	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 95	CES49 = 8	CES74 = 60	CES99 = 0
CES25 = 79	CES50 = 12	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)