

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1057060

Luminaire Tested: CB3R-030D-840-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057060
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3R-030D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2281.3 lumens
Efficiency: N/A
Efficacy: 137.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 16.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1057060

CATALOG NUMBER: CB3R-030D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1057060

CATALOG NUMBER: CB3R-030D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	96	98	95	93	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	72	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5391	5391	5391
5°	5365	5369	5399
10°	5341	5334	5334
15°	5259	5259	5228
20°	5174	5122	5076
25°	5044	4981	4892
30°	4920	4792	4677
35°	4791	4613	4450
40°	4618	4398	4208
45°	4461	4207	3947
50°	4300	3979	3693
55°	4125	3758	3451
60°	3935	3530	3177
65°	3715	3270	2890
70°	3459	2966	2575
75°	3137	2603	2293
80°	2733	2183	2030
85°	2110	1843	1843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4461 cd/sqm

TEST NUMBER: P1057060

CATALOG NUMBER: CB3R-030D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.9	3.9
10°-20°	252.6	11.1
20°-30°	367.0	16.1
30°-40°	417.2	18.3
40°-50°	405.0	17.8
50°-60°	342.0	15.0
60°-70°	243.3	10.7
70°-80°	130.0	5.7
80°-90°	34.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.4	31.1
0°-40°	1126.7	49.4
0°-60°	1873.6	82.1
0°-90°	2281.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2281.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	953	953	953	953	953	
5°	945	957	945	944	951	90
15°	898	906	898	893	893	253
25°	808	811	798	787	784	372
35°	694	687	668	648	644	432
45°	558	549	526	501	493	430
55°	418	407	381	356	350	374
65°	278	268	244	222	216	275
75°	144	136	119	107	105	153
85°	32	30	28	28	28	40
90°	0	0	0	0	0	

TEST NUMBER: P1057060

CATALOG NUMBER: CB3R-030D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	952.9	952.9	952.9	952.9	952.9
2.5°	948.0	957.5	949.1	950.2	952.3
5°	944.7	956.6	945.4	944.2	950.8
7.5°	937.4	948.3	936.6	933.9	939.9
10°	929.8	941.8	928.5	925.2	928.5
12.5°	916.3	928.7	918.2	912.7	915.5
15°	898.0	906.0	898.0	892.6	892.6
17.5°	875.7	884.0	869.1	865.3	863.8
20°	859.5	866.7	850.7	845.2	843.2
22.5°	837.8	844.6	831.2	821.9	819.4
25°	808.0	810.7	797.9	787.0	783.7
27.5°	778.1	778.8	761.2	748.0	743.6
30°	753.2	753.9	733.6	719.3	716.0
32.5°	728.3	726.3	707.1	690.1	687.8
35°	693.7	687.0	667.9	648.2	644.3
37.5°	651.8	647.9	625.3	605.5	599.6
40°	625.3	618.7	595.5	575.8	569.8
42.5°	598.8	591.1	567.4	545.4	539.0
45°	557.6	549.0	525.8	500.6	493.3
47.5°	516.2	506.8	481.3	456.9	448.8
50°	488.6	478.7	452.1	428.2	419.6
52.5°	460.5	450.0	423.4	399.0	392.0
55°	418.2	407.0	381.0	356.5	349.9
57.5°	376.0	364.9	339.0	315.9	307.9
60°	347.8	337.3	312.0	288.8	280.8
62.5°	319.2	309.1	284.4	261.7	254.3
65°	277.5	267.5	244.3	222.5	215.9
67.5°	236.2	227.7	204.8	184.8	179.5
70°	209.1	201.2	179.3	160.9	155.7
72.5°	183.1	174.7	153.9	138.2	134.5
75°	143.5	135.5	119.1	106.9	104.9
77.5°	107.2	100.7	86.5	79.6	78.5
80°	83.9	78.0	67.0	62.3	62.3
82.5°	62.3	57.4	50.2	48.2	48.2
85°	32.5	29.8	28.4	28.4	28.4
87.5°	9.7	9.7	9.2	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)