

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1056955

Luminaire Tested: CB2R-055D-840-1D-UNV-STD-W-8

Issue Date: 7/31/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056955
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 7/31/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2R-055D-840-1D-UNV-STD-W-8
Description: CORELITE BASIC SLOT LED LUMINAIRE
2-INCH APERTURE
DOWNLIGHT 550 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4358.4 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 8' x H: 0')
CIE Type: Direct


Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1056955

CATALOG NUMBER: CB2R-055D-840-1D-UNV-STD-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P1056955

CATALOG NUMBER: CB2R-055D-840-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	95	98	95	92	94	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55
5	78	65	56	50	76	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	55	48	43	53	47	43
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16277	16277	16277
5°	16138	16164	16277
10°	16047	16009	15996
15°	15793	15689	15561
20°	15544	15199	14988
25°	15126	14701	14288
30°	14708	14060	13527
35°	14226	13404	12765
40°	13715	12788	12039
45°	13201	12143	11333
50°	12738	11517	10645
55°	12168	10865	9995
60°	11516	10245	9348
65°	10823	9555	8700
70°	10058	8782	7870
75°	9149	7944	7127
80°	8180	6961	6459
85°	6295	5715	4716

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13201 cd/sqm

TEST NUMBER: P1056955

CATALOG NUMBER: CB2R-055D-840-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.8	4.0
10°-20°	489.9	11.2
20°-30°	704.5	16.2
30°-40°	791.8	18.2
40°-50°	764.9	17.5
50°-60°	646.3	14.8
60°-70°	464.2	10.7
70°-80°	253.7	5.8
80°-90°	67.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.2	31.4
0°-40°	2162.0	49.6
0°-60°	3573.1	82.0
0°-90°	4358.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4358.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1869	1869	1869	1869	1869	
5°	1846	1871	1849	1849	1862	175
15°	1752	1767	1740	1723	1726	494
25°	1574	1576	1530	1495	1487	725
35°	1338	1323	1261	1212	1201	836
45°	1072	1050	986	934	920	828
55°	801	772	716	671	658	716
65°	525	506	464	431	422	521
75°	272	255	236	217	212	291
85°	63	59	57	50	47	77
90°	0	0	0	0	0	

TEST NUMBER: P1056955

CATALOG NUMBER: CB2R-055D-840-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1869.0	1869.0	1869.0	1869.0	1869.0
2.5°	1856.4	1878.8	1862.2	1864.5	1867.9
5°	1846.1	1871.3	1849.0	1849.3	1861.9
7.5°	1833.0	1856.8	1828.7	1823.5	1835.3
10°	1814.6	1838.4	1810.4	1800.5	1808.9
12.5°	1790.6	1813.3	1786.3	1770.7	1778.0
15°	1751.7	1767.1	1740.2	1723.1	1725.9
17.5°	1709.3	1718.8	1680.1	1665.7	1662.9
20°	1677.3	1685.7	1640.0	1620.0	1617.2
22.5°	1636.0	1643.3	1595.4	1570.7	1566.8
25°	1574.2	1575.6	1529.9	1495.3	1486.9
27.5°	1509.5	1505.1	1454.3	1413.4	1402.5
30°	1462.6	1457.0	1398.2	1355.0	1345.2
32.5°	1412.2	1402.1	1343.2	1296.6	1286.9
35°	1338.1	1322.7	1260.8	1211.9	1200.7
37.5°	1259.1	1241.7	1181.0	1127.7	1115.1
40°	1206.4	1186.8	1124.9	1071.6	1059.0
42.5°	1153.8	1131.9	1068.8	1015.5	1001.8
45°	1071.9	1049.5	986.0	934.2	920.2
47.5°	994.0	965.5	903.9	852.3	838.3
50°	940.2	909.5	850.1	799.7	785.7
52.5°	885.3	853.4	796.3	748.2	734.2
55°	801.4	772.0	715.6	670.9	658.3
57.5°	718.4	690.2	638.6	595.9	583.6
60°	661.2	637.4	588.2	547.9	536.7
62.5°	606.2	584.7	537.8	500.9	489.7
65°	525.2	505.6	463.7	430.6	422.2
67.5°	446.5	426.9	393.0	363.3	353.8
70°	395.0	375.4	344.9	317.5	309.1
72.5°	345.8	325.0	300.2	275.2	269.0
75°	271.9	255.1	236.1	217.4	211.8
77.5°	206.7	190.4	176.6	163.4	162.0
80°	163.1	149.2	138.8	130.2	128.8
82.5°	121.9	111.3	104.5	98.2	97.9
85°	63.0	58.8	57.2	50.0	47.2
87.5°	18.3	18.3	16.0	13.7	13.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)