

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P257520

Luminaire Tested: **D3X-WO-20L935-LD5-UNV-22-T1-STD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P257520  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1806-819-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: D3X-WO-20L935-LD5-UNV-22-T1-STD  
Description: CORELITE D3X 2X2 LED LUMINAIRE  
Light Source: (126) 3500 CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1772.2 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.27 / 1.33  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P257520

CATALOG NUMBER: D3X-WO-20L935-LD5-UNV-22-T1-STD

### Luminous Intensity Polar Plot





TEST NUMBER: P257520

CATALOG NUMBER: D3X-WO-20L935-LD5-UNV-22-T1-STD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	70	62	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	61	48	40	34	60	47	39	34	46	39	34	45	38	33	44	38	33	31
9	57	44	36	31	56	44	36	31	43	35	30	41	35	30	40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	28	38	32	28	38	32	27	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1821	1821	1821
5°	1814	1821	1828
10°	1799	1815	1835
15°	1775	1807	1841
20°	1746	1794	1844
25°	1711	1771	1836
30°	1667	1741	1812
35°	1618	1702	1780
40°	1559	1652	1736
45°	1504	1595	1682
50°	1441	1529	1603
55°	1374	1457	1528
60°	1297	1372	1434
65°	1225	1270	1331
70°	1124	1160	1201
75°	1000	1027	1055
80°	862	848	848
85°	655	599	543



TEST NUMBER: P257520

CATALOG NUMBER: D3X-WO-20L935-LD5-UNV-22-T1-STD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.0	3.6
10°-20°	183.0	10.3
20°-30°	274.8	15.5
30°-40°	323.4	18.2
40°-50°	322.5	18.2
50°-60°	276.8	15.6
60°-70°	198.2	11.2
70°-80°	105.0	5.9
80°-90°	24.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.8	29.4
0°-40°	845.1	47.7
0°-60°	1444.4	81.5
0°-90°	1772.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1772.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	677	677	677	677	677	
5°	672	672	674	676	677	64
15°	637	640	648	657	661	180
25°	576	582	596	612	618	265
35°	492	498	518	536	542	308
45°	395	402	419	434	442	305
55°	293	297	311	321	326	262
65°	192	193	199	207	209	190
75°	96	96	99	101	102	103
85°	21	20	19	18	18	26
90°	0	0	0	0	0	



TEST NUMBER: P257520

CATALOG NUMBER: D3X-WO-20L935-LD5-UNV-22-T1-STD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	676.8	676.8	676.8	676.8	676.8
2.5°	674.1	674.1	675.9	677.7	678.5
5°	671.5	671.5	674.1	675.9	676.8
7.5°	666.2	666.2	669.7	673.3	675.0
10°	658.3	660.0	664.4	669.7	671.5
12.5°	649.4	651.2	657.4	664.4	667.1
15°	637.1	639.7	648.5	657.4	660.9
17.5°	623.8	627.4	638.0	648.5	653.0
20°	609.7	613.3	626.5	638.8	644.1
22.5°	593.8	598.3	613.3	626.5	631.8
25°	576.2	581.5	596.5	611.5	618.5
27.5°	556.8	563.0	579.7	595.6	601.8
30°	536.5	543.5	560.3	577.1	583.2
32.5°	514.4	520.6	540.9	556.8	563.0
35°	492.4	498.5	518.0	535.6	541.8
37.5°	468.5	476.5	495.9	511.8	518.0
40°	443.8	451.8	470.3	488.8	494.1
42.5°	420.0	427.1	444.7	461.5	466.8
45°	395.3	401.5	419.1	434.1	442.1
47.5°	369.7	375.9	393.5	407.7	412.1
50°	344.1	350.3	365.3	377.7	383.0
52.5°	318.5	324.7	338.8	350.3	355.6
55°	292.9	297.4	310.6	321.2	325.6
57.5°	267.4	270.9	281.5	292.9	295.6
60°	240.9	245.3	255.0	262.9	266.5
62.5°	217.1	218.8	227.7	234.7	239.1
65°	192.4	193.2	199.4	207.4	209.1
67.5°	166.8	167.7	173.8	178.2	180.0
70°	142.9	142.9	147.4	150.9	152.7
72.5°	120.0	119.1	121.8	125.3	127.1
75°	96.2	96.2	98.8	100.6	101.5
77.5°	75.9	74.1	75.9	77.6	77.6
80°	55.6	54.7	54.7	55.6	54.7
82.5°	37.9	37.1	37.9	36.2	35.3
85°	21.2	20.3	19.4	17.6	17.6
87.5°	7.1	6.2	6.2	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)