

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036262

Luminaire Tested: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 500 LUMENS PER FOOT DOV

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1876.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036262

CATALOG NUMBER: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1036262

CATALOG NUMBER: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6762	6762	6762
5°	6812	6770	6746
10°	6801	6753	6723
15°	6756	6719	6681
20°	6710	6673	6622
25°	6630	6585	6520
30°	6508	6474	6392
35°	6339	6295	6215
40°	6134	6095	6026
45°	5968	5926	5868
50°	5753	5717	5661
55°	5456	5384	5342
60°	4966	4825	4801
65°	4377	4194	4178
70°	3777	3623	3623
75°	3255	3205	3158
80°	2864	2901	2827
85°	2234	2456	2456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5968 cd/sqm

TEST NUMBER: P1036262

CATALOG NUMBER: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	3.7
10°-20°	197.9	10.5
20°-30°	296.4	15.8
30°-40°	347.7	18.5
40°-50°	348.8	18.6
50°-60°	297.5	15.9
60°-70°	194.1	10.3
70°-80°	97.4	5.2
80°-90°	26.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	563.6	30.0
0°-40°	911.3	48.6
0°-60°	1557.6	83.0
0°-90°	1876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1876.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	733	733	733	733	733	
5°	736	729	731	728	728	70
15°	707	700	703	701	700	200
25°	651	644	647	641	640	300
35°	563	557	559	552	552	352
45°	457	454	454	450	450	352
55°	339	338	335	333	332	301
65°	200	197	192	191	191	200
75°	91	91	90	89	89	99
85°	21	23	23	23	23	26
90°	0	0	0	0	0	

TEST NUMBER: P1036262

CATALOG NUMBER: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	732.9	732.9	732.9	732.9	732.9
2.5°	737.5	731.6	732.9	731.9	728.8
5°	735.5	728.6	731.0	728.4	728.4
7.5°	730.5	723.0	725.3	722.8	722.7
10°	725.9	718.4	720.8	718.2	717.6
12.5°	719.2	711.7	714.5	711.5	711.4
15°	707.3	700.3	703.4	700.8	699.5
17.5°	693.8	686.3	689.9	686.4	685.8
20°	683.4	675.9	679.6	674.5	674.5
22.5°	671.2	663.7	667.9	661.1	661.1
25°	651.3	643.8	646.9	641.1	640.5
27.5°	627.8	620.4	623.6	617.0	616.9
30°	610.9	604.0	607.7	600.6	600.0
32.5°	592.4	586.0	588.7	581.6	580.9
35°	562.8	557.1	558.9	552.4	551.8
37.5°	531.5	525.8	527.7	522.2	522.0
40°	509.3	505.6	506.1	501.6	500.3
42.5°	488.9	484.6	485.1	480.6	480.4
45°	457.4	454.2	454.2	449.7	449.7
47.5°	424.0	421.6	420.9	417.1	417.0
50°	400.8	399.0	398.3	395.0	394.4
52.5°	376.7	375.8	373.6	370.9	370.8
55°	339.2	337.9	334.7	332.7	332.1
57.5°	298.5	295.9	292.3	289.6	289.9
60°	269.1	266.6	261.5	260.2	260.2
62.5°	240.9	237.9	232.7	230.9	231.9
65°	200.5	196.7	192.1	190.8	191.4
67.5°	163.7	160.3	155.3	155.3	154.8
70°	140.0	138.1	134.3	134.3	134.3
72.5°	119.0	118.0	115.3	115.2	114.8
75°	91.3	91.3	89.9	89.2	88.6
77.5°	68.3	68.6	68.0	67.3	66.2
80°	53.9	55.3	54.6	53.9	53.2
82.5°	40.6	41.9	41.8	40.6	40.4
85°	21.1	23.0	23.2	23.2	23.2
87.5°	5.7	7.6	8.2	8.2	8.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036262

CATALOG NUMBER: SQ4R-PP3-050D-B2750-1D-UNV-W2A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.73	19.31	18.09	19.63	19.94	17.56	19.15	17.93	19.47	19.78
	3H	19.04	20.47	19.42	20.79	21.16	18.84	20.27	19.22	20.59	20.95
	4H	19.53	20.87	19.92	21.21	21.59	19.32	20.67	19.72	21.01	21.39
	6H	19.84	21.08	20.25	21.45	21.84	19.64	20.89	20.06	21.25	21.64
	8H	19.97	21.15	20.39	21.54	21.94	19.77	20.96	20.20	21.35	21.75
	12H	20.04	21.17	20.47	21.55	21.98	19.86	20.99	20.29	21.37	21.80
4H	2H	18.19	19.54	18.59	19.88	20.26	18.06	19.40	18.46	19.75	20.13
	3H	19.73	20.85	20.14	21.25	21.65	19.56	20.68	19.97	21.08	21.48
	4H	20.33	21.33	20.76	21.75	22.18	20.16	21.16	20.59	21.58	22.01
	6H	20.76	21.64	21.22	22.08	22.54	20.59	21.47	21.05	21.91	22.37
	8H	20.94	21.76	21.40	22.20	22.67	20.77	21.59	21.23	22.03	22.50
	12H	21.05	21.78	21.53	22.26	22.73	20.90	21.63	21.38	22.11	22.58
8H	4H	20.53	21.35	20.99	21.79	22.26	20.38	21.20	20.84	21.64	22.11
	6H	21.08	21.76	21.58	22.25	22.73	20.93	21.61	21.42	22.10	22.57
	8H	21.33	21.94	21.84	22.45	22.94	21.18	21.79	21.69	22.30	22.79
	12H	21.51	22.05	22.02	22.54	23.10	21.38	21.92	21.88	22.41	22.97
12H	4H	20.55	21.28	21.03	21.76	22.23	20.40	21.13	20.88	21.61	22.08
	6H	21.12	21.73	21.63	22.24	22.73	20.97	21.58	21.48	22.09	22.58
	8H	21.43	21.97	21.94	22.46	23.02	21.28	21.82	21.79	22.31	22.88