

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036240

Luminaire Tested: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOV

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2740.9 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036240

CATALOG NUMBER: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036240

CATALOG NUMBER: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	80	72	66	88	79	71	65	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	46	41		52
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	32	27	52	40	32	27	39	32	27		38	31	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9265	9265	9265
5°	9336	9274	9241
10°	9313	9269	9243
15°	9264	9264	9256
20°	9204	9230	9230
25°	9117	9181	9154
30°	9004	9114	9075
35°	8871	9007	8944
40°	8723	8847	8760
45°	8566	8627	8493
50°	8342	8342	8209
55°	8078	7972	7853
60°	7687	7532	7412
65°	7104	6962	6901
70°	6223	6269	6248
75°	5005	5536	5572
80°	3560	4692	4745
85°	2181	3938	3938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 8627 cd/sqm

TEST NUMBER: P1036240

CATALOG NUMBER: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	3.5
10°-20°	272.7	10.0
20°-30°	413.0	15.1
30°-40°	495.2	18.1
40°-50°	504.9	18.4
50°-60°	440.8	16.1
60°-70°	315.5	11.5
70°-80°	162.5	5.9
80°-90°	41.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.8	28.5
0°-40°	1276.0	46.6
0°-60°	2221.7	81.1
0°-90°	2740.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2740.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1004	1004	1004	1004	1004	
5°	1008	998	1001	999	998	96
15°	970	962	970	970	969	273
25°	896	889	902	899	899	412
35°	788	786	800	794	794	493
45°	656	655	661	653	651	505
55°	502	496	496	488	488	448
65°	325	318	319	316	316	322
75°	140	147	155	156	156	152
85°	21	31	37	38	37	29
90°	0	0	0	0	0	

TEST NUMBER: P1036240

CATALOG NUMBER: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1004.2	1004.2	1004.2	1004.2	1004.2
2.5°	1010.3	1001.4	1004.2	1002.0	998.3
5°	1008.1	997.9	1001.4	998.6	997.8
7.5°	1000.7	990.8	995.4	993.4	992.5
10°	994.1	984.0	989.4	987.5	986.6
12.5°	985.2	975.8	981.9	980.2	979.8
15°	969.9	961.7	969.9	969.9	969.0
17.5°	950.7	943.3	951.9	952.6	951.9
20°	937.4	929.2	940.1	939.2	940.1
22.5°	921.0	914.3	925.9	923.6	924.5
25°	895.6	889.1	901.9	899.2	899.2
27.5°	865.4	860.7	874.8	871.8	871.8
30°	845.2	840.7	855.5	851.8	851.8
32.5°	822.9	819.9	834.0	829.5	829.5
35°	787.6	785.7	799.7	794.1	794.1
37.5°	751.1	749.5	762.2	755.4	753.2
40°	724.3	723.5	734.6	727.3	727.3
42.5°	697.5	696.6	706.4	697.5	697.5
45°	656.5	654.6	661.2	652.7	650.9
47.5°	611.7	609.9	613.9	604.7	603.8
50°	581.2	579.3	581.2	572.7	571.9
52.5°	550.0	546.6	546.9	538.6	538.4
55°	502.2	495.8	495.6	488.2	488.2
57.5°	451.5	443.2	444.0	437.6	436.6
60°	416.6	407.5	408.2	402.6	401.7
62.5°	382.3	371.9	374.0	367.7	367.6
65°	325.4	318.2	318.9	316.1	316.1
67.5°	270.8	264.0	268.9	266.8	266.6
70°	230.7	226.0	232.4	232.4	231.6
72.5°	193.5	193.3	201.2	201.2	201.8
75°	140.4	146.8	155.3	156.3	156.3
77.5°	93.8	105.0	114.4	114.7	114.6
80°	67.0	79.7	88.3	90.3	89.3
82.5°	45.3	58.8	66.1	67.8	67.0
85°	20.6	31.4	37.2	38.2	37.2
87.5°	5.9	12.5	14.9	14.9	13.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036240

CATALOG NUMBER: SQ4R-PC3-075D-B2750-1D-UNV-W2A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.20	20.82	19.57	21.13	21.45	19.09	20.70	19.45	21.02	21.33
	3H	20.75	22.20	21.12	22.53	22.89	20.69	22.15	21.07	22.47	22.83
	4H	21.26	22.63	21.65	22.97	23.35	21.29	22.66	21.69	23.01	23.38
	6H	21.49	22.76	21.90	23.13	23.52	21.66	22.92	22.07	23.29	23.68
	8H	21.56	22.77	21.98	23.16	23.56	21.79	23.00	22.22	23.39	23.79
	12H	21.58	22.74	22.01	23.12	23.55	21.88	23.04	22.31	23.42	23.85
4H	2H	19.80	21.17	20.19	21.51	21.89	19.71	21.08	20.10	21.42	21.80
	3H	21.55	22.70	21.96	23.09	23.49	21.53	22.67	21.94	23.07	23.47
	4H	22.16	23.19	22.59	23.61	24.04	22.23	23.26	22.66	23.68	24.11
	6H	22.50	23.40	22.96	23.84	24.30	22.71	23.61	23.16	24.05	24.51
	8H	22.60	23.44	23.06	23.89	24.35	22.89	23.74	23.35	24.18	24.64
	12H	22.65	23.41	23.13	23.89	24.36	23.02	23.78	23.50	24.25	24.72
8H	4H	22.42	23.26	22.88	23.70	24.17	22.48	23.32	22.94	23.76	24.23
	6H	22.86	23.56	23.36	24.05	24.52	23.07	23.77	23.56	24.26	24.73
	8H	23.03	23.65	23.54	24.16	24.65	23.33	23.96	23.84	24.46	24.95
	12H	23.13	23.68	23.64	24.18	24.74	23.52	24.08	24.03	24.57	25.13
12H	4H	22.44	23.19	22.92	23.67	24.14	22.49	23.25	22.98	23.73	24.20
	6H	22.91	23.54	23.42	24.04	24.53	23.11	23.73	23.62	24.24	24.73
	8H	23.13	23.69	23.64	24.18	24.74	23.42	23.98	23.93	24.47	25.03