

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036279

Luminaire Tested: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1000 LUMENS PER FOOT DC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3632.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036279

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036279

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13093	13093	13093
5°	13188	13108	13062
10°	13167	13074	13016
15°	13080	13008	12937
20°	12993	12919	12822
25°	12838	12750	12624
30°	12601	12535	12375
35°	12271	12188	12032
40°	11878	11803	11669
45°	11555	11474	11359
50°	11138	11068	10960
55°	10562	10423	10345
60°	9616	9341	9294
65°	8473	8117	8091
70°	7310	7011	7011
75°	6299	6206	6114
80°	5552	5616	5478
85°	4340	4742	4742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11555 cd/sqm

TEST NUMBER: P1036279

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.2	3.7
10°-20°	383.2	10.5
20°-30°	573.9	15.8
30°-40°	673.2	18.5
40°-50°	675.2	18.6
50°-60°	576.1	15.9
60°-70°	375.7	10.3
70°-80°	188.5	5.2
80°-90°	52.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1091.3	30.0
0°-40°	1764.4	48.6
0°-60°	3015.7	83.0
0°-90°	3632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3632.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1419	1419	1419	1419	1419	
5°	1424	1411	1415	1410	1410	135
15°	1369	1356	1362	1357	1354	386
25°	1261	1246	1252	1241	1240	580
35°	1090	1079	1082	1070	1068	681
45°	886	879	879	871	871	682
55°	657	654	648	644	643	584
65°	388	381	372	370	371	387
75°	177	177	174	173	172	192
85°	41	45	45	45	45	50
90°	0	0	0	0	0	

TEST NUMBER: P1036279

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1419.1	1419.1	1419.1	1419.1	1419.1
2.5°	1427.9	1416.4	1419.1	1417.0	1411.2
5°	1424.0	1410.8	1415.3	1410.4	1410.4
7.5°	1414.4	1399.8	1404.4	1399.4	1399.2
10°	1405.4	1390.8	1395.5	1390.4	1389.3
12.5°	1392.5	1378.0	1383.5	1377.5	1377.3
15°	1369.4	1355.9	1361.9	1356.8	1354.4
17.5°	1343.2	1328.7	1335.8	1328.9	1327.8
20°	1323.3	1308.7	1315.8	1305.9	1305.9
22.5°	1299.5	1284.9	1293.0	1279.9	1279.9
25°	1261.1	1246.5	1252.5	1241.2	1240.1
27.5°	1215.6	1201.3	1207.5	1194.7	1194.4
30°	1182.8	1169.4	1176.6	1162.9	1161.6
32.5°	1147.0	1134.6	1139.7	1126.1	1124.7
35°	1089.5	1078.6	1082.1	1069.7	1068.3
37.5°	1029.0	1017.9	1021.8	1011.0	1010.6
40°	986.2	978.9	980.0	971.2	968.9
42.5°	946.5	938.1	939.2	930.4	930.0
45°	885.6	879.4	879.4	870.6	870.6
47.5°	820.9	816.1	814.9	807.5	807.3
50°	776.0	772.4	771.1	764.9	763.6
52.5°	729.3	727.6	723.3	718.2	718.0
55°	656.6	654.2	648.0	644.1	643.1
57.5°	577.9	573.0	565.9	560.5	561.4
60°	521.1	516.1	506.2	503.7	503.7
62.5°	466.4	460.6	450.5	447.1	449.1
65°	388.1	380.8	371.8	369.5	370.6
67.5°	317.0	310.3	300.6	300.6	299.8
70°	271.0	267.4	259.9	259.9	259.9
72.5°	230.3	228.6	223.3	223.0	222.1
75°	176.7	176.7	174.1	172.9	171.5
77.5°	132.3	132.8	131.7	130.3	128.0
80°	104.5	107.0	105.7	104.5	103.1
82.5°	78.7	81.0	80.8	78.7	78.3
85°	41.0	44.6	44.8	44.8	44.8
87.5°	11.0	14.8	15.9	15.9	17.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036279

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.02	21.61	20.39	21.92	22.24	19.86	21.45	20.22	21.76	22.07
	3H	21.34	22.76	21.71	23.09	23.45	21.13	22.56	21.51	22.89	23.25
	4H	21.82	23.16	22.22	23.51	23.89	21.62	22.96	22.02	23.31	23.68
	6H	22.14	23.38	22.55	23.74	24.13	21.94	23.18	22.35	23.54	23.94
	8H	22.26	23.44	22.69	23.83	24.23	22.07	23.25	22.49	23.64	24.04
	12H	22.33	23.46	22.76	23.85	24.28	22.15	23.28	22.58	23.67	24.09
4H	2H	20.49	21.83	20.89	22.18	22.56	20.36	21.70	20.75	22.04	22.42
	3H	22.03	23.14	22.44	23.54	23.94	21.86	22.97	22.27	23.37	23.77
	4H	22.62	23.63	23.05	24.04	24.48	22.45	23.46	22.88	23.87	24.31
	6H	23.06	23.93	23.51	24.38	24.83	22.89	23.76	23.34	24.21	24.66
	8H	23.23	24.05	23.69	24.49	24.96	23.07	23.89	23.53	24.33	24.79
	12H	23.34	24.08	23.82	24.55	25.02	23.19	23.93	23.67	24.40	24.87
8H	4H	22.83	23.65	23.29	24.09	24.56	22.67	23.49	23.13	23.93	24.40
	6H	23.38	24.06	23.87	24.55	25.02	23.22	23.90	23.72	24.39	24.87
	8H	23.63	24.24	24.14	24.75	25.23	23.48	24.09	23.99	24.59	25.08
	12H	23.81	24.35	24.31	24.84	25.40	23.67	24.21	24.18	24.70	25.27
12H	4H	22.84	23.58	23.32	24.06	24.53	22.69	23.43	23.17	23.90	24.37
	6H	23.42	24.03	23.93	24.54	25.02	23.27	23.88	23.78	24.39	24.87
	8H	23.72	24.26	24.23	24.76	25.32	23.58	24.12	24.09	24.61	25.17