

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036280

Luminaire Tested: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1000 LUMENS PER FOOT DC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3568.2 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036280

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036280

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12862	12862	12862
5°	12957	12877	12833
10°	12935	12844	12787
15°	12850	12780	12708
20°	12764	12692	12596
25°	12613	12526	12402
30°	12379	12314	12158
35°	12056	11973	11821
40°	11669	11596	11463
45°	11353	11273	11160
50°	10943	10873	10768
55°	10377	10240	10163
60°	9446	9176	9132
65°	8324	7975	7949
70°	7184	6887	6887
75°	6188	6099	6007
80°	5451	5520	5382
85°	4266	4658	4658

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11353 cd/sqm

TEST NUMBER: P1036280

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	3.7
10°-20°	376.4	10.5
20°-30°	563.8	15.8
30°-40°	661.3	18.5
40°-50°	663.4	18.6
50°-60°	565.9	15.9
60°-70°	369.1	10.3
70°-80°	185.2	5.2
80°-90°	51.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.1	30.0
0°-40°	1733.4	48.6
0°-60°	2962.7	83.0
0°-90°	3568.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3568.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1399	1386	1390	1386	1386	133
15°	1345	1332	1338	1333	1330	380
25°	1239	1225	1230	1219	1218	570
35°	1070	1060	1063	1051	1050	669
45°	870	864	864	855	855	670
55°	645	643	637	633	632	573
65°	381	374	365	363	364	380
75°	174	174	171	170	168	188
85°	40	44	44	44	44	49
90°	0	0	0	0	0	

TEST NUMBER: P1036280

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1394.1	1394.1	1394.1	1394.1	1394.1
2.5°	1402.8	1391.5	1394.1	1392.1	1386.4
5°	1399.0	1386.0	1390.4	1385.6	1385.6
7.5°	1389.6	1375.2	1379.7	1374.8	1374.6
10°	1380.7	1366.3	1371.0	1366.0	1364.9
12.5°	1368.1	1353.8	1359.2	1353.3	1353.1
15°	1345.3	1332.1	1338.0	1332.9	1330.5
17.5°	1319.6	1305.3	1312.3	1305.5	1304.5
20°	1300.0	1285.7	1292.7	1282.9	1282.9
22.5°	1276.7	1262.3	1270.3	1257.4	1257.4
25°	1239.0	1224.6	1230.5	1219.4	1218.3
27.5°	1194.2	1180.1	1186.2	1173.7	1173.4
30°	1162.0	1148.8	1155.9	1142.4	1141.2
32.5°	1126.8	1114.6	1119.7	1106.3	1104.9
35°	1070.4	1059.6	1063.0	1050.8	1049.5
37.5°	1011.0	1000.0	1003.8	993.2	992.9
40°	968.9	961.7	962.8	954.1	951.8
42.5°	929.8	921.7	922.7	914.0	913.7
45°	870.1	864.0	864.0	855.3	855.3
47.5°	806.5	801.8	800.6	793.3	793.1
50°	762.4	758.9	757.5	751.4	750.2
52.5°	716.5	714.8	710.6	705.5	705.4
55°	645.1	642.7	636.6	632.8	631.8
57.5°	567.8	562.9	556.0	550.7	551.5
60°	511.9	507.0	497.3	494.9	494.9
62.5°	458.2	452.5	442.6	439.3	441.2
65°	381.3	374.1	365.3	363.0	364.1
67.5°	311.4	304.8	295.3	295.3	294.6
70°	266.3	262.7	255.3	255.3	255.3
72.5°	226.3	224.6	219.3	219.1	218.2
75°	173.6	173.6	171.1	169.8	168.5
77.5°	130.0	130.4	129.4	128.0	125.8
80°	102.6	105.1	103.9	102.6	101.3
82.5°	77.3	79.6	79.4	77.3	76.9
85°	40.3	43.8	44.0	44.0	44.0
87.5°	10.8	14.6	15.6	15.6	16.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036280

CATALOG NUMBER: SQ4R-PP3-100D-B2750-1D-UNV-W2A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.96	21.55	20.33	21.86	22.18	19.80	21.38	20.16	21.70	22.01
	3H	21.27	22.70	21.65	23.03	23.39	21.07	22.50	21.45	22.83	23.19
	4H	21.76	23.10	22.16	23.45	23.83	21.56	22.90	21.96	23.25	23.62
	6H	22.08	23.32	22.49	23.68	24.07	21.88	23.12	22.29	23.48	23.87
	8H	22.20	23.38	22.62	23.77	24.17	22.01	23.19	22.43	23.58	23.98
	12H	22.27	23.40	22.70	23.78	24.21	22.09	23.22	22.52	23.60	24.03
4H	2H	20.43	21.77	20.83	22.12	22.49	20.29	21.64	20.69	21.98	22.36
	3H	21.97	23.08	22.38	23.48	23.88	21.80	22.91	22.21	23.31	23.71
	4H	22.56	23.57	22.99	23.98	24.42	22.39	23.39	22.82	23.81	24.25
	6H	23.00	23.87	23.45	24.31	24.77	22.83	23.70	23.28	24.14	24.60
	8H	23.17	23.99	23.63	24.43	24.90	23.00	23.82	23.47	24.27	24.73
	12H	23.28	24.02	23.76	24.49	24.96	23.13	23.86	23.61	24.34	24.81
8H	4H	22.77	23.59	23.23	24.03	24.49	22.61	23.43	23.07	23.87	24.34
	6H	23.32	24.00	23.81	24.49	24.96	23.16	23.84	23.66	24.33	24.81
	8H	23.57	24.18	24.08	24.68	25.17	23.41	24.03	23.93	24.53	25.02
	12H	23.74	24.28	24.25	24.78	25.34	23.61	24.15	24.12	24.64	25.20
12H	4H	22.78	23.52	23.26	23.99	24.46	22.63	23.36	23.11	23.84	24.31
	6H	23.35	23.97	23.87	24.47	24.96	23.21	23.82	23.72	24.33	24.81
	8H	23.66	24.20	24.17	24.69	25.26	23.52	24.06	24.02	24.55	25.11