

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036256

Luminaire Tested: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1250 LUMENS PER FOOT DC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4505.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 45.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036256

CATALOG NUMBER: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036256

CATALOG NUMBER: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	80	72	66	88	79	71	65	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	46	41		52
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	32	27	52	40	32	27	39	32	27		38	31	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15228	15228	15228
5°	15345	15245	15189
10°	15308	15236	15192
15°	15227	15227	15211
20°	15127	15170	15170
25°	14984	15092	15046
30°	14800	14979	14915
35°	14582	14804	14699
40°	14338	14543	14396
45°	14080	14179	13960
50°	13712	13712	13492
55°	13277	13103	12909
60°	12634	12382	12182
65°	11675	11446	11341
70°	10226	10305	10270
75°	8227	9101	9158
80°	5850	7715	7794
85°	3567	6468	6468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 14179 cd/sqm

TEST NUMBER: P1036256

CATALOG NUMBER: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	3.5
10°-20°	448.3	10.0
20°-30°	678.9	15.1
30°-40°	813.9	18.1
40°-50°	829.9	18.4
50°-60°	724.4	16.1
60°-70°	518.6	11.5
70°-80°	267.2	5.9
80°-90°	67.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.4	28.5
0°-40°	2097.3	46.6
0°-60°	3651.6	81.1
0°-90°	4505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4505.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1650	1650	1650	1650	1650	
5°	1657	1640	1646	1641	1640	157
15°	1594	1581	1594	1594	1592	449
25°	1472	1461	1482	1478	1478	677
35°	1295	1291	1314	1305	1305	810
45°	1079	1076	1087	1073	1070	831
55°	825	815	815	802	802	736
65°	535	523	524	520	520	529
75°	231	241	255	257	257	249
85°	34	52	61	63	61	47
90°	0	0	0	0	0	

TEST NUMBER: P1036256

CATALOG NUMBER: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1650.5	1650.5	1650.5	1650.5	1650.5
2.5°	1660.5	1646.1	1650.5	1646.8	1640.8
5°	1656.9	1640.2	1646.1	1641.3	1640.0
7.5°	1644.7	1628.4	1636.1	1632.9	1631.3
10°	1634.0	1617.3	1626.3	1623.1	1621.6
12.5°	1619.2	1603.9	1614.0	1611.0	1610.5
15°	1594.2	1580.7	1594.2	1594.2	1592.5
17.5°	1562.6	1550.5	1564.7	1565.7	1564.7
20°	1540.7	1527.2	1545.1	1543.6	1545.1
22.5°	1513.8	1502.8	1522.0	1518.0	1519.6
25°	1471.9	1461.4	1482.5	1478.0	1478.0
27.5°	1422.4	1414.7	1437.9	1432.9	1432.9
30°	1389.2	1381.9	1406.0	1400.0	1400.0
32.5°	1352.5	1347.6	1370.7	1363.4	1363.4
35°	1294.7	1291.4	1314.4	1305.1	1305.1
37.5°	1234.6	1231.9	1252.8	1241.6	1238.0
40°	1190.5	1189.3	1207.5	1195.3	1195.3
42.5°	1146.5	1145.0	1161.1	1146.3	1146.3
45°	1079.1	1076.0	1086.7	1072.7	1069.9
47.5°	1005.3	1002.5	1009.1	994.0	992.4
50°	955.3	952.1	955.3	941.4	940.0
52.5°	903.9	898.4	898.9	885.2	884.9
55°	825.4	814.8	814.6	802.5	802.5
57.5°	742.1	728.5	729.7	719.3	717.6
60°	684.7	669.7	671.0	661.8	660.2
62.5°	628.3	611.2	614.6	604.3	604.1
65°	534.8	522.9	524.3	519.5	519.5
67.5°	445.0	433.9	442.1	438.4	438.1
70°	379.1	371.5	382.0	382.0	380.7
72.5°	318.0	317.7	330.6	330.6	331.7
75°	230.8	241.3	255.3	256.9	256.9
77.5°	154.1	172.6	188.1	188.6	188.4
80°	110.1	130.9	145.2	148.3	146.7
82.5°	74.5	96.7	108.5	111.5	110.1
85°	33.7	51.6	61.1	62.7	61.1
87.5°	9.7	20.6	24.5	24.5	22.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036256

CATALOG NUMBER: SQ4R-PC3-125D-B2750-1D-UNV-W2A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.93	22.54	21.29	22.86	23.17	20.81	22.43	21.18	22.74	23.06
	3H	22.47	23.93	22.85	24.26	24.62	22.42	23.87	22.79	24.20	24.56
	4H	22.98	24.35	23.38	24.70	25.08	23.02	24.39	23.41	24.73	25.11
	6H	23.22	24.49	23.63	24.85	25.24	23.38	24.65	23.79	25.02	25.41
	8H	23.28	24.49	23.71	24.88	25.28	23.52	24.73	23.94	25.12	25.52
	12H	23.31	24.47	23.74	24.85	25.28	23.61	24.77	24.04	25.15	25.58
4H	2H	21.52	22.89	21.92	23.24	23.62	21.43	22.80	21.83	23.15	23.53
	3H	23.28	24.42	23.69	24.82	25.22	23.25	24.40	23.66	24.80	25.20
	4H	23.89	24.92	24.32	25.33	25.77	23.96	24.99	24.39	25.41	25.84
	6H	24.23	25.13	24.68	25.57	26.03	24.44	25.34	24.89	25.78	26.23
	8H	24.33	25.17	24.79	25.61	26.08	24.62	25.46	25.08	25.91	26.37
	12H	24.38	25.14	24.86	25.61	26.08	24.75	25.50	25.23	25.98	26.45
8H	4H	24.14	24.99	24.60	25.43	25.89	24.21	25.05	24.67	25.49	25.96
	6H	24.59	25.29	25.08	25.78	26.25	24.79	25.49	25.29	25.98	26.46
	8H	24.75	25.38	25.26	25.89	26.37	25.05	25.68	25.57	26.19	26.68
	12H	24.86	25.41	25.36	25.90	26.46	25.25	25.80	25.76	26.30	26.86
12H	4H	24.17	24.92	24.65	25.40	25.87	24.22	24.98	24.70	25.45	25.92
	6H	24.63	25.26	25.14	25.77	26.26	24.83	25.46	25.34	25.97	26.45
	8H	24.86	25.41	25.36	25.90	26.46	25.15	25.70	25.66	26.19	26.76