

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036335

Luminaire Tested: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P564826)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOV

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2747.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036335

CATALOG NUMBER: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036335

CATALOG NUMBER: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	101	97	107	102	99	95	98	95	92		94	92	89		91
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		80
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		71
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		64
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		57
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		52
7	66	53	44	38	64	52	44	38	50	43	38		49	42	37		48
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		44
9	58	44	36	31	56	44	36	31	43	35	31		42	35	30		41
10	54	41	33	28	53	40	33	28	39	33	28		39	32	28		38

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9962	9962	9962
5°	10026	9948	9904
10°	9947	9867	9814
15°	9842	9732	9696
20°	9724	9574	9556
25°	9588	9414	9384
30°	9386	9244	9183
35°	9120	8989	8936
40°	8835	8696	8662
45°	8490	8379	8340
50°	8140	8071	8015
55°	7758	7758	7636
60°	7287	7427	7163
65°	6667	6999	6501
70°	5873	6442	5724
75°	5023	5764	4880
80°	3895	4856	3948
85°	2509	3737	3313

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8490 cd/sqm

TEST NUMBER: P1036335

CATALOG NUMBER: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	3.7
10°-20°	287.1	10.4
20°-30°	425.8	15.5
30°-40°	498.3	18.1
40°-50°	496.0	18.1
50°-60°	428.3	15.6
60°-70°	308.3	11.2
70°-80°	161.7	5.9
80°-90°	40.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.6	29.7
0°-40°	1312.8	47.8
0°-60°	2237.2	81.4
0°-90°	2747.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2747.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1080	1080	1080	1080	1080	
5°	1083	1070	1074	1071	1069	103
15°	1030	1017	1019	1017	1015	290
25°	942	926	925	919	922	433
35°	810	798	798	791	793	506
45°	651	645	642	640	639	502
55°	482	482	482	476	475	430
65°	305	315	321	308	298	303
75°	141	154	162	151	137	151
85°	24	31	35	33	31	32
90°	0	0	0	0	0	

TEST NUMBER: P1036335

CATALOG NUMBER: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1079.7	1079.7	1079.7	1079.7	1079.7
2.5°	1085.9	1076.9	1079.7	1077.4	1072.2
5°	1082.6	1070.5	1074.1	1071.2	1069.4
7.5°	1071.7	1060.5	1063.0	1060.1	1058.9
10°	1061.7	1050.6	1053.2	1049.4	1047.5
12.5°	1050.4	1038.4	1041.1	1037.1	1036.1
15°	1030.4	1017.2	1018.9	1016.9	1015.1
17.5°	1007.1	994.0	994.2	991.2	990.7
20°	990.4	976.4	975.1	971.3	973.3
22.5°	972.2	957.4	956.1	950.8	953.5
25°	941.8	926.0	924.8	919.1	921.8
27.5°	906.8	891.3	891.3	883.3	886.2
30°	881.0	866.1	867.7	858.2	862.0
32.5°	853.6	840.2	841.0	831.6	835.3
35°	809.7	798.5	798.1	790.6	793.4
37.5°	764.7	754.9	753.3	749.0	749.6
40°	733.6	725.1	722.0	719.2	719.2
42.5°	700.7	693.2	690.1	687.9	687.3
45°	650.7	645.1	642.2	640.3	639.2
47.5°	601.2	596.1	593.5	592.2	591.2
50°	567.1	563.3	562.3	559.3	558.4
52.5°	532.8	530.6	529.5	525.9	524.9
55°	482.3	481.5	482.3	475.7	474.7
57.5°	429.8	431.3	434.4	425.4	423.1
60°	394.9	398.5	402.5	392.0	388.2
62.5°	358.9	365.0	370.5	358.4	353.0
65°	305.4	314.7	320.6	308.0	297.8
67.5°	253.7	265.1	272.2	258.7	247.1
70°	217.7	230.9	238.8	225.1	212.2
72.5°	186.6	201.2	207.6	194.7	181.7
75°	140.9	153.8	161.7	150.9	136.9
77.5°	99.9	112.2	118.7	109.4	97.8
80°	73.3	86.2	91.4	83.4	74.3
82.5°	51.9	62.8	66.3	61.5	55.1
85°	23.7	31.2	35.3	33.3	31.3
87.5°	6.1	11.3	14.4	14.4	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036335

CATALOG NUMBER: SQ4R-PW1-075D-B2750-1D-UNV-W2A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.00	20.60	19.36	20.91	21.23	18.90	20.50	19.26	20.81	21.13
	3H	20.56	22.00	20.93	22.32	22.69	20.43	21.87	20.80	22.20	22.56
	4H	21.11	22.46	21.50	22.81	23.19	20.97	22.32	21.37	22.67	23.05
	6H	21.40	22.66	21.81	23.02	23.41	21.27	22.52	21.68	22.89	23.28
	8H	21.49	22.69	21.92	23.08	23.48	21.37	22.57	21.79	22.96	23.36
	12H	21.53	22.68	21.96	23.06	23.49	21.43	22.58	21.86	22.96	23.39
4H	2H	19.64	21.00	20.04	21.34	21.72	19.56	20.92	19.96	21.27	21.64
	3H	21.44	22.57	21.85	22.97	23.37	21.33	22.46	21.74	22.86	23.26
	4H	22.10	23.12	22.53	23.54	23.97	21.98	23.00	22.41	23.41	23.85
	6H	22.50	23.40	22.96	23.84	24.29	22.38	23.27	22.84	23.71	24.17
	8H	22.63	23.47	23.09	23.91	24.38	22.52	23.36	22.98	23.80	24.27
	12H	22.70	23.45	23.18	23.92	24.39	22.62	23.37	23.10	23.84	24.31
8H	4H	22.38	23.21	22.84	23.65	24.12	22.27	23.10	22.73	23.54	24.01
	6H	22.90	23.59	23.39	24.08	24.55	22.78	23.48	23.28	23.96	24.44
	8H	23.10	23.72	23.61	24.22	24.71	23.00	23.62	23.51	24.12	24.61
	12H	23.22	23.76	23.72	24.25	24.82	23.15	23.70	23.66	24.19	24.75
12H	4H	22.39	23.14	22.88	23.62	24.09	22.29	23.04	22.77	23.51	23.98
	6H	22.94	23.56	23.45	24.07	24.56	22.83	23.45	23.34	23.96	24.45
	8H	23.20	23.74	23.70	24.24	24.80	23.10	23.65	23.61	24.14	24.70