

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036368

Luminaire Tested: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P519276)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOV

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2417.1 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036368

CATALOG NUMBER: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1036368

CATALOG NUMBER: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		85
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	56	52		61
7	73	61	53	48	71	60	53	48	59	52	48		58	52	47		56
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49
10	61	49	42	37	60	48	42	37	48	41	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15304	15304	15304
5°	15114	15058	15147
10°	14279	14408	14741
15°	13180	13488	14092
20°	11970	12419	13241
25°	10737	11321	12337
30°	9600	10227	11398
35°	8394	9000	10289
40°	7065	7626	8907
45°	5830	6333	7436
50°	4867	5306	6194
55°	4132	4554	5115
60°	3534	3949	4084
65°	2814	3321	2637
70°	2495	2592	1610
75°	2310	2103	987
80°	2125	1934	850
85°	1916	1778	699

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7436 cd/sqm

TEST NUMBER: P1036368

CATALOG NUMBER: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	6.3
10°-20°	395.7	16.4
20°-30°	512.6	21.2
30°-40°	502.0	20.8
40°-50°	384.2	15.9
50°-60°	256.0	10.6
60°-70°	139.7	5.8
70°-80°	58.2	2.4
80°-90°	16.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1060.5	43.9
0°-40°	1562.4	64.6
0°-60°	2202.6	91.1
0°-90°	2417.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2417.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1632	1615	1626	1630	1636	152
15°	1380	1375	1412	1450	1475	385
25°	1055	1057	1112	1161	1212	485
35°	745	749	799	853	914	463
45°	447	455	485	522	570	348
55°	257	268	283	294	318	233
65°	129	140	152	133	121	134
75°	65	65	59	40	28	69
85°	18	18	17	11	7	21
90°	0	0	0	0	0	

TEST NUMBER: P1036368

CATALOG NUMBER: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1662.8	1648.0	1651.8	1651.6	1647.0
5°	1631.9	1615.3	1625.9	1629.7	1635.5
7.5°	1571.2	1558.9	1578.1	1592.3	1603.9
10°	1524.1	1513.4	1537.9	1558.7	1573.5
12.5°	1469.4	1460.3	1490.8	1518.4	1538.1
15°	1379.9	1375.0	1412.1	1450.4	1475.3
17.5°	1284.4	1281.9	1324.4	1369.2	1401.0
20°	1219.1	1218.4	1264.9	1311.7	1348.6
22.5°	1153.3	1154.8	1203.7	1252.4	1294.5
25°	1054.7	1057.4	1112.1	1160.6	1211.9
27.5°	963.4	964.7	1021.0	1072.3	1127.0
30°	901.1	904.6	960.0	1013.0	1069.9
32.5°	838.8	842.9	897.1	951.9	1009.9
35°	745.3	748.9	799.1	853.0	913.5
37.5°	648.9	653.8	698.4	749.2	808.9
40°	586.6	593.8	633.2	681.2	739.5
42.5°	526.6	535.5	572.1	617.6	670.1
45°	446.8	455.4	485.4	522.2	569.9
47.5°	378.1	388.0	411.1	442.7	483.4
50°	339.1	348.5	369.7	393.1	431.5
52.5°	304.8	314.0	333.0	351.1	383.9
55°	256.9	267.5	283.1	294.0	318.0
57.5°	217.6	227.9	240.2	245.0	259.7
60°	191.5	202.9	214.0	213.3	221.3
62.5°	167.5	177.3	188.4	180.5	181.0
65°	128.9	139.5	152.1	133.0	120.8
67.5°	104.1	106.3	119.3	92.8	78.3
70°	92.5	92.5	96.1	71.8	59.7
72.5°	81.4	81.4	78.1	58.3	45.6
75°	64.8	64.8	59.0	40.5	27.7
77.5°	49.9	49.4	45.1	30.1	20.1
80°	40.0	40.0	36.4	23.9	16.0
82.5°	31.3	31.3	28.2	18.6	11.8
85°	18.1	18.1	16.8	10.9	6.6
87.5°	6.5	6.5	5.8	3.4	2.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036368

CATALOG NUMBER: SQ4R-WB-075D-B2750-1D-UNV-W2A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.23	16.60	15.59	16.92	17.23	15.85	17.23	16.22	17.54	17.85
	3H	16.20	17.43	16.58	17.75	18.12	16.31	17.53	16.69	17.86	18.23
	4H	16.64	17.78	17.04	18.13	18.51	16.39	17.53	16.79	17.88	18.26
	6H	16.95	18.00	17.36	18.37	18.76	16.40	17.45	16.81	17.82	18.21
	8H	17.08	18.07	17.51	18.47	18.87	16.39	17.39	16.82	17.78	18.18
	12H	17.16	18.11	17.59	18.50	18.93	16.38	17.33	16.81	17.71	18.14
4H	2H	15.72	16.86	16.12	17.21	17.59	16.23	17.37	16.64	17.73	18.11
	3H	16.88	17.82	17.30	18.22	18.63	16.87	17.80	17.28	18.21	18.61
	4H	17.42	18.26	17.85	18.68	19.12	17.00	17.84	17.44	18.26	18.70
	6H	17.84	18.56	18.30	19.01	19.47	17.07	17.80	17.53	18.24	18.71
	8H	18.02	18.69	18.48	19.14	19.61	17.08	17.76	17.55	18.20	18.67
	12H	18.14	18.74	18.63	19.22	19.70	17.08	17.68	17.56	18.16	18.63
8H	4H	17.53	18.20	18.00	18.65	19.12	17.15	17.82	17.61	18.27	18.74
	6H	18.06	18.62	18.57	19.11	19.59	17.30	17.85	17.80	18.34	18.82
	8H	18.33	18.82	18.85	19.34	19.83	17.35	17.85	17.87	18.36	18.85
	12H	18.53	18.97	19.04	19.46	20.03	17.38	17.82	17.90	18.32	18.89
12H	4H	17.51	18.11	18.00	18.59	19.06	17.15	17.75	17.64	18.23	18.71
	6H	18.07	18.57	18.59	19.08	19.57	17.33	17.83	17.85	18.35	18.84
	8H	18.39	18.83	18.90	19.32	19.89	17.44	17.88	17.95	18.37	18.94