

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1036379

Luminaire Tested: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-2019
Report Number: P1036379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P519276)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1000 LUMENS PER FOOT DC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3089.3 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036379

CATALOG NUMBER: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1036379

CATALOG NUMBER: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		85
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	56	52		61
7	73	61	53	48	71	60	53	48	59	52	48		58	52	47		56
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49
10	61	49	42	37	60	48	42	37	48	41	37		47	41	37		46

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19560	19560	19560
5°	19317	19247	19360
10°	18249	18415	18842
15°	16846	17239	18012
20°	15299	15873	16924
25°	13723	14471	15768
30°	12271	13071	14568
35°	10728	11503	13151
40°	9029	9747	11384
45°	7452	8095	9504
50°	6221	6783	7916
55°	5282	5820	6537
60°	4515	5047	5218
65°	3596	4244	3369
70°	3186	3313	2058
75°	2948	2688	1262
80°	2720	2476	1089
85°	2445	2276	889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 9504 cd/sqm

TEST NUMBER: P1036379

CATALOG NUMBER: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.5	6.3
10°-20°	505.8	16.4
20°-30°	655.2	21.2
30°-40°	641.6	20.8
40°-50°	491.1	15.9
50°-60°	327.2	10.6
60°-70°	178.6	5.8
70°-80°	74.4	2.4
80°-90°	21.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1355.4	43.9
0°-40°	1997.0	64.6
0°-60°	2815.3	91.1
0°-90°	3089.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3089.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2120	2120	2120	2120	2120	
5°	2086	2065	2078	2083	2090	194
15°	1764	1757	1805	1854	1886	493
25°	1348	1352	1422	1483	1549	620
35°	952	957	1021	1090	1168	592
45°	571	582	620	667	728	445
55°	328	342	362	376	406	298
65°	165	178	194	170	154	171
75°	83	83	75	52	35	88
85°	23	23	22	14	8	26
90°	0	0	0	0	0	

TEST NUMBER: P1036379

CATALOG NUMBER: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2120.1	2120.1	2120.1	2120.1	2120.1
2.5°	2125.3	2106.4	2111.2	2111.0	2105.1
5°	2085.7	2064.7	2078.2	2082.9	2090.4
7.5°	2008.2	1992.4	2017.1	2035.1	2049.9
10°	1947.9	1934.3	1965.6	1992.2	2011.2
12.5°	1878.1	1866.4	1905.5	1940.8	1965.9
15°	1763.7	1757.4	1804.8	1853.9	1885.7
17.5°	1641.6	1638.4	1692.7	1750.0	1790.7
20°	1558.2	1557.3	1616.7	1676.5	1723.7
22.5°	1474.1	1476.0	1538.6	1600.7	1654.6
25°	1348.0	1351.6	1421.5	1483.4	1548.9
27.5°	1231.3	1233.1	1305.0	1370.5	1440.4
30°	1151.8	1156.1	1226.9	1294.8	1367.4
32.5°	1072.2	1077.4	1146.7	1216.6	1290.8
35°	952.5	957.2	1021.3	1090.3	1167.6
37.5°	829.3	835.6	892.7	957.5	1033.8
40°	749.7	759.0	809.3	870.6	945.2
42.5°	673.1	684.4	731.2	789.3	856.4
45°	571.1	582.1	620.4	667.4	728.4
47.5°	483.3	495.9	525.4	565.9	617.9
50°	433.4	445.4	472.6	502.5	551.5
52.5°	389.6	401.4	425.7	448.8	490.7
55°	328.4	342.0	361.8	375.7	406.4
57.5°	278.2	291.2	307.0	313.1	331.9
60°	244.7	259.2	273.5	272.8	282.8
62.5°	214.2	226.6	240.7	230.8	231.4
65°	164.7	178.4	194.4	169.9	154.3
67.5°	133.1	135.9	152.5	118.5	100.1
70°	118.1	118.1	122.8	91.8	76.3
72.5°	104.1	104.1	99.9	74.5	58.4
75°	82.7	82.7	75.4	51.8	35.4
77.5°	63.8	63.2	57.7	38.6	25.7
80°	51.2	51.2	46.6	30.6	20.5
82.5°	40.0	40.0	36.0	23.8	15.1
85°	23.1	23.1	21.5	13.9	8.4
87.5°	8.2	8.2	7.3	4.4	3.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1036379

CATALOG NUMBER: SQ4R-WB-100D-B2750-1D-UNV-W2A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.08	17.45	16.44	17.77	18.08	16.70	18.08	17.07	18.39	18.71
	3H	17.05	18.28	17.43	18.61	18.97	17.16	18.38	17.54	18.71	19.08
	4H	17.49	18.63	17.89	18.98	19.36	17.24	18.38	17.64	18.73	19.11
	6H	17.80	18.85	18.22	19.22	19.61	17.25	18.30	17.67	18.67	19.06
	8H	17.93	18.93	18.36	19.32	19.72	17.25	18.24	17.68	18.63	19.04
	12H	18.01	18.97	18.45	19.35	19.78	17.23	18.18	17.66	18.57	19.00
4H	2H	16.57	17.71	16.97	18.06	18.44	17.09	18.23	17.49	18.58	18.96
	3H	17.74	18.67	18.15	19.07	19.48	17.72	18.66	18.13	19.06	19.46
	4H	18.27	19.11	18.70	19.53	19.97	17.85	18.69	18.29	19.11	19.55
	6H	18.69	19.42	19.15	19.86	20.33	17.92	18.65	18.39	19.09	19.56
	8H	18.87	19.54	19.34	19.99	20.46	17.93	18.61	18.40	19.06	19.53
	12H	18.99	19.59	19.48	20.07	20.55	17.93	18.53	18.42	19.01	19.49
8H	4H	18.38	19.05	18.85	19.50	19.97	18.00	18.68	18.47	19.12	19.59
	6H	18.92	19.47	19.42	19.97	20.45	18.15	18.70	18.65	19.20	19.68
	8H	19.18	19.68	19.70	20.19	20.68	18.20	18.70	18.72	19.21	19.70
	12H	19.38	19.82	19.90	20.32	20.89	18.24	18.68	18.75	19.17	19.74
12H	4H	18.36	18.96	18.85	19.44	19.91	18.01	18.61	18.49	19.09	19.56
	6H	18.92	19.42	19.44	19.93	20.42	18.19	18.68	18.71	19.20	19.69
	8H	19.24	19.68	19.75	20.17	20.74	18.29	18.73	18.81	19.23	19.80