

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055036

Luminaire Tested: SQ4R-FA-075D-830-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-830-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2697.1 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	89	87
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73
3	91	81	73	66	88	79	72	66	76	70	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	51	43	37	50	42	37	48	42	37	47	41	37
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10012	10012	10012	10012
5°	10098	8186	10098	10412
10°	10042	7551	10042	10561
15°	9944	8885	9944	10640
20°	9747	9174	9747	10676
25°	9333	9260	9333	10577
30°	8794	9111	8794	10555
35°	7852	8916	7852	10442
40°	6554	8854	6554	10251
45°	5868	8748	5868	9966
50°	6249	8664	6249	9550
55°	5896	8852	5896	9067
60°	6100	8676	6100	8241
65°	5558	8292	5558	7420
70°	3876	7783	3876	6621
75°	3441	6881	3441	5747
80°	2839	5345	2839	4912
85°	1734	3700	1734	4352

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 10181 cd/sqm

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.9	3.5
10°-20°	266.6	9.9
20°-30°	412.1	15.3
30°-40°	491.9	18.2
40°-50°	494.8	18.3
50°-60°	430.6	16.0
60°-70°	305.3	11.3
70°-80°	161.6	6.0
80°-90°	40.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.5	28.6
0°-40°	1264.5	46.9
0°-60°	2189.9	81.2
0°-90°	2697.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2697.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1040	1040	1040	1040	1040	
5°	1045	847	1045	1077	1045	99
15°	998	891	998	1068	998	281
25°	879	872	879	996	879	403
35°	668	759	668	888	668	413
45°	431	642	431	732	431	345
55°	351	527	351	540	351	323
65°	244	364	244	326	244	233
75°	92	185	92	154	92	97
85°	16	34	16	39	16	21
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1048.8	1046.9	1043.9	1042.0	1039.0	1038.0	1037.0	1036.1	1035.1	1032.1	1030.2
5°	1044.9	1041.0	1036.1	1032.1	1027.2	1023.3	1020.3	1016.4	1012.4	1006.5	1000.6
7.5°	1037.0	1030.2	1023.3	1016.4	1009.5	1000.6	991.8	982.9	974.1	958.3	939.6
10°	1027.2	1017.4	1006.5	996.7	985.9	965.2	944.6	922.9	902.2	874.7	856.0
12.5°	1013.4	996.7	979.0	962.3	944.6	915.0	886.5	857.0	827.5	808.8	798.0
15°	997.7	971.1	943.6	917.0	889.5	863.9	838.3	811.7	786.1	772.4	764.5
17.5°	976.0	940.6	906.2	870.8	835.3	815.7	795.0	775.3	754.7	744.8	738.9
20°	951.4	913.1	873.7	835.3	796.0	780.2	764.5	747.8	732.0	723.2	720.2
22.5°	918.0	880.6	843.2	805.8	768.4	753.7	738.9	723.2	708.4	701.5	703.5
25°	878.6	846.2	812.7	780.2	746.8	733.0	718.3	704.5	689.7	681.8	687.8
27.5°	837.3	809.8	782.2	754.7	727.1	712.4	697.6	681.8	667.1	664.1	677.9
30°	791.1	770.4	748.8	728.1	706.4	690.7	675.0	659.2	643.5	642.5	664.1
32.5°	738.9	724.2	710.4	695.6	680.9	666.1	651.3	635.6	620.8	619.9	646.4
35°	668.1	664.1	660.2	655.3	651.3	636.6	621.8	607.1	592.3	593.3	622.8
37.5°	590.3	597.2	605.1	612.0	618.9	605.1	592.3	578.5	564.8	564.8	596.2
40°	521.5	535.2	549.0	562.8	576.6	567.7	557.9	549.0	539.2	536.2	568.7
42.5°	470.3	483.1	495.9	507.7	520.5	517.5	515.6	512.6	509.7	505.7	537.2
45°	431.0	432.9	435.9	437.8	439.8	449.6	459.5	469.3	479.2	476.2	504.7
47.5°	418.2	405.4	391.6	378.8	365.0	385.7	406.4	426.0	446.7	445.7	471.3
50°	417.2	391.6	365.0	339.4	312.9	337.5	362.1	385.7	410.3	414.2	433.9
52.5°	378.8	355.2	331.6	307.0	283.4	305.0	325.7	347.3	368.0	379.8	397.5
55°	351.3	328.6	306.0	283.4	260.7	275.5	289.3	304.0	317.8	343.4	359.1
57.5°	345.4	317.8	290.3	261.7	234.2	244.0	252.9	262.7	271.6	296.2	315.8
60°	316.8	289.3	261.7	233.2	205.6	212.5	218.4	225.3	231.2	249.9	273.5
62.5°	287.3	261.7	237.1	211.5	186.0	192.8	198.7	205.6	211.5	215.5	241.1
65°	244.0	225.3	206.6	187.9	169.2	175.1	180.1	186.0	190.9	191.9	215.5
67.5°	186.0	178.1	170.2	161.4	153.5	159.4	164.3	170.2	175.1	176.1	195.8
70°	137.7	137.7	137.7	136.8	136.8	141.7	147.6	152.5	157.4	159.4	174.2
72.5°	114.1	116.1	119.1	121.0	123.0	126.9	130.9	134.8	138.7	140.7	151.5
75°	92.5	96.4	100.4	103.3	107.2	110.2	113.1	115.1	118.1	119.1	126.9
77.5°	67.9	72.8	77.7	81.7	86.6	89.5	91.5	94.5	96.4	94.5	100.4
80°	51.2	54.1	57.1	59.0	62.0	64.0	66.9	68.9	70.8	68.9	72.8
82.5°	34.4	35.4	37.4	38.4	39.4	41.3	43.3	45.3	47.2	45.3	48.2
85°	15.7	16.7	18.7	19.7	20.7	22.6	23.6	25.6	26.6	25.6	26.6
87.5°	4.9	5.9	6.9	6.9	7.9	8.9	9.8	10.8	11.8	11.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1029.2	1027.2	1023.3	1020.3	1016.4	1012.4	1010.5	1008.5	1006.5	1004.6	1006.5
5°	993.7	987.8	979.0	970.1	961.3	952.4	940.6	928.8	920.0	911.1	909.1
7.5°	920.0	901.3	885.5	868.8	853.0	836.3	827.5	818.6	810.7	802.9	800.9
10°	836.3	817.6	806.8	797.0	786.1	775.3	770.4	764.5	763.5	761.5	762.5
12.5°	786.1	775.3	769.4	763.5	756.6	750.7	749.7	748.8	751.7	753.7	760.6
15°	756.6	748.8	746.8	744.8	741.9	739.9	745.8	750.7	768.4	785.2	804.8
17.5°	734.0	728.1	733.0	736.9	741.9	745.8	776.3	806.8	830.4	853.0	859.9
20°	718.3	715.3	735.0	755.6	775.3	795.0	818.6	841.2	850.1	858.0	861.9
22.5°	704.5	706.4	736.0	764.5	794.0	822.5	832.4	841.2	847.1	853.0	856.0
25°	694.6	700.5	730.1	760.6	790.1	819.6	825.5	830.4	832.4	833.4	840.3
27.5°	691.7	705.5	731.0	756.6	781.2	806.8	810.7	814.7	816.6	817.6	824.5
30°	684.8	706.4	728.1	748.8	770.4	791.1	790.1	789.1	793.0	797.0	803.9
32.5°	673.0	699.6	716.3	734.0	750.7	767.4	766.5	765.5	771.4	776.3	781.2
35°	653.3	682.8	697.6	711.4	726.1	739.9	740.9	740.9	745.8	750.7	753.7
37.5°	628.7	660.2	674.0	687.8	700.5	714.3	713.3	712.4	714.3	715.3	720.2
40°	600.2	632.7	646.4	660.2	673.0	686.8	683.8	679.9	679.9	678.9	684.8
42.5°	567.7	599.2	613.0	626.8	639.5	653.3	647.4	640.5	642.5	643.5	651.3
45°	534.3	562.8	575.6	589.4	602.2	614.9	611.0	606.1	610.0	614.0	621.8
47.5°	496.9	522.5	536.2	550.0	563.8	577.6	575.6	572.6	576.6	580.5	589.4
50°	454.6	474.2	491.0	507.7	524.4	541.2	541.2	541.2	545.1	548.0	556.9
52.5°	414.2	431.9	451.6	471.3	490.0	509.7	510.6	511.6	515.6	518.5	526.4
55°	374.9	390.6	412.3	433.9	455.6	477.2	479.2	481.1	485.1	488.0	495.9
57.5°	334.5	354.2	376.8	400.5	423.1	445.7	446.7	447.7	450.6	453.6	460.5
60°	297.1	320.8	342.4	365.0	386.7	408.3	412.3	415.2	417.2	419.1	425.0
62.5°	267.6	293.2	312.9	333.5	353.2	372.9	377.8	381.8	383.7	384.7	388.6
65°	240.1	263.7	282.4	300.1	318.8	336.5	340.4	344.4	347.3	349.3	352.2
67.5°	215.5	235.2	249.9	264.7	279.4	294.2	300.1	305.0	307.0	308.9	310.9
70°	189.9	204.7	217.4	230.2	243.0	255.8	260.7	265.7	267.6	268.6	269.6
72.5°	162.3	173.2	183.0	192.8	202.7	212.5	217.4	222.4	224.3	225.3	226.3
75°	133.8	141.7	149.6	157.4	165.3	173.2	177.1	180.1	181.0	182.0	182.0
77.5°	105.3	111.2	117.1	123.0	127.9	133.8	136.8	139.7	139.7	139.7	139.7
80°	75.8	79.7	83.6	87.6	91.5	95.4	96.4	97.4	98.4	99.4	99.4
82.5°	50.2	53.1	55.1	58.1	60.0	62.0	62.0	62.0	62.0	62.0	63.0
85°	28.5	29.5	30.5	31.5	32.5	33.5	34.4	34.4	34.4	34.4	34.4
87.5°	12.8	13.8	13.8	14.8	14.8	14.8	14.8	13.8	13.8	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1007.5	1009.5	1010.5	1008.5	1005.6	1003.6	1000.6	1001.6	1002.6	1003.6	1004.6
5°	906.2	904.2	901.3	894.4	887.5	880.6	875.7	871.7	867.8	863.9	859.9
7.5°	798.0	796.0	793.0	791.1	789.1	787.1	783.2	782.2	781.2	780.2	779.3
10°	763.5	763.5	764.5	765.5	765.5	766.5	767.4	769.4	770.4	772.4	773.4
12.5°	767.4	773.4	780.2	793.0	806.8	819.6	828.5	836.3	845.2	853.0	860.9
15°	825.5	845.2	864.9	869.8	875.7	880.6	883.6	885.5	887.5	888.5	890.4
17.5°	866.8	872.7	879.6	881.6	884.5	886.5	887.5	888.5	890.4	891.4	892.4
20°	865.8	868.8	872.7	875.7	878.6	881.6	883.6	886.5	888.5	891.4	893.4
22.5°	859.9	862.9	865.8	870.8	874.7	879.6	883.6	885.5	887.5	889.5	891.4
25°	846.2	853.0	859.0	862.9	865.8	869.8	869.8	869.8	870.8	870.8	870.8
27.5°	831.4	838.3	845.2	846.2	848.1	849.1	851.1	853.0	854.0	856.0	857.0
30°	810.7	817.6	824.5	826.5	828.5	830.4	828.5	827.5	826.5	824.5	823.5
32.5°	787.1	792.0	797.0	798.0	798.0	798.9	794.0	793.0	792.0	790.1	789.1
35°	757.6	760.6	763.5	762.5	762.5	761.5	762.5	762.5	762.5	761.5	761.5
37.5°	724.2	729.1	733.0	734.0	734.0	735.0	736.9	736.9	736.9	736.0	736.0
40°	691.7	697.6	703.5	704.5	706.4	707.4	708.4	708.4	708.4	707.4	707.4
42.5°	659.2	667.1	675.0	676.9	678.9	680.9	679.9	678.9	678.9	677.9	676.9
45°	630.7	638.6	646.4	647.4	649.4	650.4	651.3	650.4	648.4	647.4	645.4
47.5°	598.2	606.1	614.9	616.9	617.9	619.9	619.9	618.9	617.9	615.9	614.9
50°	566.7	575.6	584.4	585.4	586.4	587.4	586.4	584.4	583.5	581.5	579.5
52.5°	535.2	543.1	551.0	551.0	550.0	550.0	550.0	550.0	551.0	551.0	551.0
55°	502.8	510.6	517.5	517.5	517.5	517.5	518.5	520.5	522.5	523.4	525.4
57.5°	468.3	475.2	482.1	483.1	483.1	484.1	484.1	485.1	487.0	488.0	489.0
60°	431.9	437.8	443.7	444.7	444.7	445.7	447.7	448.7	449.6	450.6	451.6
62.5°	392.6	395.5	399.5	401.4	403.4	405.4	407.3	407.3	408.3	408.3	408.3
65°	355.2	357.2	360.1	361.1	362.1	363.1	365.0	365.0	366.0	366.0	366.0
67.5°	312.9	313.9	315.8	316.8	318.8	319.8	318.8	318.8	318.8	317.8	317.8
70°	270.6	271.6	272.5	273.5	274.5	275.5	275.5	275.5	275.5	274.5	274.5
72.5°	226.3	227.3	227.3	227.3	228.3	228.3	227.3	228.3	229.3	230.2	231.2
75°	183.0	183.0	183.0	183.0	182.0	182.0	184.0	184.0	183.0	183.0	182.0
77.5°	139.7	139.7	139.7	139.7	138.7	138.7	140.7	140.7	139.7	139.7	138.7
80°	99.4	98.4	98.4	98.4	98.4	98.4	97.4	97.4	97.4	97.4	97.4
82.5°	63.0	64.0	64.0	64.0	63.0	63.0	62.0	62.0	62.0	62.0	62.0
85°	33.5	33.5	32.5	33.5	33.5	34.4	35.4	35.4	34.4	34.4	33.5
87.5°	13.8	13.8	13.8	13.8	12.8	12.8	11.8	11.8	11.8	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1001.6	999.7	996.7	993.7	996.7	999.7	1001.6	1004.6	1003.6	1002.6	1001.6
5°	857.0	854.0	850.1	847.1	850.1	854.0	857.0	859.9	863.9	867.8	871.7
7.5°	777.3	775.3	773.4	771.4	773.4	775.3	777.3	779.3	780.2	781.2	782.2
10°	773.4	773.4	772.4	772.4	772.4	773.4	773.4	773.4	772.4	770.4	769.4
12.5°	860.9	859.9	859.9	859.0	859.9	859.9	860.9	860.9	853.0	845.2	836.3
15°	890.4	891.4	891.4	891.4	891.4	891.4	890.4	890.4	888.5	887.5	885.5
17.5°	892.4	892.4	892.4	892.4	892.4	892.4	892.4	892.4	891.4	890.4	888.5
20°	894.4	894.4	895.4	895.4	895.4	894.4	894.4	893.4	891.4	888.5	886.5
22.5°	891.4	891.4	890.4	890.4	890.4	891.4	891.4	891.4	889.5	887.5	885.5
25°	870.8	871.7	871.7	871.7	871.7	871.7	870.8	870.8	870.8	870.8	869.8
27.5°	857.0	857.0	856.0	856.0	856.0	857.0	857.0	857.0	856.0	854.0	853.0
30°	822.5	821.6	820.6	819.6	820.6	821.6	822.5	823.5	824.5	826.5	827.5
32.5°	788.1	788.1	787.1	786.1	787.1	788.1	788.1	789.1	790.1	792.0	793.0
35°	760.6	760.6	759.6	758.6	759.6	760.6	760.6	761.5	761.5	762.5	762.5
37.5°	735.0	734.0	733.0	732.0	733.0	734.0	735.0	736.0	736.0	736.9	736.9
40°	706.4	706.4	705.5	704.5	705.5	706.4	706.4	707.4	707.4	708.4	708.4
42.5°	676.9	675.9	675.9	675.0	675.9	675.9	676.9	676.9	677.9	678.9	678.9
45°	644.5	644.5	643.5	642.5	643.5	644.5	644.5	645.4	647.4	648.4	650.4
47.5°	614.0	614.0	613.0	612.0	613.0	614.0	614.0	614.9	615.9	617.9	618.9
50°	579.5	579.5	578.5	578.5	578.5	579.5	579.5	579.5	581.5	583.5	584.4
52.5°	552.0	552.0	553.0	553.0	553.0	552.0	552.0	551.0	551.0	551.0	550.0
55°	526.4	526.4	527.4	527.4	527.4	526.4	526.4	525.4	523.4	522.5	520.5
57.5°	489.0	489.0	489.0	489.0	489.0	489.0	489.0	489.0	488.0	487.0	485.1
60°	451.6	451.6	450.6	450.6	450.6	451.6	451.6	451.6	450.6	449.6	448.7
62.5°	408.3	407.3	407.3	406.4	407.3	407.3	408.3	408.3	408.3	408.3	407.3
65°	366.0	365.0	365.0	364.0	365.0	365.0	366.0	366.0	366.0	366.0	365.0
67.5°	318.8	319.8	320.8	321.7	320.8	319.8	318.8	317.8	317.8	318.8	318.8
70°	275.5	275.5	276.5	276.5	276.5	275.5	275.5	274.5	274.5	275.5	275.5
72.5°	230.2	230.2	229.3	228.3	229.3	230.2	230.2	231.2	230.2	229.3	228.3
75°	183.0	184.0	184.0	185.0	184.0	184.0	183.0	182.0	183.0	183.0	184.0
77.5°	138.7	138.7	138.7	138.7	138.7	138.7	138.7	138.7	139.7	139.7	140.7
80°	97.4	97.4	96.4	96.4	96.4	97.4	97.4	97.4	97.4	97.4	97.4
82.5°	63.0	63.0	64.0	64.0	64.0	63.0	63.0	62.0	62.0	62.0	62.0
85°	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	34.4	34.4	35.4
87.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1000.6	1003.6	1005.6	1008.5	1010.5	1009.5	1007.5	1006.5	1004.6	1006.5	1008.5
5°	875.7	880.6	887.5	894.4	901.3	904.2	906.2	909.1	911.1	920.0	928.8
7.5°	783.2	787.1	789.1	791.1	793.0	796.0	798.0	800.9	802.9	810.7	818.6
10°	767.4	766.5	765.5	765.5	764.5	763.5	763.5	762.5	761.5	763.5	764.5
12.5°	828.5	819.6	806.8	793.0	780.2	773.4	767.4	760.6	753.7	751.7	748.8
15°	883.6	880.6	875.7	869.8	864.9	845.2	825.5	804.8	785.2	768.4	750.7
17.5°	887.5	886.5	884.5	881.6	879.6	872.7	866.8	859.9	853.0	830.4	806.8
20°	883.6	881.6	878.6	875.7	872.7	868.8	865.8	861.9	858.0	850.1	841.2
22.5°	883.6	879.6	874.7	870.8	865.8	862.9	859.9	856.0	853.0	847.1	841.2
25°	869.8	869.8	865.8	862.9	859.0	853.0	846.2	840.3	833.4	832.4	830.4
27.5°	851.1	849.1	848.1	846.2	845.2	838.3	831.4	824.5	817.6	816.6	814.7
30°	828.5	830.4	828.5	826.5	824.5	817.6	810.7	803.9	797.0	793.0	789.1
32.5°	794.0	798.9	798.0	798.0	797.0	792.0	787.1	781.2	776.3	771.4	765.5
35°	762.5	761.5	762.5	762.5	763.5	760.6	757.6	753.7	750.7	745.8	740.9
37.5°	736.9	735.0	734.0	734.0	733.0	729.1	724.2	720.2	715.3	714.3	712.4
40°	708.4	707.4	706.4	704.5	703.5	697.6	691.7	684.8	678.9	679.9	679.9
42.5°	679.9	680.9	678.9	676.9	675.0	667.1	659.2	651.3	643.5	642.5	640.5
45°	651.3	650.4	649.4	647.4	646.4	638.6	630.7	621.8	614.0	610.0	606.1
47.5°	619.9	619.9	617.9	616.9	614.9	606.1	598.2	589.4	580.5	576.6	572.6
50°	586.4	587.4	586.4	585.4	584.4	575.6	566.7	556.9	548.0	545.1	541.2
52.5°	550.0	550.0	550.0	551.0	551.0	543.1	535.2	526.4	518.5	515.6	511.6
55°	518.5	517.5	517.5	517.5	517.5	510.6	502.8	495.9	488.0	485.1	481.1
57.5°	484.1	484.1	483.1	483.1	482.1	475.2	468.3	460.5	453.6	450.6	447.7
60°	447.7	445.7	444.7	444.7	443.7	437.8	431.9	425.0	419.1	417.2	415.2
62.5°	407.3	405.4	403.4	401.4	399.5	395.5	392.6	388.6	384.7	383.7	381.8
65°	365.0	363.1	362.1	361.1	360.1	357.2	355.2	352.2	349.3	347.3	344.4
67.5°	318.8	319.8	318.8	316.8	315.8	313.9	312.9	310.9	308.9	307.0	305.0
70°	275.5	275.5	274.5	273.5	272.5	271.6	270.6	269.6	268.6	267.6	265.7
72.5°	227.3	228.3	228.3	227.3	227.3	227.3	226.3	226.3	225.3	224.3	222.4
75°	184.0	182.0	182.0	183.0	183.0	183.0	183.0	182.0	182.0	181.0	180.1
77.5°	140.7	138.7	138.7	139.7	139.7	139.7	139.7	139.7	139.7	139.7	139.7
80°	97.4	98.4	98.4	98.4	98.4	98.4	99.4	99.4	99.4	98.4	97.4
82.5°	62.0	63.0	63.0	64.0	64.0	64.0	63.0	63.0	62.0	62.0	62.0
85°	35.4	34.4	33.5	33.5	32.5	33.5	33.5	34.4	34.4	34.4	34.4
87.5°	11.8	12.8	12.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1010.5	1012.4	1016.4	1020.3	1023.3	1027.2	1029.2	1030.2	1032.1	1035.1	1036.1
5°	940.6	952.4	961.3	970.1	979.0	987.8	993.7	1000.6	1006.5	1012.4	1016.4
7.5°	827.5	836.3	853.0	868.8	885.5	901.3	920.0	939.6	958.3	974.1	982.9
10°	770.4	775.3	786.1	797.0	806.8	817.6	836.3	856.0	874.7	902.2	922.9
12.5°	749.7	750.7	756.6	763.5	769.4	775.3	786.1	798.0	808.8	827.5	857.0
15°	745.8	739.9	741.9	744.8	746.8	748.8	756.6	764.5	772.4	786.1	811.7
17.5°	776.3	745.8	741.9	736.9	733.0	728.1	734.0	738.9	744.8	754.7	775.3
20°	818.6	795.0	775.3	755.6	735.0	715.3	718.3	720.2	723.2	732.0	747.8
22.5°	832.4	822.5	794.0	764.5	736.0	706.4	704.5	703.5	701.5	708.4	723.2
25°	825.5	819.6	790.1	760.6	730.1	700.5	694.6	687.8	681.8	689.7	704.5
27.5°	810.7	806.8	781.2	756.6	731.0	705.5	691.7	677.9	664.1	667.1	681.8
30°	790.1	791.1	770.4	748.8	728.1	706.4	684.8	664.1	642.5	643.5	659.2
32.5°	766.5	767.4	750.7	734.0	716.3	699.6	673.0	646.4	619.9	620.8	635.6
35°	740.9	739.9	726.1	711.4	697.6	682.8	653.3	622.8	593.3	592.3	607.1
37.5°	713.3	714.3	700.5	687.8	674.0	660.2	628.7	596.2	564.8	564.8	578.5
40°	683.8	686.8	673.0	660.2	646.4	632.7	600.2	568.7	536.2	539.2	549.0
42.5°	647.4	653.3	639.5	626.8	613.0	599.2	567.7	537.2	505.7	509.7	512.6
45°	611.0	614.9	602.2	589.4	575.6	562.8	534.3	504.7	476.2	479.2	469.3
47.5°	575.6	577.6	563.8	550.0	536.2	522.5	496.9	471.3	445.7	446.7	426.0
50°	541.2	541.2	524.4	507.7	491.0	474.2	454.6	433.9	414.2	410.3	385.7
52.5°	510.6	509.7	490.0	471.3	451.6	431.9	414.2	397.5	379.8	368.0	347.3
55°	479.2	477.2	455.6	433.9	412.3	390.6	374.9	359.1	343.4	317.8	304.0
57.5°	446.7	445.7	423.1	400.5	376.8	354.2	334.5	315.8	296.2	271.6	262.7
60°	412.3	408.3	386.7	365.0	342.4	320.8	297.1	273.5	249.9	231.2	225.3
62.5°	377.8	372.9	353.2	333.5	312.9	293.2	267.6	241.1	215.5	211.5	205.6
65°	340.4	336.5	318.8	300.1	282.4	263.7	240.1	215.5	191.9	190.9	186.0
67.5°	300.1	294.2	279.4	264.7	249.9	235.2	215.5	195.8	176.1	175.1	170.2
70°	260.7	255.8	243.0	230.2	217.4	204.7	189.9	174.2	159.4	157.4	152.5
72.5°	217.4	212.5	202.7	192.8	183.0	173.2	162.3	151.5	140.7	138.7	134.8
75°	177.1	173.2	165.3	157.4	149.6	141.7	133.8	126.9	119.1	118.1	115.1
77.5°	136.8	133.8	127.9	123.0	117.1	111.2	105.3	100.4	94.5	96.4	94.5
80°	96.4	95.4	91.5	87.6	83.6	79.7	75.8	72.8	68.9	70.8	68.9
82.5°	62.0	62.0	60.0	58.1	55.1	53.1	50.2	48.2	45.3	47.2	45.3
85°	34.4	33.5	32.5	31.5	30.5	29.5	28.5	26.6	25.6	26.6	25.6
87.5°	14.8	14.8	14.8	14.8	13.8	13.8	12.8	12.8	11.8	11.8	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1037.0	1038.0	1039.0	1042.0	1043.9	1046.9	1048.8	1048.8	1048.8	1048.8	1048.8
5°	1020.3	1023.3	1027.2	1032.1	1036.1	1041.0	1044.9	1046.9	1048.8	1050.8	1052.8
7.5°	991.8	1000.6	1009.5	1016.4	1023.3	1030.2	1037.0	1041.0	1044.9	1047.9	1051.8
10°	944.6	965.2	985.9	996.7	1006.5	1017.4	1027.2	1032.1	1038.0	1042.9	1047.9
12.5°	886.5	915.0	944.6	962.3	979.0	996.7	1013.4	1020.3	1028.2	1035.1	1042.0
15°	838.3	863.9	889.5	917.0	943.6	971.1	997.7	1006.5	1014.4	1023.3	1031.1
17.5°	795.0	815.7	835.3	870.8	906.2	940.6	976.0	986.9	996.7	1007.5	1017.4
20°	764.5	780.2	796.0	835.3	873.7	913.1	951.4	963.2	975.1	986.9	998.7
22.5°	738.9	753.7	768.4	805.8	843.2	880.6	918.0	933.7	948.5	964.2	979.0
25°	718.3	733.0	746.8	780.2	812.7	846.2	878.6	898.3	918.0	937.7	957.3
27.5°	697.6	712.4	727.1	754.7	782.2	809.8	837.3	860.9	883.6	907.2	929.8
30°	675.0	690.7	706.4	728.1	748.8	770.4	791.1	816.6	841.2	866.8	891.4
32.5°	651.3	666.1	680.9	695.6	710.4	724.2	738.9	762.5	787.1	810.7	834.4
35°	621.8	636.6	651.3	655.3	660.2	664.1	668.1	698.6	729.1	759.6	790.1
37.5°	592.3	605.1	618.9	612.0	605.1	597.2	590.3	630.7	671.0	711.4	751.7
40°	557.9	567.7	576.6	562.8	549.0	535.2	521.5	563.8	607.1	649.4	691.7
42.5°	515.6	517.5	520.5	507.7	495.9	483.1	470.3	509.7	548.0	587.4	625.8
45°	459.5	449.6	439.8	437.8	435.9	432.9	431.0	475.2	519.5	563.8	608.1
47.5°	406.4	385.7	365.0	378.8	391.6	405.4	418.2	456.5	495.9	534.3	572.6
50°	362.1	337.5	312.9	339.4	365.0	391.6	417.2	446.7	475.2	504.7	533.3
52.5°	325.7	305.0	283.4	307.0	331.6	355.2	378.8	405.4	431.9	458.5	485.1
55°	289.3	275.5	260.7	283.4	306.0	328.6	351.3	371.9	393.6	414.2	434.9
57.5°	252.9	244.0	234.2	261.7	290.3	317.8	345.4	349.3	354.2	358.1	362.1
60°	218.4	212.5	205.6	233.2	261.7	289.3	316.8	303.0	289.3	275.5	261.7
62.5°	198.7	192.8	186.0	211.5	237.1	261.7	287.3	262.7	239.1	214.5	189.9
65°	180.1	175.1	169.2	187.9	206.6	225.3	244.0	223.3	201.7	181.0	159.4
67.5°	164.3	159.4	153.5	161.4	170.2	178.1	186.0	172.2	158.4	143.7	129.9
70°	147.6	141.7	136.8	136.8	137.7	137.7	137.7	125.0	112.2	99.4	86.6
72.5°	130.9	126.9	123.0	121.0	119.1	116.1	114.1	103.3	92.5	80.7	69.9
75°	113.1	110.2	107.2	103.3	100.4	96.4	92.5	87.6	83.6	78.7	73.8
77.5°	91.5	89.5	86.6	81.7	77.7	72.8	67.9	67.9	68.9	68.9	68.9
80°	66.9	64.0	62.0	59.0	57.1	54.1	51.2	52.1	53.1	53.1	54.1
82.5°	43.3	41.3	39.4	38.4	37.4	35.4	34.4	34.4	34.4	34.4	34.4
85°	23.6	22.6	20.7	19.7	18.7	16.7	15.7	16.7	17.7	18.7	19.7
87.5°	9.8	8.9	7.9	6.9	6.9	5.9	4.9	5.9	6.9	7.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1050.8	1051.8	1053.8	1054.8	1056.7	1056.7	1056.7	1056.7	1055.7	1055.7	1054.8
5°	1055.7	1058.7	1060.7	1063.6	1065.6	1066.6	1066.6	1067.5	1067.5	1067.5	1066.6
7.5°	1055.7	1058.7	1062.6	1065.6	1068.5	1069.5	1070.5	1071.5	1070.5	1070.5	1069.5
10°	1051.8	1055.7	1059.7	1063.6	1065.6	1066.6	1067.5	1068.5	1067.5	1067.5	1066.6
12.5°	1045.9	1049.8	1052.8	1056.7	1058.7	1059.7	1061.6	1062.6	1062.6	1062.6	1061.6
15°	1035.1	1038.0	1042.0	1044.9	1046.9	1048.8	1051.8	1053.8	1053.8	1052.8	1052.8
17.5°	1021.3	1025.2	1029.2	1033.1	1036.1	1038.0	1039.0	1041.0	1041.0	1041.0	1040.0
20°	1003.6	1008.5	1012.4	1017.4	1020.3	1022.3	1023.3	1025.2	1025.2	1025.2	1025.2
22.5°	983.9	988.8	993.7	998.7	1000.6	1002.6	1004.6	1006.5	1006.5	1006.5	1006.5
25°	961.3	966.2	970.1	974.1	980.0	981.9	983.9	985.9	986.9	987.8	987.8
27.5°	935.7	940.6	946.5	951.4	955.4	958.3	960.3	963.2	964.2	965.2	965.2
30°	899.3	908.1	916.0	923.9	927.8	931.8	936.7	940.6	941.6	941.6	942.6
32.5°	850.1	864.9	880.6	895.4	904.2	908.1	912.1	916.0	915.0	913.1	912.1
35°	809.8	829.4	849.1	868.8	876.7	879.6	882.6	885.5	883.6	882.6	880.6
37.5°	774.3	797.0	818.6	841.2	847.1	849.1	852.1	854.0	852.1	850.1	847.1
40°	721.2	750.7	779.3	808.8	812.7	814.7	816.6	818.6	816.6	815.7	813.7
42.5°	663.2	700.5	736.9	774.3	779.3	778.3	776.3	775.3	776.3	778.3	779.3
45°	640.5	673.0	704.5	736.9	742.9	740.9	738.9	736.9	738.9	740.9	742.9
47.5°	604.1	636.6	668.1	699.6	699.6	698.6	697.6	696.6	699.6	701.5	704.5
50°	561.8	591.3	619.9	648.4	644.5	649.4	653.3	658.2	661.2	664.1	667.1
52.5°	509.7	534.3	557.9	582.5	597.2	604.1	612.0	618.9	620.8	622.8	623.8
55°	456.5	479.2	500.8	522.5	552.0	559.8	566.7	574.6	576.6	579.5	581.5
57.5°	388.6	415.2	440.8	467.4	504.7	513.6	523.4	532.3	532.3	532.3	531.3
60°	298.1	335.5	371.9	408.3	452.6	462.4	471.3	481.1	480.1	480.1	479.2
62.5°	228.3	265.7	304.0	341.4	391.6	405.4	418.2	431.9	431.9	431.9	431.0
65°	180.1	201.7	222.4	243.0	325.7	345.4	364.0	383.7	384.7	384.7	385.7
67.5°	138.7	147.6	155.5	164.3	271.6	293.2	315.8	337.5	337.5	336.5	336.5
70°	93.5	100.4	107.2	114.1	220.4	244.0	268.6	292.2	291.2	290.3	288.3
72.5°	73.8	76.7	80.7	83.6	171.2	195.8	221.4	246.0	245.0	243.0	242.0
75°	71.8	68.9	66.9	64.0	126.9	151.5	175.1	199.7	198.7	197.8	196.8
77.5°	64.9	60.0	56.1	51.2	93.5	115.1	136.8	158.4	157.4	155.5	154.5
80°	50.2	46.2	42.3	38.4	64.0	80.7	97.4	114.1	114.1	114.1	114.1
82.5°	33.5	31.5	30.5	28.5	40.3	53.1	64.9	77.7	76.7	76.7	75.8
85°	19.7	18.7	18.7	17.7	24.6	30.5	36.4	42.3	43.3	43.3	44.3
87.5°	9.8	9.8	10.8	10.8	13.8	16.7	18.7	21.6	21.6	22.6	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1053.8	1052.8	1050.8	1052.8	1053.8	1055.7	1058.7	1060.7	1062.6	1063.6	1064.6
5°	1066.6	1065.6	1064.6	1065.6	1066.6	1069.5	1071.5	1074.4	1076.4	1077.4	1077.4
7.5°	1068.5	1068.5	1067.5	1068.5	1069.5	1072.5	1074.4	1077.4	1079.3	1080.3	1080.3
10°	1065.6	1065.6	1065.6	1067.5	1069.5	1072.5	1074.4	1077.4	1079.3	1080.3	1080.3
12.5°	1061.6	1061.6	1060.7	1062.6	1064.6	1067.5	1069.5	1072.5	1074.4	1075.4	1075.4
15°	1051.8	1051.8	1051.8	1053.8	1055.7	1058.7	1061.6	1063.6	1066.6	1067.5	1068.5
17.5°	1040.0	1041.0	1041.0	1042.9	1044.9	1047.9	1049.8	1052.8	1054.8	1055.7	1055.7
20°	1025.2	1025.2	1025.2	1028.2	1030.2	1033.1	1035.1	1038.0	1040.0	1041.0	1042.9
22.5°	1006.5	1007.5	1008.5	1012.4	1015.4	1017.4	1020.3	1022.3	1024.2	1024.2	1025.2
25°	988.8	990.8	991.8	993.7	995.7	996.7	997.7	997.7	998.7	998.7	997.7
27.5°	966.2	968.2	970.1	971.1	971.1	971.1	972.1	972.1	972.1	973.1	974.1
30°	942.6	940.6	938.6	939.6	940.6	941.6	943.6	944.6	945.5	946.5	946.5
32.5°	910.1	910.1	909.1	911.1	912.1	914.1	916.0	918.0	920.0	920.0	920.0
35°	878.6	880.6	882.6	883.6	883.6	884.5	886.5	887.5	888.5	889.5	890.4
37.5°	845.2	848.1	851.1	853.0	854.0	855.0	856.0	857.0	858.0	857.0	857.0
40°	811.7	814.7	817.6	818.6	819.6	820.6	820.6	821.6	821.6	820.6	820.6
42.5°	780.2	781.2	782.2	784.2	786.1	785.2	785.2	784.2	783.2	782.2	780.2
45°	744.8	746.8	747.8	747.8	747.8	745.8	743.8	740.9	738.9	737.9	737.9
47.5°	706.4	709.4	711.4	708.4	704.5	702.5	700.5	697.6	695.6	694.6	693.7
50°	670.0	668.1	665.1	662.2	658.2	656.3	655.3	653.3	651.3	647.4	644.5
52.5°	625.8	621.8	617.9	614.9	611.0	608.1	605.1	602.2	599.2	597.2	596.2
55°	583.5	576.6	568.7	565.7	561.8	557.9	553.0	549.0	544.1	543.1	542.1
57.5°	531.3	527.4	522.5	516.6	509.7	505.7	502.8	498.8	494.9	493.9	492.9
60°	478.2	474.2	470.3	464.4	458.5	455.6	451.6	448.7	444.7	443.7	443.7
62.5°	431.0	428.0	424.1	415.2	406.4	404.4	401.4	399.5	396.5	394.5	393.6
65°	385.7	378.8	370.9	365.0	358.1	355.2	353.2	350.3	347.3	345.4	343.4
67.5°	335.5	326.7	316.8	313.9	310.9	308.0	304.0	301.1	297.1	296.2	295.2
70°	287.3	280.4	272.5	269.6	265.7	262.7	259.8	255.8	252.9	250.9	247.9
72.5°	240.1	234.2	227.3	223.3	219.4	216.5	214.5	211.5	208.6	206.6	204.7
75°	195.8	189.9	184.0	180.1	176.1	174.2	172.2	169.2	167.3	164.3	162.3
77.5°	152.5	149.6	145.6	140.7	135.8	134.8	133.8	132.8	131.8	128.9	126.9
80°	114.1	111.2	108.2	105.3	101.3	99.4	98.4	96.4	94.5	93.5	91.5
82.5°	74.8	72.8	70.8	69.9	68.9	67.9	66.9	65.9	64.9	64.0	64.0
85°	44.3	44.3	44.3	43.3	42.3	42.3	42.3	41.3	41.3	40.3	40.3
87.5°	22.6	23.6	23.6	23.6	23.6	23.6	23.6	23.6	23.6	23.6	24.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1065.6	1064.6	1065.6	1065.6	1066.6	1066.6	1065.6	1065.6	1064.6	1063.6	1064.6
5°	1078.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1078.4	1078.4	1077.4	1078.4
7.5°	1081.3	1081.3	1082.3	1082.3	1083.3	1083.3	1082.3	1082.3	1081.3	1080.3	1081.3
10°	1081.3	1082.3	1082.3	1083.3	1083.3	1083.3	1082.3	1082.3	1081.3	1080.3	1081.3
12.5°	1076.4	1076.4	1077.4	1077.4	1078.4	1078.4	1078.4	1077.4	1077.4	1076.4	1077.4
15°	1069.5	1068.5	1069.5	1069.5	1070.5	1070.5	1069.5	1069.5	1068.5	1067.5	1068.5
17.5°	1056.7	1057.7	1057.7	1058.7	1058.7	1058.7	1057.7	1056.7	1055.7	1054.8	1055.7
20°	1043.9	1043.9	1043.9	1044.9	1044.9	1044.9	1043.9	1043.9	1042.9	1042.0	1042.9
22.5°	1025.2	1025.2	1025.2	1024.2	1024.2	1023.3	1022.3	1022.3	1021.3	1020.3	1021.3
25°	997.7	998.7	998.7	998.7	998.7	998.7	997.7	997.7	996.7	995.7	996.7
27.5°	975.1	973.1	974.1	974.1	975.1	975.1	975.1	974.1	974.1	973.1	974.1
30°	947.5	949.5	950.5	950.5	951.4	951.4	951.4	950.5	950.5	949.5	950.5
32.5°	920.0	921.9	921.9	921.9	921.9	921.9	921.9	920.9	920.9	920.0	920.9
35°	891.4	890.4	890.4	891.4	891.4	891.4	890.4	890.4	889.5	888.5	889.5
37.5°	856.0	856.0	856.0	856.0	856.0	856.0	855.0	855.0	854.0	853.0	854.0
40°	819.6	818.6	818.6	819.6	819.6	819.6	818.6	817.6	816.6	815.7	816.6
42.5°	779.3	779.3	779.3	779.3	778.3	778.3	778.3	778.3	777.3	777.3	777.3
45°	736.9	736.0	736.0	735.0	735.0	734.0	734.0	733.0	733.0	732.0	733.0
47.5°	692.7	692.7	691.7	689.7	688.7	686.8	685.8	684.8	682.8	681.8	682.8
50°	640.5	640.5	639.5	638.6	637.6	636.6	636.6	637.6	637.6	637.6	637.6
52.5°	594.3	590.3	589.4	589.4	588.4	587.4	587.4	587.4	586.4	586.4	586.4
55°	541.2	539.2	539.2	539.2	538.2	538.2	539.2	539.2	540.2	540.2	540.2
57.5°	492.0	491.0	491.0	490.0	490.0	489.0	488.0	488.0	487.0	486.1	487.0
60°	442.8	440.8	438.8	436.9	433.9	431.9	431.0	430.0	429.0	428.0	429.0
62.5°	391.6	387.7	386.7	384.7	383.7	381.8	379.8	378.8	376.8	374.9	376.8
65°	341.4	340.4	337.5	334.5	331.6	328.6	327.6	327.6	326.7	325.7	326.7
67.5°	294.2	288.3	286.3	284.3	282.4	280.4	280.4	280.4	280.4	280.4	280.4
70°	246.0	242.0	241.1	239.1	238.1	236.1	236.1	236.1	235.2	235.2	235.2
72.5°	202.7	198.7	197.8	196.8	194.8	193.8	193.8	193.8	192.8	192.8	192.8
75°	159.4	160.4	159.4	158.4	157.4	156.4	156.4	155.5	155.5	154.5	155.5
77.5°	124.0	124.0	123.0	122.0	121.0	120.0	120.0	120.0	120.0	120.0	120.0
80°	90.5	90.5	90.5	90.5	89.5	89.5	89.5	89.5	88.6	88.6	88.6
82.5°	63.0	63.0	63.0	63.0	63.0	63.0	63.0	62.0	62.0	61.0	62.0
85°	39.4	40.3	40.3	40.3	39.4	39.4	39.4	39.4	39.4	39.4	39.4
87.5°	24.6	24.6	24.6	25.6	25.6	25.6	25.6	25.6	24.6	24.6	24.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1065.6	1065.6	1066.6	1066.6	1065.6	1065.6	1064.6	1065.6	1064.6	1063.6	1062.6
5°	1078.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1078.4	1077.4	1077.4	1076.4
7.5°	1082.3	1082.3	1083.3	1083.3	1082.3	1082.3	1081.3	1081.3	1080.3	1080.3	1079.3
10°	1082.3	1082.3	1083.3	1083.3	1083.3	1082.3	1082.3	1081.3	1080.3	1080.3	1079.3
12.5°	1077.4	1078.4	1078.4	1078.4	1077.4	1077.4	1076.4	1076.4	1075.4	1075.4	1074.4
15°	1069.5	1069.5	1070.5	1070.5	1069.5	1069.5	1068.5	1069.5	1068.5	1067.5	1066.6
17.5°	1056.7	1057.7	1058.7	1058.7	1058.7	1057.7	1057.7	1056.7	1055.7	1055.7	1054.8
20°	1043.9	1043.9	1044.9	1044.9	1044.9	1043.9	1043.9	1043.9	1042.9	1041.0	1040.0
22.5°	1022.3	1022.3	1023.3	1024.2	1024.2	1025.2	1025.2	1025.2	1025.2	1024.2	1024.2
25°	997.7	997.7	998.7	998.7	998.7	998.7	998.7	997.7	997.7	998.7	998.7
27.5°	974.1	975.1	975.1	975.1	974.1	974.1	973.1	975.1	974.1	973.1	972.1
30°	950.5	951.4	951.4	951.4	950.5	950.5	949.5	947.5	946.5	946.5	945.5
32.5°	920.9	921.9	921.9	921.9	921.9	921.9	921.9	920.0	920.0	920.0	920.0
35°	890.4	890.4	891.4	891.4	891.4	890.4	890.4	891.4	890.4	889.5	888.5
37.5°	855.0	855.0	856.0	856.0	856.0	856.0	856.0	856.0	857.0	857.0	858.0
40°	817.6	818.6	819.6	819.6	819.6	818.6	818.6	819.6	820.6	820.6	821.6
42.5°	778.3	778.3	778.3	778.3	779.3	779.3	779.3	779.3	780.2	782.2	783.2
45°	733.0	734.0	734.0	735.0	735.0	736.0	736.0	736.9	737.9	737.9	738.9
47.5°	684.8	685.8	686.8	688.7	689.7	691.7	692.7	692.7	693.7	694.6	695.6
50°	637.6	636.6	636.6	637.6	638.6	639.5	640.5	640.5	644.5	647.4	651.3
52.5°	587.4	587.4	587.4	588.4	589.4	589.4	590.3	594.3	596.2	597.2	599.2
55°	539.2	539.2	538.2	538.2	539.2	539.2	539.2	541.2	542.1	543.1	544.1
57.5°	488.0	488.0	489.0	490.0	490.0	491.0	491.0	492.0	492.9	493.9	494.9
60°	430.0	431.0	431.9	433.9	436.9	438.8	440.8	442.8	443.7	443.7	444.7
62.5°	378.8	379.8	381.8	383.7	384.7	386.7	387.7	391.6	393.6	394.5	396.5
65°	327.6	327.6	328.6	331.6	334.5	337.5	340.4	341.4	343.4	345.4	347.3
67.5°	280.4	280.4	280.4	282.4	284.3	286.3	288.3	294.2	295.2	296.2	297.1
70°	236.1	236.1	236.1	238.1	239.1	241.1	242.0	246.0	247.9	250.9	252.9
72.5°	193.8	193.8	193.8	194.8	196.8	197.8	198.7	202.7	204.7	206.6	208.6
75°	155.5	156.4	156.4	157.4	158.4	159.4	160.4	159.4	162.3	164.3	167.3
77.5°	120.0	120.0	120.0	121.0	122.0	123.0	124.0	124.0	126.9	128.9	131.8
80°	89.5	89.5	89.5	89.5	90.5	90.5	90.5	90.5	91.5	93.5	94.5
82.5°	62.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	64.0	64.0	64.9
85°	39.4	39.4	39.4	39.4	40.3	40.3	40.3	39.4	40.3	40.3	41.3
87.5°	25.6	25.6	25.6	25.6	25.6	24.6	24.6	24.6	24.6	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1060.7	1058.7	1055.7	1053.8	1052.8	1050.8	1052.8	1053.8	1054.8	1055.7	1055.7
5°	1074.4	1071.5	1069.5	1066.6	1065.6	1064.6	1065.6	1066.6	1066.6	1067.5	1067.5
7.5°	1077.4	1074.4	1072.5	1069.5	1068.5	1067.5	1068.5	1068.5	1069.5	1070.5	1070.5
10°	1077.4	1074.4	1072.5	1069.5	1067.5	1065.6	1065.6	1065.6	1066.6	1067.5	1067.5
12.5°	1072.5	1069.5	1067.5	1064.6	1062.6	1060.7	1061.6	1061.6	1061.6	1062.6	1062.6
15°	1063.6	1061.6	1058.7	1055.7	1053.8	1051.8	1051.8	1051.8	1052.8	1052.8	1053.8
17.5°	1052.8	1049.8	1047.9	1044.9	1042.9	1041.0	1041.0	1040.0	1040.0	1041.0	1041.0
20°	1038.0	1035.1	1033.1	1030.2	1028.2	1025.2	1025.2	1025.2	1025.2	1025.2	1025.2
22.5°	1022.3	1020.3	1017.4	1015.4	1011.5	1008.5	1007.5	1006.5	1006.5	1006.5	1006.5
25°	997.7	997.7	996.7	995.7	993.7	991.8	990.8	988.8	987.8	987.8	986.9
27.5°	972.1	972.1	971.1	971.1	971.1	970.1	968.2	966.2	965.2	965.2	964.2
30°	944.6	943.6	941.6	940.6	939.6	938.6	940.6	942.6	942.6	941.6	941.6
32.5°	918.0	916.0	914.1	912.1	911.1	909.1	910.1	910.1	912.1	913.1	915.0
35°	887.5	886.5	884.5	883.6	883.6	882.6	880.6	878.6	880.6	882.6	883.6
37.5°	857.0	856.0	855.0	854.0	853.0	851.1	848.1	845.2	847.1	849.1	852.1
40°	821.6	820.6	820.6	819.6	818.6	817.6	814.7	811.7	813.7	815.7	816.6
42.5°	784.2	785.2	785.2	786.1	784.2	782.2	781.2	780.2	779.3	778.3	776.3
45°	740.9	743.8	745.8	747.8	747.8	747.8	746.8	744.8	742.9	740.9	738.9
47.5°	697.6	700.5	702.5	704.5	708.4	711.4	709.4	706.4	704.5	701.5	699.6
50°	653.3	655.3	656.3	658.2	662.2	665.1	668.1	670.0	667.1	664.1	661.2
52.5°	602.2	605.1	608.1	611.0	614.9	617.9	621.8	625.8	623.8	622.8	620.8
55°	549.0	553.0	557.9	561.8	565.7	568.7	576.6	583.5	581.5	579.5	576.6
57.5°	498.8	501.8	505.7	509.7	516.6	522.5	527.4	531.3	531.3	532.3	532.3
60°	448.7	451.6	455.6	458.5	464.4	470.3	474.2	478.2	479.2	480.1	480.1
62.5°	399.5	401.4	404.4	406.4	415.2	424.1	428.0	431.0	431.0	431.9	431.9
65°	350.3	353.2	355.2	358.1	365.0	370.9	378.8	385.7	385.7	384.7	384.7
67.5°	301.1	304.0	308.0	310.9	313.9	316.8	326.7	335.5	336.5	336.5	337.5
70°	255.8	259.8	262.7	265.7	269.6	272.5	280.4	287.3	288.3	290.3	291.2
72.5°	211.5	214.5	216.5	219.4	223.3	227.3	234.2	240.1	242.0	243.0	245.0
75°	169.2	172.2	174.2	176.1	180.1	184.0	189.9	195.8	196.8	197.8	198.7
77.5°	132.8	133.8	134.8	135.8	140.7	145.6	149.6	152.5	154.5	155.5	157.4
80°	96.4	98.4	99.4	101.3	105.3	108.2	111.2	114.1	114.1	114.1	114.1
82.5°	65.9	66.9	67.9	68.9	69.9	70.8	72.8	74.8	75.8	76.7	76.7
85°	41.3	42.3	42.3	42.3	43.3	44.3	44.3	44.3	44.3	43.3	43.3
87.5°	23.6	23.6	23.6	23.6	23.6	23.6	23.6	22.6	22.6	22.6	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0	1040.0
2.5°	1056.7	1056.7	1056.7	1056.7	1054.8	1053.8	1051.8	1050.8	1048.8	1048.8	1048.8
5°	1067.5	1066.6	1066.6	1065.6	1063.6	1060.7	1057.7	1055.7	1052.8	1050.8	1048.8
7.5°	1071.5	1070.5	1069.5	1068.5	1065.6	1062.6	1058.7	1055.7	1051.8	1047.9	1043.9
10°	1068.5	1067.5	1066.6	1065.6	1063.6	1059.7	1055.7	1051.8	1047.9	1042.9	1037.0
12.5°	1062.6	1061.6	1059.7	1058.7	1056.7	1052.8	1048.8	1045.9	1042.0	1035.1	1027.2
15°	1053.8	1051.8	1048.8	1046.9	1044.9	1042.0	1038.0	1035.1	1031.1	1023.3	1014.4
17.5°	1041.0	1039.0	1038.0	1036.1	1033.1	1029.2	1025.2	1021.3	1017.4	1007.5	996.7
20°	1025.2	1023.3	1022.3	1020.3	1017.4	1012.4	1007.5	1003.6	998.7	986.9	975.1
22.5°	1006.5	1004.6	1002.6	1000.6	998.7	993.7	988.8	983.9	979.0	964.2	948.5
25°	985.9	983.9	981.9	980.0	974.1	970.1	965.2	961.3	957.3	937.7	918.0
27.5°	963.2	960.3	958.3	955.4	951.4	946.5	940.6	935.7	929.8	907.2	883.6
30°	940.6	936.7	931.8	927.8	923.9	916.0	907.2	899.3	891.4	866.8	841.2
32.5°	916.0	912.1	908.1	904.2	895.4	880.6	864.9	850.1	834.4	810.7	786.1
35°	885.5	882.6	879.6	876.7	868.8	849.1	829.4	809.8	790.1	759.6	729.1
37.5°	854.0	852.1	849.1	847.1	841.2	818.6	796.0	774.3	751.7	711.4	671.0
40°	818.6	816.6	814.7	812.7	808.8	779.3	749.7	721.2	691.7	649.4	606.1
42.5°	775.3	776.3	778.3	779.3	774.3	736.9	699.6	663.2	625.8	587.4	548.0
45°	736.9	738.9	740.9	742.9	736.9	704.5	672.0	640.5	608.1	563.8	519.5
47.5°	696.6	697.6	698.6	699.6	699.6	668.1	635.6	604.1	572.6	534.3	494.9
50°	658.2	653.3	649.4	644.5	648.4	619.9	590.3	561.8	533.3	504.7	475.2
52.5°	618.9	612.0	604.1	597.2	582.5	557.9	533.3	509.7	485.1	458.5	431.9
55°	574.6	566.7	559.8	552.0	522.5	500.8	478.2	456.5	434.9	414.2	392.6
57.5°	532.3	523.4	513.6	504.7	467.4	440.8	414.2	388.6	362.1	358.1	353.2
60°	481.1	471.3	462.4	452.6	408.3	371.9	334.5	298.1	261.7	275.5	289.3
62.5°	431.9	418.2	405.4	391.6	341.4	304.0	265.7	228.3	189.9	214.5	239.1
65°	383.7	364.0	345.4	325.7	243.0	222.4	200.7	180.1	159.4	181.0	201.7
67.5°	337.5	315.8	293.2	271.6	164.3	155.5	146.6	138.7	129.9	143.7	158.4
70°	292.2	268.6	244.0	220.4	114.1	107.2	100.4	93.5	86.6	99.4	112.2
72.5°	246.0	221.4	195.8	171.2	83.6	80.7	76.7	73.8	69.9	80.7	92.5
75°	199.7	175.1	151.5	126.9	64.0	66.9	68.9	71.8	73.8	78.7	83.6
77.5°	158.4	136.8	115.1	93.5	51.2	56.1	60.0	64.9	68.9	68.9	68.9
80°	114.1	97.4	80.7	64.0	38.4	42.3	46.2	50.2	54.1	53.1	53.1
82.5°	77.7	64.9	53.1	40.3	28.5	30.5	31.5	33.5	34.4	34.4	34.4
85°	42.3	36.4	30.5	24.6	17.7	18.7	18.7	19.7	19.7	18.7	17.7
87.5°	21.6	18.7	16.7	13.8	10.8	10.8	9.8	9.8	8.9	7.9	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1040.0	1040.0
2.5°	1048.8	1048.8
5°	1046.9	1044.9
7.5°	1041.0	1037.0
10°	1032.1	1027.2
12.5°	1020.3	1013.4
15°	1006.5	997.7
17.5°	986.9	976.0
20°	963.2	951.4
22.5°	933.7	918.0
25°	898.3	878.6
27.5°	860.9	837.3
30°	816.6	791.1
32.5°	762.5	738.9
35°	698.6	668.1
37.5°	630.7	590.3
40°	563.8	521.5
42.5°	509.7	470.3
45°	475.2	431.0
47.5°	456.5	418.2
50°	446.7	417.2
52.5°	405.4	378.8
55°	371.9	351.3
57.5°	349.3	345.4
60°	303.0	316.8
62.5°	262.7	287.3
65°	223.3	244.0
67.5°	172.2	186.0
70°	125.0	137.7
72.5°	103.3	114.1
75°	87.6	92.5
77.5°	67.9	67.9
80°	52.1	51.2
82.5°	34.4	34.4
85°	16.7	15.7
87.5°	5.9	4.9
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055036

CATALOG NUMBER: SQ4R-FA-075D-830-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.10	19.71	18.46	20.02	20.34	20.01	21.62	20.38	21.94	22.25
	3H	18.76	20.22	19.14	20.54	20.90	21.81	23.26	22.19	23.59	23.95
	4H	19.09	20.46	19.49	20.81	21.19	22.43	23.80	22.83	24.15	24.52
	6H	19.38	20.65	19.80	21.01	21.41	22.81	24.08	23.23	24.44	24.84
	8H	19.46	20.67	19.89	21.06	21.46	22.91	24.12	23.34	24.51	24.91
	12H	19.49	20.65	19.92	21.03	21.46	22.96	24.11	23.39	24.50	24.92
4H	2H	19.23	20.59	19.63	20.94	21.32	20.58	21.95	20.98	22.30	22.67
	3H	20.55	21.69	20.96	22.09	22.49	22.61	23.75	23.02	24.15	24.55
	4H	20.98	22.01	21.41	22.42	22.86	23.35	24.38	23.78	24.80	25.23
	6H	21.27	22.17	21.73	22.61	23.07	23.85	24.75	24.30	25.19	25.64
	8H	21.35	22.19	21.81	22.63	23.10	23.97	24.81	24.43	25.26	25.72
	12H	21.39	22.15	21.87	22.62	23.09	24.05	24.80	24.53	25.28	25.75
8H	4H	21.57	22.41	22.03	22.85	23.32	23.58	24.42	24.04	24.86	25.33
	6H	22.05	22.75	22.54	23.24	23.71	24.18	24.87	24.67	25.36	25.84
	8H	22.18	22.80	22.69	23.31	23.80	24.36	24.98	24.87	25.49	25.97
	12H	22.25	22.80	22.76	23.30	23.86	24.48	25.03	24.99	25.52	26.08
12H	4H	21.62	22.37	22.10	22.85	23.32	23.59	24.34	24.07	24.82	25.29
	6H	22.15	22.78	22.66	23.28	23.77	24.19	24.82	24.70	25.33	25.81
	8H	22.36	22.91	22.86	23.40	23.96	24.42	24.97	24.93	25.46	26.02

END OF REPORT