

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055040

Luminaire Tested: SQ4R-FA-075D-930-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-930-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2240.5 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	89	87
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73
3	91	81	73	66	88	79	72	66	76	70	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	51	43	37	50	42	37	48	42	37	47	41	37
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8318	8318	8318	8318
5°	8388	6802	8388	8649
10°	8342	6272	8342	8774
15°	8261	7381	8261	8839
20°	8098	7620	8098	8868
25°	7753	7693	7753	8787
30°	7306	7569	7306	8769
35°	6523	7407	6523	8675
40°	5444	7355	5444	8516
45°	4874	7266	4874	8279
50°	5191	7198	5191	7934
55°	4898	7353	4898	7531
60°	5068	7209	5068	6847
65°	4618	6889	4618	6162
70°	3220	6466	3220	5500
75°	2857	5717	2857	4772
80°	2356	4441	2356	4081
85°	1447	3071	1447	3612

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 8458 cd/sqm

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	3.5
10°-20°	221.5	9.9
20°-30°	342.3	15.3
30°-40°	408.7	18.2
40°-50°	411.1	18.3
50°-60°	357.7	16.0
60°-70°	253.7	11.3
70°-80°	134.2	6.0
80°-90°	33.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	641.8	28.6
0°-40°	1050.4	46.9
0°-60°	1819.2	81.2
0°-90°	2240.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2240.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	864	864	864	864	864	
5°	868	704	868	895	868	82
15°	829	740	829	887	829	233
25°	730	724	730	827	730	335
35°	555	630	555	738	555	343
45°	358	534	358	608	358	287
55°	292	438	292	449	292	268
65°	203	302	203	270	203	194
75°	77	154	77	128	77	81
85°	13	28	13	33	13	18
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	871.3	869.7	867.2	865.6	863.1	862.3	861.5	860.7	859.9	857.4	855.8
5°	868.0	864.8	860.7	857.4	853.3	850.1	847.6	844.3	841.1	836.2	831.3
7.5°	861.5	855.8	850.1	844.3	838.6	831.3	823.9	816.6	809.2	796.1	780.6
10°	853.3	845.2	836.2	828.0	819.0	801.8	784.7	766.7	749.5	726.6	711.1
12.5°	841.9	828.0	813.3	799.4	784.7	760.2	736.4	711.9	687.4	671.9	662.9
15°	828.8	806.7	783.9	761.8	738.9	717.6	696.4	674.3	653.1	641.6	635.1
17.5°	810.8	781.4	752.8	723.4	693.9	677.6	660.4	644.1	626.9	618.7	613.8
20°	790.4	758.5	725.8	693.9	661.3	648.2	635.1	621.2	608.1	600.8	598.3
22.5°	762.6	731.5	700.5	669.4	638.4	626.1	613.8	600.8	588.5	582.8	584.4
25°	729.9	702.9	675.1	648.2	620.4	608.9	596.7	585.2	573.0	566.4	571.3
27.5°	695.6	672.7	649.8	626.9	604.0	591.8	579.5	566.4	554.2	551.7	563.2
30°	657.2	640.0	622.0	604.9	586.9	573.8	560.7	547.6	534.6	533.7	551.7
32.5°	613.8	601.6	590.1	577.9	565.6	553.4	541.1	528.0	515.8	514.9	537.0
35°	555.0	551.7	548.5	544.4	541.1	528.8	516.6	504.3	492.1	492.9	517.4
37.5°	490.4	496.1	502.7	508.4	514.1	502.7	492.1	480.6	469.2	469.2	495.3
40°	433.2	444.6	456.1	467.5	479.0	471.6	463.4	456.1	447.9	445.5	472.4
42.5°	390.7	401.3	412.0	421.8	432.4	429.9	428.3	425.8	423.4	420.1	446.3
45°	358.0	359.6	362.1	363.7	365.4	373.5	381.7	389.9	398.1	395.6	419.3
47.5°	347.4	336.8	325.3	314.7	303.2	320.4	337.6	353.9	371.1	370.3	391.5
50°	346.6	325.3	303.2	282.0	259.9	280.4	300.8	320.4	340.8	344.1	360.5
52.5°	314.7	295.1	275.5	255.0	235.4	253.4	270.5	288.5	305.7	315.5	330.2
55°	291.8	273.0	254.2	235.4	216.6	228.9	240.3	252.6	264.0	285.3	298.3
57.5°	286.9	264.0	241.1	217.4	194.5	202.7	210.1	218.2	225.6	246.0	262.4
60°	263.2	240.3	217.4	193.7	170.8	176.6	181.5	187.2	192.1	207.6	227.2
62.5°	238.7	217.4	197.0	175.7	154.5	160.2	165.1	170.8	175.7	179.0	200.3
65°	202.7	187.2	171.6	156.1	140.6	145.5	149.6	154.5	158.6	159.4	179.0
67.5°	154.5	147.9	141.4	134.0	127.5	132.4	136.5	141.4	145.5	146.3	162.7
70°	114.4	114.4	114.4	113.6	113.6	117.7	122.6	126.7	130.8	132.4	144.7
72.5°	94.8	96.4	98.9	100.5	102.2	105.4	108.7	112.0	115.2	116.9	125.9
75°	76.8	80.1	83.4	85.8	89.1	91.5	94.0	95.6	98.1	98.9	105.4
77.5°	56.4	60.5	64.6	67.8	71.9	74.4	76.0	78.5	80.1	78.5	83.4
80°	42.5	45.0	47.4	49.0	51.5	53.1	55.6	57.2	58.9	57.2	60.5
82.5°	28.6	29.4	31.1	31.9	32.7	34.3	36.0	37.6	39.2	37.6	40.1
85°	13.1	13.9	15.5	16.3	17.2	18.8	19.6	21.3	22.1	21.3	22.1
87.5°	4.1	4.9	5.7	5.7	6.5	7.4	8.2	9.0	9.8	9.8	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	855.0	853.3	850.1	847.6	844.3	841.1	839.4	837.8	836.2	834.5	836.2
5°	825.5	820.6	813.3	805.9	798.6	791.2	781.4	771.6	764.2	756.9	755.2
7.5°	764.2	748.7	735.6	721.7	708.7	694.8	687.4	680.1	673.5	667.0	665.3
10°	694.8	679.2	670.2	662.1	653.1	644.1	640.0	635.1	634.3	632.6	633.5
12.5°	653.1	644.1	639.2	634.3	628.6	623.7	622.8	622.0	624.5	626.1	631.8
15°	628.6	622.0	620.4	618.7	616.3	614.7	619.6	623.7	638.4	652.3	668.6
17.5°	609.8	604.9	608.9	612.2	616.3	619.6	644.9	670.2	689.9	708.7	714.4
20°	596.7	594.2	610.6	627.7	644.1	660.4	680.1	698.8	706.2	712.7	716.0
22.5°	585.2	586.9	611.4	635.1	659.6	683.3	691.5	698.8	703.8	708.7	711.1
25°	577.1	582.0	606.5	631.8	656.3	680.9	685.8	689.9	691.5	692.3	698.0
27.5°	574.6	586.1	607.3	628.6	649.0	670.2	673.5	676.8	678.4	679.2	685.0
30°	568.9	586.9	604.9	622.0	640.0	657.2	656.3	655.5	658.8	662.1	667.8
32.5°	559.1	581.1	595.0	609.8	623.7	637.5	636.7	635.9	640.8	644.9	649.0
35°	542.7	567.3	579.5	591.0	603.2	614.7	615.5	615.5	619.6	623.7	626.1
37.5°	522.3	548.5	559.9	571.3	582.0	593.4	592.6	591.8	593.4	594.2	598.3
40°	498.6	525.6	537.0	548.5	559.1	570.5	568.1	564.8	564.8	564.0	568.9
42.5°	471.6	497.8	509.2	520.7	531.3	542.7	537.8	532.1	533.7	534.6	541.1
45°	443.8	467.5	478.2	489.6	500.2	510.9	507.6	503.5	506.8	510.0	516.6
47.5°	412.8	434.0	445.5	456.9	468.4	479.8	478.2	475.7	479.0	482.2	489.6
50°	377.6	394.0	407.9	421.8	435.7	449.6	449.6	449.6	452.8	455.3	462.6
52.5°	344.1	358.8	375.2	391.5	407.0	423.4	424.2	425.0	428.3	430.8	437.3
55°	311.4	324.5	342.5	360.5	378.4	396.4	398.1	399.7	403.0	405.4	412.0
57.5°	277.9	294.3	313.1	332.7	351.5	370.3	371.1	371.9	374.4	376.8	382.5
60°	246.8	266.5	284.4	303.2	321.2	339.2	342.5	344.9	346.6	348.2	353.1
62.5°	222.3	243.6	259.9	277.1	293.4	309.8	313.9	317.1	318.8	319.6	322.9
65°	199.4	219.1	234.6	249.3	264.8	279.5	282.8	286.1	288.5	290.2	292.6
67.5°	179.0	195.4	207.6	219.9	232.1	244.4	249.3	253.4	255.0	256.7	258.3
70°	157.8	170.0	180.6	191.3	201.9	212.5	216.6	220.7	222.3	223.1	224.0
72.5°	134.9	143.9	152.0	160.2	168.4	176.6	180.6	184.7	186.4	187.2	188.0
75°	111.2	117.7	124.2	130.8	137.3	143.9	147.1	149.6	150.4	151.2	151.2
77.5°	87.5	92.4	97.3	102.2	106.3	111.2	113.6	116.1	116.1	116.1	116.1
80°	62.9	66.2	69.5	72.7	76.0	79.3	80.1	80.9	81.7	82.6	82.6
82.5°	41.7	44.1	45.8	48.2	49.9	51.5	51.5	51.5	51.5	51.5	52.3
85°	23.7	24.5	25.3	26.2	27.0	27.8	28.6	28.6	28.6	28.6	28.6
87.5°	10.6	11.4	11.4	12.3	12.3	12.3	12.3	11.4	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	837.0	838.6	839.4	837.8	835.4	833.7	831.3	832.1	832.9	833.7	834.5
5°	752.8	751.2	748.7	743.0	737.3	731.5	727.5	724.2	720.9	717.6	714.4
7.5°	662.9	661.3	658.8	657.2	655.5	653.9	650.6	649.8	649.0	648.2	647.4
10°	634.3	634.3	635.1	635.9	635.9	636.7	637.5	639.2	640.0	641.6	642.5
12.5°	637.5	642.5	648.2	658.8	670.2	680.9	688.2	694.8	702.1	708.7	715.2
15°	685.8	702.1	718.5	722.6	727.5	731.5	734.0	735.6	737.3	738.1	739.7
17.5°	720.1	725.0	730.7	732.4	734.8	736.4	737.3	738.1	739.7	740.5	741.4
20°	719.3	721.7	725.0	727.5	729.9	732.4	734.0	736.4	738.1	740.5	742.2
22.5°	714.4	716.8	719.3	723.4	726.6	730.7	734.0	735.6	737.3	738.9	740.5
25°	702.9	708.7	713.6	716.8	719.3	722.6	722.6	722.6	723.4	723.4	723.4
27.5°	690.7	696.4	702.1	702.9	704.6	705.4	707.0	708.7	709.5	711.1	711.9
30°	673.5	679.2	685.0	686.6	688.2	689.9	688.2	687.4	686.6	685.0	684.1
32.5°	653.9	658.0	662.1	662.9	662.9	663.7	659.6	658.8	658.0	656.3	655.5
35°	629.4	631.8	634.3	633.5	633.5	632.6	633.5	633.5	633.5	632.6	632.6
37.5°	601.6	605.7	608.9	609.8	609.8	610.6	612.2	612.2	612.2	611.4	611.4
40°	574.6	579.5	584.4	585.2	586.9	587.7	588.5	588.5	588.5	587.7	587.7
42.5°	547.6	554.2	560.7	562.3	564.0	565.6	564.8	564.0	564.0	563.2	562.3
45°	523.9	530.5	537.0	537.8	539.5	540.3	541.1	540.3	538.6	537.8	536.2
47.5°	497.0	503.5	510.9	512.5	513.3	514.9	514.9	514.1	513.3	511.7	510.9
50°	470.8	478.2	485.5	486.3	487.2	488.0	487.2	485.5	484.7	483.1	481.4
52.5°	444.6	451.2	457.7	457.7	456.9	456.9	456.9	456.9	457.7	457.7	457.7
55°	417.7	424.2	429.9	429.9	429.9	429.9	430.8	432.4	434.0	434.8	436.5
57.5°	389.1	394.8	400.5	401.3	401.3	402.1	402.1	403.0	404.6	405.4	406.2
60°	358.8	363.7	368.6	369.5	369.5	370.3	371.9	372.7	373.5	374.4	375.2
62.5°	326.1	328.6	331.9	333.5	335.1	336.8	338.4	338.4	339.2	339.2	339.2
65°	295.1	296.7	299.2	300.0	300.8	301.6	303.2	303.2	304.1	304.1	304.1
67.5°	259.9	260.7	262.4	263.2	264.8	265.6	264.8	264.8	264.8	264.0	264.0
70°	224.8	225.6	226.4	227.2	228.0	228.9	228.9	228.9	228.9	228.0	228.0
72.5°	188.0	188.8	188.8	188.8	189.6	189.6	188.8	189.6	190.4	191.3	192.1
75°	152.0	152.0	152.0	152.0	151.2	151.2	152.8	152.8	152.0	152.0	151.2
77.5°	116.1	116.1	116.1	116.1	115.2	115.2	116.9	116.9	116.1	116.1	115.2
80°	82.6	81.7	81.7	81.7	81.7	81.7	80.9	80.9	80.9	80.9	80.9
82.5°	52.3	53.1	53.1	53.1	52.3	52.3	51.5	51.5	51.5	51.5	51.5
85°	27.8	27.8	27.0	27.8	27.8	28.6	29.4	29.4	28.6	28.6	27.8
87.5°	11.4	11.4	11.4	11.4	10.6	10.6	9.8	9.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	832.1	830.4	828.0	825.5	828.0	830.4	832.1	834.5	833.7	832.9	832.1
5°	711.9	709.5	706.2	703.8	706.2	709.5	711.9	714.4	717.6	720.9	724.2
7.5°	645.7	644.1	642.5	640.8	642.5	644.1	645.7	647.4	648.2	649.0	649.8
10°	642.5	642.5	641.6	641.6	641.6	642.5	642.5	642.5	641.6	640.0	639.2
12.5°	715.2	714.4	714.4	713.6	714.4	714.4	715.2	715.2	708.7	702.1	694.8
15°	739.7	740.5	740.5	740.5	740.5	740.5	739.7	739.7	738.1	737.3	735.6
17.5°	741.4	741.4	741.4	741.4	741.4	741.4	741.4	741.4	740.5	739.7	738.1
20°	743.0	743.0	743.8	743.8	743.8	743.0	743.0	742.2	740.5	738.1	736.4
22.5°	740.5	740.5	739.7	739.7	739.7	740.5	740.5	740.5	738.9	737.3	735.6
25°	723.4	724.2	724.2	724.2	724.2	724.2	723.4	723.4	723.4	723.4	722.6
27.5°	711.9	711.9	711.1	711.1	711.1	711.9	711.9	711.9	711.1	709.5	708.7
30°	683.3	682.5	681.7	680.9	681.7	682.5	683.3	684.1	685.0	686.6	687.4
32.5°	654.7	654.7	653.9	653.1	653.9	654.7	654.7	655.5	656.3	658.0	658.8
35°	631.8	631.8	631.0	630.2	631.0	631.8	631.8	632.6	632.6	633.5	633.5
37.5°	610.6	609.8	608.9	608.1	608.9	609.8	610.6	611.4	611.4	612.2	612.2
40°	586.9	586.9	586.1	585.2	586.1	586.9	586.9	587.7	587.7	588.5	588.5
42.5°	562.3	561.5	561.5	560.7	561.5	561.5	562.3	562.3	563.2	564.0	564.0
45°	535.4	535.4	534.6	533.7	534.6	535.4	535.4	536.2	537.8	538.6	540.3
47.5°	510.0	510.0	509.2	508.4	509.2	510.0	510.0	510.9	511.7	513.3	514.1
50°	481.4	481.4	480.6	480.6	480.6	481.4	481.4	481.4	483.1	484.7	485.5
52.5°	458.5	458.5	459.4	459.4	459.4	458.5	458.5	457.7	457.7	457.7	456.9
55°	437.3	437.3	438.1	438.1	438.1	437.3	437.3	436.5	434.8	434.0	432.4
57.5°	406.2	406.2	406.2	406.2	406.2	406.2	406.2	406.2	405.4	404.6	403.0
60°	375.2	375.2	374.4	374.4	374.4	375.2	375.2	375.2	374.4	373.5	372.7
62.5°	339.2	338.4	338.4	337.6	338.4	338.4	339.2	339.2	339.2	339.2	338.4
65°	304.1	303.2	303.2	302.4	303.2	303.2	304.1	304.1	304.1	304.1	303.2
67.5°	264.8	265.6	266.5	267.3	266.5	265.6	264.8	264.0	264.0	264.8	264.8
70°	228.9	228.9	229.7	229.7	229.7	228.9	228.9	228.0	228.0	228.9	228.9
72.5°	191.3	191.3	190.4	189.6	190.4	191.3	191.3	192.1	191.3	190.4	189.6
75°	152.0	152.8	152.8	153.7	152.8	152.8	152.0	151.2	152.0	152.0	152.8
77.5°	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2	116.1	116.1	116.9
80°	80.9	80.9	80.1	80.1	80.1	80.9	80.9	80.9	80.9	80.9	80.9
82.5°	52.3	52.3	53.1	53.1	53.1	52.3	52.3	51.5	51.5	51.5	51.5
85°	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	28.6	28.6	29.4
87.5°	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	831.3	833.7	835.4	837.8	839.4	838.6	837.0	836.2	834.5	836.2	837.8
5°	727.5	731.5	737.3	743.0	748.7	751.2	752.8	755.2	756.9	764.2	771.6
7.5°	650.6	653.9	655.5	657.2	658.8	661.3	662.9	665.3	667.0	673.5	680.1
10°	637.5	636.7	635.9	635.9	635.1	634.3	634.3	633.5	632.6	634.3	635.1
12.5°	688.2	680.9	670.2	658.8	648.2	642.5	637.5	631.8	626.1	624.5	622.0
15°	734.0	731.5	727.5	722.6	718.5	702.1	685.8	668.6	652.3	638.4	623.7
17.5°	737.3	736.4	734.8	732.4	730.7	725.0	720.1	714.4	708.7	689.9	670.2
20°	734.0	732.4	729.9	727.5	725.0	721.7	719.3	716.0	712.7	706.2	698.8
22.5°	734.0	730.7	726.6	723.4	719.3	716.8	714.4	711.1	708.7	703.8	698.8
25°	722.6	722.6	719.3	716.8	713.6	708.7	702.9	698.0	692.3	691.5	689.9
27.5°	707.0	705.4	704.6	702.9	702.1	696.4	690.7	685.0	679.2	678.4	676.8
30°	688.2	689.9	688.2	686.6	685.0	679.2	673.5	667.8	662.1	658.8	655.5
32.5°	659.6	663.7	662.9	662.9	662.1	658.0	653.9	649.0	644.9	640.8	635.9
35°	633.5	632.6	633.5	633.5	634.3	631.8	629.4	626.1	623.7	619.6	615.5
37.5°	612.2	610.6	609.8	609.8	608.9	605.7	601.6	598.3	594.2	593.4	591.8
40°	588.5	587.7	586.9	585.2	584.4	579.5	574.6	568.9	564.0	564.8	564.8
42.5°	564.8	565.6	564.0	562.3	560.7	554.2	547.6	541.1	534.6	533.7	532.1
45°	541.1	540.3	539.5	537.8	537.0	530.5	523.9	516.6	510.0	506.8	503.5
47.5°	514.9	514.9	513.3	512.5	510.9	503.5	497.0	489.6	482.2	479.0	475.7
50°	487.2	488.0	487.2	486.3	485.5	478.2	470.8	462.6	455.3	452.8	449.6
52.5°	456.9	456.9	456.9	457.7	457.7	451.2	444.6	437.3	430.8	428.3	425.0
55°	430.8	429.9	429.9	429.9	429.9	424.2	417.7	412.0	405.4	403.0	399.7
57.5°	402.1	402.1	401.3	401.3	400.5	394.8	389.1	382.5	376.8	374.4	371.9
60°	371.9	370.3	369.5	369.5	368.6	363.7	358.8	353.1	348.2	346.6	344.9
62.5°	338.4	336.8	335.1	333.5	331.9	328.6	326.1	322.9	319.6	318.8	317.1
65°	303.2	301.6	300.8	300.0	299.2	296.7	295.1	292.6	290.2	288.5	286.1
67.5°	264.8	265.6	264.8	263.2	262.4	260.7	259.9	258.3	256.7	255.0	253.4
70°	228.9	228.9	228.0	227.2	226.4	225.6	224.8	224.0	223.1	222.3	220.7
72.5°	188.8	189.6	189.6	188.8	188.8	188.8	188.0	188.0	187.2	186.4	184.7
75°	152.8	151.2	151.2	152.0	152.0	152.0	152.0	151.2	151.2	150.4	149.6
77.5°	116.9	115.2	115.2	116.1	116.1	116.1	116.1	116.1	116.1	116.1	116.1
80°	80.9	81.7	81.7	81.7	81.7	81.7	82.6	82.6	82.6	81.7	80.9
82.5°	51.5	52.3	52.3	53.1	53.1	53.1	52.3	52.3	51.5	51.5	51.5
85°	29.4	28.6	27.8	27.8	27.0	27.8	27.8	28.6	28.6	28.6	28.6
87.5°	9.8	10.6	10.6	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	839.4	841.1	844.3	847.6	850.1	853.3	855.0	855.8	857.4	859.9	860.7
5°	781.4	791.2	798.6	805.9	813.3	820.6	825.5	831.3	836.2	841.1	844.3
7.5°	687.4	694.8	708.7	721.7	735.6	748.7	764.2	780.6	796.1	809.2	816.6
10°	640.0	644.1	653.1	662.1	670.2	679.2	694.8	711.1	726.6	749.5	766.7
12.5°	622.8	623.7	628.6	634.3	639.2	644.1	653.1	662.9	671.9	687.4	711.9
15°	619.6	614.7	616.3	618.7	620.4	622.0	628.6	635.1	641.6	653.1	674.3
17.5°	644.9	619.6	616.3	612.2	608.9	604.9	609.8	613.8	618.7	626.9	644.1
20°	680.1	660.4	644.1	627.7	610.6	594.2	596.7	598.3	600.8	608.1	621.2
22.5°	691.5	683.3	659.6	635.1	611.4	586.9	585.2	584.4	582.8	588.5	600.8
25°	685.8	680.9	656.3	631.8	606.5	582.0	577.1	571.3	566.4	573.0	585.2
27.5°	673.5	670.2	649.0	628.6	607.3	586.1	574.6	563.2	551.7	554.2	566.4
30°	656.3	657.2	640.0	622.0	604.9	586.9	568.9	551.7	533.7	534.6	547.6
32.5°	636.7	637.5	623.7	609.8	595.0	581.1	559.1	537.0	514.9	515.8	528.0
35°	615.5	614.7	603.2	591.0	579.5	567.3	542.7	517.4	492.9	492.1	504.3
37.5°	592.6	593.4	582.0	571.3	559.9	548.5	522.3	495.3	469.2	469.2	480.6
40°	568.1	570.5	559.1	548.5	537.0	525.6	498.6	472.4	445.5	447.9	456.1
42.5°	537.8	542.7	531.3	520.7	509.2	497.8	471.6	446.3	420.1	423.4	425.8
45°	507.6	510.9	500.2	489.6	478.2	467.5	443.8	419.3	395.6	398.1	389.9
47.5°	478.2	479.8	468.4	456.9	445.5	434.0	412.8	391.5	370.3	371.1	353.9
50°	449.6	449.6	435.7	421.8	407.9	394.0	377.6	360.5	344.1	340.8	320.4
52.5°	424.2	423.4	407.0	391.5	375.2	358.8	344.1	330.2	315.5	305.7	288.5
55°	398.1	396.4	378.4	360.5	342.5	324.5	311.4	298.3	285.3	264.0	252.6
57.5°	371.1	370.3	351.5	332.7	313.1	294.3	277.9	262.4	246.0	225.6	218.2
60°	342.5	339.2	321.2	303.2	284.4	266.5	246.8	227.2	207.6	192.1	187.2
62.5°	313.9	309.8	293.4	277.1	259.9	243.6	222.3	200.3	179.0	175.7	170.8
65°	282.8	279.5	264.8	249.3	234.6	219.1	199.4	179.0	159.4	158.6	154.5
67.5°	249.3	244.4	232.1	219.9	207.6	195.4	179.0	162.7	146.3	145.5	141.4
70°	216.6	212.5	201.9	191.3	180.6	170.0	157.8	144.7	132.4	130.8	126.7
72.5°	180.6	176.6	168.4	160.2	152.0	143.9	134.9	125.9	116.9	115.2	112.0
75°	147.1	143.9	137.3	130.8	124.2	117.7	111.2	105.4	98.9	98.1	95.6
77.5°	113.6	111.2	106.3	102.2	97.3	92.4	87.5	83.4	78.5	80.1	78.5
80°	80.1	79.3	76.0	72.7	69.5	66.2	62.9	60.5	57.2	58.9	57.2
82.5°	51.5	51.5	49.9	48.2	45.8	44.1	41.7	40.1	37.6	39.2	37.6
85°	28.6	27.8	27.0	26.2	25.3	24.5	23.7	22.1	21.3	22.1	21.3
87.5°	12.3	12.3	12.3	12.3	11.4	11.4	10.6	10.6	9.8	9.8	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	861.5	862.3	863.1	865.6	867.2	869.7	871.3	871.3	871.3	871.3	871.3
5°	847.6	850.1	853.3	857.4	860.7	864.8	868.0	869.7	871.3	872.9	874.6
7.5°	823.9	831.3	838.6	844.3	850.1	855.8	861.5	864.8	868.0	870.5	873.8
10°	784.7	801.8	819.0	828.0	836.2	845.2	853.3	857.4	862.3	866.4	870.5
12.5°	736.4	760.2	784.7	799.4	813.3	828.0	841.9	847.6	854.1	859.9	865.6
15°	696.4	717.6	738.9	761.8	783.9	806.7	828.8	836.2	842.7	850.1	856.6
17.5°	660.4	677.6	693.9	723.4	752.8	781.4	810.8	819.8	828.0	837.0	845.2
20°	635.1	648.2	661.3	693.9	725.8	758.5	790.4	800.2	810.0	819.8	829.6
22.5°	613.8	626.1	638.4	669.4	700.5	731.5	762.6	775.7	787.9	801.0	813.3
25°	596.7	608.9	620.4	648.2	675.1	702.9	729.9	746.3	762.6	779.0	795.3
27.5°	579.5	591.8	604.0	626.9	649.8	672.7	695.6	715.2	734.0	753.6	772.4
30°	560.7	573.8	586.9	604.9	622.0	640.0	657.2	678.4	698.8	720.1	740.5
32.5°	541.1	553.4	565.6	577.9	590.1	601.6	613.8	633.5	653.9	673.5	693.1
35°	516.6	528.8	541.1	544.4	548.5	551.7	555.0	580.3	605.7	631.0	656.3
37.5°	492.1	502.7	514.1	508.4	502.7	496.1	490.4	523.9	557.4	591.0	624.5
40°	463.4	471.6	479.0	467.5	456.1	444.6	433.2	468.4	504.3	539.5	574.6
42.5°	428.3	429.9	432.4	421.8	412.0	401.3	390.7	423.4	455.3	488.0	519.8
45°	381.7	373.5	365.4	363.7	362.1	359.6	358.0	394.8	431.6	468.4	505.1
47.5°	337.6	320.4	303.2	314.7	325.3	336.8	347.4	379.3	412.0	443.8	475.7
50°	300.8	280.4	259.9	282.0	303.2	325.3	346.6	371.1	394.8	419.3	443.0
52.5°	270.5	253.4	235.4	255.0	275.5	295.1	314.7	336.8	358.8	380.9	403.0
55°	240.3	228.9	216.6	235.4	254.2	273.0	291.8	309.0	326.9	344.1	361.3
57.5°	210.1	202.7	194.5	217.4	241.1	264.0	286.9	290.2	294.3	297.5	300.8
60°	181.5	176.6	170.8	193.7	217.4	240.3	263.2	251.7	240.3	228.9	217.4
62.5°	165.1	160.2	154.5	175.7	197.0	217.4	238.7	218.2	198.6	178.2	157.8
65°	149.6	145.5	140.6	156.1	171.6	187.2	202.7	185.5	167.6	150.4	132.4
67.5°	136.5	132.4	127.5	134.0	141.4	147.9	154.5	143.0	131.6	119.3	107.9
70°	122.6	117.7	113.6	113.6	114.4	114.4	114.4	103.8	93.2	82.6	71.9
72.5°	108.7	105.4	102.2	100.5	98.9	96.4	94.8	85.8	76.8	67.0	58.0
75°	94.0	91.5	89.1	85.8	83.4	80.1	76.8	72.7	69.5	65.4	61.3
77.5°	76.0	74.4	71.9	67.8	64.6	60.5	56.4	56.4	57.2	57.2	57.2
80°	55.6	53.1	51.5	49.0	47.4	45.0	42.5	43.3	44.1	44.1	45.0
82.5°	36.0	34.3	32.7	31.9	31.1	29.4	28.6	28.6	28.6	28.6	28.6
85°	19.6	18.8	17.2	16.3	15.5	13.9	13.1	13.9	14.7	15.5	16.3
87.5°	8.2	7.4	6.5	5.7	5.7	4.9	4.1	4.9	5.7	6.5	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	872.9	873.8	875.4	876.2	877.9	877.9	877.9	877.9	877.0	877.0	876.2
5°	877.0	879.5	881.1	883.6	885.2	886.0	886.0	886.8	886.8	886.8	886.0
7.5°	877.0	879.5	882.8	885.2	887.7	888.5	889.3	890.1	889.3	889.3	888.5
10°	873.8	877.0	880.3	883.6	885.2	886.0	886.8	887.7	886.8	886.8	886.0
12.5°	868.9	872.1	874.6	877.9	879.5	880.3	881.9	882.8	882.8	882.8	881.9
15°	859.9	862.3	865.6	868.0	869.7	871.3	873.8	875.4	875.4	874.6	874.6
17.5°	848.4	851.7	855.0	858.2	860.7	862.3	863.1	864.8	864.8	864.8	864.0
20°	833.7	837.8	841.1	845.2	847.6	849.2	850.1	851.7	851.7	851.7	851.7
22.5°	817.4	821.5	825.5	829.6	831.3	832.9	834.5	836.2	836.2	836.2	836.2
25°	798.6	802.7	805.9	809.2	814.1	815.7	817.4	819.0	819.8	820.6	820.6
27.5°	777.3	781.4	786.3	790.4	793.7	796.1	797.8	800.2	801.0	801.8	801.8
30°	747.1	754.4	761.0	767.5	770.8	774.0	778.1	781.4	782.2	782.2	783.0
32.5°	706.2	718.5	731.5	743.8	751.2	754.4	757.7	761.0	760.2	758.5	757.7
35°	672.7	689.0	705.4	721.7	728.3	730.7	733.2	735.6	734.0	733.2	731.5
37.5°	643.3	662.1	680.1	698.8	703.8	705.4	707.8	709.5	707.8	706.2	703.8
40°	599.1	623.7	647.4	671.9	675.1	676.8	678.4	680.1	678.4	677.6	676.0
42.5°	550.9	582.0	612.2	643.3	647.4	646.5	644.9	644.1	644.9	646.5	647.4
45°	532.1	559.1	585.2	612.2	617.1	615.5	613.8	612.2	613.8	615.5	617.1
47.5°	501.9	528.8	555.0	581.1	581.1	580.3	579.5	578.7	581.1	582.8	585.2
50°	466.7	491.2	514.9	538.6	535.4	539.5	542.7	546.8	549.3	551.7	554.2
52.5°	423.4	443.8	463.4	483.9	496.1	501.9	508.4	514.1	515.8	517.4	518.2
55°	379.3	398.1	416.0	434.0	458.5	465.1	470.8	477.3	479.0	481.4	483.1
57.5°	322.9	344.9	366.2	388.2	419.3	426.7	434.8	442.2	442.2	442.2	441.4
60°	247.7	278.7	309.0	339.2	376.0	384.2	391.5	399.7	398.9	398.9	398.1
62.5°	189.6	220.7	252.6	283.6	325.3	336.8	347.4	358.8	358.8	358.8	358.0
65°	149.6	167.6	184.7	201.9	270.5	286.9	302.4	318.8	319.6	319.6	320.4
67.5°	115.2	122.6	129.1	136.5	225.6	243.6	262.4	280.4	280.4	279.5	279.5
70°	77.6	83.4	89.1	94.8	183.1	202.7	223.1	242.8	241.9	241.1	239.5
72.5°	61.3	63.8	67.0	69.5	142.2	162.7	183.9	204.3	203.5	201.9	201.1
75°	59.7	57.2	55.6	53.1	105.4	125.9	145.5	165.9	165.1	164.3	163.5
77.5°	53.9	49.9	46.6	42.5	77.6	95.6	113.6	131.6	130.8	129.1	128.3
80°	41.7	38.4	35.1	31.9	53.1	67.0	80.9	94.8	94.8	94.8	94.8
82.5°	27.8	26.2	25.3	23.7	33.5	44.1	53.9	64.6	63.8	63.8	62.9
85°	16.3	15.5	15.5	14.7	20.4	25.3	30.2	35.1	36.0	36.0	36.8
87.5°	8.2	8.2	9.0	9.0	11.4	13.9	15.5	18.0	18.0	18.8	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	875.4	874.6	872.9	874.6	875.4	877.0	879.5	881.1	882.8	883.6	884.4
5°	886.0	885.2	884.4	885.2	886.0	888.5	890.1	892.6	894.2	895.0	895.0
7.5°	887.7	887.7	886.8	887.7	888.5	890.9	892.6	895.0	896.7	897.5	897.5
10°	885.2	885.2	885.2	886.8	888.5	890.9	892.6	895.0	896.7	897.5	897.5
12.5°	881.9	881.9	881.1	882.8	884.4	886.8	888.5	890.9	892.6	893.4	893.4
15°	873.8	873.8	873.8	875.4	877.0	879.5	881.9	883.6	886.0	886.8	887.7
17.5°	864.0	864.8	864.8	866.4	868.0	870.5	872.1	874.6	876.2	877.0	877.0
20°	851.7	851.7	851.7	854.1	855.8	858.2	859.9	862.3	864.0	864.8	866.4
22.5°	836.2	837.0	837.8	841.1	843.5	845.2	847.6	849.2	850.9	850.9	851.7
25°	821.5	823.1	823.9	825.5	827.2	828.0	828.8	828.8	829.6	829.6	828.8
27.5°	802.7	804.3	805.9	806.7	806.7	806.7	807.6	807.6	807.6	808.4	809.2
30°	783.0	781.4	779.8	780.6	781.4	782.2	783.9	784.7	785.5	786.3	786.3
32.5°	756.1	756.1	755.2	756.9	757.7	759.3	761.0	762.6	764.2	764.2	764.2
35°	729.9	731.5	733.2	734.0	734.0	734.8	736.4	737.3	738.1	738.9	739.7
37.5°	702.1	704.6	707.0	708.7	709.5	710.3	711.1	711.9	712.7	711.9	711.9
40°	674.3	676.8	679.2	680.1	680.9	681.7	681.7	682.5	682.5	681.7	681.7
42.5°	648.2	649.0	649.8	651.4	653.1	652.3	652.3	651.4	650.6	649.8	648.2
45°	618.7	620.4	621.2	621.2	621.2	619.6	617.9	615.5	613.8	613.0	613.0
47.5°	586.9	589.3	591.0	588.5	585.2	583.6	582.0	579.5	577.9	577.1	576.2
50°	556.6	555.0	552.5	550.1	546.8	545.2	544.4	542.7	541.1	537.8	535.4
52.5°	519.8	516.6	513.3	510.9	507.6	505.1	502.7	500.2	497.8	496.1	495.3
55°	484.7	479.0	472.4	470.0	466.7	463.4	459.4	456.1	452.0	451.2	450.4
57.5°	441.4	438.1	434.0	429.1	423.4	420.1	417.7	414.4	411.1	410.3	409.5
60°	397.2	394.0	390.7	385.8	380.9	378.4	375.2	372.7	369.5	368.6	368.6
62.5°	358.0	355.6	352.3	344.9	337.6	335.9	333.5	331.9	329.4	327.8	326.9
65°	320.4	314.7	308.1	303.2	297.5	295.1	293.4	291.0	288.5	286.9	285.3
67.5°	278.7	271.4	263.2	260.7	258.3	255.8	252.6	250.1	246.8	246.0	245.2
70°	238.7	232.9	226.4	224.0	220.7	218.2	215.8	212.5	210.1	208.4	206.0
72.5°	199.4	194.5	188.8	185.5	182.3	179.8	178.2	175.7	173.3	171.6	170.0
75°	162.7	157.8	152.8	149.6	146.3	144.7	143.0	140.6	139.0	136.5	134.9
77.5°	126.7	124.2	121.0	116.9	112.8	112.0	111.2	110.3	109.5	107.1	105.4
80°	94.8	92.4	89.9	87.5	84.2	82.6	81.7	80.1	78.5	77.6	76.0
82.5°	62.1	60.5	58.9	58.0	57.2	56.4	55.6	54.8	53.9	53.1	53.1
85°	36.8	36.8	36.8	36.0	35.1	35.1	35.1	34.3	34.3	33.5	33.5
87.5°	18.8	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	19.6	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	885.2	884.4	885.2	885.2	886.0	886.0	885.2	885.2	884.4	883.6	884.4
5°	895.8	896.7	896.7	896.7	896.7	896.7	896.7	895.8	895.8	895.0	895.8
7.5°	898.3	898.3	899.1	899.1	899.9	899.9	899.1	899.1	898.3	897.5	898.3
10°	898.3	899.1	899.1	899.9	899.9	899.9	899.1	899.1	898.3	897.5	898.3
12.5°	894.2	894.2	895.0	895.0	895.8	895.8	895.8	895.0	895.0	894.2	895.0
15°	888.5	887.7	888.5	888.5	889.3	889.3	888.5	888.5	887.7	886.8	887.7
17.5°	877.9	878.7	878.7	879.5	879.5	879.5	878.7	877.9	877.0	876.2	877.0
20°	867.2	867.2	867.2	868.0	868.0	868.0	867.2	867.2	866.4	865.6	866.4
22.5°	851.7	851.7	851.7	850.9	850.9	850.1	849.2	849.2	848.4	847.6	848.4
25°	828.8	829.6	829.6	829.6	829.6	829.6	828.8	828.8	828.0	827.2	828.0
27.5°	810.0	808.4	809.2	809.2	810.0	810.0	810.0	809.2	809.2	808.4	809.2
30°	787.1	788.8	789.6	789.6	790.4	790.4	790.4	789.6	789.6	788.8	789.6
32.5°	764.2	765.9	765.9	765.9	765.9	765.9	765.9	765.1	765.1	764.2	765.1
35°	740.5	739.7	739.7	740.5	740.5	740.5	739.7	739.7	738.9	738.1	738.9
37.5°	711.1	711.1	711.1	711.1	711.1	711.1	710.3	710.3	709.5	708.7	709.5
40°	680.9	680.1	680.1	680.9	680.9	680.9	680.1	679.2	678.4	677.6	678.4
42.5°	647.4	647.4	647.4	647.4	646.5	646.5	646.5	646.5	645.7	645.7	645.7
45°	612.2	611.4	611.4	610.6	610.6	609.8	609.8	608.9	608.9	608.1	608.9
47.5°	575.4	575.4	574.6	573.0	572.2	570.5	569.7	568.9	567.3	566.4	567.3
50°	532.1	532.1	531.3	530.5	529.7	528.8	528.8	529.7	529.7	529.7	529.7
52.5°	493.7	490.4	489.6	489.6	488.8	488.0	488.0	488.0	487.2	487.2	487.2
55°	449.6	447.9	447.9	447.9	447.1	447.1	447.9	447.9	448.7	448.7	448.7
57.5°	408.7	407.9	407.9	407.0	407.0	406.2	405.4	405.4	404.6	403.8	404.6
60°	367.8	366.2	364.5	362.9	360.5	358.8	358.0	357.2	356.4	355.6	356.4
62.5°	325.3	322.0	321.2	319.6	318.8	317.1	315.5	314.7	313.1	311.4	313.1
65°	283.6	282.8	280.4	277.9	275.5	273.0	272.2	272.2	271.4	270.5	271.4
67.5°	244.4	239.5	237.9	236.2	234.6	232.9	232.9	232.9	232.9	232.9	232.9
70°	204.3	201.1	200.3	198.6	197.8	196.2	196.2	196.2	195.4	195.4	195.4
72.5°	168.4	165.1	164.3	163.5	161.8	161.0	161.0	161.0	160.2	160.2	160.2
75°	132.4	133.2	132.4	131.6	130.8	130.0	130.0	129.1	129.1	128.3	129.1
77.5°	103.0	103.0	102.2	101.4	100.5	99.7	99.7	99.7	99.7	99.7	99.7
80°	75.2	75.2	75.2	75.2	74.4	74.4	74.4	74.4	73.6	73.6	73.6
82.5°	52.3	52.3	52.3	52.3	52.3	52.3	52.3	51.5	51.5	50.7	51.5
85°	32.7	33.5	33.5	33.5	32.7	32.7	32.7	32.7	32.7	32.7	32.7
87.5°	20.4	20.4	20.4	21.3	21.3	21.3	21.3	21.3	20.4	20.4	20.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	885.2	885.2	886.0	886.0	885.2	885.2	884.4	885.2	884.4	883.6	882.8
5°	895.8	896.7	896.7	896.7	896.7	896.7	896.7	895.8	895.0	895.0	894.2
7.5°	899.1	899.1	899.9	899.9	899.1	899.1	898.3	898.3	897.5	897.5	896.7
10°	899.1	899.1	899.9	899.9	899.9	899.1	899.1	898.3	897.5	897.5	896.7
12.5°	895.0	895.8	895.8	895.8	895.0	895.0	894.2	894.2	893.4	893.4	892.6
15°	888.5	888.5	889.3	889.3	888.5	888.5	887.7	888.5	887.7	886.8	886.0
17.5°	877.9	878.7	879.5	879.5	879.5	878.7	878.7	877.9	877.0	877.0	876.2
20°	867.2	867.2	868.0	868.0	868.0	867.2	867.2	867.2	866.4	864.8	864.0
22.5°	849.2	849.2	850.1	850.9	850.9	851.7	851.7	851.7	851.7	850.9	850.9
25°	828.8	828.8	829.6	829.6	829.6	829.6	829.6	828.8	828.8	829.6	829.6
27.5°	809.2	810.0	810.0	810.0	809.2	809.2	808.4	810.0	809.2	808.4	807.6
30°	789.6	790.4	790.4	790.4	789.6	789.6	788.8	787.1	786.3	786.3	785.5
32.5°	765.1	765.9	765.9	765.9	765.9	765.9	765.9	764.2	764.2	764.2	764.2
35°	739.7	739.7	740.5	740.5	740.5	739.7	739.7	740.5	739.7	738.9	738.1
37.5°	710.3	710.3	711.1	711.1	711.1	711.1	711.1	711.1	711.9	711.9	712.7
40°	679.2	680.1	680.9	680.9	680.9	680.1	680.1	680.9	681.7	681.7	682.5
42.5°	646.5	646.5	646.5	646.5	647.4	647.4	647.4	647.4	648.2	649.8	650.6
45°	608.9	609.8	609.8	610.6	610.6	611.4	611.4	612.2	613.0	613.0	613.8
47.5°	568.9	569.7	570.5	572.2	573.0	574.6	575.4	575.4	576.2	577.1	577.9
50°	529.7	528.8	528.8	529.7	530.5	531.3	532.1	532.1	535.4	537.8	541.1
52.5°	488.0	488.0	488.0	488.8	489.6	489.6	490.4	493.7	495.3	496.1	497.8
55°	447.9	447.9	447.1	447.1	447.9	447.9	447.9	449.6	450.4	451.2	452.0
57.5°	405.4	405.4	406.2	407.0	407.0	407.9	407.9	408.7	409.5	410.3	411.1
60°	357.2	358.0	358.8	360.5	362.9	364.5	366.2	367.8	368.6	368.6	369.5
62.5°	314.7	315.5	317.1	318.8	319.6	321.2	322.0	325.3	326.9	327.8	329.4
65°	272.2	272.2	273.0	275.5	277.9	280.4	282.8	283.6	285.3	286.9	288.5
67.5°	232.9	232.9	232.9	234.6	236.2	237.9	239.5	244.4	245.2	246.0	246.8
70°	196.2	196.2	196.2	197.8	198.6	200.3	201.1	204.3	206.0	208.4	210.1
72.5°	161.0	161.0	161.0	161.8	163.5	164.3	165.1	168.4	170.0	171.6	173.3
75°	129.1	130.0	130.0	130.8	131.6	132.4	133.2	132.4	134.9	136.5	139.0
77.5°	99.7	99.7	99.7	100.5	101.4	102.2	103.0	103.0	105.4	107.1	109.5
80°	74.4	74.4	74.4	74.4	75.2	75.2	75.2	75.2	76.0	77.6	78.5
82.5°	51.5	52.3	52.3	52.3	52.3	52.3	52.3	52.3	53.1	53.1	53.9
85°	32.7	32.7	32.7	32.7	33.5	33.5	33.5	32.7	33.5	33.5	34.3
87.5°	21.3	21.3	21.3	21.3	21.3	20.4	20.4	20.4	20.4	19.6	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	881.1	879.5	877.0	875.4	874.6	872.9	874.6	875.4	876.2	877.0	877.0
5°	892.6	890.1	888.5	886.0	885.2	884.4	885.2	886.0	886.0	886.8	886.8
7.5°	895.0	892.6	890.9	888.5	887.7	886.8	887.7	887.7	888.5	889.3	889.3
10°	895.0	892.6	890.9	888.5	886.8	885.2	885.2	885.2	886.0	886.8	886.8
12.5°	890.9	888.5	886.8	884.4	882.8	881.1	881.9	881.9	881.9	882.8	882.8
15°	883.6	881.9	879.5	877.0	875.4	873.8	873.8	873.8	874.6	874.6	875.4
17.5°	874.6	872.1	870.5	868.0	866.4	864.8	864.8	864.0	864.0	864.8	864.8
20°	862.3	859.9	858.2	855.8	854.1	851.7	851.7	851.7	851.7	851.7	851.7
22.5°	849.2	847.6	845.2	843.5	840.3	837.8	837.0	836.2	836.2	836.2	836.2
25°	828.8	828.8	828.0	827.2	825.5	823.9	823.1	821.5	820.6	820.6	819.8
27.5°	807.6	807.6	806.7	806.7	806.7	805.9	804.3	802.7	801.8	801.8	801.0
30°	784.7	783.9	782.2	781.4	780.6	779.8	781.4	783.0	783.0	782.2	782.2
32.5°	762.6	761.0	759.3	757.7	756.9	755.2	756.1	756.1	757.7	758.5	760.2
35°	737.3	736.4	734.8	734.0	734.0	733.2	731.5	729.9	731.5	733.2	734.0
37.5°	711.9	711.1	710.3	709.5	708.7	707.0	704.6	702.1	703.8	705.4	707.8
40°	682.5	681.7	681.7	680.9	680.1	679.2	676.8	674.3	676.0	677.6	678.4
42.5°	651.4	652.3	652.3	653.1	651.4	649.8	649.0	648.2	647.4	646.5	644.9
45°	615.5	617.9	619.6	621.2	621.2	621.2	620.4	618.7	617.1	615.5	613.8
47.5°	579.5	582.0	583.6	585.2	588.5	591.0	589.3	586.9	585.2	582.8	581.1
50°	542.7	544.4	545.2	546.8	550.1	552.5	555.0	556.6	554.2	551.7	549.3
52.5°	500.2	502.7	505.1	507.6	510.9	513.3	516.6	519.8	518.2	517.4	515.8
55°	456.1	459.4	463.4	466.7	470.0	472.4	479.0	484.7	483.1	481.4	479.0
57.5°	414.4	416.9	420.1	423.4	429.1	434.0	438.1	441.4	441.4	442.2	442.2
60°	372.7	375.2	378.4	380.9	385.8	390.7	394.0	397.2	398.1	398.9	398.9
62.5°	331.9	333.5	335.9	337.6	344.9	352.3	355.6	358.0	358.0	358.8	358.8
65°	291.0	293.4	295.1	297.5	303.2	308.1	314.7	320.4	320.4	319.6	319.6
67.5°	250.1	252.6	255.8	258.3	260.7	263.2	271.4	278.7	279.5	279.5	280.4
70°	212.5	215.8	218.2	220.7	224.0	226.4	232.9	238.7	239.5	241.1	241.9
72.5°	175.7	178.2	179.8	182.3	185.5	188.8	194.5	199.4	201.1	201.9	203.5
75°	140.6	143.0	144.7	146.3	149.6	152.8	157.8	162.7	163.5	164.3	165.1
77.5°	110.3	111.2	112.0	112.8	116.9	121.0	124.2	126.7	128.3	129.1	130.8
80°	80.1	81.7	82.6	84.2	87.5	89.9	92.4	94.8	94.8	94.8	94.8
82.5°	54.8	55.6	56.4	57.2	58.0	58.9	60.5	62.1	62.9	63.8	63.8
85°	34.3	35.1	35.1	35.1	36.0	36.8	36.8	36.8	36.8	36.0	36.0
87.5°	19.6	19.6	19.6	19.6	19.6	19.6	19.6	18.8	18.8	18.8	18.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0	864.0
2.5°	877.9	877.9	877.9	877.9	876.2	875.4	873.8	872.9	871.3	871.3	871.3
5°	886.8	886.0	886.0	885.2	883.6	881.1	878.7	877.0	874.6	872.9	871.3
7.5°	890.1	889.3	888.5	887.7	885.2	882.8	879.5	877.0	873.8	870.5	867.2
10°	887.7	886.8	886.0	885.2	883.6	880.3	877.0	873.8	870.5	866.4	861.5
12.5°	882.8	881.9	880.3	879.5	877.9	874.6	871.3	868.9	865.6	859.9	853.3
15°	875.4	873.8	871.3	869.7	868.0	865.6	862.3	859.9	856.6	850.1	842.7
17.5°	864.8	863.1	862.3	860.7	858.2	855.0	851.7	848.4	845.2	837.0	828.0
20°	851.7	850.1	849.2	847.6	845.2	841.1	837.0	833.7	829.6	819.8	810.0
22.5°	836.2	834.5	832.9	831.3	829.6	825.5	821.5	817.4	813.3	801.0	787.9
25°	819.0	817.4	815.7	814.1	809.2	805.9	801.8	798.6	795.3	779.0	762.6
27.5°	800.2	797.8	796.1	793.7	790.4	786.3	781.4	777.3	772.4	753.6	734.0
30°	781.4	778.1	774.0	770.8	767.5	761.0	753.6	747.1	740.5	720.1	698.8
32.5°	761.0	757.7	754.4	751.2	743.8	731.5	718.5	706.2	693.1	673.5	653.1
35°	735.6	733.2	730.7	728.3	721.7	705.4	689.0	672.7	656.3	631.0	605.7
37.5°	709.5	707.8	705.4	703.8	698.8	680.1	661.3	643.3	624.5	591.0	557.4
40°	680.1	678.4	676.8	675.1	671.9	647.4	622.8	599.1	574.6	539.5	503.5
42.5°	644.1	644.9	646.5	647.4	643.3	612.2	581.1	550.9	519.8	488.0	455.3
45°	612.2	613.8	615.5	617.1	612.2	585.2	558.3	532.1	505.1	468.4	431.6
47.5°	578.7	579.5	580.3	581.1	581.1	555.0	528.0	501.9	475.7	443.8	411.1
50°	546.8	542.7	539.5	535.4	538.6	514.9	490.4	466.7	443.0	419.3	394.8
52.5°	514.1	508.4	501.9	496.1	483.9	463.4	443.0	423.4	403.0	380.9	358.8
55°	477.3	470.8	465.1	458.5	434.0	416.0	397.2	379.3	361.3	344.1	326.1
57.5°	442.2	434.8	426.7	419.3	388.2	366.2	344.1	322.9	300.8	297.5	293.4
60°	399.7	391.5	384.2	376.0	339.2	309.0	277.9	247.7	217.4	228.9	240.3
62.5°	358.8	347.4	336.8	325.3	283.6	252.6	220.7	189.6	157.8	178.2	198.6
65°	318.8	302.4	286.9	270.5	201.9	184.7	166.7	149.6	132.4	150.4	167.6
67.5°	280.4	262.4	243.6	225.6	136.5	129.1	121.8	115.2	107.9	119.3	131.6
70°	242.8	223.1	202.7	183.1	94.8	89.1	83.4	77.6	71.9	82.6	93.2
72.5°	204.3	183.9	162.7	142.2	69.5	67.0	63.8	61.3	58.0	67.0	76.8
75°	165.9	145.5	125.9	105.4	53.1	55.6	57.2	59.7	61.3	65.4	69.5
77.5°	131.6	113.6	95.6	77.6	42.5	46.6	49.9	53.9	57.2	57.2	57.2
80°	94.8	80.9	67.0	53.1	31.9	35.1	38.4	41.7	45.0	44.1	44.1
82.5°	64.6	53.9	44.1	33.5	23.7	25.3	26.2	27.8	28.6	28.6	28.6
85°	35.1	30.2	25.3	20.4	14.7	15.5	15.5	16.3	16.3	15.5	14.7
87.5°	18.0	15.5	13.9	11.4	9.0	9.0	8.2	8.2	7.4	6.5	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	864.0	864.0
2.5°	871.3	871.3
5°	869.7	868.0
7.5°	864.8	861.5
10°	857.4	853.3
12.5°	847.6	841.9
15°	836.2	828.8
17.5°	819.8	810.8
20°	800.2	790.4
22.5°	775.7	762.6
25°	746.3	729.9
27.5°	715.2	695.6
30°	678.4	657.2
32.5°	633.5	613.8
35°	580.3	555.0
37.5°	523.9	490.4
40°	468.4	433.2
42.5°	423.4	390.7
45°	394.8	358.0
47.5°	379.3	347.4
50°	371.1	346.6
52.5°	336.8	314.7
55°	309.0	291.8
57.5°	290.2	286.9
60°	251.7	263.2
62.5°	218.2	238.7
65°	185.5	202.7
67.5°	143.0	154.5
70°	103.8	114.4
72.5°	85.8	94.8
75°	72.7	76.8
77.5°	56.4	56.4
80°	43.3	42.5
82.5°	28.6	28.6
85°	13.9	13.1
87.5°	4.9	4.1
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055040

CATALOG NUMBER: SQ4R-FA-075D-930-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.45	19.07	17.82	19.38	19.69	19.37	20.98	19.73	21.29	21.61
	3H	18.12	19.57	18.49	19.90	20.26	21.17	22.62	21.54	22.95	23.31
	4H	18.45	19.82	18.85	20.16	20.54	21.79	23.15	22.19	23.50	23.88
	6H	18.74	20.00	19.15	20.37	20.76	22.17	23.44	22.58	23.80	24.19
	8H	18.82	20.02	19.24	20.41	20.81	22.27	23.47	22.69	23.86	24.26
	12H	18.85	20.00	19.27	20.38	20.81	22.31	23.47	22.74	23.85	24.28
4H	2H	18.58	19.95	18.98	20.30	20.67	19.94	21.31	20.34	21.65	22.03
	3H	19.90	21.04	20.31	21.44	21.84	21.97	23.11	22.38	23.51	23.91
	4H	20.34	21.37	20.77	21.78	22.22	22.71	23.74	23.14	24.15	24.59
	6H	20.63	21.53	21.08	21.97	22.42	23.20	24.10	23.66	24.54	25.00
	8H	20.71	21.55	21.17	21.99	22.45	23.33	24.17	23.79	24.61	25.08
	12H	20.75	21.50	21.23	21.98	22.45	23.40	24.16	23.88	24.63	25.10
8H	4H	20.92	21.76	21.38	22.21	22.67	22.94	23.78	23.40	24.22	24.68
	6H	21.41	22.10	21.90	22.59	23.07	23.53	24.23	24.03	24.72	25.19
	8H	21.53	22.16	22.04	22.67	23.15	23.71	24.34	24.22	24.84	25.33
	12H	21.61	22.16	22.11	22.65	23.21	23.83	24.39	24.34	24.88	25.44
12H	4H	20.98	21.73	21.46	22.21	22.68	22.94	23.70	23.42	24.17	24.64
	6H	21.51	22.13	22.02	22.64	23.13	23.55	24.18	24.06	24.68	25.17
	8H	21.71	22.26	22.22	22.75	23.32	23.77	24.33	24.28	24.82	25.38