

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055037

Luminaire Tested: SQ4R-FA-075D-835-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-835-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2759.2 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	89	87
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73
3	91	81	73	66	88	79	72	66	76	70	64	73	68	63	71	66	62
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54
5	77	64	55	49	75	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	51	43	37	50	42	37	48	42	37	47	41	37
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10243	10243	10243	10243
5°	10331	8376	10331	10652
10°	10273	7725	10273	10804
15°	10173	9090	10173	10885
20°	9973	9385	9973	10921
25°	9549	9473	9549	10821
30°	8997	9321	8997	10799
35°	8033	9121	8033	10682
40°	6705	9057	6705	10488
45°	6003	8949	6003	10196
50°	6392	8865	6392	9770
55°	6032	9055	6032	9275
60°	6240	8876	6240	8432
65°	5686	8483	5686	7590
70°	3966	7960	3966	6773
75°	3519	7038	3519	5877
80°	2900	5467	2900	5023
85°	1778	3778	1778	4452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 10416 cd/sqm

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	3.5
10°-20°	272.7	9.9
20°-30°	421.6	15.3
30°-40°	503.3	18.2
40°-50°	506.2	18.3
50°-60°	440.5	16.0
60°-70°	312.4	11.3
70°-80°	165.3	6.0
80°-90°	41.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.3	28.6
0°-40°	1293.6	46.9
0°-60°	2240.3	81.2
0°-90°	2759.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2759.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1064	1064	1064	1064	1064	
5°	1069	867	1069	1102	1069	101
15°	1021	912	1021	1092	1021	287
25°	899	892	899	1019	899	413
35°	684	776	684	909	684	423
45°	441	657	441	749	441	353
55°	359	540	359	553	359	330
65°	250	372	250	333	250	239
75°	95	189	95	158	95	99
85°	16	34	16	40	16	22
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1073.0	1071.0	1068.0	1066.0	1063.0	1061.9	1060.9	1059.9	1058.9	1055.9	1053.9
5°	1069.0	1065.0	1059.9	1055.9	1050.9	1046.8	1043.8	1039.8	1035.8	1029.7	1023.7
7.5°	1060.9	1053.9	1046.8	1039.8	1032.8	1023.7	1014.6	1005.6	996.5	980.4	961.3
10°	1050.9	1040.8	1029.7	1019.7	1008.6	987.5	966.3	944.2	923.0	894.9	875.7
12.5°	1036.8	1019.7	1001.6	984.4	966.3	936.1	906.9	876.7	846.5	827.4	816.3
15°	1020.7	993.5	965.3	938.1	910.0	883.8	857.6	830.4	804.3	790.2	782.1
17.5°	998.5	962.3	927.1	890.8	854.6	834.5	813.3	793.2	772.0	762.0	755.9
20°	973.4	934.1	893.8	854.6	814.3	798.2	782.1	765.0	748.9	739.8	736.8
22.5°	939.1	900.9	862.6	824.4	786.1	771.0	755.9	739.8	724.7	717.7	719.7
25°	898.9	865.7	831.4	798.2	764.0	749.9	734.8	720.7	705.6	697.6	703.6
27.5°	856.6	828.4	800.2	772.0	743.9	728.8	713.7	697.6	682.5	679.4	693.5
30°	809.3	788.2	766.0	744.9	722.7	706.6	690.5	674.4	658.3	657.3	679.4
32.5°	755.9	740.8	726.8	711.7	696.6	681.5	666.4	650.3	635.2	634.1	661.3
35°	683.5	679.4	675.4	670.4	666.4	651.3	636.2	621.1	606.0	607.0	637.2
37.5°	604.0	611.0	619.0	626.1	633.1	619.0	606.0	591.9	577.8	577.8	610.0
40°	533.5	547.6	561.7	575.8	589.9	580.8	570.7	561.7	551.6	548.6	581.8
42.5°	481.1	494.2	507.3	519.4	532.5	529.5	527.4	524.4	521.4	517.4	549.6
45°	440.9	442.9	445.9	447.9	449.9	460.0	470.1	480.1	490.2	487.2	516.4
47.5°	427.8	414.7	400.6	387.5	373.4	394.6	415.7	435.9	457.0	456.0	482.2
50°	426.8	400.6	373.4	347.3	320.1	345.3	370.4	394.6	419.7	423.8	443.9
52.5°	387.5	363.4	339.2	314.1	289.9	312.0	333.2	355.3	376.5	388.5	406.7
55°	359.4	336.2	313.0	289.9	266.7	281.8	295.9	311.0	325.1	351.3	367.4
57.5°	353.3	325.1	296.9	267.8	239.6	249.6	258.7	268.8	277.8	303.0	323.1
60°	324.1	295.9	267.8	238.6	210.4	217.4	223.5	230.5	236.5	255.7	279.8
62.5°	293.9	267.8	242.6	216.4	190.2	197.3	203.3	210.4	216.4	220.4	246.6
65°	249.6	230.5	211.4	192.3	173.1	179.2	184.2	190.2	195.3	196.3	220.4
67.5°	190.2	182.2	174.1	165.1	157.0	163.1	168.1	174.1	179.2	180.2	200.3
70°	140.9	140.9	140.9	139.9	139.9	144.9	151.0	156.0	161.1	163.1	178.2
72.5°	116.8	118.8	121.8	123.8	125.8	129.8	133.9	137.9	141.9	143.9	155.0
75°	94.6	98.6	102.7	105.7	109.7	112.7	115.8	117.8	120.8	121.8	129.8
77.5°	69.5	74.5	79.5	83.5	88.6	91.6	93.6	96.6	98.6	96.6	102.7
80°	52.3	55.4	58.4	60.4	63.4	65.4	68.4	70.5	72.5	70.5	74.5
82.5°	35.2	36.2	38.3	39.3	40.3	42.3	44.3	46.3	48.3	46.3	49.3
85°	16.1	17.1	19.1	20.1	21.1	23.2	24.2	26.2	27.2	26.2	27.2
87.5°	5.0	6.0	7.0	7.0	8.1	9.1	10.1	11.1	12.1	12.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1052.9	1050.9	1046.8	1043.8	1039.8	1035.8	1033.8	1031.7	1029.7	1027.7	1029.7
5°	1016.6	1010.6	1001.6	992.5	983.4	974.4	962.3	950.2	941.2	932.1	930.1
7.5°	941.2	922.0	905.9	888.8	872.7	855.6	846.5	837.5	829.4	821.4	819.4
10°	855.6	836.5	825.4	815.3	804.3	793.2	788.2	782.1	781.1	779.1	780.1
12.5°	804.3	793.2	787.1	781.1	774.1	768.0	767.0	766.0	769.0	771.0	778.1
15°	774.1	766.0	764.0	762.0	759.0	757.0	763.0	768.0	786.1	803.3	823.4
17.5°	750.9	744.9	749.9	753.9	759.0	763.0	794.2	825.4	849.6	872.7	879.8
20°	734.8	731.8	751.9	773.1	793.2	813.3	837.5	860.6	869.7	877.7	881.8
22.5°	720.7	722.7	752.9	782.1	812.3	841.5	851.6	860.6	866.7	872.7	875.7
25°	710.6	716.7	746.9	778.1	808.3	838.5	844.5	849.6	851.6	852.6	859.6
27.5°	707.6	721.7	747.9	774.1	799.2	825.4	829.4	833.5	835.5	836.5	843.5
30°	700.6	722.7	744.9	766.0	788.2	809.3	808.3	807.3	811.3	815.3	822.4
32.5°	688.5	715.7	732.8	750.9	768.0	785.1	784.1	783.1	789.2	794.2	799.2
35°	668.4	698.6	713.7	727.8	742.9	757.0	758.0	758.0	763.0	768.0	771.0
37.5°	643.2	675.4	689.5	703.6	716.7	730.8	729.8	728.8	730.8	731.8	736.8
40°	614.0	647.2	661.3	675.4	688.5	702.6	699.6	695.5	695.5	694.5	700.6
42.5°	580.8	613.0	627.1	641.2	654.3	668.4	662.3	655.3	657.3	658.3	666.4
45°	546.6	575.8	588.9	602.9	616.0	629.1	625.1	620.1	624.1	628.1	636.2
47.5°	508.3	534.5	548.6	562.7	576.8	590.9	588.9	585.8	589.9	593.9	602.9
50°	465.0	485.2	502.3	519.4	536.5	553.6	553.6	553.6	557.6	560.7	569.7
52.5°	423.8	441.9	462.0	482.2	501.3	521.4	522.4	523.4	527.4	530.5	538.5
55°	383.5	399.6	421.8	443.9	466.0	488.2	490.2	492.2	496.2	499.3	507.3
57.5°	342.2	362.4	385.5	409.7	432.8	456.0	457.0	458.0	461.0	464.0	471.1
60°	304.0	328.1	350.3	373.4	395.6	417.7	421.8	424.8	426.8	428.8	434.8
62.5°	273.8	300.0	320.1	341.2	361.4	381.5	386.5	390.6	392.6	393.6	397.6
65°	245.6	269.8	288.9	307.0	326.1	344.3	348.3	352.3	355.3	357.3	360.4
67.5°	220.4	240.6	255.7	270.8	285.9	301.0	307.0	312.0	314.1	316.1	318.1
70°	194.3	209.4	222.5	235.5	248.6	261.7	266.7	271.8	273.8	274.8	275.8
72.5°	166.1	177.2	187.2	197.3	207.4	217.4	222.5	227.5	229.5	230.5	231.5
75°	136.9	144.9	153.0	161.1	169.1	177.2	181.2	184.2	185.2	186.2	186.2
77.5°	107.7	113.7	119.8	125.8	130.9	136.9	139.9	142.9	142.9	142.9	142.9
80°	77.5	81.5	85.6	89.6	93.6	97.6	98.6	99.7	100.7	101.7	101.7
82.5°	51.3	54.4	56.4	59.4	61.4	63.4	63.4	63.4	63.4	63.4	64.4
85°	29.2	30.2	31.2	32.2	33.2	34.2	35.2	35.2	35.2	35.2	35.2
87.5°	13.1	14.1	14.1	15.1	15.1	15.1	15.1	14.1	14.1	14.1	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1030.7	1032.8	1033.8	1031.7	1028.7	1026.7	1023.7	1024.7	1025.7	1026.7	1027.7
5°	927.1	925.1	922.0	915.0	907.9	900.9	895.9	891.8	887.8	883.8	879.8
7.5°	816.3	814.3	811.3	809.3	807.3	805.3	801.2	800.2	799.2	798.2	797.2
10°	781.1	781.1	782.1	783.1	783.1	784.1	785.1	787.1	788.2	790.2	791.2
12.5°	785.1	791.2	798.2	811.3	825.4	838.5	847.5	855.6	864.7	872.7	880.8
15°	844.5	864.7	884.8	889.8	895.9	900.9	903.9	905.9	907.9	908.9	911.0
17.5°	886.8	892.8	899.9	901.9	904.9	906.9	907.9	908.9	911.0	912.0	913.0
20°	885.8	888.8	892.8	895.9	898.9	901.9	903.9	906.9	908.9	912.0	914.0
22.5°	879.8	882.8	885.8	890.8	894.9	899.9	903.9	905.9	907.9	910.0	912.0
25°	865.7	872.7	878.7	882.8	885.8	889.8	889.8	889.8	890.8	890.8	890.8
27.5°	850.6	857.6	864.7	865.7	867.7	868.7	870.7	872.7	873.7	875.7	876.7
30°	829.4	836.5	843.5	845.5	847.5	849.6	847.5	846.5	845.5	843.5	842.5
32.5°	805.3	810.3	815.3	816.3	816.3	817.3	812.3	811.3	810.3	808.3	807.3
35°	775.1	778.1	781.1	780.1	780.1	779.1	780.1	780.1	780.1	779.1	779.1
37.5°	740.8	745.9	749.9	750.9	750.9	751.9	753.9	753.9	753.9	752.9	752.9
40°	707.6	713.7	719.7	720.7	722.7	723.7	724.7	724.7	724.7	723.7	723.7
42.5°	674.4	682.5	690.5	692.5	694.5	696.6	695.5	694.5	694.5	693.5	692.5
45°	645.2	653.3	661.3	662.3	664.3	665.4	666.4	665.4	663.3	662.3	660.3
47.5°	612.0	620.1	629.1	631.1	632.1	634.1	634.1	633.1	632.1	630.1	629.1
50°	579.8	588.9	597.9	598.9	599.9	600.9	599.9	597.9	596.9	594.9	592.9
52.5°	547.6	555.6	563.7	563.7	562.7	562.7	562.7	562.7	563.7	563.7	563.7
55°	514.4	522.4	529.5	529.5	529.5	529.5	530.5	532.5	534.5	535.5	537.5
57.5°	479.1	486.2	493.2	494.2	494.2	495.2	495.2	496.2	498.3	499.3	500.3
60°	441.9	447.9	454.0	455.0	455.0	456.0	458.0	459.0	460.0	461.0	462.0
62.5°	401.6	404.6	408.7	410.7	412.7	414.7	416.7	416.7	417.7	417.7	417.7
65°	363.4	365.4	368.4	369.4	370.4	371.4	373.4	373.4	374.4	374.4	374.4
67.5°	320.1	321.1	323.1	324.1	326.1	327.1	326.1	326.1	326.1	325.1	325.1
70°	276.8	277.8	278.8	279.8	280.8	281.8	281.8	281.8	281.8	280.8	280.8
72.5°	231.5	232.5	232.5	232.5	233.5	233.5	232.5	233.5	234.5	235.5	236.5
75°	187.2	187.2	187.2	187.2	186.2	186.2	188.2	188.2	187.2	187.2	186.2
77.5°	142.9	142.9	142.9	142.9	141.9	141.9	143.9	143.9	142.9	142.9	141.9
80°	101.7	100.7	100.7	100.7	100.7	100.7	99.7	99.7	99.7	99.7	99.7
82.5°	64.4	65.4	65.4	65.4	64.4	64.4	63.4	63.4	63.4	63.4	63.4
85°	34.2	34.2	33.2	34.2	34.2	35.2	36.2	36.2	35.2	35.2	34.2
87.5°	14.1	14.1	14.1	14.1	13.1	13.1	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1024.7	1022.7	1019.7	1016.6	1019.7	1022.7	1024.7	1027.7	1026.7	1025.7	1024.7
5°	876.7	873.7	869.7	866.7	869.7	873.7	876.7	879.8	883.8	887.8	891.8
7.5°	795.2	793.2	791.2	789.2	791.2	793.2	795.2	797.2	798.2	799.2	800.2
10°	791.2	791.2	790.2	790.2	790.2	791.2	791.2	791.2	790.2	788.2	787.1
12.5°	880.8	879.8	879.8	878.7	879.8	879.8	880.8	880.8	872.7	864.7	855.6
15°	911.0	912.0	912.0	912.0	912.0	912.0	911.0	911.0	908.9	907.9	905.9
17.5°	913.0	913.0	913.0	913.0	913.0	913.0	913.0	913.0	912.0	911.0	908.9
20°	915.0	915.0	916.0	916.0	916.0	915.0	915.0	914.0	912.0	908.9	906.9
22.5°	912.0	912.0	911.0	911.0	911.0	912.0	912.0	912.0	910.0	907.9	905.9
25°	890.8	891.8	891.8	891.8	891.8	891.8	890.8	890.8	890.8	890.8	889.8
27.5°	876.7	876.7	875.7	875.7	875.7	876.7	876.7	876.7	875.7	873.7	872.7
30°	841.5	840.5	839.5	838.5	839.5	840.5	841.5	842.5	843.5	845.5	846.5
32.5°	806.3	806.3	805.3	804.3	805.3	806.3	806.3	807.3	808.3	810.3	811.3
35°	778.1	778.1	777.1	776.1	777.1	778.1	778.1	779.1	779.1	780.1	780.1
37.5°	751.9	750.9	749.9	748.9	749.9	750.9	751.9	752.9	752.9	753.9	753.9
40°	722.7	722.7	721.7	720.7	721.7	722.7	722.7	723.7	723.7	724.7	724.7
42.5°	692.5	691.5	691.5	690.5	691.5	691.5	692.5	692.5	693.5	694.5	694.5
45°	659.3	659.3	658.3	657.3	658.3	659.3	659.3	660.3	662.3	663.3	665.4
47.5°	628.1	628.1	627.1	626.1	627.1	628.1	628.1	629.1	630.1	632.1	633.1
50°	592.9	592.9	591.9	591.9	591.9	592.9	592.9	592.9	594.9	596.9	597.9
52.5°	564.7	564.7	565.7	565.7	565.7	564.7	564.7	563.7	563.7	563.7	562.7
55°	538.5	538.5	539.5	539.5	539.5	538.5	538.5	537.5	535.5	534.5	532.5
57.5°	500.3	500.3	500.3	500.3	500.3	500.3	500.3	500.3	499.3	498.3	496.2
60°	462.0	462.0	461.0	461.0	461.0	462.0	462.0	462.0	461.0	460.0	459.0
62.5°	417.7	416.7	416.7	415.7	416.7	416.7	417.7	417.7	417.7	417.7	416.7
65°	374.4	373.4	373.4	372.4	373.4	373.4	374.4	374.4	374.4	374.4	373.4
67.5°	326.1	327.1	328.1	329.2	328.1	327.1	326.1	325.1	325.1	326.1	326.1
70°	281.8	281.8	282.8	282.8	282.8	281.8	281.8	280.8	280.8	281.8	281.8
72.5°	235.5	235.5	234.5	233.5	234.5	235.5	235.5	236.5	235.5	234.5	233.5
75°	187.2	188.2	188.2	189.2	188.2	188.2	187.2	186.2	187.2	187.2	188.2
77.5°	141.9	141.9	141.9	141.9	141.9	141.9	141.9	141.9	142.9	142.9	143.9
80°	99.7	99.7	98.6	98.6	98.6	99.7	99.7	99.7	99.7	99.7	99.7
82.5°	64.4	64.4	65.4	65.4	65.4	64.4	64.4	63.4	63.4	63.4	63.4
85°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	35.2	35.2	36.2
87.5°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1023.7	1026.7	1028.7	1031.7	1033.8	1032.8	1030.7	1029.7	1027.7	1029.7	1031.7
5°	895.9	900.9	907.9	915.0	922.0	925.1	927.1	930.1	932.1	941.2	950.2
7.5°	801.2	805.3	807.3	809.3	811.3	814.3	816.3	819.4	821.4	829.4	837.5
10°	785.1	784.1	783.1	783.1	782.1	781.1	781.1	780.1	779.1	781.1	782.1
12.5°	847.5	838.5	825.4	811.3	798.2	791.2	785.1	778.1	771.0	769.0	766.0
15°	903.9	900.9	895.9	889.8	884.8	864.7	844.5	823.4	803.3	786.1	768.0
17.5°	907.9	906.9	904.9	901.9	899.9	892.8	886.8	879.8	872.7	849.6	825.4
20°	903.9	901.9	898.9	895.9	892.8	888.8	885.8	881.8	877.7	869.7	860.6
22.5°	903.9	899.9	894.9	890.8	885.8	882.8	879.8	875.7	872.7	866.7	860.6
25°	889.8	889.8	885.8	882.8	878.7	872.7	865.7	859.6	852.6	851.6	849.6
27.5°	870.7	868.7	867.7	865.7	864.7	857.6	850.6	843.5	836.5	835.5	833.5
30°	847.5	849.6	847.5	845.5	843.5	836.5	829.4	822.4	815.3	811.3	807.3
32.5°	812.3	817.3	816.3	816.3	815.3	810.3	805.3	799.2	794.2	789.2	783.1
35°	780.1	779.1	780.1	780.1	781.1	778.1	775.1	771.0	768.0	763.0	758.0
37.5°	753.9	751.9	750.9	750.9	749.9	745.9	740.8	736.8	731.8	730.8	728.8
40°	724.7	723.7	722.7	720.7	719.7	713.7	707.6	700.6	694.5	695.5	695.5
42.5°	695.5	696.6	694.5	692.5	690.5	682.5	674.4	666.4	658.3	657.3	655.3
45°	666.4	665.4	664.3	662.3	661.3	653.3	645.2	636.2	628.1	624.1	620.1
47.5°	634.1	634.1	632.1	631.1	629.1	620.1	612.0	602.9	593.9	589.9	585.8
50°	599.9	600.9	599.9	598.9	597.9	588.9	579.8	569.7	560.7	557.6	553.6
52.5°	562.7	562.7	562.7	563.7	563.7	555.6	547.6	538.5	530.5	527.4	523.4
55°	530.5	529.5	529.5	529.5	529.5	522.4	514.4	507.3	499.3	496.2	492.2
57.5°	495.2	495.2	494.2	494.2	493.2	486.2	479.1	471.1	464.0	461.0	458.0
60°	458.0	456.0	455.0	455.0	454.0	447.9	441.9	434.8	428.8	426.8	424.8
62.5°	416.7	414.7	412.7	410.7	408.7	404.6	401.6	397.6	393.6	392.6	390.6
65°	373.4	371.4	370.4	369.4	368.4	365.4	363.4	360.4	357.3	355.3	352.3
67.5°	326.1	327.1	326.1	324.1	323.1	321.1	320.1	318.1	316.1	314.1	312.0
70°	281.8	281.8	280.8	279.8	278.8	277.8	276.8	275.8	274.8	273.8	271.8
72.5°	232.5	233.5	233.5	232.5	232.5	232.5	231.5	231.5	230.5	229.5	227.5
75°	188.2	186.2	186.2	187.2	187.2	187.2	187.2	186.2	186.2	185.2	184.2
77.5°	143.9	141.9	141.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9
80°	99.7	100.7	100.7	100.7	100.7	100.7	101.7	101.7	101.7	100.7	99.7
82.5°	63.4	64.4	64.4	65.4	65.4	65.4	64.4	64.4	63.4	63.4	63.4
85°	36.2	35.2	34.2	34.2	33.2	34.2	34.2	35.2	35.2	35.2	35.2
87.5°	12.1	13.1	13.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1033.8	1035.8	1039.8	1043.8	1046.8	1050.9	1052.9	1053.9	1055.9	1058.9	1059.9
5°	962.3	974.4	983.4	992.5	1001.6	1010.6	1016.6	1023.7	1029.7	1035.8	1039.8
7.5°	846.5	855.6	872.7	888.8	905.9	922.0	941.2	961.3	980.4	996.5	1005.6
10°	788.2	793.2	804.3	815.3	825.4	836.5	855.6	875.7	894.9	923.0	944.2
12.5°	767.0	768.0	774.1	781.1	787.1	793.2	804.3	816.3	827.4	846.5	876.7
15°	763.0	757.0	759.0	762.0	764.0	766.0	774.1	782.1	790.2	804.3	830.4
17.5°	794.2	763.0	759.0	753.9	749.9	744.9	750.9	755.9	762.0	772.0	793.2
20°	837.5	813.3	793.2	773.1	751.9	731.8	734.8	736.8	739.8	748.9	765.0
22.5°	851.6	841.5	812.3	782.1	752.9	722.7	720.7	719.7	717.7	724.7	739.8
25°	844.5	838.5	808.3	778.1	746.9	716.7	710.6	703.6	697.6	705.6	720.7
27.5°	829.4	825.4	799.2	774.1	747.9	721.7	707.6	693.5	679.4	682.5	697.6
30°	808.3	809.3	788.2	766.0	744.9	722.7	700.6	679.4	657.3	658.3	674.4
32.5°	784.1	785.1	768.0	750.9	732.8	715.7	688.5	661.3	634.1	635.2	650.3
35°	758.0	757.0	742.9	727.8	713.7	698.6	668.4	637.2	607.0	606.0	621.1
37.5°	729.8	730.8	716.7	703.6	689.5	675.4	643.2	610.0	577.8	577.8	591.9
40°	699.6	702.6	688.5	675.4	661.3	647.2	614.0	581.8	548.6	551.6	561.7
42.5°	662.3	668.4	654.3	641.2	627.1	613.0	580.8	549.6	517.4	521.4	524.4
45°	625.1	629.1	616.0	602.9	588.9	575.8	546.6	516.4	487.2	490.2	480.1
47.5°	588.9	590.9	576.8	562.7	548.6	534.5	508.3	482.2	456.0	457.0	435.9
50°	553.6	553.6	536.5	519.4	502.3	485.2	465.0	443.9	423.8	419.7	394.6
52.5°	522.4	521.4	501.3	482.2	462.0	441.9	423.8	406.7	388.5	376.5	355.3
55°	490.2	488.2	466.0	443.9	421.8	399.6	383.5	367.4	351.3	325.1	311.0
57.5°	457.0	456.0	432.8	409.7	385.5	362.4	342.2	323.1	303.0	277.8	268.8
60°	421.8	417.7	395.6	373.4	350.3	328.1	304.0	279.8	255.7	236.5	230.5
62.5°	386.5	381.5	361.4	341.2	320.1	300.0	273.8	246.6	220.4	216.4	210.4
65°	348.3	344.3	326.1	307.0	288.9	269.8	245.6	220.4	196.3	195.3	190.2
67.5°	307.0	301.0	285.9	270.8	255.7	240.6	220.4	200.3	180.2	179.2	174.1
70°	266.7	261.7	248.6	235.5	222.5	209.4	194.3	178.2	163.1	161.1	156.0
72.5°	222.5	217.4	207.4	197.3	187.2	177.2	166.1	155.0	143.9	141.9	137.9
75°	181.2	177.2	169.1	161.1	153.0	144.9	136.9	129.8	121.8	120.8	117.8
77.5°	139.9	136.9	130.9	125.8	119.8	113.7	107.7	102.7	96.6	98.6	96.6
80°	98.6	97.6	93.6	89.6	85.6	81.5	77.5	74.5	70.5	72.5	70.5
82.5°	63.4	63.4	61.4	59.4	56.4	54.4	51.3	49.3	46.3	48.3	46.3
85°	35.2	34.2	33.2	32.2	31.2	30.2	29.2	27.2	26.2	27.2	26.2
87.5°	15.1	15.1	15.1	15.1	14.1	14.1	13.1	13.1	12.1	12.1	11.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1060.9	1061.9	1063.0	1066.0	1068.0	1071.0	1073.0	1073.0	1073.0	1073.0	1073.0
5°	1043.8	1046.8	1050.9	1055.9	1059.9	1065.0	1069.0	1071.0	1073.0	1075.0	1077.0
7.5°	1014.6	1023.7	1032.8	1039.8	1046.8	1053.9	1060.9	1065.0	1069.0	1072.0	1076.0
10°	966.3	987.5	1008.6	1019.7	1029.7	1040.8	1050.9	1055.9	1061.9	1067.0	1072.0
12.5°	906.9	936.1	966.3	984.4	1001.6	1019.7	1036.8	1043.8	1051.9	1058.9	1066.0
15°	857.6	883.8	910.0	938.1	965.3	993.5	1020.7	1029.7	1037.8	1046.8	1054.9
17.5°	813.3	834.5	854.6	890.8	927.1	962.3	998.5	1009.6	1019.7	1030.7	1040.8
20°	782.1	798.2	814.3	854.6	893.8	934.1	973.4	985.4	997.5	1009.6	1021.7
22.5°	755.9	771.0	786.1	824.4	862.6	900.9	939.1	955.2	970.3	986.5	1001.6
25°	734.8	749.9	764.0	798.2	831.4	865.7	898.9	919.0	939.1	959.3	979.4
27.5°	713.7	728.8	743.9	772.0	800.2	828.4	856.6	880.8	903.9	928.1	951.2
30°	690.5	706.6	722.7	744.9	766.0	788.2	809.3	835.5	860.6	886.8	912.0
32.5°	666.4	681.5	696.6	711.7	726.8	740.8	755.9	780.1	805.3	829.4	853.6
35°	636.2	651.3	666.4	670.4	675.4	679.4	683.5	714.7	745.9	777.1	808.3
37.5°	606.0	619.0	633.1	626.1	619.0	611.0	604.0	645.2	686.5	727.8	769.0
40°	570.7	580.8	589.9	575.8	561.7	547.6	533.5	576.8	621.1	664.3	707.6
42.5°	527.4	529.5	532.5	519.4	507.3	494.2	481.1	521.4	560.7	600.9	640.2
45°	470.1	460.0	449.9	447.9	445.9	442.9	440.9	486.2	531.5	576.8	622.1
47.5°	415.7	394.6	373.4	387.5	400.6	414.7	427.8	467.1	507.3	546.6	585.8
50°	370.4	345.3	320.1	347.3	373.4	400.6	426.8	457.0	486.2	516.4	545.6
52.5°	333.2	312.0	289.9	314.1	339.2	363.4	387.5	414.7	441.9	469.1	496.2
55°	295.9	281.8	266.7	289.9	313.0	336.2	359.4	380.5	402.6	423.8	444.9
57.5°	258.7	249.6	239.6	267.8	296.9	325.1	353.3	357.3	362.4	366.4	370.4
60°	223.5	217.4	210.4	238.6	267.8	295.9	324.1	310.0	295.9	281.8	267.8
62.5°	203.3	197.3	190.2	216.4	242.6	267.8	293.9	268.8	244.6	219.4	194.3
65°	184.2	179.2	173.1	192.3	211.4	230.5	249.6	228.5	206.3	185.2	163.1
67.5°	168.1	163.1	157.0	165.1	174.1	182.2	190.2	176.2	162.1	147.0	132.9
70°	151.0	144.9	139.9	139.9	140.9	140.9	140.9	127.8	114.8	101.7	88.6
72.5°	133.9	129.8	125.8	123.8	121.8	118.8	116.8	105.7	94.6	82.5	71.5
75°	115.8	112.7	109.7	105.7	102.7	98.6	94.6	89.6	85.6	80.5	75.5
77.5°	93.6	91.6	88.6	83.5	79.5	74.5	69.5	69.5	70.5	70.5	70.5
80°	68.4	65.4	63.4	60.4	58.4	55.4	52.3	53.3	54.4	54.4	55.4
82.5°	44.3	42.3	40.3	39.3	38.3	36.2	35.2	35.2	35.2	35.2	35.2
85°	24.2	23.2	21.1	20.1	19.1	17.1	16.1	17.1	18.1	19.1	20.1
87.5°	10.1	9.1	8.1	7.0	7.0	6.0	5.0	6.0	7.0	8.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1075.0	1076.0	1078.1	1079.1	1081.1	1081.1	1081.1	1081.1	1080.1	1080.1	1079.1
5°	1080.1	1083.1	1085.1	1088.1	1090.1	1091.1	1091.1	1092.1	1092.1	1092.1	1091.1
7.5°	1080.1	1083.1	1087.1	1090.1	1093.1	1094.2	1095.2	1096.2	1095.2	1095.2	1094.2
10°	1076.0	1080.1	1084.1	1088.1	1090.1	1091.1	1092.1	1093.1	1092.1	1092.1	1091.1
12.5°	1070.0	1074.0	1077.0	1081.1	1083.1	1084.1	1086.1	1087.1	1087.1	1087.1	1086.1
15°	1058.9	1061.9	1066.0	1069.0	1071.0	1073.0	1076.0	1078.1	1078.1	1077.0	1077.0
17.5°	1044.8	1048.9	1052.9	1056.9	1059.9	1061.9	1063.0	1065.0	1065.0	1065.0	1064.0
20°	1026.7	1031.7	1035.8	1040.8	1043.8	1045.8	1046.8	1048.9	1048.9	1048.9	1048.9
22.5°	1006.6	1011.6	1016.6	1021.7	1023.7	1025.7	1027.7	1029.7	1029.7	1029.7	1029.7
25°	983.4	988.5	992.5	996.5	1002.6	1004.6	1006.6	1008.6	1009.6	1010.6	1010.6
27.5°	957.3	962.3	968.3	973.4	977.4	980.4	982.4	985.4	986.5	987.5	987.5
30°	920.0	929.1	937.1	945.2	949.2	953.2	958.3	962.3	963.3	963.3	964.3
32.5°	869.7	884.8	900.9	916.0	925.1	929.1	933.1	937.1	936.1	934.1	933.1
35°	828.4	848.5	868.7	888.8	896.9	899.9	902.9	905.9	903.9	902.9	900.9
37.5°	792.2	815.3	837.5	860.6	866.7	868.7	871.7	873.7	871.7	869.7	866.7
40°	737.8	768.0	797.2	827.4	831.4	833.5	835.5	837.5	835.5	834.5	832.4
42.5°	678.4	716.7	753.9	792.2	797.2	796.2	794.2	793.2	794.2	796.2	797.2
45°	655.3	688.5	720.7	753.9	760.0	758.0	755.9	753.9	755.9	758.0	760.0
47.5°	618.0	651.3	683.5	715.7	715.7	714.7	713.7	712.7	715.7	717.7	720.7
50°	574.8	605.0	634.1	663.3	659.3	664.3	668.4	673.4	676.4	679.4	682.5
52.5°	521.4	546.6	570.7	595.9	611.0	618.0	626.1	633.1	635.2	637.2	638.2
55°	467.1	490.2	512.4	534.5	564.7	572.7	579.8	587.8	589.9	592.9	594.9
57.5°	397.6	424.8	450.9	478.1	516.4	525.4	535.5	544.6	544.6	544.6	543.6
60°	305.0	343.2	380.5	417.7	463.0	473.1	482.2	492.2	491.2	491.2	490.2
62.5°	233.5	271.8	311.0	349.3	400.6	414.7	427.8	441.9	441.9	441.9	440.9
65°	184.2	206.3	227.5	248.6	333.2	353.3	372.4	392.6	393.6	393.6	394.6
67.5°	141.9	151.0	159.0	168.1	277.8	300.0	323.1	345.3	345.3	344.3	344.3
70°	95.6	102.7	109.7	116.8	225.5	249.6	274.8	299.0	297.9	296.9	294.9
72.5°	75.5	78.5	82.5	85.6	175.1	200.3	226.5	251.6	250.6	248.6	247.6
75°	73.5	70.5	68.4	65.4	129.8	155.0	179.2	204.3	203.3	202.3	201.3
77.5°	66.4	61.4	57.4	52.3	95.6	117.8	139.9	162.1	161.1	159.0	158.0
80°	51.3	47.3	43.3	39.3	65.4	82.5	99.7	116.8	116.8	116.8	116.8
82.5°	34.2	32.2	31.2	29.2	41.3	54.4	66.4	79.5	78.5	78.5	77.5
85°	20.1	19.1	19.1	18.1	25.2	31.2	37.2	43.3	44.3	44.3	45.3
87.5°	10.1	10.1	11.1	11.1	14.1	17.1	19.1	22.1	22.1	23.2	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1078.1	1077.0	1075.0	1077.0	1078.1	1080.1	1083.1	1085.1	1087.1	1088.1	1089.1
5°	1091.1	1090.1	1089.1	1090.1	1091.1	1094.2	1096.2	1099.2	1101.2	1102.2	1102.2
7.5°	1093.1	1093.1	1092.1	1093.1	1094.2	1097.2	1099.2	1102.2	1104.2	1105.2	1105.2
10°	1090.1	1090.1	1090.1	1092.1	1094.2	1097.2	1099.2	1102.2	1104.2	1105.2	1105.2
12.5°	1086.1	1086.1	1085.1	1087.1	1089.1	1092.1	1094.2	1097.2	1099.2	1100.2	1100.2
15°	1076.0	1076.0	1076.0	1078.1	1080.1	1083.1	1086.1	1088.1	1091.1	1092.1	1093.1
17.5°	1064.0	1065.0	1065.0	1067.0	1069.0	1072.0	1074.0	1077.0	1079.1	1080.1	1080.1
20°	1048.9	1048.9	1048.9	1051.9	1053.9	1056.9	1058.9	1061.9	1064.0	1065.0	1067.0
22.5°	1029.7	1030.7	1031.7	1035.8	1038.8	1040.8	1043.8	1045.8	1047.9	1047.9	1048.9
25°	1011.6	1013.6	1014.6	1016.6	1018.7	1019.7	1020.7	1020.7	1021.7	1021.7	1020.7
27.5°	988.5	990.5	992.5	993.5	993.5	993.5	994.5	994.5	994.5	995.5	996.5
30°	964.3	962.3	960.3	961.3	962.3	963.3	965.3	966.3	967.3	968.3	968.3
32.5°	931.1	931.1	930.1	932.1	933.1	935.1	937.1	939.1	941.2	941.2	941.2
35°	898.9	900.9	902.9	903.9	903.9	904.9	906.9	907.9	908.9	910.0	911.0
37.5°	864.7	867.7	870.7	872.7	873.7	874.7	875.7	876.7	877.7	876.7	876.7
40°	830.4	833.5	836.5	837.5	838.5	839.5	839.5	840.5	840.5	839.5	839.5
42.5°	798.2	799.2	800.2	802.2	804.3	803.3	803.3	802.2	801.2	800.2	798.2
45°	762.0	764.0	765.0	765.0	765.0	763.0	761.0	758.0	755.9	754.9	754.9
47.5°	722.7	725.7	727.8	724.7	720.7	718.7	716.7	713.7	711.7	710.6	709.6
50°	685.5	683.5	680.5	677.4	673.4	671.4	670.4	668.4	666.4	662.3	659.3
52.5°	640.2	636.2	632.1	629.1	625.1	622.1	619.0	616.0	613.0	611.0	610.0
55°	596.9	589.9	581.8	578.8	574.8	570.7	565.7	561.7	556.6	555.6	554.6
57.5°	543.6	539.5	534.5	528.5	521.4	517.4	514.4	510.3	506.3	505.3	504.3
60°	489.2	485.2	481.1	475.1	469.1	466.0	462.0	459.0	455.0	454.0	454.0
62.5°	440.9	437.9	433.8	424.8	415.7	413.7	410.7	408.7	405.7	403.6	402.6
65°	394.6	387.5	379.5	373.4	366.4	363.4	361.4	358.3	355.3	353.3	351.3
67.5°	343.2	334.2	324.1	321.1	318.1	315.1	311.0	308.0	304.0	303.0	302.0
70°	293.9	286.9	278.8	275.8	271.8	268.8	265.7	261.7	258.7	256.7	253.7
72.5°	245.6	239.6	232.5	228.5	224.5	221.4	219.4	216.4	213.4	211.4	209.4
75°	200.3	194.3	188.2	184.2	180.2	178.2	176.2	173.1	171.1	168.1	166.1
77.5°	156.0	153.0	149.0	143.9	138.9	137.9	136.9	135.9	134.9	131.9	129.8
80°	116.8	113.7	110.7	107.7	103.7	101.7	100.7	98.6	96.6	95.6	93.6
82.5°	76.5	74.5	72.5	71.5	70.5	69.5	68.4	67.4	66.4	65.4	65.4
85°	45.3	45.3	45.3	44.3	43.3	43.3	43.3	42.3	42.3	41.3	41.3
87.5°	23.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1090.1	1089.1	1090.1	1090.1	1091.1	1091.1	1090.1	1090.1	1089.1	1088.1	1089.1
5°	1103.2	1104.2	1104.2	1104.2	1104.2	1104.2	1104.2	1103.2	1103.2	1102.2	1103.2
7.5°	1106.2	1106.2	1107.2	1107.2	1108.2	1108.2	1107.2	1107.2	1106.2	1105.2	1106.2
10°	1106.2	1107.2	1107.2	1108.2	1108.2	1108.2	1107.2	1107.2	1106.2	1105.2	1106.2
12.5°	1101.2	1101.2	1102.2	1102.2	1103.2	1103.2	1103.2	1102.2	1102.2	1101.2	1102.2
15°	1094.2	1093.1	1094.2	1094.2	1095.2	1095.2	1094.2	1094.2	1093.1	1092.1	1093.1
17.5°	1081.1	1082.1	1082.1	1083.1	1083.1	1083.1	1082.1	1081.1	1080.1	1079.1	1080.1
20°	1068.0	1068.0	1068.0	1069.0	1069.0	1069.0	1068.0	1068.0	1067.0	1066.0	1067.0
22.5°	1048.9	1048.9	1048.9	1047.9	1047.9	1046.8	1045.8	1045.8	1044.8	1043.8	1044.8
25°	1020.7	1021.7	1021.7	1021.7	1021.7	1021.7	1020.7	1020.7	1019.7	1018.7	1019.7
27.5°	997.5	995.5	996.5	996.5	997.5	997.5	997.5	996.5	996.5	995.5	996.5
30°	969.3	971.4	972.4	972.4	973.4	973.4	973.4	972.4	972.4	971.4	972.4
32.5°	941.2	943.2	943.2	943.2	943.2	943.2	943.2	942.2	942.2	941.2	942.2
35°	912.0	911.0	911.0	912.0	912.0	912.0	911.0	911.0	910.0	908.9	910.0
37.5°	875.7	875.7	875.7	875.7	875.7	875.7	874.7	874.7	873.7	872.7	873.7
40°	838.5	837.5	837.5	838.5	838.5	838.5	837.5	836.5	835.5	834.5	835.5
42.5°	797.2	797.2	797.2	797.2	796.2	796.2	796.2	796.2	795.2	795.2	795.2
45°	753.9	752.9	752.9	751.9	751.9	750.9	750.9	749.9	749.9	748.9	749.9
47.5°	708.6	708.6	707.6	705.6	704.6	702.6	701.6	700.6	698.6	697.6	698.6
50°	655.3	655.3	654.3	653.3	652.3	651.3	651.3	652.3	652.3	652.3	652.3
52.5°	608.0	604.0	602.9	602.9	601.9	600.9	600.9	600.9	599.9	599.9	599.9
55°	553.6	551.6	551.6	551.6	550.6	550.6	551.6	551.6	552.6	552.6	552.6
57.5°	503.3	502.3	502.3	501.3	501.3	500.3	499.3	499.3	498.3	497.3	498.3
60°	453.0	450.9	448.9	446.9	443.9	441.9	440.9	439.9	438.9	437.9	438.9
62.5°	400.6	396.6	395.6	393.6	392.6	390.6	388.5	387.5	385.5	383.5	385.5
65°	349.3	348.3	345.3	342.2	339.2	336.2	335.2	335.2	334.2	333.2	334.2
67.5°	301.0	294.9	292.9	290.9	288.9	286.9	286.9	286.9	286.9	286.9	286.9
70°	251.6	247.6	246.6	244.6	243.6	241.6	241.6	241.6	240.6	240.6	240.6
72.5°	207.4	203.3	202.3	201.3	199.3	198.3	198.3	198.3	197.3	197.3	197.3
75°	163.1	164.1	163.1	162.1	161.1	160.0	160.0	159.0	159.0	158.0	159.0
77.5°	126.8	126.8	125.8	124.8	123.8	122.8	122.8	122.8	122.8	122.8	122.8
80°	92.6	92.6	92.6	92.6	91.6	91.6	91.6	91.6	90.6	90.6	90.6
82.5°	64.4	64.4	64.4	64.4	64.4	64.4	64.4	63.4	63.4	62.4	63.4
85°	40.3	41.3	41.3	41.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3
87.5°	25.2	25.2	25.2	26.2	26.2	26.2	26.2	26.2	25.2	25.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1090.1	1090.1	1091.1	1091.1	1090.1	1090.1	1089.1	1090.1	1089.1	1088.1	1087.1
5°	1103.2	1104.2	1104.2	1104.2	1104.2	1104.2	1104.2	1103.2	1102.2	1102.2	1101.2
7.5°	1107.2	1107.2	1108.2	1108.2	1107.2	1107.2	1106.2	1106.2	1105.2	1105.2	1104.2
10°	1107.2	1107.2	1108.2	1108.2	1108.2	1107.2	1107.2	1106.2	1105.2	1105.2	1104.2
12.5°	1102.2	1103.2	1103.2	1103.2	1102.2	1102.2	1101.2	1101.2	1100.2	1100.2	1099.2
15°	1094.2	1094.2	1095.2	1095.2	1094.2	1094.2	1093.1	1094.2	1093.1	1092.1	1091.1
17.5°	1081.1	1082.1	1083.1	1083.1	1083.1	1082.1	1082.1	1081.1	1080.1	1080.1	1079.1
20°	1068.0	1068.0	1069.0	1069.0	1069.0	1068.0	1068.0	1068.0	1067.0	1065.0	1064.0
22.5°	1045.8	1045.8	1046.8	1047.9	1047.9	1048.9	1048.9	1048.9	1048.9	1047.9	1047.9
25°	1020.7	1020.7	1021.7	1021.7	1021.7	1021.7	1021.7	1020.7	1020.7	1021.7	1021.7
27.5°	996.5	997.5	997.5	997.5	996.5	996.5	995.5	997.5	996.5	995.5	994.5
30°	972.4	973.4	973.4	973.4	972.4	972.4	971.4	969.3	968.3	968.3	967.3
32.5°	942.2	943.2	943.2	943.2	943.2	943.2	943.2	941.2	941.2	941.2	941.2
35°	911.0	911.0	912.0	912.0	912.0	911.0	911.0	912.0	911.0	910.0	908.9
37.5°	874.7	874.7	875.7	875.7	875.7	875.7	875.7	875.7	876.7	876.7	877.7
40°	836.5	837.5	838.5	838.5	838.5	837.5	837.5	838.5	839.5	839.5	840.5
42.5°	796.2	796.2	796.2	796.2	797.2	797.2	797.2	797.2	798.2	800.2	801.2
45°	749.9	750.9	750.9	751.9	751.9	752.9	752.9	753.9	754.9	754.9	755.9
47.5°	700.6	701.6	702.6	704.6	705.6	707.6	708.6	708.6	709.6	710.6	711.7
50°	652.3	651.3	651.3	652.3	653.3	654.3	655.3	655.3	659.3	662.3	666.4
52.5°	600.9	600.9	600.9	601.9	602.9	602.9	604.0	608.0	610.0	611.0	613.0
55°	551.6	551.6	550.6	550.6	551.6	551.6	551.6	553.6	554.6	555.6	556.6
57.5°	499.3	499.3	500.3	501.3	501.3	502.3	502.3	503.3	504.3	505.3	506.3
60°	439.9	440.9	441.9	443.9	446.9	448.9	450.9	453.0	454.0	454.0	455.0
62.5°	387.5	388.5	390.6	392.6	393.6	395.6	396.6	400.6	402.6	403.6	405.7
65°	335.2	335.2	336.2	339.2	342.2	345.3	348.3	349.3	351.3	353.3	355.3
67.5°	286.9	286.9	286.9	288.9	290.9	292.9	294.9	301.0	302.0	303.0	304.0
70°	241.6	241.6	241.6	243.6	244.6	246.6	247.6	251.6	253.7	256.7	258.7
72.5°	198.3	198.3	198.3	199.3	201.3	202.3	203.3	207.4	209.4	211.4	213.4
75°	159.0	160.0	160.0	161.1	162.1	163.1	164.1	163.1	166.1	168.1	171.1
77.5°	122.8	122.8	122.8	123.8	124.8	125.8	126.8	126.8	129.8	131.9	134.9
80°	91.6	91.6	91.6	91.6	92.6	92.6	92.6	92.6	93.6	95.6	96.6
82.5°	63.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	65.4	65.4	66.4
85°	40.3	40.3	40.3	40.3	41.3	41.3	41.3	40.3	41.3	41.3	42.3
87.5°	26.2	26.2	26.2	26.2	26.2	25.2	25.2	25.2	25.2	24.2	24.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1085.1	1083.1	1080.1	1078.1	1077.0	1075.0	1077.0	1078.1	1079.1	1080.1	1080.1
5°	1099.2	1096.2	1094.2	1091.1	1090.1	1089.1	1090.1	1091.1	1091.1	1092.1	1092.1
7.5°	1102.2	1099.2	1097.2	1094.2	1093.1	1092.1	1093.1	1093.1	1094.2	1095.2	1095.2
10°	1102.2	1099.2	1097.2	1094.2	1092.1	1090.1	1090.1	1090.1	1091.1	1092.1	1092.1
12.5°	1097.2	1094.2	1092.1	1089.1	1087.1	1085.1	1086.1	1086.1	1086.1	1087.1	1087.1
15°	1088.1	1086.1	1083.1	1080.1	1078.1	1076.0	1076.0	1076.0	1077.0	1077.0	1078.1
17.5°	1077.0	1074.0	1072.0	1069.0	1067.0	1065.0	1065.0	1064.0	1064.0	1065.0	1065.0
20°	1061.9	1058.9	1056.9	1053.9	1051.9	1048.9	1048.9	1048.9	1048.9	1048.9	1048.9
22.5°	1045.8	1043.8	1040.8	1038.8	1034.8	1031.7	1030.7	1029.7	1029.7	1029.7	1029.7
25°	1020.7	1020.7	1019.7	1018.7	1016.6	1014.6	1013.6	1011.6	1010.6	1010.6	1009.6
27.5°	994.5	994.5	993.5	993.5	993.5	992.5	990.5	988.5	987.5	987.5	986.5
30°	966.3	965.3	963.3	962.3	961.3	960.3	962.3	964.3	964.3	963.3	963.3
32.5°	939.1	937.1	935.1	933.1	932.1	930.1	931.1	931.1	933.1	934.1	936.1
35°	907.9	906.9	904.9	903.9	903.9	902.9	900.9	898.9	900.9	902.9	903.9
37.5°	876.7	875.7	874.7	873.7	872.7	870.7	867.7	864.7	866.7	868.7	871.7
40°	840.5	839.5	839.5	838.5	837.5	836.5	833.5	830.4	832.4	834.5	835.5
42.5°	802.2	803.3	803.3	804.3	802.2	800.2	799.2	798.2	797.2	796.2	794.2
45°	758.0	761.0	763.0	765.0	765.0	765.0	764.0	762.0	760.0	758.0	755.9
47.5°	713.7	716.7	718.7	720.7	724.7	727.8	725.7	722.7	720.7	717.7	715.7
50°	668.4	670.4	671.4	673.4	677.4	680.5	683.5	685.5	682.5	679.4	676.4
52.5°	616.0	619.0	622.1	625.1	629.1	632.1	636.2	640.2	638.2	637.2	635.2
55°	561.7	565.7	570.7	574.8	578.8	581.8	589.9	596.9	594.9	592.9	589.9
57.5°	510.3	513.4	517.4	521.4	528.5	534.5	539.5	543.6	543.6	544.6	544.6
60°	459.0	462.0	466.0	469.1	475.1	481.1	485.2	489.2	490.2	491.2	491.2
62.5°	408.7	410.7	413.7	415.7	424.8	433.8	437.9	440.9	440.9	441.9	441.9
65°	358.3	361.4	363.4	366.4	373.4	379.5	387.5	394.6	394.6	393.6	393.6
67.5°	308.0	311.0	315.1	318.1	321.1	324.1	334.2	343.2	344.3	344.3	345.3
70°	261.7	265.7	268.8	271.8	275.8	278.8	286.9	293.9	294.9	296.9	297.9
72.5°	216.4	219.4	221.4	224.5	228.5	232.5	239.6	245.6	247.6	248.6	250.6
75°	173.1	176.2	178.2	180.2	184.2	188.2	194.3	200.3	201.3	202.3	203.3
77.5°	135.9	136.9	137.9	138.9	143.9	149.0	153.0	156.0	158.0	159.0	161.1
80°	98.6	100.7	101.7	103.7	107.7	110.7	113.7	116.8	116.8	116.8	116.8
82.5°	67.4	68.4	69.5	70.5	71.5	72.5	74.5	76.5	77.5	78.5	78.5
85°	42.3	43.3	43.3	43.3	44.3	45.3	45.3	45.3	45.3	44.3	44.3
87.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.2	23.2	23.2	22.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0	1064.0
2.5°	1081.1	1081.1	1081.1	1081.1	1079.1	1078.1	1076.0	1075.0	1073.0	1073.0	1073.0
5°	1092.1	1091.1	1091.1	1090.1	1088.1	1085.1	1082.1	1080.1	1077.0	1075.0	1073.0
7.5°	1096.2	1095.2	1094.2	1093.1	1090.1	1087.1	1083.1	1080.1	1076.0	1072.0	1068.0
10°	1093.1	1092.1	1091.1	1090.1	1088.1	1084.1	1080.1	1076.0	1072.0	1067.0	1060.9
12.5°	1087.1	1086.1	1084.1	1083.1	1081.1	1077.0	1073.0	1070.0	1066.0	1058.9	1050.9
15°	1078.1	1076.0	1073.0	1071.0	1069.0	1066.0	1061.9	1058.9	1054.9	1046.8	1037.8
17.5°	1065.0	1063.0	1061.9	1059.9	1056.9	1052.9	1048.9	1044.8	1040.8	1030.7	1019.7
20°	1048.9	1046.8	1045.8	1043.8	1040.8	1035.8	1030.7	1026.7	1021.7	1009.6	997.5
22.5°	1029.7	1027.7	1025.7	1023.7	1021.7	1016.6	1011.6	1006.6	1001.6	986.5	970.3
25°	1008.6	1006.6	1004.6	1002.6	996.5	992.5	987.5	983.4	979.4	959.3	939.1
27.5°	985.4	982.4	980.4	977.4	973.4	968.3	962.3	957.3	951.2	928.1	903.9
30°	962.3	958.3	953.2	949.2	945.2	937.1	928.1	920.0	912.0	886.8	860.6
32.5°	937.1	933.1	929.1	925.1	916.0	900.9	884.8	869.7	853.6	829.4	804.3
35°	905.9	902.9	899.9	896.9	888.8	868.7	848.5	828.4	808.3	777.1	745.9
37.5°	873.7	871.7	868.7	866.7	860.6	837.5	814.3	792.2	769.0	727.8	686.5
40°	837.5	835.5	833.5	831.4	827.4	797.2	767.0	737.8	707.6	664.3	620.1
42.5°	793.2	794.2	796.2	797.2	792.2	753.9	715.7	678.4	640.2	600.9	560.7
45°	753.9	755.9	758.0	760.0	753.9	720.7	687.5	655.3	622.1	576.8	531.5
47.5°	712.7	713.7	714.7	715.7	715.7	683.5	650.3	618.0	585.8	546.6	506.3
50°	673.4	668.4	664.3	659.3	663.3	634.1	604.0	574.8	545.6	516.4	486.2
52.5°	633.1	626.1	618.0	611.0	595.9	570.7	545.6	521.4	496.2	469.1	441.9
55°	587.8	579.8	572.7	564.7	534.5	512.4	489.2	467.1	444.9	423.8	401.6
57.5°	544.6	535.5	525.4	516.4	478.1	450.9	423.8	397.6	370.4	366.4	361.4
60°	492.2	482.2	473.1	463.0	417.7	380.5	342.2	305.0	267.8	281.8	295.9
62.5°	441.9	427.8	414.7	400.6	349.3	311.0	271.8	233.5	194.3	219.4	244.6
65°	392.6	372.4	353.3	333.2	248.6	227.5	205.3	184.2	163.1	185.2	206.3
67.5°	345.3	323.1	300.0	277.8	168.1	159.0	150.0	141.9	132.9	147.0	162.1
70°	299.0	274.8	249.6	225.5	116.8	109.7	102.7	95.6	88.6	101.7	114.8
72.5°	251.6	226.5	200.3	175.1	85.6	82.5	78.5	75.5	71.5	82.5	94.6
75°	204.3	179.2	155.0	129.8	65.4	68.4	70.5	73.5	75.5	80.5	85.6
77.5°	162.1	139.9	117.8	95.6	52.3	57.4	61.4	66.4	70.5	70.5	70.5
80°	116.8	99.7	82.5	65.4	39.3	43.3	47.3	51.3	55.4	54.4	54.4
82.5°	79.5	66.4	54.4	41.3	29.2	31.2	32.2	34.2	35.2	35.2	35.2
85°	43.3	37.2	31.2	25.2	18.1	19.1	19.1	20.1	20.1	19.1	18.1
87.5°	22.1	19.1	17.1	14.1	11.1	11.1	10.1	10.1	9.1	8.1	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1064.0	1064.0
2.5°	1073.0	1073.0
5°	1071.0	1069.0
7.5°	1065.0	1060.9
10°	1055.9	1050.9
12.5°	1043.8	1036.8
15°	1029.7	1020.7
17.5°	1009.6	998.5
20°	985.4	973.4
22.5°	955.2	939.1
25°	919.0	898.9
27.5°	880.8	856.6
30°	835.5	809.3
32.5°	780.1	755.9
35°	714.7	683.5
37.5°	645.2	604.0
40°	576.8	533.5
42.5°	521.4	481.1
45°	486.2	440.9
47.5°	467.1	427.8
50°	457.0	426.8
52.5°	414.7	387.5
55°	380.5	359.4
57.5°	357.3	353.3
60°	310.0	324.1
62.5°	268.8	293.9
65°	228.5	249.6
67.5°	176.2	190.2
70°	127.8	140.9
72.5°	105.7	116.8
75°	89.6	94.6
77.5°	69.5	69.5
80°	53.3	52.3
82.5°	35.2	35.2
85°	17.1	16.1
87.5°	6.0	5.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055037

CATALOG NUMBER: SQ4R-FA-075D-835-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.18	19.79	18.54	20.10	20.42	20.09	21.70	20.46	22.02	22.33
	3H	18.84	20.29	19.22	20.62	20.98	21.89	23.34	22.27	23.67	24.03
	4H	19.17	20.54	19.57	20.89	21.26	22.51	23.88	22.91	24.22	24.60
	6H	19.46	20.73	19.87	21.09	21.48	22.89	24.16	23.30	24.52	24.91
	8H	19.54	20.75	19.96	21.14	21.54	22.99	24.20	23.41	24.59	24.98
	12H	19.57	20.73	20.00	21.11	21.54	23.04	24.19	23.47	24.57	25.00
4H	2H	19.31	20.67	19.70	21.02	21.40	20.66	22.03	21.06	22.38	22.75
	3H	20.63	21.77	21.04	22.16	22.56	22.69	23.83	23.10	24.23	24.63
	4H	21.06	22.09	21.49	22.50	22.94	23.43	24.46	23.86	24.87	25.31
	6H	21.35	22.25	21.81	22.69	23.15	23.93	24.82	24.38	25.26	25.72
	8H	21.43	22.27	21.89	22.71	23.18	24.05	24.89	24.51	25.34	25.80
	12H	21.47	22.22	21.95	22.70	23.17	24.13	24.88	24.61	25.36	25.83
8H	4H	21.65	22.49	22.11	22.93	23.40	23.66	24.50	24.12	24.94	25.41
	6H	22.13	22.83	22.62	23.32	23.79	24.25	24.95	24.75	25.44	25.92
	8H	22.26	22.88	22.77	23.39	23.88	24.43	25.06	24.94	25.57	26.05
	12H	22.33	22.88	22.84	23.37	23.94	24.56	25.11	25.06	25.60	26.16
12H	4H	21.70	22.45	22.18	22.93	23.40	23.66	24.42	24.14	24.89	25.36
	6H	22.23	22.86	22.74	23.36	23.85	24.27	24.90	24.78	25.41	25.89
	8H	22.43	22.99	22.94	23.48	24.04	24.50	25.05	25.01	25.54	26.10