

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055041

Luminaire Tested: SQ4R-FA-075D-935-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-935-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2369.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	81	73	66	88	79	72	66	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8795	8795	8795	8795
5°	8870	7191	8870	9145
10°	8821	6632	8821	9276
15°	8734	7804	8734	9346
20°	8562	8057	8562	9376
25°	8199	8134	8199	9291
30°	7724	8003	7724	9271
35°	6897	7831	6897	9172
40°	5756	7777	5756	9003
45°	5153	7683	5153	8755
50°	5488	7612	5488	8387
55°	5178	7775	5178	7964
60°	5359	7621	5359	7238
65°	4882	7285	4882	6517
70°	3406	6834	3406	5815
75°	3020	6045	3020	5048
80°	2489	4696	2489	4313
85°	1524	3248	1524	3822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 8942 cd/sqm

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	3.5
10°-20°	234.2	9.9
20°-30°	362.0	15.3
30°-40°	432.1	18.2
40°-50°	434.6	18.3
50°-60°	378.2	16.0
60°-70°	268.2	11.3
70°-80°	141.9	6.0
80°-90°	35.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.6	28.6
0°-40°	1110.7	46.9
0°-60°	1923.5	81.2
0°-90°	2369.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2369.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	914	914	914	914	914	
5°	918	744	918	946	918	87
15°	876	783	876	938	876	247
25°	772	766	772	875	772	354
35°	587	666	587	780	587	363
45°	378	564	378	643	378	303
55°	308	463	308	474	308	283
65°	214	320	214	286	214	205
75°	81	162	81	136	81	85
85°	14	29	14	35	14	19
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	921.3	919.5	916.9	915.2	912.6	911.8	910.9	910.0	909.2	906.6	904.8
5°	917.8	914.4	910.0	906.6	902.3	898.8	896.2	892.7	889.3	884.1	878.9
7.5°	910.9	904.8	898.8	892.7	886.7	878.9	871.1	863.4	855.6	841.8	825.3
10°	902.3	893.6	884.1	875.5	866.0	847.8	829.7	810.6	792.5	768.3	751.9
12.5°	890.2	875.5	859.9	845.2	829.7	803.7	778.7	752.7	726.8	710.4	700.9
15°	876.3	853.0	828.8	805.5	781.3	758.8	736.3	713.0	690.5	678.4	671.5
17.5°	857.3	826.2	796.0	764.8	733.7	716.4	698.3	681.0	662.9	654.2	649.0
20°	835.7	802.0	767.4	733.7	699.2	685.3	671.5	656.8	643.0	635.2	632.6
22.5°	806.3	773.5	740.6	707.8	675.0	662.0	649.0	635.2	622.2	616.2	617.9
25°	771.8	743.2	713.9	685.3	656.0	643.9	630.9	618.8	605.8	598.9	604.1
27.5°	735.5	711.3	687.1	662.9	638.7	625.7	612.7	598.9	585.9	583.4	595.5
30°	694.8	676.7	657.7	639.5	620.5	606.7	592.9	579.0	565.2	564.3	583.4
32.5°	649.0	636.1	624.0	611.0	598.0	585.1	572.1	558.3	545.3	544.5	567.8
35°	586.8	583.4	579.9	575.6	572.1	559.2	546.2	533.2	520.3	521.1	547.1
37.5°	518.5	524.6	531.5	537.6	543.6	531.5	520.3	508.2	496.1	496.1	523.7
40°	458.0	470.1	482.2	494.3	506.4	498.7	490.0	482.2	473.6	471.0	499.5
42.5°	413.1	424.3	435.6	445.9	457.2	454.6	452.9	450.3	447.7	444.2	471.9
45°	378.5	380.3	382.9	384.6	386.3	395.0	403.6	412.2	420.9	418.3	443.3
47.5°	367.3	356.1	344.0	332.7	320.6	338.8	356.9	374.2	392.4	391.5	414.0
50°	366.4	344.0	320.6	298.2	274.8	296.4	318.0	338.8	360.4	363.8	381.1
52.5°	332.7	312.0	291.2	269.6	248.9	267.9	286.1	305.1	323.2	333.6	349.1
55°	308.5	288.7	268.8	248.9	229.0	242.0	254.1	267.0	279.1	301.6	315.4
57.5°	303.3	279.1	254.9	229.9	205.7	214.3	222.1	230.7	238.5	260.1	277.4
60°	278.3	254.1	229.9	204.8	180.6	186.7	191.9	197.9	203.1	219.5	240.3
62.5°	252.4	229.9	208.3	185.8	163.3	169.4	174.6	180.6	185.8	189.3	211.7
65°	214.3	197.9	181.5	165.1	148.6	153.8	158.2	163.3	167.7	168.5	189.3
67.5°	163.3	156.4	149.5	141.7	134.8	140.0	144.3	149.5	153.8	154.7	172.0
70°	121.0	121.0	121.0	120.1	120.1	124.4	129.6	134.0	138.3	140.0	153.0
72.5°	100.3	102.0	104.6	106.3	108.0	111.5	114.9	118.4	121.9	123.6	133.1
75°	81.2	84.7	88.2	90.7	94.2	96.8	99.4	101.1	103.7	104.6	111.5
77.5°	59.6	64.0	68.3	71.7	76.1	78.6	80.4	83.0	84.7	83.0	88.2
80°	44.9	47.5	50.1	51.9	54.4	56.2	58.8	60.5	62.2	60.5	64.0
82.5°	30.2	31.1	32.8	33.7	34.6	36.3	38.0	39.8	41.5	39.8	42.3
85°	13.8	14.7	16.4	17.3	18.1	19.9	20.7	22.5	23.3	22.5	23.3
87.5°	4.3	5.2	6.0	6.0	6.9	7.8	8.6	9.5	10.4	10.4	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	904.0	902.3	898.8	896.2	892.7	889.3	887.6	885.8	884.1	882.4	884.1
5°	872.9	867.7	859.9	852.1	844.4	836.6	826.2	815.8	808.1	800.3	798.5
7.5°	808.1	791.6	777.8	763.1	749.3	734.6	726.8	719.0	712.1	705.2	703.5
10°	734.6	718.2	708.7	700.0	690.5	681.0	676.7	671.5	670.6	668.9	669.8
12.5°	690.5	681.0	675.8	670.6	664.6	659.4	658.5	657.7	660.3	662.0	668.0
15°	664.6	657.7	656.0	654.2	651.6	649.9	655.1	659.4	675.0	689.7	706.9
17.5°	644.7	639.5	643.9	647.3	651.6	655.1	681.9	708.7	729.4	749.3	755.3
20°	630.9	628.3	645.6	663.7	681.0	698.3	719.0	738.9	746.7	753.6	757.1
22.5°	618.8	620.5	646.4	671.5	697.4	722.5	731.1	738.9	744.1	749.3	751.9
25°	610.1	615.3	641.3	668.0	694.0	719.9	725.1	729.4	731.1	732.0	738.1
27.5°	607.6	619.7	642.1	664.6	686.2	708.7	712.1	715.6	717.3	718.2	724.2
30°	601.5	620.5	639.5	657.7	676.7	694.8	694.0	693.1	696.6	700.0	706.1
32.5°	591.1	614.5	629.2	644.7	659.4	674.1	673.2	672.4	677.6	681.9	686.2
35°	573.8	599.8	612.7	624.8	637.8	649.9	650.8	650.8	655.1	659.4	662.0
37.5°	552.2	579.9	592.0	604.1	615.3	627.4	626.6	625.7	627.4	628.3	632.6
40°	527.2	555.7	567.8	579.9	591.1	603.2	600.6	597.2	597.2	596.3	601.5
42.5°	498.7	526.3	538.4	550.5	561.7	573.8	568.7	562.6	564.3	565.2	572.1
45°	469.3	494.3	505.6	517.7	528.9	540.1	536.7	532.4	535.8	539.3	546.2
47.5°	436.4	458.9	471.0	483.1	495.2	507.3	505.6	503.0	506.4	509.9	517.7
50°	399.3	416.6	431.3	445.9	460.6	475.3	475.3	475.3	478.8	481.4	489.2
52.5°	363.8	379.4	396.7	414.0	430.4	447.7	448.5	449.4	452.9	455.4	462.4
55°	329.3	343.1	362.1	381.1	400.1	419.2	420.9	422.6	426.1	428.7	435.6
57.5°	293.8	311.1	331.0	351.7	371.6	391.5	392.4	393.2	395.8	398.4	404.5
60°	261.0	281.7	300.8	320.6	339.6	358.7	362.1	364.7	366.4	368.2	373.3
62.5°	235.1	257.5	274.8	293.0	310.3	327.5	331.9	335.3	337.0	337.9	341.4
65°	210.9	231.6	248.0	263.6	280.0	295.6	299.0	302.5	305.1	306.8	309.4
67.5°	189.3	206.6	219.5	232.5	245.4	258.4	263.6	267.9	269.6	271.4	273.1
70°	166.8	179.8	191.0	202.2	213.5	224.7	229.0	233.3	235.1	235.9	236.8
72.5°	142.6	152.1	160.7	169.4	178.0	186.7	191.0	195.3	197.0	197.9	198.8
75°	117.5	124.4	131.4	138.3	145.2	152.1	155.6	158.2	159.0	159.9	159.9
77.5°	92.5	97.7	102.8	108.0	112.3	117.5	120.1	122.7	122.7	122.7	122.7
80°	66.5	70.0	73.5	76.9	80.4	83.8	84.7	85.6	86.4	87.3	87.3
82.5°	44.1	46.7	48.4	51.0	52.7	54.4	54.4	54.4	54.4	54.4	55.3
85°	25.1	25.9	26.8	27.7	28.5	29.4	30.2	30.2	30.2	30.2	30.2
87.5°	11.2	12.1	12.1	13.0	13.0	13.0	13.0	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	885.0	886.7	887.6	885.8	883.2	881.5	878.9	879.8	880.6	881.5	882.4
5°	796.0	794.2	791.6	785.6	779.5	773.5	769.2	765.7	762.3	758.8	755.3
7.5°	700.9	699.2	696.6	694.8	693.1	691.4	687.9	687.1	686.2	685.3	684.5
10°	670.6	670.6	671.5	672.4	672.4	673.2	674.1	675.8	676.7	678.4	679.3
12.5°	674.1	679.3	685.3	696.6	708.7	719.9	727.7	734.6	742.4	749.3	756.2
15°	725.1	742.4	759.7	764.0	769.2	773.5	776.1	777.8	779.5	780.4	782.1
17.5°	761.4	766.6	772.6	774.3	776.9	778.7	779.5	780.4	782.1	783.0	783.9
20°	760.5	763.1	766.6	769.2	771.8	774.3	776.1	778.7	780.4	783.0	784.7
22.5°	755.3	757.9	760.5	764.8	768.3	772.6	776.1	777.8	779.5	781.3	783.0
25°	743.2	749.3	754.5	757.9	760.5	764.0	764.0	764.0	764.8	764.8	764.8
27.5°	730.3	736.3	742.4	743.2	745.0	745.8	747.6	749.3	750.2	751.9	752.7
30°	712.1	718.2	724.2	726.0	727.7	729.4	727.7	726.8	726.0	724.2	723.4
32.5°	691.4	695.7	700.0	700.9	700.9	701.8	697.4	696.6	695.7	694.0	693.1
35°	665.5	668.0	670.6	669.8	669.8	668.9	669.8	669.8	669.8	668.9	668.9
37.5°	636.1	640.4	643.9	644.7	644.7	645.6	647.3	647.3	647.3	646.4	646.4
40°	607.6	612.7	617.9	618.8	620.5	621.4	622.2	622.2	622.2	621.4	621.4
42.5°	579.0	585.9	592.9	594.6	596.3	598.0	597.2	596.3	596.3	595.5	594.6
45°	554.0	560.9	567.8	568.7	570.4	571.3	572.1	571.3	569.5	568.7	566.9
47.5°	525.5	532.4	540.1	541.9	542.7	544.5	544.5	543.6	542.7	541.0	540.1
50°	497.8	505.6	513.4	514.2	515.1	515.9	515.1	513.4	512.5	510.8	509.0
52.5°	470.1	477.1	484.0	484.0	483.1	483.1	483.1	483.1	484.0	484.0	484.0
55°	441.6	448.5	454.6	454.6	454.6	454.6	455.4	457.2	458.9	459.8	461.5
57.5°	411.4	417.4	423.5	424.3	424.3	425.2	425.2	426.1	427.8	428.7	429.5
60°	379.4	384.6	389.8	390.6	390.6	391.5	393.2	394.1	395.0	395.8	396.7
62.5°	344.8	347.4	350.9	352.6	354.3	356.1	357.8	357.8	358.7	358.7	358.7
65°	312.0	313.7	316.3	317.2	318.0	318.9	320.6	320.6	321.5	321.5	321.5
67.5°	274.8	275.7	277.4	278.3	280.0	280.9	280.0	280.0	280.0	279.1	279.1
70°	237.7	238.5	239.4	240.3	241.1	242.0	242.0	242.0	242.0	241.1	241.1
72.5°	198.8	199.6	199.6	199.6	200.5	200.5	199.6	200.5	201.4	202.2	203.1
75°	160.7	160.7	160.7	160.7	159.9	159.9	161.6	161.6	160.7	160.7	159.9
77.5°	122.7	122.7	122.7	122.7	121.9	121.9	123.6	123.6	122.7	122.7	121.9
80°	87.3	86.4	86.4	86.4	86.4	86.4	85.6	85.6	85.6	85.6	85.6
82.5°	55.3	56.2	56.2	56.2	55.3	55.3	54.4	54.4	54.4	54.4	54.4
85°	29.4	29.4	28.5	29.4	29.4	30.2	31.1	31.1	30.2	30.2	29.4
87.5°	12.1	12.1	12.1	12.1	11.2	11.2	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	879.8	878.1	875.5	872.9	875.5	878.1	879.8	882.4	881.5	880.6	879.8
5°	752.7	750.2	746.7	744.1	746.7	750.2	752.7	755.3	758.8	762.3	765.7
7.5°	682.7	681.0	679.3	677.6	679.3	681.0	682.7	684.5	685.3	686.2	687.1
10°	679.3	679.3	678.4	678.4	678.4	679.3	679.3	679.3	678.4	676.7	675.8
12.5°	756.2	755.3	755.3	754.5	755.3	755.3	756.2	756.2	749.3	742.4	734.6
15°	782.1	783.0	783.0	783.0	783.0	783.0	782.1	782.1	780.4	779.5	777.8
17.5°	783.9	783.9	783.9	783.9	783.9	783.9	783.9	783.9	783.0	782.1	780.4
20°	785.6	785.6	786.4	786.4	786.4	785.6	785.6	784.7	783.0	780.4	778.7
22.5°	783.0	783.0	782.1	782.1	782.1	783.0	783.0	783.0	781.3	779.5	777.8
25°	764.8	765.7	765.7	765.7	765.7	765.7	764.8	764.8	764.8	764.8	764.0
27.5°	752.7	752.7	751.9	751.9	751.9	752.7	752.7	752.7	751.9	750.2	749.3
30°	722.5	721.6	720.8	719.9	720.8	721.6	722.5	723.4	724.2	726.0	726.8
32.5°	692.2	692.2	691.4	690.5	691.4	692.2	692.2	693.1	694.0	695.7	696.6
35°	668.0	668.0	667.2	666.3	667.2	668.0	668.0	668.9	668.9	669.8	669.8
37.5°	645.6	644.7	643.9	643.0	643.9	644.7	645.6	646.4	646.4	647.3	647.3
40°	620.5	620.5	619.7	618.8	619.7	620.5	620.5	621.4	621.4	622.2	622.2
42.5°	594.6	593.7	593.7	592.9	593.7	593.7	594.6	594.6	595.5	596.3	596.3
45°	566.1	566.1	565.2	564.3	565.2	566.1	566.1	566.9	568.7	569.5	571.3
47.5°	539.3	539.3	538.4	537.6	538.4	539.3	539.3	540.1	541.0	542.7	543.6
50°	509.0	509.0	508.2	508.2	508.2	509.0	509.0	509.0	510.8	512.5	513.4
52.5°	484.8	484.8	485.7	485.7	485.7	484.8	484.8	484.0	484.0	484.0	483.1
55°	462.4	462.4	463.2	463.2	463.2	462.4	462.4	461.5	459.8	458.9	457.2
57.5°	429.5	429.5	429.5	429.5	429.5	429.5	429.5	429.5	428.7	427.8	426.1
60°	396.7	396.7	395.8	395.8	395.8	396.7	396.7	396.7	395.8	395.0	394.1
62.5°	358.7	357.8	357.8	356.9	357.8	357.8	358.7	358.7	358.7	358.7	357.8
65°	321.5	320.6	320.6	319.8	320.6	320.6	321.5	321.5	321.5	321.5	320.6
67.5°	280.0	280.9	281.7	282.6	281.7	280.9	280.0	279.1	279.1	280.0	280.0
70°	242.0	242.0	242.8	242.8	242.8	242.0	242.0	241.1	241.1	242.0	242.0
72.5°	202.2	202.2	201.4	200.5	201.4	202.2	202.2	203.1	202.2	201.4	200.5
75°	160.7	161.6	161.6	162.5	161.6	161.6	160.7	159.9	160.7	160.7	161.6
77.5°	121.9	121.9	121.9	121.9	121.9	121.9	121.9	121.9	122.7	122.7	123.6
80°	85.6	85.6	84.7	84.7	84.7	85.6	85.6	85.6	85.6	85.6	85.6
82.5°	55.3	55.3	56.2	56.2	56.2	55.3	55.3	54.4	54.4	54.4	54.4
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4	30.2	30.2	31.1
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	878.9	881.5	883.2	885.8	887.6	886.7	885.0	884.1	882.4	884.1	885.8
5°	769.2	773.5	779.5	785.6	791.6	794.2	796.0	798.5	800.3	808.1	815.8
7.5°	687.9	691.4	693.1	694.8	696.6	699.2	700.9	703.5	705.2	712.1	719.0
10°	674.1	673.2	672.4	672.4	671.5	670.6	670.6	669.8	668.9	670.6	671.5
12.5°	727.7	719.9	708.7	696.6	685.3	679.3	674.1	668.0	662.0	660.3	657.7
15°	776.1	773.5	769.2	764.0	759.7	742.4	725.1	706.9	689.7	675.0	659.4
17.5°	779.5	778.7	776.9	774.3	772.6	766.6	761.4	755.3	749.3	729.4	708.7
20°	776.1	774.3	771.8	769.2	766.6	763.1	760.5	757.1	753.6	746.7	738.9
22.5°	776.1	772.6	768.3	764.8	760.5	757.9	755.3	751.9	749.3	744.1	738.9
25°	764.0	764.0	760.5	757.9	754.5	749.3	743.2	738.1	732.0	731.1	729.4
27.5°	747.6	745.8	745.0	743.2	742.4	736.3	730.3	724.2	718.2	717.3	715.6
30°	727.7	729.4	727.7	726.0	724.2	718.2	712.1	706.1	700.0	696.6	693.1
32.5°	697.4	701.8	700.9	700.9	700.0	695.7	691.4	686.2	681.9	677.6	672.4
35°	669.8	668.9	669.8	669.8	670.6	668.0	665.5	662.0	659.4	655.1	650.8
37.5°	647.3	645.6	644.7	644.7	643.9	640.4	636.1	632.6	628.3	627.4	625.7
40°	622.2	621.4	620.5	618.8	617.9	612.7	607.6	601.5	596.3	597.2	597.2
42.5°	597.2	598.0	596.3	594.6	592.9	585.9	579.0	572.1	565.2	564.3	562.6
45°	572.1	571.3	570.4	568.7	567.8	560.9	554.0	546.2	539.3	535.8	532.4
47.5°	544.5	544.5	542.7	541.9	540.1	532.4	525.5	517.7	509.9	506.4	503.0
50°	515.1	515.9	515.1	514.2	513.4	505.6	497.8	489.2	481.4	478.8	475.3
52.5°	483.1	483.1	483.1	484.0	484.0	477.1	470.1	462.4	455.4	452.9	449.4
55°	455.4	454.6	454.6	454.6	454.6	448.5	441.6	435.6	428.7	426.1	422.6
57.5°	425.2	425.2	424.3	424.3	423.5	417.4	411.4	404.5	398.4	395.8	393.2
60°	393.2	391.5	390.6	390.6	389.8	384.6	379.4	373.3	368.2	366.4	364.7
62.5°	357.8	356.1	354.3	352.6	350.9	347.4	344.8	341.4	337.9	337.0	335.3
65°	320.6	318.9	318.0	317.2	316.3	313.7	312.0	309.4	306.8	305.1	302.5
67.5°	280.0	280.9	280.0	278.3	277.4	275.7	274.8	273.1	271.4	269.6	267.9
70°	242.0	242.0	241.1	240.3	239.4	238.5	237.7	236.8	235.9	235.1	233.3
72.5°	199.6	200.5	200.5	199.6	199.6	199.6	198.8	198.8	197.9	197.0	195.3
75°	161.6	159.9	159.9	160.7	160.7	160.7	160.7	159.9	159.9	159.0	158.2
77.5°	123.6	121.9	121.9	122.7	122.7	122.7	122.7	122.7	122.7	122.7	122.7
80°	85.6	86.4	86.4	86.4	86.4	86.4	87.3	87.3	87.3	86.4	85.6
82.5°	54.4	55.3	55.3	56.2	56.2	56.2	55.3	55.3	54.4	54.4	54.4
85°	31.1	30.2	29.4	29.4	28.5	29.4	29.4	30.2	30.2	30.2	30.2
87.5°	10.4	11.2	11.2	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	887.6	889.3	892.7	896.2	898.8	902.3	904.0	904.8	906.6	909.2	910.0
5°	826.2	836.6	844.4	852.1	859.9	867.7	872.9	878.9	884.1	889.3	892.7
7.5°	726.8	734.6	749.3	763.1	777.8	791.6	808.1	825.3	841.8	855.6	863.4
10°	676.7	681.0	690.5	700.0	708.7	718.2	734.6	751.9	768.3	792.5	810.6
12.5°	658.5	659.4	664.6	670.6	675.8	681.0	690.5	700.9	710.4	726.8	752.7
15°	655.1	649.9	651.6	654.2	656.0	657.7	664.6	671.5	678.4	690.5	713.0
17.5°	681.9	655.1	651.6	647.3	643.9	639.5	644.7	649.0	654.2	662.9	681.0
20°	719.0	698.3	681.0	663.7	645.6	628.3	630.9	632.6	635.2	643.0	656.8
22.5°	731.1	722.5	697.4	671.5	646.4	620.5	618.8	617.9	616.2	622.2	635.2
25°	725.1	719.9	694.0	668.0	641.3	615.3	610.1	604.1	598.9	605.8	618.8
27.5°	712.1	708.7	686.2	664.6	642.1	619.7	607.6	595.5	583.4	585.9	598.9
30°	694.0	694.8	676.7	657.7	639.5	620.5	601.5	583.4	564.3	565.2	579.0
32.5°	673.2	674.1	659.4	644.7	629.2	614.5	591.1	567.8	544.5	545.3	558.3
35°	650.8	649.9	637.8	624.8	612.7	599.8	573.8	547.1	521.1	520.3	533.2
37.5°	626.6	627.4	615.3	604.1	592.0	579.9	552.2	523.7	496.1	496.1	508.2
40°	600.6	603.2	591.1	579.9	567.8	555.7	527.2	499.5	471.0	473.6	482.2
42.5°	568.7	573.8	561.7	550.5	538.4	526.3	498.7	471.9	444.2	447.7	450.3
45°	536.7	540.1	528.9	517.7	505.6	494.3	469.3	443.3	418.3	420.9	412.2
47.5°	505.6	507.3	495.2	483.1	471.0	458.9	436.4	414.0	391.5	392.4	374.2
50°	475.3	475.3	460.6	445.9	431.3	416.6	399.3	381.1	363.8	360.4	338.8
52.5°	448.5	447.7	430.4	414.0	396.7	379.4	363.8	349.1	333.6	323.2	305.1
55°	420.9	419.2	400.1	381.1	362.1	343.1	329.3	315.4	301.6	279.1	267.0
57.5°	392.4	391.5	371.6	351.7	331.0	311.1	293.8	277.4	260.1	238.5	230.7
60°	362.1	358.7	339.6	320.6	300.8	281.7	261.0	240.3	219.5	203.1	197.9
62.5°	331.9	327.5	310.3	293.0	274.8	257.5	235.1	211.7	189.3	185.8	180.6
65°	299.0	295.6	280.0	263.6	248.0	231.6	210.9	189.3	168.5	167.7	163.3
67.5°	263.6	258.4	245.4	232.5	219.5	206.6	189.3	172.0	154.7	153.8	149.5
70°	229.0	224.7	213.5	202.2	191.0	179.8	166.8	153.0	140.0	138.3	134.0
72.5°	191.0	186.7	178.0	169.4	160.7	152.1	142.6	133.1	123.6	121.9	118.4
75°	155.6	152.1	145.2	138.3	131.4	124.4	117.5	111.5	104.6	103.7	101.1
77.5°	120.1	117.5	112.3	108.0	102.8	97.7	92.5	88.2	83.0	84.7	83.0
80°	84.7	83.8	80.4	76.9	73.5	70.0	66.5	64.0	60.5	62.2	60.5
82.5°	54.4	54.4	52.7	51.0	48.4	46.7	44.1	42.3	39.8	41.5	39.8
85°	30.2	29.4	28.5	27.7	26.8	25.9	25.1	23.3	22.5	23.3	22.5
87.5°	13.0	13.0	13.0	13.0	12.1	12.1	11.2	11.2	10.4	10.4	9.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	910.9	911.8	912.6	915.2	916.9	919.5	921.3	921.3	921.3	921.3	921.3
5°	896.2	898.8	902.3	906.6	910.0	914.4	917.8	919.5	921.3	923.0	924.7
7.5°	871.1	878.9	886.7	892.7	898.8	904.8	910.9	914.4	917.8	920.4	923.9
10°	829.7	847.8	866.0	875.5	884.1	893.6	902.3	906.6	911.8	916.1	920.4
12.5°	778.7	803.7	829.7	845.2	859.9	875.5	890.2	896.2	903.1	909.2	915.2
15°	736.3	758.8	781.3	805.5	828.8	853.0	876.3	884.1	891.0	898.8	905.7
17.5°	698.3	716.4	733.7	764.8	796.0	826.2	857.3	866.8	875.5	885.0	893.6
20°	671.5	685.3	699.2	733.7	767.4	802.0	835.7	846.1	856.5	866.8	877.2
22.5°	649.0	662.0	675.0	707.8	740.6	773.5	806.3	820.2	833.1	846.9	859.9
25°	630.9	643.9	656.0	685.3	713.9	743.2	771.8	789.0	806.3	823.6	840.9
27.5°	612.7	625.7	638.7	662.9	687.1	711.3	735.5	756.2	776.1	796.8	816.7
30°	592.9	606.7	620.5	639.5	657.7	676.7	694.8	717.3	738.9	761.4	783.0
32.5°	572.1	585.1	598.0	611.0	624.0	636.1	649.0	669.8	691.4	712.1	732.9
35°	546.2	559.2	572.1	575.6	579.9	583.4	586.8	613.6	640.4	667.2	694.0
37.5°	520.3	531.5	543.6	537.6	531.5	524.6	518.5	554.0	589.4	624.8	660.3
40°	490.0	498.7	506.4	494.3	482.2	470.1	458.0	495.2	533.2	570.4	607.6
42.5°	452.9	454.6	457.2	445.9	435.6	424.3	413.1	447.7	481.4	515.9	549.6
45°	403.6	395.0	386.3	384.6	382.9	380.3	378.5	417.4	456.3	495.2	534.1
47.5°	356.9	338.8	320.6	332.7	344.0	356.1	367.3	401.0	435.6	469.3	503.0
50°	318.0	296.4	274.8	298.2	320.6	344.0	366.4	392.4	417.4	443.3	468.4
52.5°	286.1	267.9	248.9	269.6	291.2	312.0	332.7	356.1	379.4	402.7	426.1
55°	254.1	242.0	229.0	248.9	268.8	288.7	308.5	326.7	345.7	363.8	382.0
57.5°	222.1	214.3	205.7	229.9	254.9	279.1	303.3	306.8	311.1	314.6	318.0
60°	191.9	186.7	180.6	204.8	229.9	254.1	278.3	266.2	254.1	242.0	229.9
62.5°	174.6	169.4	163.3	185.8	208.3	229.9	252.4	230.7	210.0	188.4	166.8
65°	158.2	153.8	148.6	165.1	181.5	197.9	214.3	196.2	177.2	159.0	140.0
67.5°	144.3	140.0	134.8	141.7	149.5	156.4	163.3	151.2	139.1	126.2	114.1
70°	129.6	124.4	120.1	120.1	121.0	121.0	121.0	109.8	98.5	87.3	76.1
72.5°	114.9	111.5	108.0	106.3	104.6	102.0	100.3	90.7	81.2	70.9	61.4
75°	99.4	96.8	94.2	90.7	88.2	84.7	81.2	76.9	73.5	69.1	64.8
77.5°	80.4	78.6	76.1	71.7	68.3	64.0	59.6	59.6	60.5	60.5	60.5
80°	58.8	56.2	54.4	51.9	50.1	47.5	44.9	45.8	46.7	46.7	47.5
82.5°	38.0	36.3	34.6	33.7	32.8	31.1	30.2	30.2	30.2	30.2	30.2
85°	20.7	19.9	18.1	17.3	16.4	14.7	13.8	14.7	15.6	16.4	17.3
87.5°	8.6	7.8	6.9	6.0	6.0	5.2	4.3	5.2	6.0	6.9	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	923.0	923.9	925.6	926.5	928.2	928.2	928.2	928.2	927.3	927.3	926.5
5°	927.3	929.9	931.6	934.2	936.0	936.8	936.8	937.7	937.7	937.7	936.8
7.5°	927.3	929.9	933.4	936.0	938.6	939.4	940.3	941.1	940.3	940.3	939.4
10°	923.9	927.3	930.8	934.2	936.0	936.8	937.7	938.6	937.7	937.7	936.8
12.5°	918.7	922.1	924.7	928.2	929.9	930.8	932.5	933.4	933.4	933.4	932.5
15°	909.2	911.8	915.2	917.8	919.5	921.3	923.9	925.6	925.6	924.7	924.7
17.5°	897.1	900.5	904.0	907.4	910.0	911.8	912.6	914.4	914.4	914.4	913.5
20°	881.5	885.8	889.3	893.6	896.2	897.9	898.8	900.5	900.5	900.5	900.5
22.5°	864.2	868.6	872.9	877.2	878.9	880.6	882.4	884.1	884.1	884.1	884.1
25°	844.4	848.7	852.1	855.6	860.8	862.5	864.2	866.0	866.8	867.7	867.7
27.5°	821.9	826.2	831.4	835.7	839.2	841.8	843.5	846.1	846.9	847.8	847.8
30°	789.9	797.7	804.6	811.5	815.0	818.4	822.7	826.2	827.1	827.1	827.9
32.5°	746.7	759.7	773.5	786.4	794.2	797.7	801.1	804.6	803.7	802.0	801.1
35°	711.3	728.5	745.8	763.1	770.0	772.6	775.2	777.8	776.1	775.2	773.5
37.5°	680.1	700.0	719.0	738.9	744.1	745.8	748.4	750.2	748.4	746.7	744.1
40°	633.5	659.4	684.5	710.4	713.9	715.6	717.3	719.0	717.3	716.4	714.7
42.5°	582.5	615.3	647.3	680.1	684.5	683.6	681.9	681.0	681.9	683.6	684.5
45°	562.6	591.1	618.8	647.3	652.5	650.8	649.0	647.3	649.0	650.8	652.5
47.5°	530.6	559.2	586.8	614.5	614.5	613.6	612.7	611.9	614.5	616.2	618.8
50°	493.5	519.4	544.5	569.5	566.1	570.4	573.8	578.2	580.8	583.4	585.9
52.5°	447.7	469.3	490.0	511.6	524.6	530.6	537.6	543.6	545.3	547.1	547.9
55°	401.0	420.9	439.9	458.9	484.8	491.7	497.8	504.7	506.4	509.0	510.8
57.5°	341.4	364.7	387.2	410.5	443.3	451.1	459.8	467.5	467.5	467.5	466.7
60°	261.9	294.7	326.7	358.7	397.5	406.2	414.0	422.6	421.7	421.7	420.9
62.5°	200.5	233.3	267.0	299.9	344.0	356.1	367.3	379.4	379.4	379.4	378.5
65°	158.2	177.2	195.3	213.5	286.1	303.3	319.8	337.0	337.9	337.9	338.8
67.5°	121.9	129.6	136.5	144.3	238.5	257.5	277.4	296.4	296.4	295.6	295.6
70°	82.1	88.2	94.2	100.3	193.6	214.3	235.9	256.7	255.8	254.9	253.2
72.5°	64.8	67.4	70.9	73.5	150.4	172.0	194.5	216.1	215.2	213.5	212.6
75°	63.1	60.5	58.8	56.2	111.5	133.1	153.8	175.4	174.6	173.7	172.8
77.5°	57.0	52.7	49.3	44.9	82.1	101.1	120.1	139.1	138.3	136.5	135.7
80°	44.1	40.6	37.2	33.7	56.2	70.9	85.6	100.3	100.3	100.3	100.3
82.5°	29.4	27.7	26.8	25.1	35.4	46.7	57.0	68.3	67.4	67.4	66.5
85°	17.3	16.4	16.4	15.6	21.6	26.8	32.0	37.2	38.0	38.0	38.9
87.5°	8.6	8.6	9.5	9.5	12.1	14.7	16.4	19.0	19.0	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	925.6	924.7	923.0	924.7	925.6	927.3	929.9	931.6	933.4	934.2	935.1
5°	936.8	936.0	935.1	936.0	936.8	939.4	941.1	943.7	945.5	946.3	946.3
7.5°	938.6	938.6	937.7	938.6	939.4	942.0	943.7	946.3	948.1	948.9	948.9
10°	936.0	936.0	936.0	937.7	939.4	942.0	943.7	946.3	948.1	948.9	948.9
12.5°	932.5	932.5	931.6	933.4	935.1	937.7	939.4	942.0	943.7	944.6	944.6
15°	923.9	923.9	923.9	925.6	927.3	929.9	932.5	934.2	936.8	937.7	938.6
17.5°	913.5	914.4	914.4	916.1	917.8	920.4	922.1	924.7	926.5	927.3	927.3
20°	900.5	900.5	900.5	903.1	904.8	907.4	909.2	911.8	913.5	914.4	916.1
22.5°	884.1	885.0	885.8	889.3	891.9	893.6	896.2	897.9	899.7	899.7	900.5
25°	868.6	870.3	871.1	872.9	874.6	875.5	876.3	876.3	877.2	877.2	876.3
27.5°	848.7	850.4	852.1	853.0	853.0	853.0	853.9	853.9	853.9	854.7	855.6
30°	827.9	826.2	824.5	825.3	826.2	827.1	828.8	829.7	830.5	831.4	831.4
32.5°	799.4	799.4	798.5	800.3	801.1	802.9	804.6	806.3	808.1	808.1	808.1
35°	771.8	773.5	775.2	776.1	776.1	776.9	778.7	779.5	780.4	781.3	782.1
37.5°	742.4	745.0	747.6	749.3	750.2	751.0	751.9	752.7	753.6	752.7	752.7
40°	713.0	715.6	718.2	719.0	719.9	720.8	720.8	721.6	721.6	720.8	720.8
42.5°	685.3	686.2	687.1	688.8	690.5	689.7	689.7	688.8	687.9	687.1	685.3
45°	654.2	656.0	656.8	656.8	656.8	655.1	653.4	650.8	649.0	648.2	648.2
47.5°	620.5	623.1	624.8	622.2	618.8	617.1	615.3	612.7	611.0	610.1	609.3
50°	588.5	586.8	584.2	581.6	578.2	576.4	575.6	573.8	572.1	568.7	566.1
52.5°	549.6	546.2	542.7	540.1	536.7	534.1	531.5	528.9	526.3	524.6	523.7
55°	512.5	506.4	499.5	496.9	493.5	490.0	485.7	482.2	477.9	477.1	476.2
57.5°	466.7	463.2	458.9	453.7	447.7	444.2	441.6	438.2	434.7	433.8	433.0
60°	420.0	416.6	413.1	407.9	402.7	400.1	396.7	394.1	390.6	389.8	389.8
62.5°	378.5	375.9	372.5	364.7	356.9	355.2	352.6	350.9	348.3	346.6	345.7
65°	338.8	332.7	325.8	320.6	314.6	312.0	310.3	307.7	305.1	303.3	301.6
67.5°	294.7	286.9	278.3	275.7	273.1	270.5	267.0	264.5	261.0	260.1	259.3
70°	252.4	246.3	239.4	236.8	233.3	230.7	228.2	224.7	222.1	220.4	217.8
72.5°	210.9	205.7	199.6	196.2	192.7	190.1	188.4	185.8	183.2	181.5	179.8
75°	172.0	166.8	161.6	158.2	154.7	153.0	151.2	148.6	146.9	144.3	142.6
77.5°	134.0	131.4	127.9	123.6	119.3	118.4	117.5	116.7	115.8	113.2	111.5
80°	100.3	97.7	95.1	92.5	89.0	87.3	86.4	84.7	83.0	82.1	80.4
82.5°	65.7	64.0	62.2	61.4	60.5	59.6	58.8	57.9	57.0	56.2	56.2
85°	38.9	38.9	38.9	38.0	37.2	37.2	37.2	36.3	36.3	35.4	35.4
87.5°	19.9	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	936.0	935.1	936.0	936.0	936.8	936.8	936.0	936.0	935.1	934.2	935.1
5°	947.2	948.1	948.1	948.1	948.1	948.1	948.1	947.2	947.2	946.3	947.2
7.5°	949.8	949.8	950.7	950.7	951.5	951.5	950.7	950.7	949.8	948.9	949.8
10°	949.8	950.7	950.7	951.5	951.5	951.5	950.7	950.7	949.8	948.9	949.8
12.5°	945.5	945.5	946.3	946.3	947.2	947.2	947.2	946.3	946.3	945.5	946.3
15°	939.4	938.6	939.4	939.4	940.3	940.3	939.4	939.4	938.6	937.7	938.6
17.5°	928.2	929.0	929.0	929.9	929.9	929.9	929.0	928.2	927.3	926.5	927.3
20°	916.9	916.9	916.9	917.8	917.8	917.8	916.9	916.9	916.1	915.2	916.1
22.5°	900.5	900.5	900.5	899.7	899.7	898.8	897.9	897.9	897.1	896.2	897.1
25°	876.3	877.2	877.2	877.2	877.2	877.2	876.3	876.3	875.5	874.6	875.5
27.5°	856.5	854.7	855.6	855.6	856.5	856.5	856.5	855.6	855.6	854.7	855.6
30°	832.3	834.0	834.8	834.8	835.7	835.7	835.7	834.8	834.8	834.0	834.8
32.5°	808.1	809.8	809.8	809.8	809.8	809.8	809.8	808.9	808.9	808.1	808.9
35°	783.0	782.1	782.1	783.0	783.0	783.0	782.1	782.1	781.3	780.4	781.3
37.5°	751.9	751.9	751.9	751.9	751.9	751.9	751.0	751.0	750.2	749.3	750.2
40°	719.9	719.0	719.0	719.9	719.9	719.9	719.0	718.2	717.3	716.4	717.3
42.5°	684.5	684.5	684.5	684.5	683.6	683.6	683.6	683.6	682.7	682.7	682.7
45°	647.3	646.4	646.4	645.6	645.6	644.7	644.7	643.9	643.9	643.0	643.9
47.5°	608.4	608.4	607.6	605.8	605.0	603.2	602.4	601.5	599.8	598.9	599.8
50°	562.6	562.6	561.7	560.9	560.0	559.2	559.2	560.0	560.0	560.0	560.0
52.5°	522.0	518.5	517.7	517.7	516.8	515.9	515.9	515.9	515.1	515.1	515.1
55°	475.3	473.6	473.6	473.6	472.7	472.7	473.6	473.6	474.5	474.5	474.5
57.5°	432.1	431.3	431.3	430.4	430.4	429.5	428.7	428.7	427.8	426.9	427.8
60°	388.9	387.2	385.4	383.7	381.1	379.4	378.5	377.7	376.8	375.9	376.8
62.5°	344.0	340.5	339.6	337.9	337.0	335.3	333.6	332.7	331.0	329.3	331.0
65°	299.9	299.0	296.4	293.8	291.2	288.7	287.8	287.8	286.9	286.1	286.9
67.5°	258.4	253.2	251.5	249.8	248.0	246.3	246.3	246.3	246.3	246.3	246.3
70°	216.1	212.6	211.7	210.0	209.1	207.4	207.4	207.4	206.6	206.6	206.6
72.5°	178.0	174.6	173.7	172.8	171.1	170.3	170.3	170.3	169.4	169.4	169.4
75°	140.0	140.9	140.0	139.1	138.3	137.4	137.4	136.5	136.5	135.7	136.5
77.5°	108.9	108.9	108.0	107.2	106.3	105.4	105.4	105.4	105.4	105.4	105.4
80°	79.5	79.5	79.5	79.5	78.6	78.6	78.6	78.6	77.8	77.8	77.8
82.5°	55.3	55.3	55.3	55.3	55.3	55.3	55.3	54.4	54.4	53.6	54.4
85°	34.6	35.4	35.4	35.4	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	21.6	21.6	21.6	22.5	22.5	22.5	22.5	22.5	21.6	21.6	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	936.0	936.0	936.8	936.8	936.0	936.0	935.1	936.0	935.1	934.2	933.4
5°	947.2	948.1	948.1	948.1	948.1	948.1	948.1	947.2	946.3	946.3	945.5
7.5°	950.7	950.7	951.5	951.5	950.7	950.7	949.8	949.8	948.9	948.9	948.1
10°	950.7	950.7	951.5	951.5	951.5	950.7	950.7	949.8	948.9	948.9	948.1
12.5°	946.3	947.2	947.2	947.2	946.3	946.3	945.5	945.5	944.6	944.6	943.7
15°	939.4	939.4	940.3	940.3	939.4	939.4	938.6	939.4	938.6	937.7	936.8
17.5°	928.2	929.0	929.9	929.9	929.9	929.0	929.0	928.2	927.3	927.3	926.5
20°	916.9	916.9	917.8	917.8	917.8	916.9	916.9	916.9	916.1	914.4	913.5
22.5°	897.9	897.9	898.8	899.7	899.7	900.5	900.5	900.5	900.5	899.7	899.7
25°	876.3	876.3	877.2	877.2	877.2	877.2	877.2	876.3	876.3	877.2	877.2
27.5°	855.6	856.5	856.5	856.5	855.6	855.6	854.7	856.5	855.6	854.7	853.9
30°	834.8	835.7	835.7	835.7	834.8	834.8	834.0	832.3	831.4	831.4	830.5
32.5°	808.9	809.8	809.8	809.8	809.8	809.8	809.8	808.1	808.1	808.1	808.1
35°	782.1	782.1	783.0	783.0	783.0	782.1	782.1	783.0	782.1	781.3	780.4
37.5°	751.0	751.0	751.9	751.9	751.9	751.9	751.9	751.9	752.7	752.7	753.6
40°	718.2	719.0	719.9	719.9	719.9	719.0	719.0	719.9	720.8	720.8	721.6
42.5°	683.6	683.6	683.6	683.6	684.5	684.5	684.5	684.5	685.3	687.1	687.9
45°	643.9	644.7	644.7	645.6	645.6	646.4	646.4	647.3	648.2	648.2	649.0
47.5°	601.5	602.4	603.2	605.0	605.8	607.6	608.4	608.4	609.3	610.1	611.0
50°	560.0	559.2	559.2	560.0	560.9	561.7	562.6	562.6	566.1	568.7	572.1
52.5°	515.9	515.9	515.9	516.8	517.7	517.7	518.5	522.0	523.7	524.6	526.3
55°	473.6	473.6	472.7	472.7	473.6	473.6	473.6	475.3	476.2	477.1	477.9
57.5°	428.7	428.7	429.5	430.4	430.4	431.3	431.3	432.1	433.0	433.8	434.7
60°	377.7	378.5	379.4	381.1	383.7	385.4	387.2	388.9	389.8	389.8	390.6
62.5°	332.7	333.6	335.3	337.0	337.9	339.6	340.5	344.0	345.7	346.6	348.3
65°	287.8	287.8	288.7	291.2	293.8	296.4	299.0	299.9	301.6	303.3	305.1
67.5°	246.3	246.3	246.3	248.0	249.8	251.5	253.2	258.4	259.3	260.1	261.0
70°	207.4	207.4	207.4	209.1	210.0	211.7	212.6	216.1	217.8	220.4	222.1
72.5°	170.3	170.3	170.3	171.1	172.8	173.7	174.6	178.0	179.8	181.5	183.2
75°	136.5	137.4	137.4	138.3	139.1	140.0	140.9	140.0	142.6	144.3	146.9
77.5°	105.4	105.4	105.4	106.3	107.2	108.0	108.9	108.9	111.5	113.2	115.8
80°	78.6	78.6	78.6	78.6	79.5	79.5	79.5	79.5	80.4	82.1	83.0
82.5°	54.4	55.3	55.3	55.3	55.3	55.3	55.3	55.3	56.2	56.2	57.0
85°	34.6	34.6	34.6	34.6	35.4	35.4	35.4	34.6	35.4	35.4	36.3
87.5°	22.5	22.5	22.5	22.5	22.5	21.6	21.6	21.6	21.6	20.7	20.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	931.6	929.9	927.3	925.6	924.7	923.0	924.7	925.6	926.5	927.3	927.3
5°	943.7	941.1	939.4	936.8	936.0	935.1	936.0	936.8	936.8	937.7	937.7
7.5°	946.3	943.7	942.0	939.4	938.6	937.7	938.6	938.6	939.4	940.3	940.3
10°	946.3	943.7	942.0	939.4	937.7	936.0	936.0	936.0	936.8	937.7	937.7
12.5°	942.0	939.4	937.7	935.1	933.4	931.6	932.5	932.5	932.5	933.4	933.4
15°	934.2	932.5	929.9	927.3	925.6	923.9	923.9	923.9	924.7	924.7	925.6
17.5°	924.7	922.1	920.4	917.8	916.1	914.4	914.4	913.5	913.5	914.4	914.4
20°	911.8	909.2	907.4	904.8	903.1	900.5	900.5	900.5	900.5	900.5	900.5
22.5°	897.9	896.2	893.6	891.9	888.4	885.8	885.0	884.1	884.1	884.1	884.1
25°	876.3	876.3	875.5	874.6	872.9	871.1	870.3	868.6	867.7	867.7	866.8
27.5°	853.9	853.9	853.0	853.0	853.0	852.1	850.4	848.7	847.8	847.8	846.9
30°	829.7	828.8	827.1	826.2	825.3	824.5	826.2	827.9	827.9	827.1	827.1
32.5°	806.3	804.6	802.9	801.1	800.3	798.5	799.4	799.4	801.1	802.0	803.7
35°	779.5	778.7	776.9	776.1	776.1	775.2	773.5	771.8	773.5	775.2	776.1
37.5°	752.7	751.9	751.0	750.2	749.3	747.6	745.0	742.4	744.1	745.8	748.4
40°	721.6	720.8	720.8	719.9	719.0	718.2	715.6	713.0	714.7	716.4	717.3
42.5°	688.8	689.7	689.7	690.5	688.8	687.1	686.2	685.3	684.5	683.6	681.9
45°	650.8	653.4	655.1	656.8	656.8	656.8	656.0	654.2	652.5	650.8	649.0
47.5°	612.7	615.3	617.1	618.8	622.2	624.8	623.1	620.5	618.8	616.2	614.5
50°	573.8	575.6	576.4	578.2	581.6	584.2	586.8	588.5	585.9	583.4	580.8
52.5°	528.9	531.5	534.1	536.7	540.1	542.7	546.2	549.6	547.9	547.1	545.3
55°	482.2	485.7	490.0	493.5	496.9	499.5	506.4	512.5	510.8	509.0	506.4
57.5°	438.2	440.8	444.2	447.7	453.7	458.9	463.2	466.7	466.7	467.5	467.5
60°	394.1	396.7	400.1	402.7	407.9	413.1	416.6	420.0	420.9	421.7	421.7
62.5°	350.9	352.6	355.2	356.9	364.7	372.5	375.9	378.5	378.5	379.4	379.4
65°	307.7	310.3	312.0	314.6	320.6	325.8	332.7	338.8	338.8	337.9	337.9
67.5°	264.5	267.0	270.5	273.1	275.7	278.3	286.9	294.7	295.6	295.6	296.4
70°	224.7	228.2	230.7	233.3	236.8	239.4	246.3	252.4	253.2	254.9	255.8
72.5°	185.8	188.4	190.1	192.7	196.2	199.6	205.7	210.9	212.6	213.5	215.2
75°	148.6	151.2	153.0	154.7	158.2	161.6	166.8	172.0	172.8	173.7	174.6
77.5°	116.7	117.5	118.4	119.3	123.6	127.9	131.4	134.0	135.7	136.5	138.3
80°	84.7	86.4	87.3	89.0	92.5	95.1	97.7	100.3	100.3	100.3	100.3
82.5°	57.9	58.8	59.6	60.5	61.4	62.2	64.0	65.7	66.5	67.4	67.4
85°	36.3	37.2	37.2	37.2	38.0	38.9	38.9	38.9	38.9	38.0	38.0
87.5°	20.7	20.7	20.7	20.7	20.7	20.7	20.7	19.9	19.9	19.9	19.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5	913.5
2.5°	928.2	928.2	928.2	928.2	926.5	925.6	923.9	923.0	921.3	921.3	921.3
5°	937.7	936.8	936.8	936.0	934.2	931.6	929.0	927.3	924.7	923.0	921.3
7.5°	941.1	940.3	939.4	938.6	936.0	933.4	929.9	927.3	923.9	920.4	916.9
10°	938.6	937.7	936.8	936.0	934.2	930.8	927.3	923.9	920.4	916.1	910.9
12.5°	933.4	932.5	930.8	929.9	928.2	924.7	921.3	918.7	915.2	909.2	902.3
15°	925.6	923.9	921.3	919.5	917.8	915.2	911.8	909.2	905.7	898.8	891.0
17.5°	914.4	912.6	911.8	910.0	907.4	904.0	900.5	897.1	893.6	885.0	875.5
20°	900.5	898.8	897.9	896.2	893.6	889.3	885.0	881.5	877.2	866.8	856.5
22.5°	884.1	882.4	880.6	878.9	877.2	872.9	868.6	864.2	859.9	846.9	833.1
25°	866.0	864.2	862.5	860.8	855.6	852.1	847.8	844.4	840.9	823.6	806.3
27.5°	846.1	843.5	841.8	839.2	835.7	831.4	826.2	821.9	816.7	796.8	776.1
30°	826.2	822.7	818.4	815.0	811.5	804.6	796.8	789.9	783.0	761.4	738.9
32.5°	804.6	801.1	797.7	794.2	786.4	773.5	759.7	746.7	732.9	712.1	690.5
35°	777.8	775.2	772.6	770.0	763.1	745.8	728.5	711.3	694.0	667.2	640.4
37.5°	750.2	748.4	745.8	744.1	738.9	719.0	699.2	680.1	660.3	624.8	589.4
40°	719.0	717.3	715.6	713.9	710.4	684.5	658.5	633.5	607.6	570.4	532.4
42.5°	681.0	681.9	683.6	684.5	680.1	647.3	614.5	582.5	549.6	515.9	481.4
45°	647.3	649.0	650.8	652.5	647.3	618.8	590.3	562.6	534.1	495.2	456.3
47.5°	611.9	612.7	613.6	614.5	614.5	586.8	558.3	530.6	503.0	469.3	434.7
50°	578.2	573.8	570.4	566.1	569.5	544.5	518.5	493.5	468.4	443.3	417.4
52.5°	543.6	537.6	530.6	524.6	511.6	490.0	468.4	447.7	426.1	402.7	379.4
55°	504.7	497.8	491.7	484.8	458.9	439.9	420.0	401.0	382.0	363.8	344.8
57.5°	467.5	459.8	451.1	443.3	410.5	387.2	363.8	341.4	318.0	314.6	310.3
60°	422.6	414.0	406.2	397.5	358.7	326.7	293.8	261.9	229.9	242.0	254.1
62.5°	379.4	367.3	356.1	344.0	299.9	267.0	233.3	200.5	166.8	188.4	210.0
65°	337.0	319.8	303.3	286.1	213.5	195.3	176.3	158.2	140.0	159.0	177.2
67.5°	296.4	277.4	257.5	238.5	144.3	136.5	128.8	121.9	114.1	126.2	139.1
70°	256.7	235.9	214.3	193.6	100.3	94.2	88.2	82.1	76.1	87.3	98.5
72.5°	216.1	194.5	172.0	150.4	73.5	70.9	67.4	64.8	61.4	70.9	81.2
75°	175.4	153.8	133.1	111.5	56.2	58.8	60.5	63.1	64.8	69.1	73.5
77.5°	139.1	120.1	101.1	82.1	44.9	49.3	52.7	57.0	60.5	60.5	60.5
80°	100.3	85.6	70.9	56.2	33.7	37.2	40.6	44.1	47.5	46.7	46.7
82.5°	68.3	57.0	46.7	35.4	25.1	26.8	27.7	29.4	30.2	30.2	30.2
85°	37.2	32.0	26.8	21.6	15.6	16.4	16.4	17.3	17.3	16.4	15.6
87.5°	19.0	16.4	14.7	12.1	9.5	9.5	8.6	8.6	7.8	6.9	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	913.5	913.5
2.5°	921.3	921.3
5°	919.5	917.8
7.5°	914.4	910.9
10°	906.6	902.3
12.5°	896.2	890.2
15°	884.1	876.3
17.5°	866.8	857.3
20°	846.1	835.7
22.5°	820.2	806.3
25°	789.0	771.8
27.5°	756.2	735.5
30°	717.3	694.8
32.5°	669.8	649.0
35°	613.6	586.8
37.5°	554.0	518.5
40°	495.2	458.0
42.5°	447.7	413.1
45°	417.4	378.5
47.5°	401.0	367.3
50°	392.4	366.4
52.5°	356.1	332.7
55°	326.7	308.5
57.5°	306.8	303.3
60°	266.2	278.3
62.5°	230.7	252.4
65°	196.2	214.3
67.5°	151.2	163.3
70°	109.8	121.0
72.5°	90.7	100.3
75°	76.9	81.2
77.5°	59.6	59.6
80°	45.8	44.9
82.5°	30.2	30.2
85°	14.7	13.8
87.5°	5.2	4.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055041

CATALOG NUMBER: SQ4R-FA-075D-935-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.65	19.26	18.01	19.57	19.89	19.56	21.17	19.93	21.49	21.80
	3H	18.31	19.76	18.69	20.09	20.45	21.36	22.81	21.74	23.14	23.50
	4H	18.64	20.01	19.04	20.36	20.73	21.98	23.35	22.38	23.69	24.07
	6H	18.93	20.20	19.34	20.56	20.95	22.36	23.63	22.78	23.99	24.39
	8H	19.01	20.22	19.43	20.61	21.01	22.46	23.67	22.88	24.06	24.46
	12H	19.04	20.20	19.47	20.58	21.01	22.51	23.66	22.94	24.05	24.47
4H	2H	18.78	20.14	19.17	20.49	20.87	20.13	21.50	20.53	21.85	22.22
	3H	20.10	21.24	20.51	21.64	22.04	22.16	23.30	22.57	23.70	24.10
	4H	20.53	21.56	20.96	21.97	22.41	22.90	23.93	23.33	24.34	24.78
	6H	20.82	21.72	21.28	22.16	22.62	23.40	24.29	23.85	24.74	25.19
	8H	20.90	21.74	21.36	22.18	22.65	23.52	24.36	23.98	24.81	25.27
	12H	20.94	21.70	21.42	22.17	22.64	23.60	24.35	24.08	24.83	25.30
8H	4H	21.12	21.96	21.58	22.40	22.87	23.13	23.97	23.59	24.41	24.88
	6H	21.60	22.30	22.09	22.79	23.26	23.73	24.42	24.22	24.91	25.39
	8H	21.73	22.35	22.24	22.86	23.35	23.90	24.53	24.41	25.04	25.52
	12H	21.80	22.35	22.31	22.84	23.41	24.03	24.58	24.53	25.07	25.63
12H	4H	21.17	21.92	21.65	22.40	22.87	23.14	23.89	23.62	24.37	24.83
	6H	21.70	22.33	22.21	22.83	23.32	23.74	24.37	24.25	24.88	25.36
	8H	21.90	22.46	22.41	22.95	23.51	23.97	24.52	24.48	25.01	25.57

END OF REPORT