

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055055

Luminaire Tested: SQ4R-FA-125D-935-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-125D-935-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3965.3 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	81	73	66	88	79	72	66	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14720	14720	14720	14720
5°	14847	12037	14847	15308
10°	14764	11101	14764	15527
15°	14620	13063	14620	15643
20°	14331	13487	14331	15695
25°	13722	13615	13722	15550
30°	12929	13396	12929	15518
35°	11544	13108	11544	15353
40°	9636	13016	9636	15071
45°	8627	12861	8627	14654
50°	9186	12740	9186	14040
55°	8668	13015	8668	13330
60°	8969	12756	8969	12117
65°	8174	12192	8174	10907
70°	5700	11442	5700	9731
75°	5059	10118	5059	8447
80°	4169	7862	4169	7219
85°	2552	5435	2552	6396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 14968 cd/sqm

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.5
10°-20°	391.9	9.9
20°-30°	605.8	15.3
30°-40°	723.2	18.2
40°-50°	727.5	18.3
50°-60°	633.0	16.0
60°-70°	448.9	11.3
70°-80°	237.6	6.0
80°-90°	59.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.8	28.6
0°-40°	1859.1	46.9
0°-60°	3219.6	81.2
0°-90°	3965.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3965.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1529	1529	1529	1529	1529	
5°	1536	1246	1536	1584	1536	146
15°	1467	1311	1467	1570	1467	413
25°	1292	1282	1292	1464	1292	593
35°	982	1115	982	1306	982	608
45°	634	945	634	1076	634	508
55°	516	775	516	794	516	475
65°	359	535	359	479	359	343
75°	136	272	136	227	136	143
85°	23	49	23	58	23	31
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1542.1	1539.2	1534.8	1531.9	1527.6	1526.1	1524.7	1523.2	1521.8	1517.5	1514.6
5°	1536.3	1530.5	1523.2	1517.5	1510.2	1504.4	1500.1	1494.3	1488.5	1479.8	1471.2
7.5°	1524.7	1514.6	1504.4	1494.3	1484.2	1471.2	1458.2	1445.1	1432.1	1409.0	1381.5
10°	1510.2	1495.8	1479.8	1465.4	1449.5	1419.1	1388.7	1356.9	1326.5	1286.0	1258.5
12.5°	1490.0	1465.4	1439.3	1414.8	1388.7	1345.3	1303.4	1260.0	1216.6	1189.1	1173.2
15°	1466.8	1427.8	1387.3	1348.2	1307.7	1270.1	1232.5	1193.4	1155.8	1135.6	1124.0
17.5°	1435.0	1382.9	1332.3	1280.2	1228.1	1199.2	1168.8	1139.9	1109.5	1095.1	1086.4
20°	1398.8	1342.4	1284.6	1228.1	1170.3	1147.1	1124.0	1099.4	1076.3	1063.2	1058.9
22.5°	1349.7	1294.7	1239.7	1184.7	1129.8	1108.1	1086.4	1063.2	1041.5	1031.4	1034.3
25°	1291.8	1244.1	1194.9	1147.1	1098.0	1077.7	1056.0	1035.7	1014.1	1002.5	1011.2
27.5°	1231.0	1190.5	1150.0	1109.5	1069.0	1047.3	1025.6	1002.5	980.8	976.4	996.7
30°	1163.0	1132.7	1100.8	1070.5	1038.6	1015.5	992.4	969.2	946.1	944.6	976.4
32.5°	1086.4	1064.7	1044.4	1022.7	1001.0	979.3	957.6	934.5	912.8	911.3	950.4
35°	982.2	976.4	970.7	963.4	957.6	935.9	914.2	892.5	870.8	872.3	915.7
37.5°	867.9	878.1	889.6	899.8	909.9	889.6	870.8	850.6	830.3	830.3	876.6
40°	766.7	786.9	807.2	827.4	847.7	834.7	820.2	807.2	792.7	788.4	836.1
42.5°	691.5	710.3	729.1	746.4	765.2	760.9	758.0	753.7	749.3	743.5	789.8
45°	633.6	636.5	640.8	643.7	646.6	661.1	675.6	690.0	704.5	700.1	742.1
47.5°	614.8	596.0	575.7	556.9	536.7	567.1	597.4	626.4	656.7	655.3	692.9
50°	613.3	575.7	536.7	499.1	460.0	496.2	532.3	567.1	603.2	609.0	637.9
52.5°	556.9	522.2	487.5	451.3	416.6	448.4	478.8	510.6	541.0	558.4	584.4
55°	516.4	483.2	449.9	416.6	383.3	405.0	425.3	447.0	467.2	504.9	528.0
57.5°	507.7	467.2	426.7	384.8	344.3	358.8	371.8	386.2	399.3	435.4	464.4
60°	465.8	425.3	384.8	342.8	302.3	312.5	321.1	331.3	339.9	367.4	402.1
62.5°	422.4	384.8	348.6	311.0	273.4	283.5	292.2	302.3	311.0	316.8	354.4
65°	358.8	331.3	303.8	276.3	248.8	257.5	264.7	273.4	280.6	282.1	316.8
67.5°	273.4	261.8	250.3	237.2	225.7	234.3	241.6	250.3	257.5	258.9	287.9
70°	202.5	202.5	202.5	201.1	201.1	208.3	217.0	224.2	231.5	234.3	256.0
72.5°	167.8	170.7	175.0	177.9	180.8	186.6	192.4	198.2	204.0	206.9	222.8
75°	136.0	141.8	147.6	151.9	157.7	162.0	166.4	169.2	173.6	175.0	186.6
77.5°	99.8	107.0	114.3	120.1	127.3	131.6	134.5	138.9	141.8	138.9	147.6
80°	75.2	79.6	83.9	86.8	91.1	94.0	98.4	101.3	104.2	101.3	107.0
82.5°	50.6	52.1	55.0	56.4	57.9	60.8	63.6	66.5	69.4	66.5	70.9
85°	23.1	24.6	27.5	28.9	30.4	33.3	34.7	37.6	39.1	37.6	39.1
87.5°	7.2	8.7	10.1	10.1	11.6	13.0	14.5	15.9	17.4	17.4	18.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1513.1	1510.2	1504.4	1500.1	1494.3	1488.5	1485.6	1482.7	1479.8	1477.0	1479.8
5°	1461.0	1452.4	1439.3	1426.3	1413.3	1400.3	1382.9	1365.6	1352.6	1339.5	1336.6
7.5°	1352.6	1325.1	1301.9	1277.3	1254.2	1229.6	1216.6	1203.6	1192.0	1180.4	1177.5
10°	1229.6	1202.1	1186.2	1171.7	1155.8	1139.9	1132.7	1124.0	1122.5	1119.7	1121.1
12.5°	1155.8	1139.9	1131.2	1122.5	1112.4	1103.7	1102.3	1100.8	1105.2	1108.1	1118.2
15°	1112.4	1100.8	1098.0	1095.1	1090.7	1087.8	1096.5	1103.7	1129.8	1154.4	1183.3
17.5°	1079.1	1070.5	1077.7	1083.5	1090.7	1096.5	1141.3	1186.2	1220.9	1254.2	1264.3
20°	1056.0	1051.7	1080.6	1111.0	1139.9	1168.8	1203.6	1236.8	1249.8	1261.4	1267.2
22.5°	1035.7	1038.6	1082.0	1124.0	1167.4	1209.3	1223.8	1236.8	1245.5	1254.2	1258.5
25°	1021.3	1030.0	1073.4	1118.2	1161.6	1205.0	1213.7	1220.9	1223.8	1225.3	1235.4
27.5°	1016.9	1037.2	1074.8	1112.4	1148.6	1186.2	1192.0	1197.8	1200.7	1202.1	1212.2
30°	1006.8	1038.6	1070.5	1100.8	1132.7	1163.0	1161.6	1160.2	1165.9	1171.7	1181.9
32.5°	989.5	1028.5	1053.1	1079.1	1103.7	1128.3	1126.9	1125.4	1134.1	1141.3	1148.6
35°	960.5	1003.9	1025.6	1045.9	1067.6	1087.8	1089.3	1089.3	1096.5	1103.7	1108.1
37.5°	924.4	970.7	990.9	1011.2	1030.0	1050.2	1048.8	1047.3	1050.2	1051.7	1058.9
40°	882.4	930.1	950.4	970.7	989.5	1009.7	1005.4	999.6	999.6	998.1	1006.8
42.5°	834.7	881.0	901.2	921.5	940.3	960.5	951.8	941.7	944.6	946.1	957.6
45°	785.5	827.4	846.2	866.5	885.3	904.1	898.3	891.1	896.9	902.7	914.2
47.5°	730.5	768.1	788.4	808.6	828.9	849.1	846.2	841.9	847.7	853.5	866.5
50°	668.3	697.3	721.8	746.4	771.0	795.6	795.6	795.6	801.4	805.7	818.8
52.5°	609.0	635.0	664.0	692.9	720.4	749.3	750.8	752.2	758.0	762.3	773.9
55°	551.1	574.3	606.1	637.9	669.8	701.6	704.5	707.4	713.2	717.5	729.1
57.5°	491.8	520.8	554.0	588.8	622.0	655.3	656.7	658.2	662.5	666.9	677.0
60°	436.9	471.6	503.4	536.7	568.5	600.3	606.1	610.5	613.3	616.2	624.9
62.5°	393.5	431.1	460.0	490.4	519.3	548.3	555.5	561.3	564.2	565.6	571.4
65°	353.0	387.7	415.2	441.2	468.7	494.7	500.5	506.3	510.6	513.5	517.9
67.5°	316.8	345.7	367.4	389.1	410.8	432.5	441.2	448.4	451.3	454.2	457.1
70°	279.2	300.9	319.7	338.5	357.3	376.1	383.3	390.6	393.5	394.9	396.4
72.5°	238.7	254.6	269.1	283.5	298.0	312.5	319.7	326.9	329.8	331.3	332.7
75°	196.7	208.3	219.9	231.5	243.0	254.6	260.4	264.7	266.2	267.6	267.6
77.5°	154.8	163.5	172.1	180.8	188.1	196.7	201.1	205.4	205.4	205.4	205.4
80°	111.4	117.2	123.0	128.7	134.5	140.3	141.8	143.2	144.7	146.1	146.1
82.5°	73.8	78.1	81.0	85.3	88.2	91.1	91.1	91.1	91.1	91.1	92.6
85°	42.0	43.4	44.8	46.3	47.7	49.2	50.6	50.6	50.6	50.6	50.6
87.5°	18.8	20.3	20.3	21.7	21.7	21.7	21.7	20.3	20.3	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1481.3	1484.2	1485.6	1482.7	1478.4	1475.5	1471.2	1472.6	1474.1	1475.5	1477.0
5°	1332.3	1329.4	1325.1	1314.9	1304.8	1294.7	1287.5	1281.7	1275.9	1270.1	1264.3
7.5°	1173.2	1170.3	1165.9	1163.0	1160.2	1157.3	1151.5	1150.0	1148.6	1147.1	1145.7
10°	1122.5	1122.5	1124.0	1125.4	1125.4	1126.9	1128.3	1131.2	1132.7	1135.6	1137.0
12.5°	1128.3	1137.0	1147.1	1165.9	1186.2	1205.0	1218.0	1229.6	1242.6	1254.2	1265.8
15°	1213.7	1242.6	1271.5	1278.8	1287.5	1294.7	1299.0	1301.9	1304.8	1306.3	1309.2
17.5°	1274.4	1283.1	1293.2	1296.1	1300.5	1303.4	1304.8	1306.3	1309.2	1310.6	1312.0
20°	1273.0	1277.3	1283.1	1287.5	1291.8	1296.1	1299.0	1303.4	1306.3	1310.6	1313.5
22.5°	1264.3	1268.6	1273.0	1280.2	1286.0	1293.2	1299.0	1301.9	1304.8	1307.7	1310.6
25°	1244.1	1254.2	1262.9	1268.6	1273.0	1278.8	1278.8	1278.8	1280.2	1280.2	1280.2
27.5°	1222.4	1232.5	1242.6	1244.1	1247.0	1248.4	1251.3	1254.2	1255.6	1258.5	1260.0
30°	1192.0	1202.1	1212.2	1215.1	1218.0	1220.9	1218.0	1216.6	1215.1	1212.2	1210.8
32.5°	1157.3	1164.5	1171.7	1173.2	1173.2	1174.6	1167.4	1165.9	1164.5	1161.6	1160.2
35°	1113.9	1118.2	1122.5	1121.1	1121.1	1119.7	1121.1	1121.1	1121.1	1119.7	1119.7
37.5°	1064.7	1071.9	1077.7	1079.1	1079.1	1080.6	1083.5	1083.5	1083.5	1082.0	1082.0
40°	1016.9	1025.6	1034.3	1035.7	1038.6	1040.1	1041.5	1041.5	1041.5	1040.1	1040.1
42.5°	969.2	980.8	992.4	995.2	998.1	1001.0	999.6	998.1	998.1	996.7	995.2
45°	927.3	938.8	950.4	951.8	954.7	956.2	957.6	956.2	953.3	951.8	949.0
47.5°	879.5	891.1	904.1	907.0	908.5	911.3	911.3	909.9	908.5	905.6	904.1
50°	833.2	846.2	859.3	860.7	862.2	863.6	862.2	859.3	857.8	854.9	852.0
52.5°	786.9	798.5	810.1	810.1	808.6	808.6	808.6	808.6	810.1	810.1	810.1
55°	739.2	750.8	760.9	760.9	760.9	760.9	762.3	765.2	768.1	769.6	772.5
57.5°	688.6	698.7	708.8	710.3	710.3	711.7	711.7	713.2	716.1	717.5	718.9
60°	635.0	643.7	652.4	653.9	653.9	655.3	658.2	659.6	661.1	662.5	664.0
62.5°	577.2	581.5	587.3	590.2	593.1	596.0	598.9	598.9	600.3	600.3	600.3
65°	522.2	525.1	529.4	530.9	532.3	533.8	536.7	536.7	538.1	538.1	538.1
67.5°	460.0	461.5	464.4	465.8	468.7	470.1	468.7	468.7	468.7	467.2	467.2
70°	397.8	399.3	400.7	402.1	403.6	405.0	405.0	405.0	405.0	403.6	403.6
72.5°	332.7	334.2	334.2	334.2	335.6	335.6	334.2	335.6	337.1	338.5	339.9
75°	269.1	269.1	269.1	269.1	267.6	267.6	270.5	270.5	269.1	269.1	267.6
77.5°	205.4	205.4	205.4	205.4	204.0	204.0	206.9	206.9	205.4	205.4	204.0
80°	146.1	144.7	144.7	144.7	144.7	144.7	143.2	143.2	143.2	143.2	143.2
82.5°	92.6	94.0	94.0	94.0	92.6	92.6	91.1	91.1	91.1	91.1	91.1
85°	49.2	49.2	47.7	49.2	49.2	50.6	52.1	52.1	50.6	50.6	49.2
87.5°	20.3	20.3	20.3	20.3	18.8	18.8	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1472.6	1469.7	1465.4	1461.0	1465.4	1469.7	1472.6	1477.0	1475.5	1474.1	1472.6
5°	1260.0	1255.6	1249.8	1245.5	1249.8	1255.6	1260.0	1264.3	1270.1	1275.9	1281.7
7.5°	1142.8	1139.9	1137.0	1134.1	1137.0	1139.9	1142.8	1145.7	1147.1	1148.6	1150.0
10°	1137.0	1137.0	1135.6	1135.6	1135.6	1137.0	1137.0	1137.0	1135.6	1132.7	1131.2
12.5°	1265.8	1264.3	1264.3	1262.9	1264.3	1264.3	1265.8	1265.8	1254.2	1242.6	1229.6
15°	1309.2	1310.6	1310.6	1310.6	1310.6	1310.6	1309.2	1309.2	1306.3	1304.8	1301.9
17.5°	1312.0	1312.0	1312.0	1312.0	1312.0	1312.0	1312.0	1312.0	1310.6	1309.2	1306.3
20°	1314.9	1314.9	1316.4	1316.4	1316.4	1314.9	1314.9	1313.5	1310.6	1306.3	1303.4
22.5°	1310.6	1310.6	1309.2	1309.2	1309.2	1310.6	1310.6	1310.6	1307.7	1304.8	1301.9
25°	1280.2	1281.7	1281.7	1281.7	1281.7	1281.7	1280.2	1280.2	1280.2	1280.2	1278.8
27.5°	1260.0	1260.0	1258.5	1258.5	1258.5	1260.0	1260.0	1260.0	1258.5	1255.6	1254.2
30°	1209.3	1207.9	1206.4	1205.0	1206.4	1207.9	1209.3	1210.8	1212.2	1215.1	1216.6
32.5°	1158.7	1158.7	1157.3	1155.8	1157.3	1158.7	1158.7	1160.2	1161.6	1164.5	1165.9
35°	1118.2	1118.2	1116.8	1115.3	1116.8	1118.2	1118.2	1119.7	1119.7	1121.1	1121.1
37.5°	1080.6	1079.1	1077.7	1076.3	1077.7	1079.1	1080.6	1082.0	1082.0	1083.5	1083.5
40°	1038.6	1038.6	1037.2	1035.7	1037.2	1038.6	1038.6	1040.1	1040.1	1041.5	1041.5
42.5°	995.2	993.8	993.8	992.4	993.8	993.8	995.2	995.2	996.7	998.1	998.1
45°	947.5	947.5	946.1	944.6	946.1	947.5	947.5	949.0	951.8	953.3	956.2
47.5°	902.7	902.7	901.2	899.8	901.2	902.7	902.7	904.1	905.6	908.5	909.9
50°	852.0	852.0	850.6	850.6	850.6	852.0	852.0	852.0	854.9	857.8	859.3
52.5°	811.5	811.5	813.0	813.0	813.0	811.5	811.5	810.1	810.1	810.1	808.6
55°	773.9	773.9	775.4	775.4	775.4	773.9	773.9	772.5	769.6	768.1	765.2
57.5°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	717.5	716.1	713.2
60°	664.0	664.0	662.5	662.5	662.5	664.0	664.0	664.0	662.5	661.1	659.6
62.5°	600.3	598.9	598.9	597.4	598.9	598.9	600.3	600.3	600.3	600.3	598.9
65°	538.1	536.7	536.7	535.2	536.7	536.7	538.1	538.1	538.1	538.1	536.7
67.5°	468.7	470.1	471.6	473.0	471.6	470.1	468.7	467.2	467.2	468.7	468.7
70°	405.0	405.0	406.5	406.5	406.5	405.0	405.0	403.6	403.6	405.0	405.0
72.5°	338.5	338.5	337.1	335.6	337.1	338.5	338.5	339.9	338.5	337.1	335.6
75°	269.1	270.5	270.5	272.0	270.5	270.5	269.1	267.6	269.1	269.1	270.5
77.5°	204.0	204.0	204.0	204.0	204.0	204.0	204.0	204.0	205.4	205.4	206.9
80°	143.2	143.2	141.8	141.8	141.8	143.2	143.2	143.2	143.2	143.2	143.2
82.5°	92.6	92.6	94.0	94.0	94.0	92.6	92.6	91.1	91.1	91.1	91.1
85°	49.2	49.2	49.2	49.2	49.2	49.2	49.2	49.2	50.6	50.6	52.1
87.5°	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1471.2	1475.5	1478.4	1482.7	1485.6	1484.2	1481.3	1479.8	1477.0	1479.8	1482.7
5°	1287.5	1294.7	1304.8	1314.9	1325.1	1329.4	1332.3	1336.6	1339.5	1352.6	1365.6
7.5°	1151.5	1157.3	1160.2	1163.0	1165.9	1170.3	1173.2	1177.5	1180.4	1192.0	1203.6
10°	1128.3	1126.9	1125.4	1125.4	1124.0	1122.5	1122.5	1121.1	1119.7	1122.5	1124.0
12.5°	1218.0	1205.0	1186.2	1165.9	1147.1	1137.0	1128.3	1118.2	1108.1	1105.2	1100.8
15°	1299.0	1294.7	1287.5	1278.8	1271.5	1242.6	1213.7	1183.3	1154.4	1129.8	1103.7
17.5°	1304.8	1303.4	1300.5	1296.1	1293.2	1283.1	1274.4	1264.3	1254.2	1220.9	1186.2
20°	1299.0	1296.1	1291.8	1287.5	1283.1	1277.3	1273.0	1267.2	1261.4	1249.8	1236.8
22.5°	1299.0	1293.2	1286.0	1280.2	1273.0	1268.6	1264.3	1258.5	1254.2	1245.5	1236.8
25°	1278.8	1278.8	1273.0	1268.6	1262.9	1254.2	1244.1	1235.4	1225.3	1223.8	1220.9
27.5°	1251.3	1248.4	1247.0	1244.1	1242.6	1232.5	1222.4	1212.2	1202.1	1200.7	1197.8
30°	1218.0	1220.9	1218.0	1215.1	1212.2	1202.1	1192.0	1181.9	1171.7	1165.9	1160.2
32.5°	1167.4	1174.6	1173.2	1173.2	1171.7	1164.5	1157.3	1148.6	1141.3	1134.1	1125.4
35°	1121.1	1119.7	1121.1	1121.1	1122.5	1118.2	1113.9	1108.1	1103.7	1096.5	1089.3
37.5°	1083.5	1080.6	1079.1	1079.1	1077.7	1071.9	1064.7	1058.9	1051.7	1050.2	1047.3
40°	1041.5	1040.1	1038.6	1035.7	1034.3	1025.6	1016.9	1006.8	998.1	999.6	999.6
42.5°	999.6	1001.0	998.1	995.2	992.4	980.8	969.2	957.6	946.1	944.6	941.7
45°	957.6	956.2	954.7	951.8	950.4	938.8	927.3	914.2	902.7	896.9	891.1
47.5°	911.3	911.3	908.5	907.0	904.1	891.1	879.5	866.5	853.5	847.7	841.9
50°	862.2	863.6	862.2	860.7	859.3	846.2	833.2	818.8	805.7	801.4	795.6
52.5°	808.6	808.6	808.6	810.1	810.1	798.5	786.9	773.9	762.3	758.0	752.2
55°	762.3	760.9	760.9	760.9	760.9	750.8	739.2	729.1	717.5	713.2	707.4
57.5°	711.7	711.7	710.3	710.3	708.8	698.7	688.6	677.0	666.9	662.5	658.2
60°	658.2	655.3	653.9	653.9	652.4	643.7	635.0	624.9	616.2	613.3	610.5
62.5°	598.9	596.0	593.1	590.2	587.3	581.5	577.2	571.4	565.6	564.2	561.3
65°	536.7	533.8	532.3	530.9	529.4	525.1	522.2	517.9	513.5	510.6	506.3
67.5°	468.7	470.1	468.7	465.8	464.4	461.5	460.0	457.1	454.2	451.3	448.4
70°	405.0	405.0	403.6	402.1	400.7	399.3	397.8	396.4	394.9	393.5	390.6
72.5°	334.2	335.6	335.6	334.2	334.2	334.2	332.7	332.7	331.3	329.8	326.9
75°	270.5	267.6	267.6	269.1	269.1	269.1	269.1	267.6	267.6	266.2	264.7
77.5°	206.9	204.0	204.0	205.4	205.4	205.4	205.4	205.4	205.4	205.4	205.4
80°	143.2	144.7	144.7	144.7	144.7	144.7	146.1	146.1	146.1	144.7	143.2
82.5°	91.1	92.6	92.6	94.0	94.0	94.0	92.6	92.6	91.1	91.1	91.1
85°	52.1	50.6	49.2	49.2	47.7	49.2	49.2	50.6	50.6	50.6	50.6
87.5°	17.4	18.8	18.8	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1485.6	1488.5	1494.3	1500.1	1504.4	1510.2	1513.1	1514.6	1517.5	1521.8	1523.2
5°	1382.9	1400.3	1413.3	1426.3	1439.3	1452.4	1461.0	1471.2	1479.8	1488.5	1494.3
7.5°	1216.6	1229.6	1254.2	1277.3	1301.9	1325.1	1352.6	1381.5	1409.0	1432.1	1445.1
10°	1132.7	1139.9	1155.8	1171.7	1186.2	1202.1	1229.6	1258.5	1286.0	1326.5	1356.9
12.5°	1102.3	1103.7	1112.4	1122.5	1131.2	1139.9	1155.8	1173.2	1189.1	1216.6	1260.0
15°	1096.5	1087.8	1090.7	1095.1	1098.0	1100.8	1112.4	1124.0	1135.6	1155.8	1193.4
17.5°	1141.3	1096.5	1090.7	1083.5	1077.7	1070.5	1079.1	1086.4	1095.1	1109.5	1139.9
20°	1203.6	1168.8	1139.9	1111.0	1080.6	1051.7	1056.0	1058.9	1063.2	1076.3	1099.4
22.5°	1223.8	1209.3	1167.4	1124.0	1082.0	1038.6	1035.7	1034.3	1031.4	1041.5	1063.2
25°	1213.7	1205.0	1161.6	1118.2	1073.4	1030.0	1021.3	1011.2	1002.5	1014.1	1035.7
27.5°	1192.0	1186.2	1148.6	1112.4	1074.8	1037.2	1016.9	996.7	976.4	980.8	1002.5
30°	1161.6	1163.0	1132.7	1100.8	1070.5	1038.6	1006.8	976.4	944.6	946.1	969.2
32.5°	1126.9	1128.3	1103.7	1079.1	1053.1	1028.5	989.5	950.4	911.3	912.8	934.5
35°	1089.3	1087.8	1067.6	1045.9	1025.6	1003.9	960.5	915.7	872.3	870.8	892.5
37.5°	1048.8	1050.2	1030.0	1011.2	990.9	970.7	924.4	876.6	830.3	830.3	850.6
40°	1005.4	1009.7	989.5	970.7	950.4	930.1	882.4	836.1	788.4	792.7	807.2
42.5°	951.8	960.5	940.3	921.5	901.2	881.0	834.7	789.8	743.5	749.3	753.7
45°	898.3	904.1	885.3	866.5	846.2	827.4	785.5	742.1	700.1	704.5	690.0
47.5°	846.2	849.1	828.9	808.6	788.4	768.1	730.5	692.9	655.3	656.7	626.4
50°	795.6	795.6	771.0	746.4	721.8	697.3	668.3	637.9	609.0	603.2	567.1
52.5°	750.8	749.3	720.4	692.9	664.0	635.0	609.0	584.4	558.4	541.0	510.6
55°	704.5	701.6	669.8	637.9	606.1	574.3	551.1	528.0	504.9	467.2	447.0
57.5°	656.7	655.3	622.0	588.8	554.0	520.8	491.8	464.4	435.4	399.3	386.2
60°	606.1	600.3	568.5	536.7	503.4	471.6	436.9	402.1	367.4	339.9	331.3
62.5°	555.5	548.3	519.3	490.4	460.0	431.1	393.5	354.4	316.8	311.0	302.3
65°	500.5	494.7	468.7	441.2	415.2	387.7	353.0	316.8	282.1	280.6	273.4
67.5°	441.2	432.5	410.8	389.1	367.4	345.7	316.8	287.9	258.9	257.5	250.3
70°	383.3	376.1	357.3	338.5	319.7	300.9	279.2	256.0	234.3	231.5	224.2
72.5°	319.7	312.5	298.0	283.5	269.1	254.6	238.7	222.8	206.9	204.0	198.2
75°	260.4	254.6	243.0	231.5	219.9	208.3	196.7	186.6	175.0	173.6	169.2
77.5°	201.1	196.7	188.1	180.8	172.1	163.5	154.8	147.6	138.9	141.8	138.9
80°	141.8	140.3	134.5	128.7	123.0	117.2	111.4	107.0	101.3	104.2	101.3
82.5°	91.1	91.1	88.2	85.3	81.0	78.1	73.8	70.9	66.5	69.4	66.5
85°	50.6	49.2	47.7	46.3	44.8	43.4	42.0	39.1	37.6	39.1	37.6
87.5°	21.7	21.7	21.7	21.7	20.3	20.3	18.8	18.8	17.4	17.4	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1524.7	1526.1	1527.6	1531.9	1534.8	1539.2	1542.1	1542.1	1542.1	1542.1	1542.1
5°	1500.1	1504.4	1510.2	1517.5	1523.2	1530.5	1536.3	1539.2	1542.1	1544.9	1547.8
7.5°	1458.2	1471.2	1484.2	1494.3	1504.4	1514.6	1524.7	1530.5	1536.3	1540.6	1546.4
10°	1388.7	1419.1	1449.5	1465.4	1479.8	1495.8	1510.2	1517.5	1526.1	1533.4	1540.6
12.5°	1303.4	1345.3	1388.7	1414.8	1439.3	1465.4	1490.0	1500.1	1511.7	1521.8	1531.9
15°	1232.5	1270.1	1307.7	1348.2	1387.3	1427.8	1466.8	1479.8	1491.4	1504.4	1516.0
17.5°	1168.8	1199.2	1228.1	1280.2	1332.3	1382.9	1435.0	1450.9	1465.4	1481.3	1495.8
20°	1124.0	1147.1	1170.3	1228.1	1284.6	1342.4	1398.8	1416.2	1433.6	1450.9	1468.3
22.5°	1086.4	1108.1	1129.8	1184.7	1239.7	1294.7	1349.7	1372.8	1394.5	1417.6	1439.3
25°	1056.0	1077.7	1098.0	1147.1	1194.9	1244.1	1291.8	1320.7	1349.7	1378.6	1407.5
27.5°	1025.6	1047.3	1069.0	1109.5	1150.0	1190.5	1231.0	1265.8	1299.0	1333.7	1367.0
30°	992.4	1015.5	1038.6	1070.5	1100.8	1132.7	1163.0	1200.7	1236.8	1274.4	1310.6
32.5°	957.6	979.3	1001.0	1022.7	1044.4	1064.7	1086.4	1121.1	1157.3	1192.0	1226.7
35°	914.2	935.9	957.6	963.4	970.7	976.4	982.2	1027.1	1071.9	1116.8	1161.6
37.5°	870.8	889.6	909.9	899.8	889.6	878.1	867.9	927.3	986.6	1045.9	1105.2
40°	820.2	834.7	847.7	827.4	807.2	786.9	766.7	828.9	892.5	954.7	1016.9
42.5°	758.0	760.9	765.2	746.4	729.1	710.3	691.5	749.3	805.7	863.6	920.0
45°	675.6	661.1	646.6	643.7	640.8	636.5	633.6	698.7	763.8	828.9	894.0
47.5°	597.4	567.1	536.7	556.9	575.7	596.0	614.8	671.2	729.1	785.5	841.9
50°	532.3	496.2	460.0	499.1	536.7	575.7	613.3	656.7	698.7	742.1	784.0
52.5°	478.8	448.4	416.6	451.3	487.5	522.2	556.9	596.0	635.0	674.1	713.2
55°	425.3	405.0	383.3	416.6	449.9	483.2	516.4	546.8	578.6	609.0	639.4
57.5°	371.8	358.8	344.3	384.8	426.7	467.2	507.7	513.5	520.8	526.6	532.3
60°	321.1	312.5	302.3	342.8	384.8	425.3	465.8	445.5	425.3	405.0	384.8
62.5°	292.2	283.5	273.4	311.0	348.6	384.8	422.4	386.2	351.5	315.4	279.2
65°	264.7	257.5	248.8	276.3	303.8	331.3	358.8	328.4	296.5	266.2	234.3
67.5°	241.6	234.3	225.7	237.2	250.3	261.8	273.4	253.2	232.9	211.2	190.9
70°	217.0	208.3	201.1	201.1	202.5	202.5	202.5	183.7	164.9	146.1	127.3
72.5°	192.4	186.6	180.8	177.9	175.0	170.7	167.8	151.9	136.0	118.6	102.7
75°	166.4	162.0	157.7	151.9	147.6	141.8	136.0	128.7	123.0	115.7	108.5
77.5°	134.5	131.6	127.3	120.1	114.3	107.0	99.8	99.8	101.3	101.3	101.3
80°	98.4	94.0	91.1	86.8	83.9	79.6	75.2	76.7	78.1	78.1	79.6
82.5°	63.6	60.8	57.9	56.4	55.0	52.1	50.6	50.6	50.6	50.6	50.6
85°	34.7	33.3	30.4	28.9	27.5	24.6	23.1	24.6	26.0	27.5	28.9
87.5°	14.5	13.0	11.6	10.1	10.1	8.7	7.2	8.7	10.1	11.6	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1544.9	1546.4	1549.3	1550.7	1553.6	1553.6	1553.6	1553.6	1552.2	1552.2	1550.7
5°	1552.2	1556.5	1559.4	1563.8	1566.6	1568.1	1568.1	1569.5	1569.5	1569.5	1568.1
7.5°	1552.2	1556.5	1562.3	1566.6	1571.0	1572.4	1573.9	1575.3	1573.9	1573.9	1572.4
10°	1546.4	1552.2	1558.0	1563.8	1566.6	1568.1	1569.5	1571.0	1569.5	1569.5	1568.1
12.5°	1537.7	1543.5	1547.8	1553.6	1556.5	1558.0	1560.9	1562.3	1562.3	1562.3	1560.9
15°	1521.8	1526.1	1531.9	1536.3	1539.2	1542.1	1546.4	1549.3	1549.3	1547.8	1547.8
17.5°	1501.5	1507.3	1513.1	1518.9	1523.2	1526.1	1527.6	1530.5	1530.5	1530.5	1529.0
20°	1475.5	1482.7	1488.5	1495.8	1500.1	1503.0	1504.4	1507.3	1507.3	1507.3	1507.3
22.5°	1446.6	1453.8	1461.0	1468.3	1471.2	1474.1	1477.0	1479.8	1479.8	1479.8	1479.8
25°	1413.3	1420.5	1426.3	1432.1	1440.8	1443.7	1446.6	1449.5	1450.9	1452.4	1452.4
27.5°	1375.7	1382.9	1391.6	1398.8	1404.6	1409.0	1411.9	1416.2	1417.6	1419.1	1419.1
30°	1322.2	1335.2	1346.8	1358.3	1364.1	1369.9	1377.1	1382.9	1384.4	1384.4	1385.8
32.5°	1249.8	1271.5	1294.7	1316.4	1329.4	1335.2	1341.0	1346.8	1345.3	1342.4	1341.0
35°	1190.5	1219.5	1248.4	1277.3	1288.9	1293.2	1297.6	1301.9	1299.0	1297.6	1294.7
37.5°	1138.5	1171.7	1203.6	1236.8	1245.5	1248.4	1252.7	1255.6	1252.7	1249.8	1245.5
40°	1060.3	1103.7	1145.7	1189.1	1194.9	1197.8	1200.7	1203.6	1200.7	1199.2	1196.3
42.5°	975.0	1030.0	1083.5	1138.5	1145.7	1144.2	1141.3	1139.9	1141.3	1144.2	1145.7
45°	941.7	989.5	1035.7	1083.5	1092.2	1089.3	1086.4	1083.5	1086.4	1089.3	1092.2
47.5°	888.2	935.9	982.2	1028.5	1028.5	1027.1	1025.6	1024.2	1028.5	1031.4	1035.7
50°	826.0	869.4	911.3	953.3	947.5	954.7	960.5	967.8	972.1	976.4	980.8
52.5°	749.3	785.5	820.2	856.4	878.1	888.2	899.8	909.9	912.8	915.7	917.1
55°	671.2	704.5	736.3	768.1	811.5	823.1	833.2	844.8	847.7	852.0	854.9
57.5°	571.4	610.5	648.1	687.1	742.1	755.1	769.6	782.6	782.6	782.6	781.2
60°	438.3	493.3	546.8	600.3	665.4	679.9	692.9	707.4	705.9	705.9	704.5
62.5°	335.6	390.6	447.0	502.0	575.7	596.0	614.8	635.0	635.0	635.0	633.6
65°	264.7	296.5	326.9	357.3	478.8	507.7	535.2	564.2	565.6	565.6	567.1
67.5°	204.0	217.0	228.6	241.6	399.3	431.1	464.4	496.2	496.2	494.7	494.7
70°	137.4	147.6	157.7	167.8	324.0	358.8	394.9	429.6	428.2	426.7	423.8
72.5°	108.5	112.8	118.6	123.0	251.7	287.9	325.5	361.6	360.2	357.3	355.9
75°	105.6	101.3	98.4	94.0	186.6	222.8	257.5	293.7	292.2	290.8	289.3
77.5°	95.5	88.2	82.5	75.2	137.4	169.2	201.1	232.9	231.5	228.6	227.1
80°	73.8	68.0	62.2	56.4	94.0	118.6	143.2	167.8	167.8	167.8	167.8
82.5°	49.2	46.3	44.8	42.0	59.3	78.1	95.5	114.3	112.8	112.8	111.4
85°	28.9	27.5	27.5	26.0	36.2	44.8	53.5	62.2	63.6	63.6	65.1
87.5°	14.5	14.5	15.9	15.9	20.3	24.6	27.5	31.8	31.8	33.3	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1549.3	1547.8	1544.9	1547.8	1549.3	1552.2	1556.5	1559.4	1562.3	1563.8	1565.2
5°	1568.1	1566.6	1565.2	1566.6	1568.1	1572.4	1575.3	1579.7	1582.6	1584.0	1584.0
7.5°	1571.0	1571.0	1569.5	1571.0	1572.4	1576.8	1579.7	1584.0	1586.9	1588.3	1588.3
10°	1566.6	1566.6	1566.6	1569.5	1572.4	1576.8	1579.7	1584.0	1586.9	1588.3	1588.3
12.5°	1560.9	1560.9	1559.4	1562.3	1565.2	1569.5	1572.4	1576.8	1579.7	1581.1	1581.1
15°	1546.4	1546.4	1546.4	1549.3	1552.2	1556.5	1560.9	1563.8	1568.1	1569.5	1571.0
17.5°	1529.0	1530.5	1530.5	1533.4	1536.3	1540.6	1543.5	1547.8	1550.7	1552.2	1552.2
20°	1507.3	1507.3	1507.3	1511.7	1514.6	1518.9	1521.8	1526.1	1529.0	1530.5	1533.4
22.5°	1479.8	1481.3	1482.7	1488.5	1492.9	1495.8	1500.1	1503.0	1505.9	1505.9	1507.3
25°	1453.8	1456.7	1458.2	1461.0	1463.9	1465.4	1466.8	1466.8	1468.3	1468.3	1466.8
27.5°	1420.5	1423.4	1426.3	1427.8	1427.8	1427.8	1429.2	1429.2	1429.2	1430.7	1432.1
30°	1385.8	1382.9	1380.0	1381.5	1382.9	1384.4	1387.3	1388.7	1390.2	1391.6	1391.6
32.5°	1338.1	1338.1	1336.6	1339.5	1341.0	1343.9	1346.8	1349.7	1352.6	1352.6	1352.6
35°	1291.8	1294.7	1297.6	1299.0	1299.0	1300.5	1303.4	1304.8	1306.3	1307.7	1309.2
37.5°	1242.6	1247.0	1251.3	1254.2	1255.6	1257.1	1258.5	1260.0	1261.4	1260.0	1260.0
40°	1193.4	1197.8	1202.1	1203.6	1205.0	1206.4	1206.4	1207.9	1207.9	1206.4	1206.4
42.5°	1147.1	1148.6	1150.0	1152.9	1155.8	1154.4	1154.4	1152.9	1151.5	1150.0	1147.1
45°	1095.1	1098.0	1099.4	1099.4	1099.4	1096.5	1093.6	1089.3	1086.4	1084.9	1084.9
47.5°	1038.6	1043.0	1045.9	1041.5	1035.7	1032.9	1030.0	1025.6	1022.7	1021.3	1019.8
50°	985.1	982.2	977.9	973.5	967.8	964.9	963.4	960.5	957.6	951.8	947.5
52.5°	920.0	914.2	908.5	904.1	898.3	894.0	889.6	885.3	881.0	878.1	876.6
55°	857.8	847.7	836.1	831.8	826.0	820.2	813.0	807.2	800.0	798.5	797.1
57.5°	781.2	775.4	768.1	759.5	749.3	743.5	739.2	733.4	727.6	726.2	724.7
60°	703.0	697.3	691.5	682.8	674.1	669.8	664.0	659.6	653.9	652.4	652.4
62.5°	633.6	629.3	623.5	610.5	597.4	594.5	590.2	587.3	583.0	580.1	578.6
65°	567.1	556.9	545.4	536.7	526.6	522.2	519.3	515.0	510.6	507.7	504.9
67.5°	493.3	480.3	465.8	461.5	457.1	452.8	447.0	442.7	436.9	435.4	434.0
70°	422.4	412.3	400.7	396.4	390.6	386.2	381.9	376.1	371.8	368.9	364.5
72.5°	353.0	344.3	334.2	328.4	322.6	318.2	315.4	311.0	306.7	303.8	300.9
75°	287.9	279.2	270.5	264.7	258.9	256.0	253.2	248.8	245.9	241.6	238.7
77.5°	224.2	219.9	214.1	206.9	199.6	198.2	196.7	195.3	193.8	189.5	186.6
80°	167.8	163.5	159.1	154.8	149.0	146.1	144.7	141.8	138.9	137.4	134.5
82.5°	109.9	107.0	104.2	102.7	101.3	99.8	98.4	96.9	95.5	94.0	94.0
85°	65.1	65.1	65.1	63.6	62.2	62.2	62.2	60.8	60.8	59.3	59.3
87.5°	33.3	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	34.7	36.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1566.6	1565.2	1566.6	1566.6	1568.1	1568.1	1566.6	1566.6	1565.2	1563.8	1565.2
5°	1585.4	1586.9	1586.9	1586.9	1586.9	1586.9	1586.9	1585.4	1585.4	1584.0	1585.4
7.5°	1589.8	1589.8	1591.2	1591.2	1592.7	1592.7	1591.2	1591.2	1589.8	1588.3	1589.8
10°	1589.8	1591.2	1591.2	1592.7	1592.7	1592.7	1591.2	1591.2	1589.8	1588.3	1589.8
12.5°	1582.6	1582.6	1584.0	1584.0	1585.4	1585.4	1585.4	1584.0	1584.0	1582.6	1584.0
15°	1572.4	1571.0	1572.4	1572.4	1573.9	1573.9	1572.4	1572.4	1571.0	1569.5	1571.0
17.5°	1553.6	1555.1	1555.1	1556.5	1556.5	1556.5	1555.1	1553.6	1552.2	1550.7	1552.2
20°	1534.8	1534.8	1534.8	1536.3	1536.3	1536.3	1534.8	1534.8	1533.4	1531.9	1533.4
22.5°	1507.3	1507.3	1507.3	1505.9	1505.9	1504.4	1503.0	1503.0	1501.5	1500.1	1501.5
25°	1466.8	1468.3	1468.3	1468.3	1468.3	1468.3	1466.8	1466.8	1465.4	1463.9	1465.4
27.5°	1433.6	1430.7	1432.1	1432.1	1433.6	1433.6	1433.6	1432.1	1432.1	1430.7	1432.1
30°	1393.1	1395.9	1397.4	1397.4	1398.8	1398.8	1398.8	1397.4	1397.4	1395.9	1397.4
32.5°	1352.6	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1354.0	1354.0	1352.6	1354.0
35°	1310.6	1309.2	1309.2	1310.6	1310.6	1310.6	1309.2	1309.2	1307.7	1306.3	1307.7
37.5°	1258.5	1258.5	1258.5	1258.5	1258.5	1258.5	1257.1	1257.1	1255.6	1254.2	1255.6
40°	1205.0	1203.6	1203.6	1205.0	1205.0	1205.0	1203.6	1202.1	1200.7	1199.2	1200.7
42.5°	1145.7	1145.7	1145.7	1145.7	1144.2	1144.2	1144.2	1144.2	1142.8	1142.8	1142.8
45°	1083.5	1082.0	1082.0	1080.6	1080.6	1079.1	1079.1	1077.7	1077.7	1076.3	1077.7
47.5°	1018.4	1018.4	1016.9	1014.1	1012.6	1009.7	1008.3	1006.8	1003.9	1002.5	1003.9
50°	941.7	941.7	940.3	938.8	937.4	935.9	935.9	937.4	937.4	937.4	937.4
52.5°	873.7	867.9	866.5	866.5	865.1	863.6	863.6	863.6	862.2	862.2	862.2
55°	795.6	792.7	792.7	792.7	791.3	791.3	792.7	792.7	794.2	794.2	794.2
57.5°	723.3	721.8	721.8	720.4	720.4	718.9	717.5	717.5	716.1	714.6	716.1
60°	651.0	648.1	645.2	642.3	637.9	635.0	633.6	632.2	630.7	629.3	630.7
62.5°	575.7	570.0	568.5	565.6	564.2	561.3	558.4	556.9	554.0	551.1	554.0
65°	502.0	500.5	496.2	491.8	487.5	483.2	481.7	481.7	480.3	478.8	480.3
67.5°	432.5	423.8	421.0	418.1	415.2	412.3	412.3	412.3	412.3	412.3	412.3
70°	361.6	355.9	354.4	351.5	350.1	347.2	347.2	347.2	345.7	345.7	345.7
72.5°	298.0	292.2	290.8	289.3	286.4	285.0	285.0	285.0	283.5	283.5	283.5
75°	234.3	235.8	234.3	232.9	231.5	230.0	230.0	228.6	228.6	227.1	228.6
77.5°	182.3	182.3	180.8	179.4	177.9	176.5	176.5	176.5	176.5	176.5	176.5
80°	133.1	133.1	133.1	133.1	131.6	131.6	131.6	131.6	130.2	130.2	130.2
82.5°	92.6	92.6	92.6	92.6	92.6	92.6	92.6	91.1	91.1	89.7	91.1
85°	57.9	59.3	59.3	59.3	57.9	57.9	57.9	57.9	57.9	57.9	57.9
87.5°	36.2	36.2	36.2	37.6	37.6	37.6	37.6	37.6	36.2	36.2	36.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1566.6	1566.6	1568.1	1568.1	1566.6	1566.6	1565.2	1566.6	1565.2	1563.8	1562.3
5°	1585.4	1586.9	1586.9	1586.9	1586.9	1586.9	1586.9	1585.4	1584.0	1584.0	1582.6
7.5°	1591.2	1591.2	1592.7	1592.7	1591.2	1591.2	1589.8	1589.8	1588.3	1588.3	1586.9
10°	1591.2	1591.2	1592.7	1592.7	1592.7	1591.2	1591.2	1589.8	1588.3	1588.3	1586.9
12.5°	1584.0	1585.4	1585.4	1585.4	1584.0	1584.0	1582.6	1582.6	1581.1	1581.1	1579.7
15°	1572.4	1572.4	1573.9	1573.9	1572.4	1572.4	1571.0	1572.4	1571.0	1569.5	1568.1
17.5°	1553.6	1555.1	1556.5	1556.5	1556.5	1555.1	1555.1	1553.6	1552.2	1552.2	1550.7
20°	1534.8	1534.8	1536.3	1536.3	1536.3	1534.8	1534.8	1534.8	1533.4	1530.5	1529.0
22.5°	1503.0	1503.0	1504.4	1505.9	1505.9	1507.3	1507.3	1507.3	1507.3	1505.9	1505.9
25°	1466.8	1466.8	1468.3	1468.3	1468.3	1468.3	1468.3	1466.8	1466.8	1468.3	1468.3
27.5°	1432.1	1433.6	1433.6	1433.6	1432.1	1432.1	1430.7	1433.6	1432.1	1430.7	1429.2
30°	1397.4	1398.8	1398.8	1398.8	1397.4	1397.4	1395.9	1393.1	1391.6	1391.6	1390.2
32.5°	1354.0	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1352.6	1352.6	1352.6	1352.6
35°	1309.2	1309.2	1310.6	1310.6	1310.6	1309.2	1309.2	1310.6	1309.2	1307.7	1306.3
37.5°	1257.1	1257.1	1258.5	1258.5	1258.5	1258.5	1258.5	1258.5	1260.0	1260.0	1261.4
40°	1202.1	1203.6	1205.0	1205.0	1205.0	1203.6	1203.6	1205.0	1206.4	1206.4	1207.9
42.5°	1144.2	1144.2	1144.2	1144.2	1145.7	1145.7	1145.7	1145.7	1147.1	1150.0	1151.5
45°	1077.7	1079.1	1079.1	1080.6	1080.6	1082.0	1082.0	1083.5	1084.9	1084.9	1086.4
47.5°	1006.8	1008.3	1009.7	1012.6	1014.1	1016.9	1018.4	1018.4	1019.8	1021.3	1022.7
50°	937.4	935.9	935.9	937.4	938.8	940.3	941.7	941.7	947.5	951.8	957.6
52.5°	863.6	863.6	863.6	865.1	866.5	866.5	867.9	873.7	876.6	878.1	881.0
55°	792.7	792.7	791.3	791.3	792.7	792.7	792.7	795.6	797.1	798.5	800.0
57.5°	717.5	717.5	718.9	720.4	720.4	721.8	721.8	723.3	724.7	726.2	727.6
60°	632.2	633.6	635.0	637.9	642.3	645.2	648.1	651.0	652.4	652.4	653.9
62.5°	556.9	558.4	561.3	564.2	565.6	568.5	570.0	575.7	578.6	580.1	583.0
65°	481.7	481.7	483.2	487.5	491.8	496.2	500.5	502.0	504.9	507.7	510.6
67.5°	412.3	412.3	412.3	415.2	418.1	421.0	423.8	432.5	434.0	435.4	436.9
70°	347.2	347.2	347.2	350.1	351.5	354.4	355.9	361.6	364.5	368.9	371.8
72.5°	285.0	285.0	285.0	286.4	289.3	290.8	292.2	298.0	300.9	303.8	306.7
75°	228.6	230.0	230.0	231.5	232.9	234.3	235.8	234.3	238.7	241.6	245.9
77.5°	176.5	176.5	176.5	177.9	179.4	180.8	182.3	182.3	186.6	189.5	193.8
80°	131.6	131.6	131.6	131.6	133.1	133.1	133.1	133.1	134.5	137.4	138.9
82.5°	91.1	92.6	92.6	92.6	92.6	92.6	92.6	92.6	94.0	94.0	95.5
85°	57.9	57.9	57.9	57.9	59.3	59.3	59.3	57.9	59.3	59.3	60.8
87.5°	37.6	37.6	37.6	37.6	37.6	36.2	36.2	36.2	36.2	34.7	34.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1559.4	1556.5	1552.2	1549.3	1547.8	1544.9	1547.8	1549.3	1550.7	1552.2	1552.2
5°	1579.7	1575.3	1572.4	1568.1	1566.6	1565.2	1566.6	1568.1	1568.1	1569.5	1569.5
7.5°	1584.0	1579.7	1576.8	1572.4	1571.0	1569.5	1571.0	1571.0	1572.4	1573.9	1573.9
10°	1584.0	1579.7	1576.8	1572.4	1569.5	1566.6	1566.6	1566.6	1568.1	1569.5	1569.5
12.5°	1576.8	1572.4	1569.5	1565.2	1562.3	1559.4	1560.9	1560.9	1560.9	1562.3	1562.3
15°	1563.8	1560.9	1556.5	1552.2	1549.3	1546.4	1546.4	1546.4	1547.8	1547.8	1549.3
17.5°	1547.8	1543.5	1540.6	1536.3	1533.4	1530.5	1530.5	1529.0	1529.0	1530.5	1530.5
20°	1526.1	1521.8	1518.9	1514.6	1511.7	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3
22.5°	1503.0	1500.1	1495.8	1492.9	1487.1	1482.7	1481.3	1479.8	1479.8	1479.8	1479.8
25°	1466.8	1466.8	1465.4	1463.9	1461.0	1458.2	1456.7	1453.8	1452.4	1452.4	1450.9
27.5°	1429.2	1429.2	1427.8	1427.8	1427.8	1426.3	1423.4	1420.5	1419.1	1419.1	1417.6
30°	1388.7	1387.3	1384.4	1382.9	1381.5	1380.0	1382.9	1385.8	1385.8	1384.4	1384.4
32.5°	1349.7	1346.8	1343.9	1341.0	1339.5	1336.6	1338.1	1338.1	1341.0	1342.4	1345.3
35°	1304.8	1303.4	1300.5	1299.0	1299.0	1297.6	1294.7	1291.8	1294.7	1297.6	1299.0
37.5°	1260.0	1258.5	1257.1	1255.6	1254.2	1251.3	1247.0	1242.6	1245.5	1248.4	1252.7
40°	1207.9	1206.4	1206.4	1205.0	1203.6	1202.1	1197.8	1193.4	1196.3	1199.2	1200.7
42.5°	1152.9	1154.4	1154.4	1155.8	1152.9	1150.0	1148.6	1147.1	1145.7	1144.2	1141.3
45°	1089.3	1093.6	1096.5	1099.4	1099.4	1099.4	1098.0	1095.1	1092.2	1089.3	1086.4
47.5°	1025.6	1030.0	1032.9	1035.7	1041.5	1045.9	1043.0	1038.6	1035.7	1031.4	1028.5
50°	960.5	963.4	964.9	967.8	973.5	977.9	982.2	985.1	980.8	976.4	972.1
52.5°	885.3	889.6	894.0	898.3	904.1	908.5	914.2	920.0	917.1	915.7	912.8
55°	807.2	813.0	820.2	826.0	831.8	836.1	847.7	857.8	854.9	852.0	847.7
57.5°	733.4	737.8	743.5	749.3	759.5	768.1	775.4	781.2	781.2	782.6	782.6
60°	659.6	664.0	669.8	674.1	682.8	691.5	697.3	703.0	704.5	705.9	705.9
62.5°	587.3	590.2	594.5	597.4	610.5	623.5	629.3	633.6	633.6	635.0	635.0
65°	515.0	519.3	522.2	526.6	536.7	545.4	556.9	567.1	567.1	565.6	565.6
67.5°	442.7	447.0	452.8	457.1	461.5	465.8	480.3	493.3	494.7	494.7	496.2
70°	376.1	381.9	386.2	390.6	396.4	400.7	412.3	422.4	423.8	426.7	428.2
72.5°	311.0	315.4	318.2	322.6	328.4	334.2	344.3	353.0	355.9	357.3	360.2
75°	248.8	253.2	256.0	258.9	264.7	270.5	279.2	287.9	289.3	290.8	292.2
77.5°	195.3	196.7	198.2	199.6	206.9	214.1	219.9	224.2	227.1	228.6	231.5
80°	141.8	144.7	146.1	149.0	154.8	159.1	163.5	167.8	167.8	167.8	167.8
82.5°	96.9	98.4	99.8	101.3	102.7	104.2	107.0	109.9	111.4	112.8	112.8
85°	60.8	62.2	62.2	62.2	63.6	65.1	65.1	65.1	65.1	63.6	63.6
87.5°	34.7	34.7	34.7	34.7	34.7	34.7	34.7	33.3	33.3	33.3	31.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0	1529.0
2.5°	1553.6	1553.6	1553.6	1553.6	1550.7	1549.3	1546.4	1544.9	1542.1	1542.1	1542.1
5°	1569.5	1568.1	1568.1	1566.6	1563.8	1559.4	1555.1	1552.2	1547.8	1544.9	1542.1
7.5°	1575.3	1573.9	1572.4	1571.0	1566.6	1562.3	1556.5	1552.2	1546.4	1540.6	1534.8
10°	1571.0	1569.5	1568.1	1566.6	1563.8	1558.0	1552.2	1546.4	1540.6	1533.4	1524.7
12.5°	1562.3	1560.9	1558.0	1556.5	1553.6	1547.8	1542.1	1537.7	1531.9	1521.8	1510.2
15°	1549.3	1546.4	1542.1	1539.2	1536.3	1531.9	1526.1	1521.8	1516.0	1504.4	1491.4
17.5°	1530.5	1527.6	1526.1	1523.2	1518.9	1513.1	1507.3	1501.5	1495.8	1481.3	1465.4
20°	1507.3	1504.4	1503.0	1500.1	1495.8	1488.5	1481.3	1475.5	1468.3	1450.9	1433.6
22.5°	1479.8	1477.0	1474.1	1471.2	1468.3	1461.0	1453.8	1446.6	1439.3	1417.6	1394.5
25°	1449.5	1446.6	1443.7	1440.8	1432.1	1426.3	1419.1	1413.3	1407.5	1378.6	1349.7
27.5°	1416.2	1411.9	1409.0	1404.6	1398.8	1391.6	1382.9	1375.7	1367.0	1333.7	1299.0
30°	1382.9	1377.1	1369.9	1364.1	1358.3	1346.8	1333.7	1322.2	1310.6	1274.4	1236.8
32.5°	1346.8	1341.0	1335.2	1329.4	1316.4	1294.7	1271.5	1249.8	1226.7	1192.0	1155.8
35°	1301.9	1297.6	1293.2	1288.9	1277.3	1248.4	1219.5	1190.5	1161.6	1116.8	1071.9
37.5°	1255.6	1252.7	1248.4	1245.5	1236.8	1203.6	1170.3	1138.5	1105.2	1045.9	986.6
40°	1203.6	1200.7	1197.8	1194.9	1189.1	1145.7	1102.3	1060.3	1016.9	954.7	891.1
42.5°	1139.9	1141.3	1144.2	1145.7	1138.5	1083.5	1028.5	975.0	920.0	863.6	805.7
45°	1083.5	1086.4	1089.3	1092.2	1083.5	1035.7	988.0	941.7	894.0	828.9	763.8
47.5°	1024.2	1025.6	1027.1	1028.5	1028.5	982.2	934.5	888.2	841.9	785.5	727.6
50°	967.8	960.5	954.7	947.5	953.3	911.3	867.9	826.0	784.0	742.1	698.7
52.5°	909.9	899.8	888.2	878.1	856.4	820.2	784.0	749.3	713.2	674.1	635.0
55°	844.8	833.2	823.1	811.5	768.1	736.3	703.0	671.2	639.4	609.0	577.2
57.5°	782.6	769.6	755.1	742.1	687.1	648.1	609.0	571.4	532.3	526.6	519.3
60°	707.4	692.9	679.9	665.4	600.3	546.8	491.8	438.3	384.8	405.0	425.3
62.5°	635.0	614.8	596.0	575.7	502.0	447.0	390.6	335.6	279.2	315.4	351.5
65°	564.2	535.2	507.7	478.8	357.3	326.9	295.1	264.7	234.3	266.2	296.5
67.5°	496.2	464.4	431.1	399.3	241.6	228.6	215.5	204.0	190.9	211.2	232.9
70°	429.6	394.9	358.8	324.0	167.8	157.7	147.6	137.4	127.3	146.1	164.9
72.5°	361.6	325.5	287.9	251.7	123.0	118.6	112.8	108.5	102.7	118.6	136.0
75°	293.7	257.5	222.8	186.6	94.0	98.4	101.3	105.6	108.5	115.7	123.0
77.5°	232.9	201.1	169.2	137.4	75.2	82.5	88.2	95.5	101.3	101.3	101.3
80°	167.8	143.2	118.6	94.0	56.4	62.2	68.0	73.8	79.6	78.1	78.1
82.5°	114.3	95.5	78.1	59.3	42.0	44.8	46.3	49.2	50.6	50.6	50.6
85°	62.2	53.5	44.8	36.2	26.0	27.5	27.5	28.9	28.9	27.5	26.0
87.5°	31.8	27.5	24.6	20.3	15.9	15.9	14.5	14.5	13.0	11.6	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1529.0	1529.0
2.5°	1542.1	1542.1
5°	1539.2	1536.3
7.5°	1530.5	1524.7
10°	1517.5	1510.2
12.5°	1500.1	1490.0
15°	1479.8	1466.8
17.5°	1450.9	1435.0
20°	1416.2	1398.8
22.5°	1372.8	1349.7
25°	1320.7	1291.8
27.5°	1265.8	1231.0
30°	1200.7	1163.0
32.5°	1121.1	1086.4
35°	1027.1	982.2
37.5°	927.3	867.9
40°	828.9	766.7
42.5°	749.3	691.5
45°	698.7	633.6
47.5°	671.2	614.8
50°	656.7	613.3
52.5°	596.0	556.9
55°	546.8	516.4
57.5°	513.5	507.7
60°	445.5	465.8
62.5°	386.2	422.4
65°	328.4	358.8
67.5°	253.2	273.4
70°	183.7	202.5
72.5°	151.9	167.8
75°	128.7	136.0
77.5°	99.8	99.8
80°	76.7	75.2
82.5°	50.6	50.6
85°	24.6	23.1
87.5°	8.7	7.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055055

CATALOG NUMBER: SQ4R-FA-125D-935-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.44	21.05	19.80	21.36	21.68	21.35	22.96	21.72	23.28	23.59
	3H	20.10	21.55	20.48	21.88	22.24	23.15	24.60	23.53	24.93	25.29
	4H	20.43	21.80	20.83	22.15	22.52	23.77	25.14	24.17	25.48	25.86
	6H	20.72	21.99	21.13	22.35	22.74	24.15	25.42	24.56	25.78	26.17
	8H	20.80	22.01	21.22	22.40	22.80	24.25	25.46	24.67	25.85	26.25
	12H	20.83	21.99	21.26	22.37	22.80	24.30	25.45	24.73	25.84	26.26
4H	2H	20.57	21.93	20.96	22.28	22.66	21.92	23.29	22.32	23.64	24.01
	3H	21.89	23.03	22.30	23.42	23.82	23.95	25.09	24.36	25.49	25.89
	4H	22.32	23.35	22.75	23.76	24.20	24.69	25.72	25.12	26.13	26.57
	6H	22.61	23.51	23.07	23.95	24.41	25.19	26.08	25.64	26.53	26.98
	8H	22.69	23.53	23.15	23.97	24.44	25.31	26.15	25.77	26.60	27.06
	12H	22.73	23.48	23.21	23.96	24.43	25.39	26.14	25.87	26.62	27.09
8H	4H	22.91	23.75	23.37	24.19	24.66	24.92	25.76	25.38	26.20	26.67
	6H	23.39	24.09	23.88	24.58	25.05	25.52	26.21	26.01	26.70	27.18
	8H	23.52	24.14	24.03	24.65	25.14	25.69	26.32	26.20	26.83	27.31
	12H	23.59	24.14	24.10	24.63	25.20	25.82	26.37	26.32	26.86	27.42
12H	4H	22.96	23.71	23.44	24.19	24.66	24.93	25.68	25.41	26.16	26.62
	6H	23.49	24.12	24.00	24.62	25.11	25.53	26.16	26.04	26.67	27.15
	8H	23.69	24.25	24.20	24.74	25.30	25.76	26.31	26.27	26.80	27.36