

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1055038

Luminaire Tested: SQ4R-FA-075D-840-1-UNV-STD-W-4

Issue Date: 7/23/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-892-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/23/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4R-FA-075D-840-1-UNV-STD-W-4
Description: CORELITE SQ4R RECESSED LED LUMINAIRE WITH ASYMMETRIC FROSTED CONTINUOUS ROLL LENS
750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2836.1 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular (W 0.29' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	105	100	97	106	102	98	95	98	95	92		94	92	89		91
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		80
3	91	81	73	66	88	79	72	66	76	70	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	51	43	37	50	42	37		48	42	37		47
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10528	10528	10528	10528
5°	10619	8609	10619	10948
10°	10559	7940	10559	11105
15°	10456	9343	10456	11189
20°	10250	9646	10250	11226
25°	9814	9738	9814	11122
30°	9247	9580	9247	11099
35°	8256	9375	8256	10981
40°	6891	9310	6891	10779
45°	6170	9198	6170	10481
50°	6571	9112	6571	10041
55°	6200	9309	6200	9534
60°	6414	9125	6414	8667
65°	5845	8720	5845	7802
70°	4076	8183	4076	6961
75°	3619	7235	3619	6041
80°	2983	5622	2983	5162
85°	1834	3888	1834	4573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 225°

Vertical Angle: 45°

Luminance: 10706 cd/sqm

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.7	3.5
10°-20°	280.3	9.9
20°-30°	433.3	15.3
30°-40°	517.3	18.2
40°-50°	520.3	18.3
50°-60°	452.8	16.0
60°-70°	321.1	11.3
70°-80°	169.9	6.0
80°-90°	42.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.4	28.6
0°-40°	1329.6	46.9
0°-60°	2302.7	81.2
0°-90°	2836.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2836.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1094	1094	1094	1094	1094	
5°	1099	891	1099	1133	1099	104
15°	1049	937	1049	1123	1049	295
25°	924	917	924	1047	924	424
35°	702	798	702	934	702	435
45°	453	676	453	770	453	363
55°	369	555	369	568	369	339
65°	257	383	257	342	257	245
75°	97	194	97	162	97	102
85°	17	35	17	41	17	22
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1102.9	1100.8	1097.7	1095.7	1092.6	1091.5	1090.5	1089.5	1088.4	1085.3	1083.2
5°	1098.8	1094.6	1089.5	1085.3	1080.1	1076.0	1072.9	1068.8	1064.6	1058.4	1052.2
7.5°	1090.5	1083.2	1076.0	1068.8	1061.5	1052.2	1042.9	1033.6	1024.3	1007.7	988.1
10°	1080.1	1069.8	1058.4	1048.1	1036.7	1015.0	993.2	970.5	948.7	919.8	900.1
12.5°	1065.7	1048.1	1029.4	1011.9	993.2	962.2	932.2	901.2	870.1	850.5	839.1
15°	1049.1	1021.2	992.2	964.3	935.3	908.4	881.5	853.6	826.7	812.2	803.9
17.5°	1026.3	989.1	952.9	915.6	878.4	857.7	836.0	815.3	793.6	783.2	777.0
20°	1000.5	960.1	918.7	878.4	837.0	820.5	803.9	786.3	769.8	760.4	757.3
22.5°	965.3	926.0	886.7	847.4	808.0	792.5	777.0	760.4	744.9	737.7	739.8
25°	923.9	889.8	854.6	820.5	785.3	770.8	755.3	740.8	725.3	717.0	723.2
27.5°	880.5	851.5	822.5	793.6	764.6	749.1	733.5	717.0	701.5	698.4	712.9
30°	831.8	810.1	787.3	765.6	742.9	726.3	709.7	693.2	676.6	675.6	698.4
32.5°	777.0	761.5	747.0	731.5	716.0	700.4	684.9	668.4	652.8	651.8	679.7
35°	702.5	698.4	694.2	689.1	684.9	669.4	653.9	638.4	622.8	623.9	654.9
37.5°	620.8	628.0	636.3	643.5	650.8	636.3	622.8	608.4	593.9	593.9	627.0
40°	548.3	562.8	577.3	591.8	606.3	597.0	586.6	577.3	567.0	563.9	598.0
42.5°	494.5	508.0	521.4	533.9	547.3	544.2	542.1	539.0	535.9	531.8	564.9
45°	453.2	455.2	458.3	460.4	462.5	472.8	483.2	493.5	503.9	500.8	530.8
47.5°	439.7	426.3	411.8	398.3	383.8	405.6	427.3	448.0	469.7	468.7	495.6
50°	438.7	411.8	383.8	356.9	329.0	354.9	380.7	405.6	431.4	435.6	456.3
52.5°	398.3	373.5	348.7	322.8	298.0	320.7	342.5	365.2	386.9	399.4	418.0
55°	369.4	345.6	321.8	298.0	274.2	289.7	304.2	319.7	334.2	361.1	377.6
57.5°	363.2	334.2	305.2	275.2	246.2	256.6	265.9	276.2	285.6	311.4	332.1
60°	333.1	304.2	275.2	245.2	216.2	223.5	229.7	236.9	243.1	262.8	287.6
62.5°	302.1	275.2	249.3	222.4	195.5	202.8	209.0	216.2	222.4	226.6	253.5
65°	256.6	236.9	217.3	197.6	178.0	184.2	189.3	195.5	200.7	201.8	226.6
67.5°	195.5	187.3	179.0	169.7	161.4	167.6	172.8	179.0	184.2	185.2	205.9
70°	144.8	144.8	144.8	143.8	143.8	149.0	155.2	160.4	165.5	167.6	183.1
72.5°	120.0	122.1	125.2	127.3	129.3	133.5	137.6	141.7	145.9	148.0	159.3
75°	97.3	101.4	105.5	108.6	112.8	115.9	119.0	121.1	124.2	125.2	133.5
77.5°	71.4	76.6	81.7	85.9	91.0	94.2	96.2	99.3	101.4	99.3	105.5
80°	53.8	56.9	60.0	62.1	65.2	67.3	70.4	72.4	74.5	72.4	76.6
82.5°	36.2	37.2	39.3	40.4	41.4	43.5	45.5	47.6	49.7	47.6	50.7
85°	16.6	17.6	19.7	20.7	21.7	23.8	24.8	26.9	27.9	26.9	27.9
87.5°	5.2	6.2	7.2	7.2	8.3	9.3	10.3	11.4	12.4	12.4	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1082.2	1080.1	1076.0	1072.9	1068.8	1064.6	1062.6	1060.5	1058.4	1056.3	1058.4
5°	1045.0	1038.8	1029.4	1020.1	1010.8	1001.5	989.1	976.7	967.4	958.1	956.0
7.5°	967.4	947.7	931.2	913.6	897.0	879.4	870.1	860.8	852.5	844.2	842.2
10°	879.4	859.8	848.4	838.0	826.7	815.3	810.1	803.9	802.9	800.8	801.8
12.5°	826.7	815.3	809.1	802.9	795.6	789.4	788.4	787.3	790.4	792.5	799.8
15°	795.6	787.3	785.3	783.2	780.1	778.0	784.2	789.4	808.0	825.6	846.3
17.5°	771.8	765.6	770.8	774.9	780.1	784.2	816.3	848.4	873.2	897.0	904.3
20°	755.3	752.2	772.9	794.6	815.3	836.0	860.8	884.6	893.9	902.2	906.3
22.5°	740.8	742.9	773.9	803.9	834.9	864.9	875.3	884.6	890.8	897.0	900.1
25°	730.4	736.6	767.7	799.8	830.8	861.8	868.0	873.2	875.3	876.3	883.6
27.5°	727.3	741.8	768.7	795.6	821.5	848.4	852.5	856.7	858.7	859.8	867.0
30°	720.1	742.9	765.6	787.3	810.1	831.8	830.8	829.8	833.9	838.0	845.3
32.5°	707.7	735.6	753.2	771.8	789.4	807.0	806.0	804.9	811.1	816.3	821.5
35°	687.0	718.0	733.5	748.0	763.5	778.0	779.1	779.1	784.2	789.4	792.5
37.5°	661.1	694.2	708.7	723.2	736.6	751.1	750.1	749.1	751.1	752.2	757.3
40°	631.1	665.3	679.7	694.2	707.7	722.2	719.1	714.9	714.9	713.9	720.1
42.5°	597.0	630.1	644.6	659.1	672.5	687.0	680.8	673.5	675.6	676.6	684.9
45°	561.8	591.8	605.3	619.7	633.2	646.6	642.5	637.3	641.5	645.6	653.9
47.5°	522.5	549.4	563.9	578.4	592.8	607.3	605.3	602.1	606.3	610.4	619.7
50°	478.0	498.7	516.3	533.9	551.5	569.0	569.0	569.0	573.2	576.3	585.6
52.5°	435.6	454.2	474.9	495.6	515.2	535.9	537.0	538.0	542.1	545.2	553.5
55°	394.2	410.7	433.5	456.3	479.0	501.8	503.9	505.9	510.1	513.2	521.4
57.5°	351.8	372.5	396.3	421.1	444.9	468.7	469.7	470.8	473.9	477.0	484.2
60°	312.5	337.3	360.0	383.8	406.6	429.4	433.5	436.6	438.7	440.7	447.0
62.5°	281.4	308.3	329.0	350.7	371.4	392.1	397.3	401.4	403.5	404.5	408.7
65°	252.4	277.3	296.9	315.6	335.2	353.8	358.0	362.1	365.2	367.3	370.4
67.5°	226.6	247.3	262.8	278.3	293.8	309.4	315.6	320.7	322.8	324.9	326.9
70°	199.7	215.2	228.7	242.1	255.6	269.0	274.2	279.3	281.4	282.5	283.5
72.5°	170.7	182.1	192.4	202.8	213.1	223.5	228.7	233.8	235.9	236.9	238.0
75°	140.7	149.0	157.3	165.5	173.8	182.1	186.2	189.3	190.4	191.4	191.4
77.5°	110.7	116.9	123.1	129.3	134.5	140.7	143.8	146.9	146.9	146.9	146.9
80°	79.7	83.8	87.9	92.1	96.2	100.4	101.4	102.4	103.5	104.5	104.5
82.5°	52.8	55.9	57.9	61.0	63.1	65.2	65.2	65.2	65.2	65.2	66.2
85°	30.0	31.0	32.1	33.1	34.1	35.2	36.2	36.2	36.2	36.2	36.2
87.5°	13.5	14.5	14.5	15.5	15.5	15.5	15.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1059.5	1061.5	1062.6	1060.5	1057.4	1055.3	1052.2	1053.2	1054.3	1055.3	1056.3
5°	952.9	950.8	947.7	940.5	933.2	926.0	920.8	916.7	912.5	908.4	904.3
7.5°	839.1	837.0	833.9	831.8	829.8	827.7	823.6	822.5	821.5	820.5	819.4
10°	802.9	802.9	803.9	804.9	804.9	806.0	807.0	809.1	810.1	812.2	813.2
12.5°	807.0	813.2	820.5	833.9	848.4	861.8	871.1	879.4	888.7	897.0	905.3
15°	868.0	888.7	909.4	914.6	920.8	926.0	929.1	931.2	933.2	934.3	936.3
17.5°	911.5	917.7	925.0	927.0	930.1	932.2	933.2	934.3	936.3	937.4	938.4
20°	910.5	913.6	917.7	920.8	923.9	927.0	929.1	932.2	934.3	937.4	939.4
22.5°	904.3	907.4	910.5	915.6	919.8	925.0	929.1	931.2	933.2	935.3	937.4
25°	889.8	897.0	903.2	907.4	910.5	914.6	914.6	914.6	915.6	915.6	915.6
27.5°	874.3	881.5	888.7	889.8	891.8	892.9	894.9	897.0	898.0	900.1	901.2
30°	852.5	859.8	867.0	869.1	871.1	873.2	871.1	870.1	869.1	867.0	866.0
32.5°	827.7	832.9	838.0	839.1	839.1	840.1	834.9	833.9	832.9	830.8	829.8
35°	796.7	799.8	802.9	801.8	801.8	800.8	801.8	801.8	801.8	800.8	800.8
37.5°	761.5	766.7	770.8	771.8	771.8	772.9	774.9	774.9	774.9	773.9	773.9
40°	727.3	733.5	739.8	740.8	742.9	743.9	744.9	744.9	744.9	743.9	743.9
42.5°	693.2	701.5	709.7	711.8	713.9	716.0	714.9	713.9	713.9	712.9	711.8
45°	663.2	671.5	679.7	680.8	682.8	683.9	684.9	683.9	681.8	680.8	678.7
47.5°	629.0	637.3	646.6	648.7	649.7	651.8	651.8	650.8	649.7	647.7	646.6
50°	595.9	605.3	614.6	615.6	616.6	617.7	616.6	614.6	613.5	611.5	609.4
52.5°	562.8	571.1	579.4	579.4	578.4	578.4	578.4	578.4	579.4	579.4	579.4
55°	528.7	537.0	544.2	544.2	544.2	544.2	545.2	547.3	549.4	550.4	552.5
57.5°	492.5	499.7	507.0	508.0	508.0	509.0	509.0	510.1	512.1	513.2	514.2
60°	454.2	460.4	466.6	467.6	467.6	468.7	470.8	471.8	472.8	473.9	474.9
62.5°	412.8	415.9	420.1	422.1	424.2	426.3	428.3	428.3	429.4	429.4	429.4
65°	373.5	375.6	378.7	379.7	380.7	381.8	383.8	383.8	384.9	384.9	384.9
67.5°	329.0	330.0	332.1	333.1	335.2	336.3	335.2	335.2	335.2	334.2	334.2
70°	284.5	285.6	286.6	287.6	288.7	289.7	289.7	289.7	289.7	288.7	288.7
72.5°	238.0	239.0	239.0	239.0	240.0	240.0	239.0	240.0	241.1	242.1	243.1
75°	192.4	192.4	192.4	192.4	191.4	191.4	193.5	193.5	192.4	192.4	191.4
77.5°	146.9	146.9	146.9	146.9	145.9	145.9	148.0	148.0	146.9	146.9	145.9
80°	104.5	103.5	103.5	103.5	103.5	103.5	102.4	102.4	102.4	102.4	102.4
82.5°	66.2	67.3	67.3	67.3	66.2	66.2	65.2	65.2	65.2	65.2	65.2
85°	35.2	35.2	34.1	35.2	35.2	36.2	37.2	37.2	36.2	36.2	35.2
87.5°	14.5	14.5	14.5	14.5	13.5	13.5	12.4	12.4	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1053.2	1051.2	1048.1	1045.0	1048.1	1051.2	1053.2	1056.3	1055.3	1054.3	1053.2
5°	901.2	898.0	893.9	890.8	893.9	898.0	901.2	904.3	908.4	912.5	916.7
7.5°	817.3	815.3	813.2	811.1	813.2	815.3	817.3	819.4	820.5	821.5	822.5
10°	813.2	813.2	812.2	812.2	812.2	813.2	813.2	813.2	812.2	810.1	809.1
12.5°	905.3	904.3	904.3	903.2	904.3	904.3	905.3	905.3	897.0	888.7	879.4
15°	936.3	937.4	937.4	937.4	937.4	937.4	936.3	936.3	934.3	933.2	931.2
17.5°	938.4	938.4	938.4	938.4	938.4	938.4	938.4	938.4	937.4	936.3	934.3
20°	940.5	940.5	941.5	941.5	941.5	940.5	940.5	939.4	937.4	934.3	932.2
22.5°	937.4	937.4	936.3	936.3	936.3	937.4	937.4	937.4	935.3	933.2	931.2
25°	915.6	916.7	916.7	916.7	916.7	916.7	915.6	915.6	915.6	915.6	914.6
27.5°	901.2	901.2	900.1	900.1	900.1	901.2	901.2	901.2	900.1	898.0	897.0
30°	864.9	863.9	862.9	861.8	862.9	863.9	864.9	866.0	867.0	869.1	870.1
32.5°	828.7	828.7	827.7	826.7	827.7	828.7	828.7	829.8	830.8	832.9	833.9
35°	799.8	799.8	798.7	797.7	798.7	799.8	799.8	800.8	800.8	801.8	801.8
37.5°	772.9	771.8	770.8	769.8	770.8	771.8	772.9	773.9	773.9	774.9	774.9
40°	742.9	742.9	741.8	740.8	741.8	742.9	742.9	743.9	743.9	744.9	744.9
42.5°	711.8	710.8	710.8	709.7	710.8	710.8	711.8	711.8	712.9	713.9	713.9
45°	677.7	677.7	676.6	675.6	676.6	677.7	677.7	678.7	680.8	681.8	683.9
47.5°	645.6	645.6	644.6	643.5	644.6	645.6	645.6	646.6	647.7	649.7	650.8
50°	609.4	609.4	608.4	608.4	608.4	609.4	609.4	609.4	611.5	613.5	614.6
52.5°	580.4	580.4	581.5	581.5	581.5	580.4	580.4	579.4	579.4	579.4	578.4
55°	553.5	553.5	554.6	554.6	554.6	553.5	553.5	552.5	550.4	549.4	547.3
57.5°	514.2	514.2	514.2	514.2	514.2	514.2	514.2	514.2	513.2	512.1	510.1
60°	474.9	474.9	473.9	473.9	473.9	474.9	474.9	474.9	473.9	472.8	471.8
62.5°	429.4	428.3	428.3	427.3	428.3	428.3	429.4	429.4	429.4	429.4	428.3
65°	384.9	383.8	383.8	382.8	383.8	383.8	384.9	384.9	384.9	384.9	383.8
67.5°	335.2	336.3	337.3	338.3	337.3	336.3	335.2	334.2	334.2	335.2	335.2
70°	289.7	289.7	290.7	290.7	290.7	289.7	289.7	288.7	288.7	289.7	289.7
72.5°	242.1	242.1	241.1	240.0	241.1	242.1	242.1	243.1	242.1	241.1	240.0
75°	192.4	193.5	193.5	194.5	193.5	193.5	192.4	191.4	192.4	192.4	193.5
77.5°	145.9	145.9	145.9	145.9	145.9	145.9	145.9	145.9	146.9	146.9	148.0
80°	102.4	102.4	101.4	101.4	101.4	102.4	102.4	102.4	102.4	102.4	102.4
82.5°	66.2	66.2	67.3	67.3	67.3	66.2	66.2	65.2	65.2	65.2	65.2
85°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	36.2	36.2	37.2
87.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1052.2	1055.3	1057.4	1060.5	1062.6	1061.5	1059.5	1058.4	1056.3	1058.4	1060.5
5°	920.8	926.0	933.2	940.5	947.7	950.8	952.9	956.0	958.1	967.4	976.7
7.5°	823.6	827.7	829.8	831.8	833.9	837.0	839.1	842.2	844.2	852.5	860.8
10°	807.0	806.0	804.9	804.9	803.9	802.9	802.9	801.8	800.8	802.9	803.9
12.5°	871.1	861.8	848.4	833.9	820.5	813.2	807.0	799.8	792.5	790.4	787.3
15°	929.1	926.0	920.8	914.6	909.4	888.7	868.0	846.3	825.6	808.0	789.4
17.5°	933.2	932.2	930.1	927.0	925.0	917.7	911.5	904.3	897.0	873.2	848.4
20°	929.1	927.0	923.9	920.8	917.7	913.6	910.5	906.3	902.2	893.9	884.6
22.5°	929.1	925.0	919.8	915.6	910.5	907.4	904.3	900.1	897.0	890.8	884.6
25°	914.6	914.6	910.5	907.4	903.2	897.0	889.8	883.6	876.3	875.3	873.2
27.5°	894.9	892.9	891.8	889.8	888.7	881.5	874.3	867.0	859.8	858.7	856.7
30°	871.1	873.2	871.1	869.1	867.0	859.8	852.5	845.3	838.0	833.9	829.8
32.5°	834.9	840.1	839.1	839.1	838.0	832.9	827.7	821.5	816.3	811.1	804.9
35°	801.8	800.8	801.8	801.8	802.9	799.8	796.7	792.5	789.4	784.2	779.1
37.5°	774.9	772.9	771.8	771.8	770.8	766.7	761.5	757.3	752.2	751.1	749.1
40°	744.9	743.9	742.9	740.8	739.8	733.5	727.3	720.1	713.9	714.9	714.9
42.5°	714.9	716.0	713.9	711.8	709.7	701.5	693.2	684.9	676.6	675.6	673.5
45°	684.9	683.9	682.8	680.8	679.7	671.5	663.2	653.9	645.6	641.5	637.3
47.5°	651.8	651.8	649.7	648.7	646.6	637.3	629.0	619.7	610.4	606.3	602.1
50°	616.6	617.7	616.6	615.6	614.6	605.3	595.9	585.6	576.3	573.2	569.0
52.5°	578.4	578.4	578.4	579.4	579.4	571.1	562.8	553.5	545.2	542.1	538.0
55°	545.2	544.2	544.2	544.2	544.2	537.0	528.7	521.4	513.2	510.1	505.9
57.5°	509.0	509.0	508.0	508.0	507.0	499.7	492.5	484.2	477.0	473.9	470.8
60°	470.8	468.7	467.6	467.6	466.6	460.4	454.2	447.0	440.7	438.7	436.6
62.5°	428.3	426.3	424.2	422.1	420.1	415.9	412.8	408.7	404.5	403.5	401.4
65°	383.8	381.8	380.7	379.7	378.7	375.6	373.5	370.4	367.3	365.2	362.1
67.5°	335.2	336.3	335.2	333.1	332.1	330.0	329.0	326.9	324.9	322.8	320.7
70°	289.7	289.7	288.7	287.6	286.6	285.6	284.5	283.5	282.5	281.4	279.3
72.5°	239.0	240.0	240.0	239.0	239.0	239.0	238.0	238.0	236.9	235.9	233.8
75°	193.5	191.4	191.4	192.4	192.4	192.4	192.4	191.4	191.4	190.4	189.3
77.5°	148.0	145.9	145.9	146.9	146.9	146.9	146.9	146.9	146.9	146.9	146.9
80°	102.4	103.5	103.5	103.5	103.5	103.5	104.5	104.5	104.5	103.5	102.4
82.5°	65.2	66.2	66.2	67.3	67.3	67.3	66.2	66.2	65.2	65.2	65.2
85°	37.2	36.2	35.2	35.2	34.1	35.2	35.2	36.2	36.2	36.2	36.2
87.5°	12.4	13.5	13.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1062.6	1064.6	1068.8	1072.9	1076.0	1080.1	1082.2	1083.2	1085.3	1088.4	1089.5
5°	989.1	1001.5	1010.8	1020.1	1029.4	1038.8	1045.0	1052.2	1058.4	1064.6	1068.8
7.5°	870.1	879.4	897.0	913.6	931.2	947.7	967.4	988.1	1007.7	1024.3	1033.6
10°	810.1	815.3	826.7	838.0	848.4	859.8	879.4	900.1	919.8	948.7	970.5
12.5°	788.4	789.4	795.6	802.9	809.1	815.3	826.7	839.1	850.5	870.1	901.2
15°	784.2	778.0	780.1	783.2	785.3	787.3	795.6	803.9	812.2	826.7	853.6
17.5°	816.3	784.2	780.1	774.9	770.8	765.6	771.8	777.0	783.2	793.6	815.3
20°	860.8	836.0	815.3	794.6	772.9	752.2	755.3	757.3	760.4	769.8	786.3
22.5°	875.3	864.9	834.9	803.9	773.9	742.9	740.8	739.8	737.7	744.9	760.4
25°	868.0	861.8	830.8	799.8	767.7	736.6	730.4	723.2	717.0	725.3	740.8
27.5°	852.5	848.4	821.5	795.6	768.7	741.8	727.3	712.9	698.4	701.5	717.0
30°	830.8	831.8	810.1	787.3	765.6	742.9	720.1	698.4	675.6	676.6	693.2
32.5°	806.0	807.0	789.4	771.8	753.2	735.6	707.7	679.7	651.8	652.8	668.4
35°	779.1	778.0	763.5	748.0	733.5	718.0	687.0	654.9	623.9	622.8	638.4
37.5°	750.1	751.1	736.6	723.2	708.7	694.2	661.1	627.0	593.9	593.9	608.4
40°	719.1	722.2	707.7	694.2	679.7	665.3	631.1	598.0	563.9	567.0	577.3
42.5°	680.8	687.0	672.5	659.1	644.6	630.1	597.0	564.9	531.8	535.9	539.0
45°	642.5	646.6	633.2	619.7	605.3	591.8	561.8	530.8	500.8	503.9	493.5
47.5°	605.3	607.3	592.8	578.4	563.9	549.4	522.5	495.6	468.7	469.7	448.0
50°	569.0	569.0	551.5	533.9	516.3	498.7	478.0	456.3	435.6	431.4	405.6
52.5°	537.0	535.9	515.2	495.6	474.9	454.2	435.6	418.0	399.4	386.9	365.2
55°	503.9	501.8	479.0	456.3	433.5	410.7	394.2	377.6	361.1	334.2	319.7
57.5°	469.7	468.7	444.9	421.1	396.3	372.5	351.8	332.1	311.4	285.6	276.2
60°	433.5	429.4	406.6	383.8	360.0	337.3	312.5	287.6	262.8	243.1	236.9
62.5°	397.3	392.1	371.4	350.7	329.0	308.3	281.4	253.5	226.6	222.4	216.2
65°	358.0	353.8	335.2	315.6	296.9	277.3	252.4	226.6	201.8	200.7	195.5
67.5°	315.6	309.4	293.8	278.3	262.8	247.3	226.6	205.9	185.2	184.2	179.0
70°	274.2	269.0	255.6	242.1	228.7	215.2	199.7	183.1	167.6	165.5	160.4
72.5°	228.7	223.5	213.1	202.8	192.4	182.1	170.7	159.3	148.0	145.9	141.7
75°	186.2	182.1	173.8	165.5	157.3	149.0	140.7	133.5	125.2	124.2	121.1
77.5°	143.8	140.7	134.5	129.3	123.1	116.9	110.7	105.5	99.3	101.4	99.3
80°	101.4	100.4	96.2	92.1	87.9	83.8	79.7	76.6	72.4	74.5	72.4
82.5°	65.2	65.2	63.1	61.0	57.9	55.9	52.8	50.7	47.6	49.7	47.6
85°	36.2	35.2	34.1	33.1	32.1	31.0	30.0	27.9	26.9	27.9	26.9
87.5°	15.5	15.5	15.5	15.5	14.5	14.5	13.5	13.5	12.4	12.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1090.5	1091.5	1092.6	1095.7	1097.7	1100.8	1102.9	1102.9	1102.9	1102.9	1102.9
5°	1072.9	1076.0	1080.1	1085.3	1089.5	1094.6	1098.8	1100.8	1102.9	1105.0	1107.0
7.5°	1042.9	1052.2	1061.5	1068.8	1076.0	1083.2	1090.5	1094.6	1098.8	1101.9	1106.0
10°	993.2	1015.0	1036.7	1048.1	1058.4	1069.8	1080.1	1085.3	1091.5	1096.7	1101.9
12.5°	932.2	962.2	993.2	1011.9	1029.4	1048.1	1065.7	1072.9	1081.2	1088.4	1095.7
15°	881.5	908.4	935.3	964.3	992.2	1021.2	1049.1	1058.4	1066.7	1076.0	1084.3
17.5°	836.0	857.7	878.4	915.6	952.9	989.1	1026.3	1037.7	1048.1	1059.5	1069.8
20°	803.9	820.5	837.0	878.4	918.7	960.1	1000.5	1012.9	1025.3	1037.7	1050.1
22.5°	777.0	792.5	808.0	847.4	886.7	926.0	965.3	981.9	997.4	1013.9	1029.4
25°	755.3	770.8	785.3	820.5	854.6	889.8	923.9	944.6	965.3	986.0	1006.7
27.5°	733.5	749.1	764.6	793.6	822.5	851.5	880.5	905.3	929.1	953.9	977.7
30°	709.7	726.3	742.9	765.6	787.3	810.1	831.8	858.7	884.6	911.5	937.4
32.5°	684.9	700.4	716.0	731.5	747.0	761.5	777.0	801.8	827.7	852.5	877.4
35°	653.9	669.4	684.9	689.1	694.2	698.4	702.5	734.6	766.7	798.7	830.8
37.5°	622.8	636.3	650.8	643.5	636.3	628.0	620.8	663.2	705.6	748.0	790.4
40°	586.6	597.0	606.3	591.8	577.3	562.8	548.3	592.8	638.4	682.8	727.3
42.5°	542.1	544.2	547.3	533.9	521.4	508.0	494.5	535.9	576.3	617.7	658.0
45°	483.2	472.8	462.5	460.4	458.3	455.2	453.2	499.7	546.3	592.8	639.4
47.5°	427.3	405.6	383.8	398.3	411.8	426.3	439.7	480.1	521.4	561.8	602.1
50°	380.7	354.9	329.0	356.9	383.8	411.8	438.7	469.7	499.7	530.8	560.8
52.5°	342.5	320.7	298.0	322.8	348.7	373.5	398.3	426.3	454.2	482.1	510.1
55°	304.2	289.7	274.2	298.0	321.8	345.6	369.4	391.1	413.8	435.6	457.3
57.5°	265.9	256.6	246.2	275.2	305.2	334.2	363.2	367.3	372.5	376.6	380.7
60°	229.7	223.5	216.2	245.2	275.2	304.2	333.1	318.7	304.2	289.7	275.2
62.5°	209.0	202.8	195.5	222.4	249.3	275.2	302.1	276.2	251.4	225.5	199.7
65°	189.3	184.2	178.0	197.6	217.3	236.9	256.6	234.9	212.1	190.4	167.6
67.5°	172.8	167.6	161.4	169.7	179.0	187.3	195.5	181.1	166.6	151.1	136.6
70°	155.2	149.0	143.8	143.8	144.8	144.8	144.8	131.4	117.9	104.5	91.0
72.5°	137.6	133.5	129.3	127.3	125.2	122.1	120.0	108.6	97.3	84.8	73.5
75°	119.0	115.9	112.8	108.6	105.5	101.4	97.3	92.1	87.9	82.8	77.6
77.5°	96.2	94.2	91.0	85.9	81.7	76.6	71.4	71.4	72.4	72.4	72.4
80°	70.4	67.3	65.2	62.1	60.0	56.9	53.8	54.8	55.9	55.9	56.9
82.5°	45.5	43.5	41.4	40.4	39.3	37.2	36.2	36.2	36.2	36.2	36.2
85°	24.8	23.8	21.7	20.7	19.7	17.6	16.6	17.6	18.6	19.7	20.7
87.5°	10.3	9.3	8.3	7.2	7.2	6.2	5.2	6.2	7.2	8.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1105.0	1106.0	1108.1	1109.1	1111.2	1111.2	1111.2	1111.2	1110.1	1110.1	1109.1
5°	1110.1	1113.3	1115.3	1118.4	1120.5	1121.5	1121.5	1122.6	1122.6	1122.6	1121.5
7.5°	1110.1	1113.3	1117.4	1120.5	1123.6	1124.6	1125.7	1126.7	1125.7	1125.7	1124.6
10°	1106.0	1110.1	1114.3	1118.4	1120.5	1121.5	1122.6	1123.6	1122.6	1122.6	1121.5
12.5°	1099.8	1103.9	1107.0	1111.2	1113.3	1114.3	1116.4	1117.4	1117.4	1117.4	1116.4
15°	1088.4	1091.5	1095.7	1098.8	1100.8	1102.9	1106.0	1108.1	1108.1	1107.0	1107.0
17.5°	1073.9	1078.1	1082.2	1086.4	1089.5	1091.5	1092.6	1094.6	1094.6	1094.6	1093.6
20°	1055.3	1060.5	1064.6	1069.8	1072.9	1075.0	1076.0	1078.1	1078.1	1078.1	1078.1
22.5°	1034.6	1039.8	1045.0	1050.1	1052.2	1054.3	1056.3	1058.4	1058.4	1058.4	1058.4
25°	1010.8	1016.0	1020.1	1024.3	1030.5	1032.6	1034.6	1036.7	1037.7	1038.8	1038.8
27.5°	983.9	989.1	995.3	1000.5	1004.6	1007.7	1009.8	1012.9	1013.9	1015.0	1015.0
30°	945.6	955.0	963.2	971.5	975.6	979.8	985.0	989.1	990.1	990.1	991.2
32.5°	893.9	909.4	926.0	941.5	950.8	955.0	959.1	963.2	962.2	960.1	959.1
35°	851.5	872.2	892.9	913.6	921.8	925.0	928.1	931.2	929.1	928.1	926.0
37.5°	814.2	838.0	860.8	884.6	890.8	892.9	896.0	898.0	896.0	893.9	890.8
40°	758.4	789.4	819.4	850.5	854.6	856.7	858.7	860.8	858.7	857.7	855.6
42.5°	697.3	736.6	774.9	814.2	819.4	818.4	816.3	815.3	816.3	818.4	819.4
45°	673.5	707.7	740.8	774.9	781.1	779.1	777.0	774.9	777.0	779.1	781.1
47.5°	635.3	669.4	702.5	735.6	735.6	734.6	733.5	732.5	735.6	737.7	740.8
50°	590.8	621.8	651.8	681.8	677.7	682.8	687.0	692.2	695.3	698.4	701.5
52.5°	535.9	561.8	586.6	612.5	628.0	635.3	643.5	650.8	652.8	654.9	655.9
55°	480.1	503.9	526.6	549.4	580.4	588.7	595.9	604.2	606.3	609.4	611.5
57.5°	408.7	436.6	463.5	491.4	530.8	540.1	550.4	559.7	559.7	559.7	558.7
60°	313.5	352.8	391.1	429.4	475.9	486.3	495.6	505.9	504.9	504.9	503.9
62.5°	240.0	279.3	319.7	359.0	411.8	426.3	439.7	454.2	454.2	454.2	453.2
65°	189.3	212.1	233.8	255.6	342.5	363.2	382.8	403.5	404.5	404.5	405.6
67.5°	145.9	155.2	163.5	172.8	285.6	308.3	332.1	354.9	354.9	353.8	353.8
70°	98.3	105.5	112.8	120.0	231.8	256.6	282.5	307.3	306.2	305.2	303.1
72.5°	77.6	80.7	84.8	87.9	180.0	205.9	232.8	258.7	257.6	255.6	254.5
75°	75.5	72.4	70.4	67.3	133.5	159.3	184.2	210.0	209.0	208.0	206.9
77.5°	68.3	63.1	59.0	53.8	98.3	121.1	143.8	166.6	165.5	163.5	162.4
80°	52.8	48.6	44.5	40.4	67.3	84.8	102.4	120.0	120.0	120.0	120.0
82.5°	35.2	33.1	32.1	30.0	42.4	55.9	68.3	81.7	80.7	80.7	79.7
85°	20.7	19.7	19.7	18.6	25.9	32.1	38.3	44.5	45.5	45.5	46.6
87.5°	10.3	10.3	11.4	11.4	14.5	17.6	19.7	22.8	22.8	23.8	23.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1108.1	1107.0	1105.0	1107.0	1108.1	1110.1	1113.3	1115.3	1117.4	1118.4	1119.5
5°	1121.5	1120.5	1119.5	1120.5	1121.5	1124.6	1126.7	1129.8	1131.9	1132.9	1132.9
7.5°	1123.6	1123.6	1122.6	1123.6	1124.6	1127.7	1129.8	1132.9	1135.0	1136.0	1136.0
10°	1120.5	1120.5	1120.5	1122.6	1124.6	1127.7	1129.8	1132.9	1135.0	1136.0	1136.0
12.5°	1116.4	1116.4	1115.3	1117.4	1119.5	1122.6	1124.6	1127.7	1129.8	1130.8	1130.8
15°	1106.0	1106.0	1106.0	1108.1	1110.1	1113.3	1116.4	1118.4	1121.5	1122.6	1123.6
17.5°	1093.6	1094.6	1094.6	1096.7	1098.8	1101.9	1103.9	1107.0	1109.1	1110.1	1110.1
20°	1078.1	1078.1	1078.1	1081.2	1083.2	1086.4	1088.4	1091.5	1093.6	1094.6	1096.7
22.5°	1058.4	1059.5	1060.5	1064.6	1067.7	1069.8	1072.9	1075.0	1077.0	1077.0	1078.1
25°	1039.8	1041.9	1042.9	1045.0	1047.0	1048.1	1049.1	1049.1	1050.1	1050.1	1049.1
27.5°	1016.0	1018.1	1020.1	1021.2	1021.2	1021.2	1022.2	1022.2	1022.2	1023.2	1024.3
30°	991.2	989.1	987.0	988.1	989.1	990.1	992.2	993.2	994.3	995.3	995.3
32.5°	957.0	957.0	956.0	958.1	959.1	961.2	963.2	965.3	967.4	967.4	967.4
35°	923.9	926.0	928.1	929.1	929.1	930.1	932.2	933.2	934.3	935.3	936.3
37.5°	888.7	891.8	894.9	897.0	898.0	899.1	900.1	901.2	902.2	901.2	901.2
40°	853.6	856.7	859.8	860.8	861.8	862.9	862.9	863.9	863.9	862.9	862.9
42.5°	820.5	821.5	822.5	824.6	826.7	825.6	825.6	824.6	823.6	822.5	820.5
45°	783.2	785.3	786.3	786.3	786.3	784.2	782.2	779.1	777.0	776.0	776.0
47.5°	742.9	746.0	748.0	744.9	740.8	738.7	736.6	733.5	731.5	730.4	729.4
50°	704.6	702.5	699.4	696.3	692.2	690.1	689.1	687.0	684.9	680.8	677.7
52.5°	658.0	653.9	649.7	646.6	642.5	639.4	636.3	633.2	630.1	628.0	627.0
55°	613.5	606.3	598.0	594.9	590.8	586.6	581.5	577.3	572.1	571.1	570.1
57.5°	558.7	554.6	549.4	543.2	535.9	531.8	528.7	524.6	520.4	519.4	518.3
60°	502.8	498.7	494.5	488.3	482.1	479.0	474.9	471.8	467.6	466.6	466.6
62.5°	453.2	450.1	445.9	436.6	427.3	425.2	422.1	420.1	417.0	414.9	413.8
65°	405.6	398.3	390.1	383.8	376.6	373.5	371.4	368.3	365.2	363.2	361.1
67.5°	352.8	343.5	333.1	330.0	326.9	323.8	319.7	316.6	312.5	311.4	310.4
70°	302.1	294.9	286.6	283.5	279.3	276.2	273.1	269.0	265.9	263.8	260.7
72.5°	252.4	246.2	239.0	234.9	230.7	227.6	225.5	222.4	219.3	217.3	215.2
75°	205.9	199.7	193.5	189.3	185.2	183.1	181.1	178.0	175.9	172.8	170.7
77.5°	160.4	157.3	153.1	148.0	142.8	141.7	140.7	139.7	138.6	135.5	133.5
80°	120.0	116.9	113.8	110.7	106.6	104.5	103.5	101.4	99.3	98.3	96.2
82.5°	78.6	76.6	74.5	73.5	72.4	71.4	70.4	69.3	68.3	67.3	67.3
85°	46.6	46.6	46.6	45.5	44.5	44.5	44.5	43.5	43.5	42.4	42.4
87.5°	23.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	24.8	25.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1120.5	1119.5	1120.5	1120.5	1121.5	1121.5	1120.5	1120.5	1119.5	1118.4	1119.5
5°	1133.9	1135.0	1135.0	1135.0	1135.0	1135.0	1135.0	1133.9	1133.9	1132.9	1133.9
7.5°	1137.0	1137.0	1138.1	1138.1	1139.1	1139.1	1138.1	1138.1	1137.0	1136.0	1137.0
10°	1137.0	1138.1	1138.1	1139.1	1139.1	1139.1	1138.1	1138.1	1137.0	1136.0	1137.0
12.5°	1131.9	1131.9	1132.9	1132.9	1133.9	1133.9	1133.9	1132.9	1132.9	1131.9	1132.9
15°	1124.6	1123.6	1124.6	1124.6	1125.7	1125.7	1124.6	1124.6	1123.6	1122.6	1123.6
17.5°	1111.2	1112.2	1112.2	1113.3	1113.3	1113.3	1112.2	1111.2	1110.1	1109.1	1110.1
20°	1097.7	1097.7	1097.7	1098.8	1098.8	1098.8	1097.7	1097.7	1096.7	1095.7	1096.7
22.5°	1078.1	1078.1	1078.1	1077.0	1077.0	1076.0	1075.0	1075.0	1073.9	1072.9	1073.9
25°	1049.1	1050.1	1050.1	1050.1	1050.1	1050.1	1049.1	1049.1	1048.1	1047.0	1048.1
27.5°	1025.3	1023.2	1024.3	1024.3	1025.3	1025.3	1025.3	1024.3	1024.3	1023.2	1024.3
30°	996.3	998.4	999.4	999.4	1000.5	1000.5	1000.5	999.4	999.4	998.4	999.4
32.5°	967.4	969.4	969.4	969.4	969.4	969.4	969.4	968.4	968.4	967.4	968.4
35°	937.4	936.3	936.3	937.4	937.4	937.4	936.3	936.3	935.3	934.3	935.3
37.5°	900.1	900.1	900.1	900.1	900.1	900.1	899.1	899.1	898.0	897.0	898.0
40°	861.8	860.8	860.8	861.8	861.8	861.8	860.8	859.8	858.7	857.7	858.7
42.5°	819.4	819.4	819.4	819.4	818.4	818.4	818.4	818.4	817.3	817.3	817.3
45°	774.9	773.9	773.9	772.9	772.9	771.8	771.8	770.8	770.8	769.8	770.8
47.5°	728.4	728.4	727.3	725.3	724.2	722.2	721.1	720.1	718.0	717.0	718.0
50°	673.5	673.5	672.5	671.5	670.4	669.4	669.4	670.4	670.4	670.4	670.4
52.5°	624.9	620.8	619.7	619.7	618.7	617.7	617.7	617.7	616.6	616.6	616.6
55°	569.0	567.0	567.0	567.0	565.9	565.9	567.0	567.0	568.0	568.0	568.0
57.5°	517.3	516.3	516.3	515.2	515.2	514.2	513.2	513.2	512.1	511.1	512.1
60°	465.6	463.5	461.4	459.4	456.3	454.2	453.2	452.1	451.1	450.1	451.1
62.5°	411.8	407.6	406.6	404.5	403.5	401.4	399.4	398.3	396.3	394.2	396.3
65°	359.0	358.0	354.9	351.8	348.7	345.6	344.5	344.5	343.5	342.5	343.5
67.5°	309.4	303.1	301.1	299.0	296.9	294.9	294.9	294.9	294.9	294.9	294.9
70°	258.7	254.5	253.5	251.4	250.4	248.3	248.3	248.3	247.3	247.3	247.3
72.5°	213.1	209.0	208.0	206.9	204.9	203.8	203.8	203.8	202.8	202.8	202.8
75°	167.6	168.6	167.6	166.6	165.5	164.5	164.5	163.5	163.5	162.4	163.5
77.5°	130.4	130.4	129.3	128.3	127.3	126.2	126.2	126.2	126.2	126.2	126.2
80°	95.2	95.2	95.2	95.2	94.2	94.2	94.2	94.2	93.1	93.1	93.1
82.5°	66.2	66.2	66.2	66.2	66.2	66.2	66.2	65.2	65.2	64.1	65.2
85°	41.4	42.4	42.4	42.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
87.5°	25.9	25.9	25.9	26.9	26.9	26.9	26.9	26.9	25.9	25.9	25.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1120.5	1120.5	1121.5	1121.5	1120.5	1120.5	1119.5	1120.5	1119.5	1118.4	1117.4
5°	1133.9	1135.0	1135.0	1135.0	1135.0	1135.0	1135.0	1133.9	1132.9	1132.9	1131.9
7.5°	1138.1	1138.1	1139.1	1139.1	1138.1	1138.1	1137.0	1137.0	1136.0	1136.0	1135.0
10°	1138.1	1138.1	1139.1	1139.1	1139.1	1138.1	1138.1	1137.0	1136.0	1136.0	1135.0
12.5°	1132.9	1133.9	1133.9	1133.9	1132.9	1132.9	1131.9	1131.9	1130.8	1130.8	1129.8
15°	1124.6	1124.6	1125.7	1125.7	1124.6	1124.6	1123.6	1124.6	1123.6	1122.6	1121.5
17.5°	1111.2	1112.2	1113.3	1113.3	1113.3	1112.2	1112.2	1111.2	1110.1	1110.1	1109.1
20°	1097.7	1097.7	1098.8	1098.8	1098.8	1097.7	1097.7	1097.7	1096.7	1094.6	1093.6
22.5°	1075.0	1075.0	1076.0	1077.0	1077.0	1078.1	1078.1	1078.1	1078.1	1077.0	1077.0
25°	1049.1	1049.1	1050.1	1050.1	1050.1	1050.1	1050.1	1049.1	1049.1	1050.1	1050.1
27.5°	1024.3	1025.3	1025.3	1025.3	1024.3	1024.3	1023.2	1025.3	1024.3	1023.2	1022.2
30°	999.4	1000.5	1000.5	1000.5	999.4	999.4	998.4	996.3	995.3	995.3	994.3
32.5°	968.4	969.4	969.4	969.4	969.4	969.4	969.4	967.4	967.4	967.4	967.4
35°	936.3	936.3	937.4	937.4	937.4	936.3	936.3	937.4	936.3	935.3	934.3
37.5°	899.1	899.1	900.1	900.1	900.1	900.1	900.1	900.1	901.2	901.2	902.2
40°	859.8	860.8	861.8	861.8	861.8	860.8	860.8	861.8	862.9	862.9	863.9
42.5°	818.4	818.4	818.4	818.4	819.4	819.4	819.4	819.4	820.5	822.5	823.6
45°	770.8	771.8	771.8	772.9	772.9	773.9	773.9	774.9	776.0	776.0	777.0
47.5°	720.1	721.1	722.2	724.2	725.3	727.3	728.4	728.4	729.4	730.4	731.5
50°	670.4	669.4	669.4	670.4	671.5	672.5	673.5	673.5	677.7	680.8	684.9
52.5°	617.7	617.7	617.7	618.7	619.7	619.7	620.8	624.9	627.0	628.0	630.1
55°	567.0	567.0	565.9	565.9	567.0	567.0	567.0	569.0	570.1	571.1	572.1
57.5°	513.2	513.2	514.2	515.2	515.2	516.3	516.3	517.3	518.3	519.4	520.4
60°	452.1	453.2	454.2	456.3	459.4	461.4	463.5	465.6	466.6	466.6	467.6
62.5°	398.3	399.4	401.4	403.5	404.5	406.6	407.6	411.8	413.8	414.9	417.0
65°	344.5	344.5	345.6	348.7	351.8	354.9	358.0	359.0	361.1	363.2	365.2
67.5°	294.9	294.9	294.9	296.9	299.0	301.1	303.1	309.4	310.4	311.4	312.5
70°	248.3	248.3	248.3	250.4	251.4	253.5	254.5	258.7	260.7	263.8	265.9
72.5°	203.8	203.8	203.8	204.9	206.9	208.0	209.0	213.1	215.2	217.3	219.3
75°	163.5	164.5	164.5	165.5	166.6	167.6	168.6	167.6	170.7	172.8	175.9
77.5°	126.2	126.2	126.2	127.3	128.3	129.3	130.4	130.4	133.5	135.5	138.6
80°	94.2	94.2	94.2	94.2	95.2	95.2	95.2	95.2	96.2	98.3	99.3
82.5°	65.2	66.2	66.2	66.2	66.2	66.2	66.2	66.2	67.3	67.3	68.3
85°	41.4	41.4	41.4	41.4	42.4	42.4	42.4	41.4	42.4	42.4	43.5
87.5°	26.9	26.9	26.9	26.9	26.9	25.9	25.9	25.9	25.9	24.8	24.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1115.3	1113.3	1110.1	1108.1	1107.0	1105.0	1107.0	1108.1	1109.1	1110.1	1110.1
5°	1129.8	1126.7	1124.6	1121.5	1120.5	1119.5	1120.5	1121.5	1121.5	1122.6	1122.6
7.5°	1132.9	1129.8	1127.7	1124.6	1123.6	1122.6	1123.6	1123.6	1124.6	1125.7	1125.7
10°	1132.9	1129.8	1127.7	1124.6	1122.6	1120.5	1120.5	1120.5	1121.5	1122.6	1122.6
12.5°	1127.7	1124.6	1122.6	1119.5	1117.4	1115.3	1116.4	1116.4	1116.4	1117.4	1117.4
15°	1118.4	1116.4	1113.3	1110.1	1108.1	1106.0	1106.0	1106.0	1107.0	1107.0	1108.1
17.5°	1107.0	1103.9	1101.9	1098.8	1096.7	1094.6	1094.6	1093.6	1093.6	1094.6	1094.6
20°	1091.5	1088.4	1086.4	1083.2	1081.2	1078.1	1078.1	1078.1	1078.1	1078.1	1078.1
22.5°	1075.0	1072.9	1069.8	1067.7	1063.6	1060.5	1059.5	1058.4	1058.4	1058.4	1058.4
25°	1049.1	1049.1	1048.1	1047.0	1045.0	1042.9	1041.9	1039.8	1038.8	1038.8	1037.7
27.5°	1022.2	1022.2	1021.2	1021.2	1021.2	1020.1	1018.1	1016.0	1015.0	1015.0	1013.9
30°	993.2	992.2	990.1	989.1	988.1	987.0	989.1	991.2	991.2	990.1	990.1
32.5°	965.3	963.2	961.2	959.1	958.1	956.0	957.0	957.0	959.1	960.1	962.2
35°	933.2	932.2	930.1	929.1	929.1	928.1	926.0	923.9	926.0	928.1	929.1
37.5°	901.2	900.1	899.1	898.0	897.0	894.9	891.8	888.7	890.8	892.9	896.0
40°	863.9	862.9	862.9	861.8	860.8	859.8	856.7	853.6	855.6	857.7	858.7
42.5°	824.6	825.6	825.6	826.7	824.6	822.5	821.5	820.5	819.4	818.4	816.3
45°	779.1	782.2	784.2	786.3	786.3	786.3	785.3	783.2	781.1	779.1	777.0
47.5°	733.5	736.6	738.7	740.8	744.9	748.0	746.0	742.9	740.8	737.7	735.6
50°	687.0	689.1	690.1	692.2	696.3	699.4	702.5	704.6	701.5	698.4	695.3
52.5°	633.2	636.3	639.4	642.5	646.6	649.7	653.9	658.0	655.9	654.9	652.8
55°	577.3	581.5	586.6	590.8	594.9	598.0	606.3	613.5	611.5	609.4	606.3
57.5°	524.6	527.7	531.8	535.9	543.2	549.4	554.6	558.7	558.7	559.7	559.7
60°	471.8	474.9	479.0	482.1	488.3	494.5	498.7	502.8	503.9	504.9	504.9
62.5°	420.1	422.1	425.2	427.3	436.6	445.9	450.1	453.2	453.2	454.2	454.2
65°	368.3	371.4	373.5	376.6	383.8	390.1	398.3	405.6	405.6	404.5	404.5
67.5°	316.6	319.7	323.8	326.9	330.0	333.1	343.5	352.8	353.8	353.8	354.9
70°	269.0	273.1	276.2	279.3	283.5	286.6	294.9	302.1	303.1	305.2	306.2
72.5°	222.4	225.5	227.6	230.7	234.9	239.0	246.2	252.4	254.5	255.6	257.6
75°	178.0	181.1	183.1	185.2	189.3	193.5	199.7	205.9	206.9	208.0	209.0
77.5°	139.7	140.7	141.7	142.8	148.0	153.1	157.3	160.4	162.4	163.5	165.5
80°	101.4	103.5	104.5	106.6	110.7	113.8	116.9	120.0	120.0	120.0	120.0
82.5°	69.3	70.4	71.4	72.4	73.5	74.5	76.6	78.6	79.7	80.7	80.7
85°	43.5	44.5	44.5	44.5	45.5	46.6	46.6	46.6	46.6	45.5	45.5
87.5°	24.8	24.8	24.8	24.8	24.8	24.8	24.8	23.8	23.8	23.8	22.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
2.5°	1111.2	1111.2	1111.2	1111.2	1109.1	1108.1	1106.0	1105.0	1102.9	1102.9	1102.9
5°	1122.6	1121.5	1121.5	1120.5	1118.4	1115.3	1112.2	1110.1	1107.0	1105.0	1102.9
7.5°	1126.7	1125.7	1124.6	1123.6	1120.5	1117.4	1113.3	1110.1	1106.0	1101.9	1097.7
10°	1123.6	1122.6	1121.5	1120.5	1118.4	1114.3	1110.1	1106.0	1101.9	1096.7	1090.5
12.5°	1117.4	1116.4	1114.3	1113.3	1111.2	1107.0	1102.9	1099.8	1095.7	1088.4	1080.1
15°	1108.1	1106.0	1102.9	1100.8	1098.8	1095.7	1091.5	1088.4	1084.3	1076.0	1066.7
17.5°	1094.6	1092.6	1091.5	1089.5	1086.4	1082.2	1078.1	1073.9	1069.8	1059.5	1048.1
20°	1078.1	1076.0	1075.0	1072.9	1069.8	1064.6	1059.5	1055.3	1050.1	1037.7	1025.3
22.5°	1058.4	1056.3	1054.3	1052.2	1050.1	1045.0	1039.8	1034.6	1029.4	1013.9	997.4
25°	1036.7	1034.6	1032.6	1030.5	1024.3	1020.1	1015.0	1010.8	1006.7	986.0	965.3
27.5°	1012.9	1009.8	1007.7	1004.6	1000.5	995.3	989.1	983.9	977.7	953.9	929.1
30°	989.1	985.0	979.8	975.6	971.5	963.2	953.9	945.6	937.4	911.5	884.6
32.5°	963.2	959.1	955.0	950.8	941.5	926.0	909.4	893.9	877.4	852.5	826.7
35°	931.2	928.1	925.0	921.8	913.6	892.9	872.2	851.5	830.8	798.7	766.7
37.5°	898.0	896.0	892.9	890.8	884.6	860.8	837.0	814.2	790.4	748.0	705.6
40°	860.8	858.7	856.7	854.6	850.5	819.4	788.4	758.4	727.3	682.8	637.3
42.5°	815.3	816.3	818.4	819.4	814.2	774.9	735.6	697.3	658.0	617.7	576.3
45°	774.9	777.0	779.1	781.1	774.9	740.8	706.6	673.5	639.4	592.8	546.3
47.5°	732.5	733.5	734.6	735.6	735.6	702.5	668.4	635.3	602.1	561.8	520.4
50°	692.2	687.0	682.8	677.7	681.8	651.8	620.8	590.8	560.8	530.8	499.7
52.5°	650.8	643.5	635.3	628.0	612.5	586.6	560.8	535.9	510.1	482.1	454.2
55°	604.2	595.9	588.7	580.4	549.4	526.6	502.8	480.1	457.3	435.6	412.8
57.5°	559.7	550.4	540.1	530.8	491.4	463.5	435.6	408.7	380.7	376.6	371.4
60°	505.9	495.6	486.3	475.9	429.4	391.1	351.8	313.5	275.2	289.7	304.2
62.5°	454.2	439.7	426.3	411.8	359.0	319.7	279.3	240.0	199.7	225.5	251.4
65°	403.5	382.8	363.2	342.5	255.6	233.8	211.1	189.3	167.6	190.4	212.1
67.5°	354.9	332.1	308.3	285.6	172.8	163.5	154.2	145.9	136.6	151.1	166.6
70°	307.3	282.5	256.6	231.8	120.0	112.8	105.5	98.3	91.0	104.5	117.9
72.5°	258.7	232.8	205.9	180.0	87.9	84.8	80.7	77.6	73.5	84.8	97.3
75°	210.0	184.2	159.3	133.5	67.3	70.4	72.4	75.5	77.6	82.8	87.9
77.5°	166.6	143.8	121.1	98.3	53.8	59.0	63.1	68.3	72.4	72.4	72.4
80°	120.0	102.4	84.8	67.3	40.4	44.5	48.6	52.8	56.9	55.9	55.9
82.5°	81.7	68.3	55.9	42.4	30.0	32.1	33.1	35.2	36.2	36.2	36.2
85°	44.5	38.3	32.1	25.9	18.6	19.7	19.7	20.7	20.7	19.7	18.6
87.5°	22.8	19.7	17.6	14.5	11.4	11.4	10.3	10.3	9.3	8.3	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1093.6	1093.6
2.5°	1102.9	1102.9
5°	1100.8	1098.8
7.5°	1094.6	1090.5
10°	1085.3	1080.1
12.5°	1072.9	1065.7
15°	1058.4	1049.1
17.5°	1037.7	1026.3
20°	1012.9	1000.5
22.5°	981.9	965.3
25°	944.6	923.9
27.5°	905.3	880.5
30°	858.7	831.8
32.5°	801.8	777.0
35°	734.6	702.5
37.5°	663.2	620.8
40°	592.8	548.3
42.5°	535.9	494.5
45°	499.7	453.2
47.5°	480.1	439.7
50°	469.7	438.7
52.5°	426.3	398.3
55°	391.1	369.4
57.5°	367.3	363.2
60°	318.7	333.1
62.5°	276.2	302.1
65°	234.9	256.6
67.5°	181.1	195.5
70°	131.4	144.8
72.5°	108.6	120.0
75°	92.1	97.3
77.5°	71.4	71.4
80°	54.8	53.8
82.5°	36.2	36.2
85°	17.6	16.6
87.5°	6.2	5.2
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

TEST NUMBER: P1055038

CATALOG NUMBER: SQ4R-FA-075D-840-1-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.27	19.88	18.64	20.20	20.51	20.19	21.80	20.55	22.11	22.43
	3H	18.94	20.39	19.31	20.72	21.08	21.99	23.44	22.36	23.76	24.13
	4H	19.27	20.64	19.67	20.98	21.36	22.61	23.97	23.00	24.32	24.70
	6H	19.56	20.82	19.97	21.19	21.58	22.99	24.25	23.40	24.62	25.01
	8H	19.63	20.84	20.06	21.23	21.63	23.09	24.29	23.51	24.68	25.08
	12H	19.66	20.82	20.09	21.20	21.63	23.13	24.29	23.56	24.67	25.10
4H	2H	19.40	20.77	19.80	21.12	21.49	20.76	22.12	21.16	22.47	22.85
	3H	20.72	21.86	21.13	22.26	22.66	22.79	23.93	23.20	24.33	24.73
	4H	21.15	22.18	21.59	22.60	23.03	23.53	24.56	23.96	24.97	25.41
	6H	21.45	22.34	21.90	22.79	23.24	24.02	24.92	24.48	25.36	25.82
	8H	21.53	22.37	21.99	22.81	23.27	24.15	24.99	24.61	25.43	25.90
	12H	21.57	22.32	22.05	22.80	23.27	24.22	24.98	24.70	25.45	25.92
8H	4H	21.74	22.58	22.20	23.03	23.49	23.76	24.60	24.22	25.04	25.50
	6H	22.23	22.92	22.72	23.41	23.89	24.35	25.05	24.84	25.54	26.01
	8H	22.35	22.98	22.86	23.49	23.97	24.53	25.16	25.04	25.66	26.15
	12H	22.43	22.98	22.93	23.47	24.03	24.65	25.21	25.16	25.70	26.26
12H	4H	21.80	22.55	22.28	23.03	23.49	23.76	24.51	24.24	24.99	25.46
	6H	22.32	22.95	22.83	23.46	23.94	24.37	25.00	24.88	25.50	25.99
	8H	22.53	23.08	23.04	23.57	24.13	24.59	25.15	25.10	25.64	26.20