

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216868

Luminaire Tested: 14-ID2-45-CFR2-L950-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216868  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 14-ID2-45-CFR2-L950-U  
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE REGRESS LENS  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4144.1 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.16 / 1.28  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 39.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216868  
CATALOG NUMBER: 14-ID2-45-CFR2-L950-U

### Luminous Intensity Polar Plot



TEST NUMBER: P1216868  
 CATALOG NUMBER: 14-ID2-45-CFR2-L950-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 110 | 105 | 101 | 98  | 107 | 103 | 99  | 96  | 99  | 96  | 93  | 95  | 93  | 90  | 91  | 89  | 88  | 88  | 88  | 86  |
| 2   | 100 | 93  | 86  | 81  | 98  | 91  | 85  | 80  | 87  | 82  | 78  | 84  | 80  | 76  | 81  | 78  | 75  | 75  | 75  | 72  |
| 3   | 92  | 82  | 74  | 68  | 89  | 80  | 73  | 67  | 77  | 71  | 66  | 75  | 70  | 65  | 72  | 68  | 64  | 64  | 64  | 62  |
| 4   | 84  | 73  | 65  | 58  | 82  | 72  | 64  | 58  | 69  | 62  | 57  | 67  | 61  | 56  | 65  | 60  | 56  | 56  | 56  | 53  |
| 5   | 78  | 66  | 57  | 51  | 76  | 64  | 56  | 50  | 62  | 55  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 49  | 49  | 47  |
| 6   | 72  | 59  | 51  | 44  | 70  | 58  | 50  | 44  | 57  | 49  | 44  | 55  | 48  | 44  | 53  | 48  | 43  | 43  | 43  | 41  |
| 7   | 67  | 54  | 45  | 40  | 65  | 53  | 45  | 39  | 52  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 39  | 39  | 39  | 37  |
| 8   | 62  | 49  | 41  | 35  | 61  | 49  | 41  | 35  | 47  | 40  | 35  | 46  | 40  | 35  | 45  | 39  | 35  | 35  | 35  | 33  |
| 9   | 58  | 45  | 37  | 32  | 57  | 45  | 37  | 32  | 44  | 37  | 32  | 43  | 36  | 32  | 42  | 36  | 31  | 31  | 31  | 30  |
| 10  | 55  | 42  | 34  | 29  | 54  | 41  | 34  | 29  | 40  | 34  | 29  | 40  | 33  | 29  | 39  | 33  | 29  | 29  | 29  | 27  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 4596 | 4596 | 4596 |
| 5°  | 4607 | 4590 | 4610 |
| 10° | 4592 | 4588 | 4608 |
| 15° | 4560 | 4554 | 4535 |
| 20° | 4508 | 4473 | 4421 |
| 25° | 4440 | 4356 | 4280 |
| 30° | 4351 | 4224 | 4123 |
| 35° | 4235 | 4065 | 3955 |
| 40° | 4108 | 3890 | 3758 |
| 45° | 3961 | 3697 | 3543 |
| 50° | 3791 | 3478 | 3306 |
| 55° | 3595 | 3244 | 3054 |
| 60° | 3392 | 2986 | 2779 |
| 65° | 3164 | 2700 | 2469 |
| 70° | 2877 | 2389 | 2124 |
| 75° | 2520 | 2030 | 1673 |
| 80° | 2035 | 1502 | 1168 |
| 85° | 1371 | 1102 | 976  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3961 cd/sqm

TEST NUMBER: P1216868  
 CATALOG NUMBER: 14-ID2-45-CFR2-L950-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 161.9  | 3.9       |
| 10°-20°   | 460.0  | 11.1      |
| 20°-30°   | 676.4  | 16.3      |
| 30°-40°   | 777.8  | 18.8      |
| 40°-50°   | 756.1  | 18.2      |
| 50°-60°   | 627.2  | 15.1      |
| 60°-70°   | 429.8  | 10.4      |
| 70°-80°   | 210.6  | 5.1       |
| 80°-90°   | 44.5   | 1.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1298.2 | 31.3      |
| 0°-40°    | 2076.0 | 50.1      |
| 0°-60°    | 3459.2 | 83.5      |
| 0°-90°    | 4144.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4144.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1708 | 1708  | 1708 | 1708  | 1708 |      |
| 5°  | 1705 | 1703  | 1699 | 1702  | 1707 | 162  |
| 15° | 1637 | 1638  | 1635 | 1628  | 1628 | 461  |
| 25° | 1495 | 1497  | 1467 | 1448  | 1441 | 688  |
| 35° | 1289 | 1282  | 1237 | 1212  | 1204 | 806  |
| 45° | 1041 | 1023  | 972  | 942   | 931  | 802  |
| 55° | 766  | 741   | 691  | 663   | 651  | 686  |
| 65° | 497  | 466   | 424  | 400   | 388  | 492  |
| 75° | 242  | 222   | 195  | 170   | 161  | 258  |
| 85° | 44   | 39    | 36   | 33    | 32   | 57   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1216868

CATALOG NUMBER: 14-ID2-45-CFR2-L950-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1708.0 | 1708.0 | 1708.0 | 1708.0 | 1708.0 |
| 2.5°  | 1710.7 | 1708.0 | 1704.0 | 1705.4 | 1708.0 |
| 5°    | 1705.4 | 1703.3 | 1699.3 | 1702.0 | 1706.7 |
| 7.5°  | 1695.3 | 1693.9 | 1691.2 | 1695.3 | 1701.3 |
| 10°   | 1680.4 | 1679.8 | 1679.1 | 1681.8 | 1686.5 |
| 12.5° | 1660.9 | 1660.9 | 1660.9 | 1658.9 | 1660.9 |
| 15°   | 1636.7 | 1638.0 | 1634.7 | 1627.9 | 1627.9 |
| 17.5° | 1607.7 | 1610.4 | 1601.7 | 1590.9 | 1588.2 |
| 20°   | 1574.1 | 1577.4 | 1561.9 | 1546.5 | 1543.8 |
| 22.5° | 1536.4 | 1539.7 | 1516.2 | 1498.0 | 1494.6 |
| 25°   | 1495.3 | 1497.3 | 1467.0 | 1447.5 | 1441.4 |
| 27.5° | 1448.8 | 1448.8 | 1415.2 | 1393.0 | 1384.9 |
| 30°   | 1400.4 | 1397.7 | 1359.3 | 1335.7 | 1327.0 |
| 32.5° | 1345.2 | 1341.8 | 1299.4 | 1275.1 | 1266.4 |
| 35°   | 1289.3 | 1282.5 | 1237.4 | 1212.5 | 1203.8 |
| 37.5° | 1230.7 | 1221.3 | 1173.5 | 1147.2 | 1137.1 |
| 40°   | 1169.4 | 1156.6 | 1107.5 | 1079.9 | 1069.8 |
| 42.5° | 1106.2 | 1091.3 | 1040.2 | 1013.2 | 1000.5 |
| 45°   | 1040.8 | 1023.3 | 971.5  | 941.9  | 931.1  |
| 47.5° | 973.5  | 954.0  | 901.5  | 873.2  | 860.4  |
| 50°   | 905.5  | 883.3  | 830.8  | 802.5  | 789.7  |
| 52.5° | 836.2  | 810.6  | 760.8  | 732.5  | 720.4  |
| 55°   | 766.2  | 741.3  | 691.4  | 663.2  | 651.0  |
| 57.5° | 699.5  | 670.6  | 622.1  | 595.8  | 582.4  |
| 60°   | 630.2  | 601.2  | 554.8  | 528.5  | 516.4  |
| 62.5° | 564.9  | 532.5  | 488.8  | 463.2  | 451.1  |
| 65°   | 496.9  | 465.9  | 424.1  | 399.9  | 387.8  |
| 67.5° | 430.2  | 401.3  | 362.9  | 338.0  | 327.9  |
| 70°   | 365.6  | 338.0  | 303.6  | 280.1  | 270.0  |
| 72.5° | 303.0  | 279.4  | 249.1  | 223.5  | 214.8  |
| 75°   | 242.4  | 222.2  | 195.2  | 170.3  | 160.9  |
| 77.5° | 185.1  | 169.0  | 143.4  | 119.2  | 109.7  |
| 80°   | 131.3  | 119.2  | 96.9   | 76.8   | 75.4   |
| 82.5° | 84.8   | 76.1   | 57.9   | 55.2   | 53.9   |
| 85°   | 44.4   | 39.0   | 35.7   | 33.0   | 31.6   |
| 87.5° | 14.1   | 14.1   | 14.1   | 11.4   | 10.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1216868

CATALOG NUMBER: 14-ID2-45-CFR2-L950-U

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 16.44            | 18.01 | 16.81 | 18.32 | 18.64 | 15.53          | 17.10 | 15.90 | 17.41 | 17.73 |
|                 | 3H   | 18.04            | 19.45 | 18.42 | 19.78 | 20.14 | 16.87          | 18.28 | 17.25 | 18.61 | 18.97 |
|                 | 4H   | 18.60            | 19.92 | 19.00 | 20.27 | 20.65 | 17.26          | 18.59 | 17.66 | 18.93 | 19.31 |
|                 | 6H   | 18.96            | 20.18 | 19.37 | 20.55 | 20.94 | 17.44          | 18.66 | 17.85 | 19.03 | 19.42 |
|                 | 8H   | 19.05            | 20.21 | 19.47 | 20.60 | 21.00 | 17.48          | 18.65 | 17.91 | 19.04 | 19.44 |
|                 | 12H  | 19.09            | 20.21 | 19.52 | 20.59 | 21.02 | 17.50          | 18.62 | 17.93 | 19.00 | 19.43 |
| 4H              | 2H   | 16.86            | 18.19 | 17.26 | 18.53 | 18.91 | 16.12          | 17.44 | 16.52 | 17.79 | 18.17 |
|                 | 3H   | 18.66            | 19.76 | 19.07 | 20.16 | 20.56 | 17.66          | 18.76 | 18.07 | 19.16 | 19.56 |
|                 | 4H   | 19.33            | 20.32 | 19.77 | 20.74 | 21.18 | 18.13          | 19.12 | 18.57 | 19.54 | 19.98 |
|                 | 6H   | 19.80            | 20.67 | 20.26 | 21.11 | 21.57 | 18.38          | 19.24 | 18.84 | 19.68 | 20.14 |
|                 | 8H   | 19.93            | 20.73 | 20.39 | 21.18 | 21.64 | 18.44          | 19.25 | 18.91 | 19.69 | 20.16 |
|                 | 12H  | 20.00            | 20.72 | 20.48 | 21.20 | 21.67 | 18.49          | 19.21 | 18.97 | 19.69 | 20.16 |
| 8H              | 4H   | 19.48            | 20.29 | 19.94 | 20.73 | 21.20 | 18.39          | 19.19 | 18.85 | 19.64 | 20.10 |
|                 | 6H   | 20.03            | 20.69 | 20.52 | 21.18 | 21.66 | 18.69          | 19.36 | 19.19 | 19.85 | 20.33 |
|                 | 8H   | 20.20            | 20.79 | 20.71 | 21.30 | 21.79 | 18.79          | 19.39 | 19.31 | 19.90 | 20.39 |
|                 | 12H  | 20.31            | 20.84 | 20.82 | 21.33 | 21.89 | 18.88          | 19.40 | 19.39 | 19.90 | 20.46 |
| 12H             | 4H   | 19.47            | 20.19 | 19.95 | 20.67 | 21.14 | 18.40          | 19.13 | 18.89 | 19.60 | 20.07 |
|                 | 6H   | 20.02            | 20.62 | 20.53 | 21.12 | 21.61 | 18.72          | 19.32 | 19.23 | 19.83 | 20.31 |
|                 | 8H   | 20.23            | 20.75 | 20.74 | 21.25 | 21.81 | 18.86          | 19.39 | 19.37 | 19.88 | 20.44 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-13  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L950-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

### Spectral Parameters

CCT (K): 4919  
 CIE  $u'$ : 0.2096  
 CIE  $v'$ : 0.4901  
 Duv: 0.0038  
 CIE x: 0.3483  
 CIE y: 0.3619  
 CIE z: 0.2898  
 Peak Wavelength (nm): 453  
 Dominant Wavelength (nm): 570  
 Purity: 13.10873  
 R<sub>f</sub>: 90.8  
 R<sub>g</sub>: 97.4

CRI (Ra): 94.0  
 R1: 94.8  
 R2: 97.7  
 R3: 98.4  
 R4: 90.8  
 R5: 92.2  
 R6: 94.3  
 R7: 94.0  
 R8: 90.0  
 R9: 77.7  
 R10: 93.1  
 R11: 92.0  
 R12: 65.9  
 R13: 95.9  
 R14: 99.0  
 R15: 91.4



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-458-13

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 419                                  | NR                             | 620               | 583                                  | NR                             | 750               | 44                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 441                                  | NR                             | 625               | 580                                  | NR                             | 755               | 37                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 472                                  | NR                             | 630               | 572                                  | NR                             | 760               | 32                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 501                                  | NR                             | 635               | 559                                  | NR                             | 765               | 27                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 524                                  | NR                             | 640               | 543                                  | NR                             | 770               | 23                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 545                                  | NR                             | 645               | 522                                  | NR                             | 775               | 20                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 559                                  | NR                             | 650               | 496                                  | NR                             | 780               | 17                                   | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 572                                  | NR                             | 655               | 468                                  | NR                             | 785               | 14                                   | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 581                                  | NR                             | 660               | 435                                  | NR                             | 790               | 12                                   | NR                             | 920               | 0                                    | NR                             |
| 405               | 7                                    | NR                             | 535               | 590                                  | NR                             | 665               | 403                                  | NR                             | 795               | 10                                   | NR                             | 925               | 0                                    | NR                             |
| 410               | 9                                    | NR                             | 540               | 595                                  | NR                             | 670               | 368                                  | NR                             | 800               | 9                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 14                                   | NR                             | 545               | 599                                  | NR                             | 675               | 335                                  | NR                             | 805               | 8                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 23                                   | NR                             | 550               | 599                                  | NR                             | 680               | 304                                  | NR                             | 810               | 6                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 40                                   | NR                             | 555               | 599                                  | NR                             | 685               | 271                                  | NR                             | 815               | 6                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 72                                   | NR                             | 560               | 595                                  | NR                             | 690               | 243                                  | NR                             | 820               | 5                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 132                                  | NR                             | 565               | 589                                  | NR                             | 695               | 215                                  | NR                             | 825               | 4                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 243                                  | NR                             | 570               | 581                                  | NR                             | 700               | 189                                  | NR                             | 830               | 3                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 488                                  | NR                             | 575               | 575                                  | NR                             | 705               | 165                                  | NR                             | 835               | 3                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 879                                  | NR                             | 580               | 573                                  | NR                             | 710               | 144                                  | NR                             | 840               | 3                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 974                                  | NR                             | 585               | 570                                  | NR                             | 715               | 124                                  | NR                             | 845               | 2                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 726                                  | NR                             | 590               | 572                                  | NR                             | 720               | 108                                  | NR                             | 850               | 2                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 627                                  | NR                             | 595               | 574                                  | NR                             | 725               | 93                                   | NR                             | 855               | 2                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 546                                  | NR                             | 600               | 576                                  | NR                             | 730               | 80                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 434                                  | NR                             | 605               | 581                                  | NR                             | 735               | 69                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 395                                  | NR                             | 610               | 582                                  | NR                             | 740               | 59                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 403                                  | NR                             | 615               | 586                                  | NR                             | 745               | 51                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2506-458-13

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.09

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 419                         | NR               | 620       | 583                         | NR               | 750       | 44                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 441                         | NR               | 625       | 580                         | NR               | 755       | 37                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 472                         | NR               | 630       | 572                         | NR               | 760       | 32                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 501                         | NR               | 635       | 559                         | NR               | 765       | 27                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 524                         | NR               | 640       | 543                         | NR               | 770       | 23                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 545                         | NR               | 645       | 522                         | NR               | 775       | 20                          | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 559                         | NR               | 650       | 496                         | NR               | 780       | 17                          | NR               | 910       | 0                           | NR               |
| 395       | 3                           | NR               | 525       | 572                         | NR               | 655       | 468                         | NR               | 785       | 14                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 581                         | NR               | 660       | 435                         | NR               | 790       | 12                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 590                         | NR               | 665       | 403                         | NR               | 795       | 10                          | NR               | 925       | 0                           | NR               |
| 410       | 9                           | NR               | 540       | 595                         | NR               | 670       | 368                         | NR               | 800       | 9                           | NR               | 930       | 0                           | NR               |
| 415       | 14                          | NR               | 545       | 599                         | NR               | 675       | 335                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 23                          | NR               | 550       | 599                         | NR               | 680       | 304                         | NR               | 810       | 6                           | NR               | 940       | 0                           | NR               |
| 425       | 40                          | NR               | 555       | 599                         | NR               | 685       | 271                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 72                          | NR               | 560       | 595                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 132                         | NR               | 565       | 589                         | NR               | 695       | 215                         | NR               | 825       | 4                           | NR               | 955       | 0                           | NR               |
| 440       | 243                         | NR               | 570       | 581                         | NR               | 700       | 189                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 488                         | NR               | 575       | 575                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 879                         | NR               | 580       | 573                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 974                         | NR               | 585       | 570                         | NR               | 715       | 124                         | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 726                         | NR               | 590       | 572                         | NR               | 720       | 108                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 627                         | NR               | 595       | 574                         | NR               | 725       | 93                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 546                         | NR               | 600       | 576                         | NR               | 730       | 80                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 434                         | NR               | 605       | 581                         | NR               | 735       | 69                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 395                         | NR               | 610       | 582                         | NR               | 740       | 59                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 403                         | NR               | 615       | 586                         | NR               | 745       | 51                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-13

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.55

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 419                         | NR               | 620       | 583                         | NR               | 750       | 44                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 441                         | NR               | 625       | 580                         | NR               | 755       | 37                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 472                         | NR               | 630       | 572                         | NR               | 760       | 32                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 501                         | NR               | 635       | 559                         | NR               | 765       | 27                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 524                         | NR               | 640       | 543                         | NR               | 770       | 23                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 545                         | NR               | 645       | 522                         | NR               | 775       | 20                          | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 559                         | NR               | 650       | 496                         | NR               | 780       | 17                          | NR               | 910       | 0                           | NR               |
| 395       | 3                           | NR               | 525       | 572                         | NR               | 655       | 468                         | NR               | 785       | 14                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 581                         | NR               | 660       | 435                         | NR               | 790       | 12                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 590                         | NR               | 665       | 403                         | NR               | 795       | 10                          | NR               | 925       | 0                           | NR               |
| 410       | 9                           | NR               | 540       | 595                         | NR               | 670       | 368                         | NR               | 800       | 9                           | NR               | 930       | 0                           | NR               |
| 415       | 14                          | NR               | 545       | 599                         | NR               | 675       | 335                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 23                          | NR               | 550       | 599                         | NR               | 680       | 304                         | NR               | 810       | 6                           | NR               | 940       | 0                           | NR               |
| 425       | 40                          | NR               | 555       | 599                         | NR               | 685       | 271                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 72                          | NR               | 560       | 595                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 132                         | NR               | 565       | 589                         | NR               | 695       | 215                         | NR               | 825       | 4                           | NR               | 955       | 0                           | NR               |
| 440       | 243                         | NR               | 570       | 581                         | NR               | 700       | 189                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 488                         | NR               | 575       | 575                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 879                         | NR               | 580       | 573                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 974                         | NR               | 585       | 570                         | NR               | 715       | 124                         | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 726                         | NR               | 590       | 572                         | NR               | 720       | 108                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 627                         | NR               | 595       | 574                         | NR               | 725       | 93                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 546                         | NR               | 600       | 576                         | NR               | 730       | 80                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 434                         | NR               | 605       | 581                         | NR               | 735       | 69                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 395                         | NR               | 610       | 582                         | NR               | 740       | 59                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 403                         | NR               | 615       | 586                         | NR               | 745       | 51                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2506-458-13



TM-30-18

### Summary

$R_f = 90.8$   
 $R_g = 97.4$   
 $CIE R_a = 94.0$   
 $R_9 = 77.7$




### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 98 | CES51 = 93 | CES76 = 91 |
| CES02 = 61 | CES27 = 86 | CES52 = 96 | CES77 = 89 |
| CES03 = 31 | CES28 = 98 | CES53 = 93 | CES78 = 87 |
| CES04 = 68 | CES29 = 90 | CES54 = 89 | CES79 = 97 |
| CES05 = 48 | CES30 = 80 | CES55 = 86 | CES80 = 94 |
| CES06 = 50 | CES31 = 92 | CES56 = 89 | CES81 = 89 |
| CES07 = 41 | CES32 = 97 | CES57 = 87 | CES82 = 97 |
| CES08 = 40 | CES33 = 89 | CES58 = 87 | CES83 = 96 |
| CES09 = 29 | CES34 = 98 | CES59 = 96 | CES84 = 94 |
| CES10 = 73 | CES35 = 98 | CES60 = 89 | CES85 = 84 |
| CES11 = 56 | CES36 = 74 | CES61 = 90 | CES86 = 90 |
| CES12 = 62 | CES37 = 97 | CES62 = 78 | CES87 = 92 |
| CES13 = 42 | CES38 = 75 | CES63 = 89 | CES88 = 95 |
| CES14 = 74 | CES39 = 97 | CES64 = 85 | CES89 = 90 |
| CES15 = 71 | CES40 = 97 | CES65 = 87 | CES90 = 92 |
| CES16 = 47 | CES41 = 91 | CES66 = 82 | CES91 = 69 |
| CES17 = 48 | CES42 = 99 | CES67 = 82 | CES92 = 81 |
| CES18 = 56 | CES43 = 97 | CES68 = 86 | CES93 = 88 |
| CES19 = 70 | CES44 = 99 | CES69 = 87 | CES94 = 86 |
| CES20 = 65 | CES45 = 97 | CES70 = 86 | CES95 = 83 |
| CES21 = 84 | CES46 = 94 | CES71 = 77 | CES96 = 94 |
| CES22 = 77 | CES47 = 90 | CES72 = 93 | CES97 = 97 |
| CES23 = 91 | CES48 = 83 | CES73 = 82 | CES98 = 94 |
| CES24 = 89 | CES49 = 95 | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 94 | CES75 = 81 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)