Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216911

Luminaire Tested: 14-ID2-20-CFD1-L850-U

Issue Date: 12/5/2025

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1216911
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-15)
Test Lab:	INNOVATION CENTER
Issue Date:	12/5/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	CORELITE
Catalog Number:	14-ID2-20-CFD1-L850-U
Description:	1X4 IN DEPTH TROFFER WITH 1INCH CUBE DROP LENS
Light Source:	5000K CCT, 80 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2203.1 lumens
Efficiency:	N/A
Efficacy:	125.2 lumens/watt
Spacing Criteria (0/90/45):	1.21 / 1.19 / 1.3
Luminous Opening:	Rectangular w/ Sides (W: 1' x L: 4' x H: 0.08')
CIE Type:	Direct

Input Watts (W):	17.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	101	101	101	99
1	108	104	99	95	106	101	97	94	97	93	90	93	90	88	89	87	85	83
2	99	90	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71	69
3	90	80	71	65	88	78	70	64	75	68	63	72	66	62	69	65	61	58
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	50
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	44
6	70	57	48	42	68	56	48	42	54	47	41	52	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	46	40	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32	30
9	57	44	35	30	55	43	35	30	42	35	30	41	34	29	39	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2242	2242	2242
5°	2241	2221	2226
10°	2227	2193	2196
15°	2204	2157	2159
20°	2171	2110	2106
25°	2129	2053	2035
30°	2074	1988	1966
35°	2011	1915	1891
40°	1944	1836	1808
45°	1865	1752	1724
50°	1781	1670	1642
55°	1689	1584	1555
60°	1592	1487	1481
65°	1485	1393	1397
70°	1369	1290	1302
75°	1231	1175	1176
80°	1048	1046	1044
85°	857	925	934

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1865 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	3.6
10°-20°	222.9	10.1
20°-30°	329.3	14.9
30°-40°	382.9	17.4
40°-50°	380.8	17.3
50°-60°	331.3	15.0
60°-70°	248.7	11.3
70°-80°	148.7	6.7
80°-90°	57.7	2.6
90°-100°	17.8	0.8
100°-110°	4.3	0.2
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.8	28.6
0°-40°	1013.7	46.0
0°-60°	1725.8	78.3
0°-90°	2180.9	99.0
90°-120°	22.2	1.0
90°-150°	22.2	1.0
90°-180°	22.0	1.0
0°-180°	2203.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	831	830	827	828	830	79
15°	795	792	789	789	792	224
25°	724	720	714	710	711	333
35°	621	618	612	606	608	388
45°	500	497	493	488	489	386
55°	370	370	372	369	369	331
65°	243	247	252	254	257	241
75°	127	134	143	146	147	135
85°	34	44	54	58	58	37
90°	9	17	27	32	32	6
95°	6	8	17	23	25	5
105°	1	1	2	7	9	1
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*833.1*	833.1	833.1	833.1	833.1
2.5°	*834.2*	*833.5*	*830.5*	*831.2*	*832.4*
5°	*831.2*	830.1	827.2	827.5	829.8
7.5°	*826.1*	823.8	821.2	821.6	823.8
10°	*817.9*	816.0	812.7	813.1	814.9
12.5°	*807.5*	805.3	801.9	802.3	804.5
15°	*795.3*	792.3	789.0	789.0	791.6
17.5°	*780.8*	777.5	773.8	772.6	775.2
20°	*763.7*	760.4	755.9	753.7	756.7
22.5°	*744.8*	741.1	735.9	732.6	735.9
25°	*723.7*	719.6	714.4	709.6	711.1
27.5°	*700.7*	696.6	690.7	685.8	687.7
30°	*675.1*	671.7	665.8	660.6	662.1
32.5°	*648.8*	645.4	639.5	633.5	635.4
35°	*620.6*	618.0	611.7	605.7	607.9
37.5°	*593.1*	589.0	583.1	576.8	579.0
40°	*562.7*	559.4	553.8	547.1	549.3
42.5°	*531.9*	528.9	524.5	518.2	519.7
45°	*500.0*	497.4	493.0	488.5	489.3
47.5°	*467.7*	465.9	463.3	458.5	459.2
50°	*435.5*	434.4	432.5	428.4	429.5
52.5°	*402.5*	401.7	401.7	398.4	400.2
55°	*370.2*	370.2	371.7	369.1	369.4
57.5°	*337.5*	339.0	341.3	339.8	342.0
60°	*306.0*	307.1	310.1	311.2	313.4
62.5°	*274.5*	277.1	280.8	282.6	284.9
65°	*243.3*	246.7	251.9	254.5	257.1
67.5°	*213.3*	217.0	224.4	227.0	229.2
70°	*183.6*	188.8	195.8	199.6	201.8
72.5°	*154.7*	161.0	169.1	172.9	173.2
75°	*127.2*	134.3	142.8	146.5	146.9
77.5°	*100.9*	107.6	117.6	121.3	121.3
80°	*75.3*	83.1	94.6	97.6	97.9
82.5°	*53.0*	61.6	72.3	75.7	75.7
85°	*34.1*	43.8	54.2	57.5	57.9
87.5°	*20.0*	29.3	39.3	43.0	43.4
90°	*9.3*	17.1	27.1	31.5	31.9
92.5°	*7.8*	13.0	22.3	27.1	28.2
95°	*6.3*	8.5	17.4	23.0	24.9
97.5°	*4.8*	4.8	13.0	18.9	20.8
100°	*3.3*	2.6	8.5	14.8	17.1
102.5°	*2.2*	1.5	4.5	10.8	13.0
105°	*1.1*	0.7	1.5	7.4	9.3
107.5°	*0.4*	0.0	0.0	3.7	5.9
110°	*0.0*	0.0	0.0	0.7	2.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	*0.0*	0.0	0.0	0.0	0.0
115°	*0.0*	0.0	0.0	0.0	0.0
117.5°	*0.0*	0.0	0.0	0.0	0.0
120°	*0.0*	0.0	0.0	0.0	0.0
122.5°	*0.0*	0.0	0.0	0.0	0.0
125°	*0.0*	0.0	0.0	0.0	0.0
127.5°	*0.0*	0.0	0.0	0.0	0.0
130°	*0.0*	0.0	0.0	0.0	0.0
132.5°	*0.0*	0.0	0.0	0.0	0.0
135°	*0.0*	0.0	0.0	0.0	0.0
137.5°	*0.0*	0.0	0.0	0.0	0.0
140°	*0.0*	0.0	0.0	0.0	0.0
142.5°	*0.0*	0.0	0.0	0.0	0.0
145°	*0.0*	0.0	0.0	0.0	0.0
147.5°	*0.0*	0.0	0.0	0.0	0.0
150°	*0.0*	0.0	0.0	0.0	0.0
152.5°	*0.0*	0.0	0.0	0.0	0.0
155°	*0.0*	0.0	0.0	0.0	0.0
157.5°	*0.0*	0.0	0.0	0.0	0.0
160°	*0.0*	0.0	0.0	0.0	0.0
162.5°	*0.0*	0.0	0.0	0.0	0.0
165°	*0.0*	0.0	0.0	0.0	0.0
167.5°	*0.0*	0.0	0.0	0.0	0.0
170°	*0.0*	0.0	0.0	0.0	0.0
172.5°	*0.0*	0.0	0.0	0.0	0.0
175°	*0.0*	0.0	0.0	0.0	0.0
177.5°	*0.0*	0.0	0.0	0.0	0.0
180°	*0.0*	0.0	0.0	0.0	0.0

TEST NUMBER: P1216911
CATALOG NUMBER: 14-ID2-20-CFD1-L850-U

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.31	14.91	13.69	15.25	15.59	13.54	15.13	13.92	15.47	15.81
	3H	14.92	16.37	15.32	16.72	17.10	15.39	16.84	15.79	17.19	17.57
	4H	15.49	16.86	15.91	17.23	17.63	16.12	17.48	16.54	17.85	18.25
	6H	15.88	17.15	16.31	17.53	17.95	16.71	17.98	17.14	18.36	18.78
	8H	15.99	17.20	16.43	17.61	18.03	16.95	18.15	17.39	18.56	18.99
	12H	16.05	17.21	16.50	17.61	18.07	17.15	18.31	17.60	18.71	19.16
4H	2H	13.93	15.29	14.34	15.66	16.06	14.11	15.47	14.52	15.84	16.24
	3H	15.77	16.91	16.19	17.33	17.76	16.18	17.33	16.61	17.74	18.17
	4H	16.47	17.51	16.91	17.94	18.40	17.05	18.08	17.49	18.52	18.98
	6H	16.97	17.88	17.44	18.34	18.82	17.78	18.69	18.25	19.15	19.63
	8H	17.13	17.98	17.60	18.44	18.93	18.07	18.93	18.55	19.39	19.88
	12H	17.23	18.00	17.73	18.49	18.98	18.35	19.11	18.84	19.61	20.10
8H	4H	16.81	17.66	17.29	18.12	18.61	17.32	18.17	17.80	18.64	19.12
	6H	17.44	18.16	17.95	18.66	19.16	18.19	18.90	18.70	19.41	19.91
	8H	17.67	18.31	18.19	18.83	19.34	18.58	19.22	19.10	19.74	20.25
	12H	17.84	18.41	18.36	18.92	19.50	18.96	19.53	19.48	20.04	20.62
12H	4H	16.86	17.63	17.36	18.12	18.61	17.35	18.11	17.84	18.61	19.10
	6H	17.53	18.17	18.05	18.69	19.20	18.24	18.88	18.77	19.41	19.91
	8H	17.81	18.38	18.34	18.89	19.47	18.69	19.26	19.21	19.77	20.35

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2506-458-7
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	08/27/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Corelite
Catalog Number:	**22ID2-55-CFR1-L850-U**
Description:	2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K):	4966
CIE u':	0.2093
CIE v':	0.4890
Duv:	0.0036
CIE x:	0.3468
CIE y:	0.3601
CIE z:	0.2931
Peak Wavelength (nm):	450
Dominant Wavelength (nm):	570
Purity:	12.1135
Rf:	84
Rg:	96.2

CRI (Ra):	83.1
R1:	81.0
R2:	87.8
R3:	92.7
R4:	82.4
R5:	81.0
R6:	82.6
R7:	88.5
R8:	68.6
R9:	10.3
R10:	70.9
R11:	81.3
R12:	55.9
R13:	82.8
R14:	96.1
R15:	75.1



Test Conditions

Stabilization Time:	37M
Operation Time:	1H 37M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2506-458-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 4966K
CIE x = 0.3468
CIE y = 0.3601
Duv = 0.0036

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR **S/P: 1.94**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.11**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

TM-30-18

Summary

R_f = 84
R_g = 96.2
CIE R_a = 83.1
R_9 = 10.3

Spectral Power Distribution Comparison



Color Vector Graphics









REPORT NUMBER: SP1-2506-458-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



REPORT NUMBER: SP1-2506-458-7

TM-30-18

Color Rendition by Hue-Angle Bin







REPORT NUMBER: SP1-2506-458-7

TM-30-18

Measure Comparisons





(END OF REPORT)