

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217140

Luminaire Tested: 14-ID2-55-CNC-L840-U

Issue Date: 12/5/2025


**Test Information**

Test Method: LM-79-2019  
Report Number: P1217140  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 14-ID2-55-CNC-L840-U  
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESS LENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5579.3 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.3  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 48.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1217140  
CATALOG NUMBER: 14-ID2-55-CNC-L840-U

### Luminous Intensity Polar Plot



TEST NUMBER: P1217140

CATALOG NUMBER: 14-ID2-55-CNC-L840-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 109 | 104 | 100 | 97  | 106 | 102 | 98  | 95  | 98  | 95  | 92  |  | 94  | 92  | 89  |  | 84  |
| 2   | 99  | 91  | 85  | 79  | 97  | 90  | 83  | 78  | 86  | 81  | 76  |  | 83  | 78  | 75  |  | 71  |
| 3   | 91  | 81  | 73  | 66  | 88  | 79  | 72  | 66  | 76  | 70  | 64  |  | 73  | 68  | 63  |  | 60  |
| 4   | 83  | 72  | 63  | 56  | 81  | 70  | 62  | 56  | 68  | 61  | 55  |  | 65  | 59  | 54  |  | 52  |
| 5   | 77  | 64  | 55  | 49  | 75  | 63  | 55  | 48  | 61  | 54  | 48  |  | 59  | 53  | 47  |  | 45  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 49  | 43  | 55  | 48  | 42  |  | 53  | 47  | 42  |  | 39  |
| 7   | 66  | 53  | 44  | 38  | 64  | 52  | 44  | 38  | 50  | 43  | 37  |  | 49  | 42  | 37  |  | 35  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  | 46  | 39  | 34  |  | 45  | 38  | 33  |  | 31  |
| 9   | 57  | 44  | 36  | 31  | 56  | 44  | 36  | 31  | 42  | 35  | 30  |  | 41  | 35  | 30  |  | 28  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  | 39  | 32  | 28  |  | 38  | 32  | 27  |  | 26  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 5866 | 5866 | 5866 |
| 5°  | 5876 | 5845 | 5858 |
| 10° | 5843 | 5809 | 5822 |
| 15° | 5782 | 5745 | 5756 |
| 20° | 5708 | 5653 | 5651 |
| 25° | 5600 | 5537 | 5518 |
| 30° | 5474 | 5388 | 5382 |
| 35° | 5323 | 5239 | 5232 |
| 40° | 5155 | 5078 | 5072 |
| 45° | 4971 | 4906 | 4895 |
| 50° | 4774 | 4726 | 4718 |
| 55° | 4562 | 4531 | 4509 |
| 60° | 4324 | 4324 | 4309 |
| 65° | 4035 | 4096 | 4059 |
| 70° | 3740 | 3821 | 3762 |
| 75° | 3304 | 3511 | 3373 |
| 80° | 2808 | 3028 | 2808 |
| 85° | 2109 | 2285 | 2195 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4971 cd/sqm

TEST NUMBER: P1217140  
 CATALOG NUMBER: 14-ID2-55-CNC-L840-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 205.7  | 3.7       |
| 10°-20°   | 582.2  | 10.4      |
| 20°-30°   | 859.3  | 15.4      |
| 30°-40°   | 1000.0 | 17.9      |
| 40°-50°   | 996.5  | 17.9      |
| 50°-60°   | 864.0  | 15.5      |
| 60°-70°   | 633.8  | 11.4      |
| 70°-80°   | 350.5  | 6.3       |
| 80°-90°   | 87.3   | 1.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1647.2 | 29.5      |
| 0°-40°    | 2647.2 | 47.4      |
| 0°-60°    | 4507.7 | 80.8      |
| 0°-90°    | 5579.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5579.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 2180 | 2180  | 2180 | 2180  | 2180 |      |
| 5°  | 2175 | 2172  | 2164 | 2164  | 2169 | 206  |
| 15° | 2076 | 2072  | 2062 | 2060  | 2066 | 585  |
| 25° | 1886 | 1875  | 1865 | 1855  | 1858 | 868  |
| 35° | 1620 | 1610  | 1595 | 1587  | 1593 | 1012 |
| 45° | 1306 | 1300  | 1289 | 1282  | 1286 | 1008 |
| 55° | 972  | 970   | 966  | 960   | 961  | 869  |
| 65° | 634  | 644   | 643  | 635   | 638  | 630  |
| 75° | 318  | 339   | 338  | 325   | 324  | 340  |
| 85° | 68   | 78    | 74   | 68    | 71   | 83   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1217140

CATALOG NUMBER: 14-ID2-55-CNC-L840-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 2180.0 | 2180.0 | 2180.0 | 2180.0 | 2180.0 |
| 2.5°  | 2183.8 | 2180.9 | 2173.3 | 2173.3 | 2177.1 |
| 5°    | 2175.2 | 2172.4 | 2163.8 | 2163.8 | 2168.6 |
| 7.5°  | 2159.1 | 2157.2 | 2147.7 | 2147.7 | 2154.3 |
| 10°   | 2138.2 | 2134.4 | 2125.9 | 2124.9 | 2130.6 |
| 12.5° | 2110.7 | 2106.9 | 2097.4 | 2095.5 | 2101.2 |
| 15°   | 2075.6 | 2071.8 | 2062.3 | 2059.5 | 2066.1 |
| 17.5° | 2038.6 | 2031.0 | 2022.5 | 2016.8 | 2022.5 |
| 20°   | 1993.1 | 1985.5 | 1974.1 | 1967.5 | 1973.2 |
| 22.5° | 1941.9 | 1933.3 | 1921.9 | 1911.5 | 1918.1 |
| 25°   | 1885.9 | 1875.4 | 1865.0 | 1854.6 | 1858.4 |
| 27.5° | 1826.1 | 1813.8 | 1801.5 | 1792.0 | 1795.8 |
| 30°   | 1761.6 | 1748.3 | 1734.1 | 1726.5 | 1732.2 |
| 32.5° | 1689.5 | 1681.9 | 1666.7 | 1658.2 | 1663.0 |
| 35°   | 1620.3 | 1609.8 | 1594.7 | 1587.1 | 1592.8 |
| 37.5° | 1545.3 | 1534.9 | 1521.6 | 1513.1 | 1518.8 |
| 40°   | 1467.5 | 1458.0 | 1445.7 | 1437.2 | 1443.8 |
| 42.5° | 1387.8 | 1382.2 | 1368.9 | 1359.4 | 1366.0 |
| 45°   | 1306.3 | 1299.6 | 1289.2 | 1281.6 | 1286.3 |
| 47.5° | 1223.7 | 1218.0 | 1209.5 | 1201.0 | 1207.6 |
| 50°   | 1140.3 | 1138.4 | 1128.9 | 1121.3 | 1127.0 |
| 52.5° | 1055.8 | 1055.8 | 1047.3 | 1040.7 | 1046.3 |
| 55°   | 972.3  | 970.5  | 965.7  | 960.0  | 961.0  |
| 57.5° | 887.9  | 887.9  | 884.1  | 878.4  | 883.2  |
| 60°   | 803.5  | 807.3  | 803.5  | 796.9  | 800.6  |
| 62.5° | 720.0  | 724.8  | 722.9  | 715.3  | 719.1  |
| 65°   | 633.7  | 644.1  | 643.2  | 634.6  | 637.5  |
| 67.5° | 555.9  | 564.4  | 563.5  | 555.9  | 557.8  |
| 70°   | 475.3  | 486.6  | 485.7  | 477.2  | 478.1  |
| 72.5° | 393.7  | 410.8  | 409.8  | 400.3  | 400.3  |
| 75°   | 317.8  | 338.7  | 337.7  | 325.4  | 324.4  |
| 77.5° | 249.5  | 267.5  | 265.6  | 252.3  | 252.3  |
| 80°   | 181.2  | 197.3  | 195.4  | 181.2  | 181.2  |
| 82.5° | 120.5  | 134.7  | 130.9  | 119.5  | 121.4  |
| 85°   | 68.3   | 77.8   | 74.0   | 68.3   | 71.1   |
| 87.5° | 24.7   | 30.4   | 29.4   | 24.7   | 27.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P1217140

CATALOG NUMBER: 14-ID2-55-CNC-L840-U

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 17.26            | 18.87 | 17.63 | 19.18 | 19.50 | 17.19          | 18.80 | 17.56 | 19.11 | 19.43 |
|                 | 3H   | 18.94            | 20.39 | 19.32 | 20.72 | 21.08 | 18.88          | 20.33 | 19.26 | 20.66 | 21.02 |
|                 | 4H   | 19.54            | 20.90 | 19.94 | 21.25 | 21.63 | 19.49          | 20.85 | 19.89 | 21.20 | 21.58 |
|                 | 6H   | 19.95            | 21.21 | 20.36 | 21.58 | 21.97 | 19.90          | 21.16 | 20.31 | 21.52 | 21.91 |
|                 | 8H   | 20.06            | 21.27 | 20.49 | 21.66 | 22.06 | 20.01          | 21.21 | 20.43 | 21.60 | 22.00 |
|                 | 12H  | 20.13            | 21.28 | 20.56 | 21.66 | 22.09 | 20.07          | 21.23 | 20.50 | 21.61 | 22.04 |
| 4H              | 2H   | 17.86            | 19.22 | 18.26 | 19.57 | 19.95 | 17.81          | 19.17 | 18.21 | 19.52 | 19.89 |
|                 | 3H   | 19.77            | 20.91 | 20.18 | 21.31 | 21.71 | 19.71          | 20.85 | 20.12 | 21.25 | 21.65 |
|                 | 4H   | 20.50            | 21.53 | 20.94 | 21.95 | 22.38 | 20.44          | 21.47 | 20.87 | 21.88 | 22.32 |
|                 | 6H   | 21.04            | 21.94 | 21.50 | 22.38 | 22.84 | 20.95          | 21.85 | 21.41 | 22.29 | 22.75 |
|                 | 8H   | 21.20            | 22.04 | 21.66 | 22.48 | 22.95 | 21.10          | 21.94 | 21.56 | 22.38 | 22.85 |
|                 | 12H  | 21.30            | 22.05 | 21.78 | 22.53 | 23.00 | 21.20          | 21.95 | 21.68 | 22.43 | 22.90 |
| 8H              | 4H   | 20.79            | 21.64 | 21.26 | 22.08 | 22.54 | 20.73          | 21.57 | 21.19 | 22.02 | 22.48 |
|                 | 6H   | 21.45            | 22.15 | 21.95 | 22.64 | 23.11 | 21.35          | 22.05 | 21.85 | 22.54 | 23.02 |
|                 | 8H   | 21.68            | 22.30 | 22.19 | 22.81 | 23.30 | 21.56          | 22.18 | 22.07 | 22.69 | 23.18 |
|                 | 12H  | 21.84            | 22.39 | 22.35 | 22.88 | 23.44 | 21.71          | 22.26 | 22.22 | 22.75 | 23.31 |
| 12H             | 4H   | 20.82            | 21.57 | 21.30 | 22.05 | 22.52 | 20.76          | 21.52 | 21.24 | 21.99 | 22.46 |
|                 | 6H   | 21.49            | 22.12 | 22.00 | 22.63 | 23.11 | 21.40          | 22.03 | 21.91 | 22.54 | 23.02 |
|                 | 8H   | 21.77            | 22.32 | 22.28 | 22.82 | 23.38 | 21.65          | 22.21 | 22.16 | 22.70 | 23.26 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-5

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L840-U

Data in this report applies to families of products including 22ID2-55-CFR1-L840-U




### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L840-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 80CRI

### Spectral Parameters

CCT (K): 3915  
 CIE  $u'$ : 0.2259  
 CIE  $v'$ : 0.5051  
 Duv: 0.0015  
 CIE x: 0.3854  
 CIE y: 0.3830  
 CIE z: 0.2316  
 Peak Wavelength (nm): 453  
 Dominant Wavelength (nm): 578  
 Purity: 30.6207  
 R<sub>f</sub>: 83.2  
 R<sub>g</sub>: 94.6

CRI (Ra): 82.3  
 R1: 80.6  
 R2: 88.9  
 R3: 94.6  
 R4: 80.5  
 R5: 80.0  
 R6: 84.0  
 R7: 86.1  
 R8: 64.0  
 R9: 7.6  
 R10: 72.9  
 R11: 78.7  
 R12: 57.3  
 R13: 82.7  
 R14: 97.1  
 R15: 74.3



### Test Conditions


Stabilization Time: 34M  
 Operation Time: 1H 34M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-5


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-458-5

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-5

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 266                      | NR            | 620    | 755                      | NR            | 750    | 24                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 307                      | NR            | 625    | 710                      | NR            | 755    | 21                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 366                      | NR            | 630    | 663                      | NR            | 760    | 18                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 430                      | NR            | 635    | 612                      | NR            | 765    | 15                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 486                      | NR            | 640    | 561                      | NR            | 770    | 13                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 536                      | NR            | 645    | 509                      | NR            | 775    | 11                       | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 571                      | NR            | 650    | 458                      | NR            | 780    | 10                       | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 600                      | NR            | 655    | 410                      | NR            | 785    | 8                        | NR            | 915    | 0                        | NR            |
| 400    | 5                        | NR            | 530    | 624                      | NR            | 660    | 363                      | NR            | 790    | 7                        | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 645                      | NR            | 665    | 321                      | NR            | 795    | 6                        | NR            | 925    | 0                        | NR            |
| 410    | 10                       | NR            | 540    | 661                      | NR            | 670    | 280                      | NR            | 800    | 5                        | NR            | 930    | 0                        | NR            |
| 415    | 16                       | NR            | 545    | 681                      | NR            | 675    | 244                      | NR            | 805    | 5                        | NR            | 935    | 0                        | NR            |
| 420    | 30                       | NR            | 550    | 701                      | NR            | 680    | 213                      | NR            | 810    | 4                        | NR            | 940    | 0                        | NR            |
| 425    | 53                       | NR            | 555    | 724                      | NR            | 685    | 183                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 95                       | NR            | 560    | 747                      | NR            | 690    | 159                      | NR            | 820    | 3                        | NR            | 950    | 0                        | NR            |
| 435    | 170                      | NR            | 565    | 772                      | NR            | 695    | 136                      | NR            | 825    | 3                        | NR            | 955    | 0                        | NR            |
| 440    | 289                      | NR            | 570    | 795                      | NR            | 700    | 117                      | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 522                      | NR            | 575    | 817                      | NR            | 705    | 100                      | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 895                      | NR            | 580    | 841                      | NR            | 710    | 85                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 957                      | NR            | 585    | 857                      | NR            | 715    | 72                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 642                      | NR            | 590    | 871                      | NR            | 720    | 62                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 487                      | NR            | 595    | 875                      | NR            | 725    | 53                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 397                      | NR            | 600    | 866                      | NR            | 730    | 45                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 289                      | NR            | 605    | 852                      | NR            | 735    | 39                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 241                      | NR            | 610    | 827                      | NR            | 740    | 33                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 245                      | NR            | 615    | 796                      | NR            | 745    | 28                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-458-5

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.65

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 266                      | NR            | 620    | 755                      | NR            | 750    | 24                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 307                      | NR            | 625    | 710                      | NR            | 755    | 21                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 366                      | NR            | 630    | 663                      | NR            | 760    | 18                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 430                      | NR            | 635    | 612                      | NR            | 765    | 15                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 486                      | NR            | 640    | 561                      | NR            | 770    | 13                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 536                      | NR            | 645    | 509                      | NR            | 775    | 11                       | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 571                      | NR            | 650    | 458                      | NR            | 780    | 10                       | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 600                      | NR            | 655    | 410                      | NR            | 785    | 8                        | NR            | 915    | 0                        | NR            |
| 400    | 5                        | NR            | 530    | 624                      | NR            | 660    | 363                      | NR            | 790    | 7                        | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 645                      | NR            | 665    | 321                      | NR            | 795    | 6                        | NR            | 925    | 0                        | NR            |
| 410    | 10                       | NR            | 540    | 661                      | NR            | 670    | 280                      | NR            | 800    | 5                        | NR            | 930    | 0                        | NR            |
| 415    | 16                       | NR            | 545    | 681                      | NR            | 675    | 244                      | NR            | 805    | 5                        | NR            | 935    | 0                        | NR            |
| 420    | 30                       | NR            | 550    | 701                      | NR            | 680    | 213                      | NR            | 810    | 4                        | NR            | 940    | 0                        | NR            |
| 425    | 53                       | NR            | 555    | 724                      | NR            | 685    | 183                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 95                       | NR            | 560    | 747                      | NR            | 690    | 159                      | NR            | 820    | 3                        | NR            | 950    | 0                        | NR            |
| 435    | 170                      | NR            | 565    | 772                      | NR            | 695    | 136                      | NR            | 825    | 3                        | NR            | 955    | 0                        | NR            |
| 440    | 289                      | NR            | 570    | 795                      | NR            | 700    | 117                      | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 522                      | NR            | 575    | 817                      | NR            | 705    | 100                      | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 895                      | NR            | 580    | 841                      | NR            | 710    | 85                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 957                      | NR            | 585    | 857                      | NR            | 715    | 72                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 642                      | NR            | 590    | 871                      | NR            | 720    | 62                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 487                      | NR            | 595    | 875                      | NR            | 725    | 53                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 397                      | NR            | 600    | 866                      | NR            | 730    | 45                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 289                      | NR            | 605    | 852                      | NR            | 735    | 39                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 241                      | NR            | 610    | 827                      | NR            | 740    | 33                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 245                      | NR            | 615    | 796                      | NR            | 745    | 28                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-458-5

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.36**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 266                                  | NR                             | 620               | 755                                  | NR                             | 750               | 24                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 307                                  | NR                             | 625               | 710                                  | NR                             | 755               | 21                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 366                                  | NR                             | 630               | 663                                  | NR                             | 760               | 18                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 430                                  | NR                             | 635               | 612                                  | NR                             | 765               | 15                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 486                                  | NR                             | 640               | 561                                  | NR                             | 770               | 13                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 536                                  | NR                             | 645               | 509                                  | NR                             | 775               | 11                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 571                                  | NR                             | 650               | 458                                  | NR                             | 780               | 10                                   | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 600                                  | NR                             | 655               | 410                                  | NR                             | 785               | 8                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 5                                    | NR                             | 530               | 624                                  | NR                             | 660               | 363                                  | NR                             | 790               | 7                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 7                                    | NR                             | 535               | 645                                  | NR                             | 665               | 321                                  | NR                             | 795               | 6                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 10                                   | NR                             | 540               | 661                                  | NR                             | 670               | 280                                  | NR                             | 800               | 5                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 16                                   | NR                             | 545               | 681                                  | NR                             | 675               | 244                                  | NR                             | 805               | 5                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 30                                   | NR                             | 550               | 701                                  | NR                             | 680               | 213                                  | NR                             | 810               | 4                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 53                                   | NR                             | 555               | 724                                  | NR                             | 685               | 183                                  | NR                             | 815               | 3                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 95                                   | NR                             | 560               | 747                                  | NR                             | 690               | 159                                  | NR                             | 820               | 3                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 170                                  | NR                             | 565               | 772                                  | NR                             | 695               | 136                                  | NR                             | 825               | 3                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 289                                  | NR                             | 570               | 795                                  | NR                             | 700               | 117                                  | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 522                                  | NR                             | 575               | 817                                  | NR                             | 705               | 100                                  | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 895                                  | NR                             | 580               | 841                                  | NR                             | 710               | 85                                   | NR                             | 840               | 2                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 957                                  | NR                             | 585               | 857                                  | NR                             | 715               | 72                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 642                                  | NR                             | 590               | 871                                  | NR                             | 720               | 62                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 487                                  | NR                             | 595               | 875                                  | NR                             | 725               | 53                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 397                                  | NR                             | 600               | 866                                  | NR                             | 730               | 45                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 289                                  | NR                             | 605               | 852                                  | NR                             | 735               | 39                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 241                                  | NR                             | 610               | 827                                  | NR                             | 740               | 33                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 245                                  | NR                             | 615               | 796                                  | NR                             | 745               | 28                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2506-458-5





TM-30-18

### Summary

$R_f = 83.2$   
 $R_g = 94.6$   
 $CIE R_a = 82.3$   
 $R_9 = 7.6$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 83 | CES51 = 92 | CES76 = 75 |
| CES02 = 61 | CES27 = 91 | CES52 = 93 | CES77 = 82 |
| CES03 = 31 | CES28 = 91 | CES53 = 88 | CES78 = 74 |
| CES04 = 70 | CES29 = 90 | CES54 = 88 | CES79 = 92 |
| CES05 = 48 | CES30 = 90 | CES55 = 85 | CES80 = 89 |
| CES06 = 50 | CES31 = 91 | CES56 = 83 | CES81 = 81 |
| CES07 = 41 | CES32 = 83 | CES57 = 82 | CES82 = 95 |
| CES08 = 40 | CES33 = 97 | CES58 = 82 | CES83 = 96 |
| CES09 = 29 | CES34 = 87 | CES59 = 90 | CES84 = 90 |
| CES10 = 74 | CES35 = 92 | CES60 = 88 | CES85 = 77 |
| CES11 = 57 | CES36 = 78 | CES61 = 85 | CES86 = 75 |
| CES12 = 63 | CES37 = 91 | CES62 = 79 | CES87 = 84 |
| CES13 = 42 | CES38 = 84 | CES63 = 82 | CES88 = 89 |
| CES14 = 74 | CES39 = 98 | CES64 = 75 | CES89 = 77 |
| CES15 = 71 | CES40 = 96 | CES65 = 74 | CES90 = 90 |
| CES16 = 47 | CES41 = 95 | CES66 = 70 | CES91 = 67 |
| CES17 = 49 | CES42 = 93 | CES67 = 69 | CES92 = 64 |
| CES18 = 56 | CES43 = 91 | CES68 = 76 | CES93 = 78 |
| CES19 = 71 | CES44 = 99 | CES69 = 80 | CES94 = 63 |
| CES20 = 65 | CES45 = 94 | CES70 = 72 | CES95 = 72 |
| CES21 = 86 | CES46 = 91 | CES71 = 64 | CES96 = 84 |
| CES22 = 78 | CES47 = 95 | CES72 = 88 | CES97 = 91 |
| CES23 = 91 | CES48 = 83 | CES73 = 66 | CES98 = 86 |
| CES24 = 90 | CES49 = 90 | CES74 = 90 | CES99 = 77 |
| CES25 = 71 | CES50 = 93 | CES75 = 68 |            |





Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)