

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217228

Luminaire Tested: 14-ID2-55-CNV-L850-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-55-CNV-L850-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP LENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5660.2 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.33
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 48.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217228
CATALOG NUMBER: 14-ID2-55-CNV-L850-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217228

CATALOG NUMBER: 14-ID2-55-CNV-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110	105	105	105	100	100	100	100	100	98
1	107	102	98	94	104	100	96	92	95	92	88	91	88	85	87	84	82	80	80	80
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69	66	66	66
3	89	78	70	63	86	76	69	62	73	66	61	70	64	60	67	62	58	56	56	56
4	81	69	60	54	79	68	59	53	65	58	52	62	56	51	60	54	50	48	48	48
5	75	62	53	46	73	61	52	46	58	51	45	56	49	44	54	48	44	41	41	41
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	49	43	38	36	36	36
7	64	51	42	36	62	50	41	35	48	40	35	46	40	35	45	39	34	32	32	32
8	60	46	38	32	58	45	37	32	44	37	31	42	36	31	41	35	31	29	29	29
9	56	42	34	29	54	42	34	29	40	33	28	39	33	28	38	32	28	26	26	26
10	52	39	31	26	51	39	31	26	37	30	26	36	30	25	35	29	25	23	23	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5352	5352	5352
5°	5341	5274	5283
10°	5293	5188	5199
15°	5225	5083	5099
20°	5135	4960	4970
25°	5034	4816	4819
30°	4899	4658	4656
35°	4756	4482	4481
40°	4596	4294	4288
45°	4439	4093	4080
50°	4258	3873	3861
55°	4067	3632	3641
60°	3846	3394	3416
65°	3611	3143	3212
70°	3339	2906	3043
75°	3022	2726	2911
80°	2608	2594	2853
85°	2278	2549	2919

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4439 cd/sqm

TEST NUMBER: P1217228
 CATALOG NUMBER: 14-ID2-55-CNV-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.0	3.3
10°-20°	535.1	9.5
20°-30°	797.3	14.1
30°-40°	938.3	16.6
40°-50°	946.7	16.7
50°-60°	834.6	14.7
60°-70°	639.4	11.3
70°-80°	418.7	7.4
80°-90°	223.9	4.0
90°-100°	95.1	1.7
100°-110°	30.4	0.5
110°-120°	7.1	0.1
120°-130°	3.3	0.1
130°-140°	1.6	0.0
140°-150°	0.6	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1520.4	26.9
0°-40°	2458.7	43.4
0°-60°	4240.0	74.9
0°-90°	5522.0	97.6
90°-120°	132.7	2.3
90°-150°	138.1	2.4
90°-180°	138.0	2.4
0°-180°	5660.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1984	1981	1976	1977	1983	188
15°	1896	1894	1894	1901	1909	534
25°	1727	1724	1729	1738	1744	795
35°	1488	1488	1500	1512	1517	930
45°	1213	1214	1228	1242	1244	935
55°	916	916	931	950	954	819
65°	616	618	643	667	678	610
75°	334	347	401	437	447	354
85°	108	148	216	257	267	109
90°	38	84	146	184	195	25
95°	31	43	89	124	135	25
105°	22	17	19	38	46	23
115°	14	11	6	0	0	14
125°	9	7	3	0	0	8
135°	5	4	2	0	0	4
145°	3	2	0	0	0	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217228

CATALOG NUMBER: 14-ID2-55-CNV-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1988.7	1988.7	1988.7	1988.7	1988.7
2.5°	1992.6	1989.7	1983.0	1984.9	1987.8
5°	1984.0	1981.1	1976.4	1977.3	1983.0
7.5°	1971.6	1967.8	1964.0	1966.9	1973.5
10°	1950.7	1948.8	1945.9	1949.7	1956.4
12.5°	1925.9	1924.0	1923.1	1927.8	1935.5
15°	1895.5	1893.6	1893.6	1901.2	1908.8
17.5°	1860.3	1859.3	1861.2	1869.8	1875.5
20°	1819.4	1818.4	1821.3	1829.8	1836.5
22.5°	1776.6	1774.6	1777.5	1785.1	1791.8
25°	1727.1	1724.2	1729.0	1737.5	1744.2
27.5°	1673.8	1669.0	1676.6	1686.2	1691.9
30°	1612.9	1613.8	1621.4	1631.0	1636.7
32.5°	1552.9	1552.0	1561.5	1572.9	1578.6
35°	1488.2	1488.2	1499.6	1512.0	1516.8
37.5°	1420.7	1423.5	1434.9	1446.4	1452.1
40°	1352.2	1356.0	1367.4	1379.8	1384.5
42.5°	1281.7	1285.5	1297.9	1311.2	1315.0
45°	1213.2	1214.2	1227.5	1241.8	1243.7
47.5°	1139.0	1140.0	1154.2	1168.5	1171.4
50°	1065.7	1066.7	1081.0	1096.2	1098.1
52.5°	991.5	992.5	1004.8	1022.9	1026.7
55°	916.3	916.3	930.6	949.7	953.5
57.5°	841.2	841.2	856.4	876.4	881.1
60°	764.1	766.0	785.0	804.1	810.7
62.5°	689.9	691.8	712.7	732.7	741.3
65°	615.7	618.5	643.3	667.0	677.5
67.5°	543.3	547.1	575.7	606.1	615.7
70°	471.0	478.6	512.9	546.2	556.7
72.5°	401.6	410.1	455.8	491.0	500.5
75°	334.0	347.3	400.6	436.8	447.2
77.5°	268.3	288.3	349.2	388.2	397.7
80°	206.5	236.0	301.6	340.7	351.1
82.5°	154.2	187.5	257.9	297.8	307.4
85°	107.5	147.5	216.0	256.9	267.4
87.5°	69.5	113.2	178.9	218.9	230.3
90°	38.1	83.7	145.6	183.6	195.1
92.5°	34.3	60.9	116.1	152.2	163.7
95°	31.4	42.8	89.4	123.7	135.1
97.5°	28.5	28.5	66.6	98.0	108.5
100°	26.6	20.9	47.6	75.2	85.6
102.5°	23.8	19.0	31.4	55.2	64.7
105°	21.9	17.1	19.0	38.1	45.7
107.5°	20.0	15.2	9.5	23.8	30.4
110°	18.1	14.3	7.6	11.4	18.1

TEST NUMBER: P1217228

CATALOG NUMBER: 14-ID2-55-CNV-L850-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	16.2	12.4	6.7	2.9	6.7
115°	14.3	11.4	5.7	0.0	0.0
117.5°	12.4	10.5	4.8	0.0	0.0
120°	11.4	8.6	4.8	0.0	0.0
122.5°	10.5	7.6	3.8	0.0	0.0
125°	8.6	6.7	2.9	0.0	0.0
127.5°	7.6	5.7	2.9	0.0	0.0
130°	6.7	5.7	1.9	0.0	0.0
132.5°	5.7	4.8	1.9	0.0	0.0
135°	4.8	3.8	1.9	0.0	0.0
137.5°	4.8	3.8	1.0	0.0	0.0
140°	3.8	2.9	1.0	0.0	0.0
142.5°	2.9	1.9	1.0	0.0	0.0
145°	2.9	1.9	0.0	0.0	0.0
147.5°	1.9	1.9	0.0	0.0	0.0
150°	1.9	1.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217228

CATALOG NUMBER: 14-ID2-55-CNV-L850-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.89	17.48	16.30	17.85	18.23	16.54	18.13	16.94	18.49	18.87
	3H	17.49	18.94	17.91	19.31	19.73	18.51	19.96	18.93	20.33	20.75
	4H	18.06	19.43	18.50	19.82	20.26	19.41	20.77	19.84	21.17	21.60
	6H	18.46	19.73	18.91	20.14	20.59	20.28	21.55	20.73	21.96	22.41
	8H	18.58	19.79	19.04	20.23	20.69	20.70	21.92	21.16	22.35	22.81
	12H	18.66	19.82	19.13	20.25	20.74	21.14	22.31	21.61	22.74	23.22
4H	2H	16.53	17.90	16.97	18.30	18.73	17.05	18.41	17.48	18.81	19.25
	3H	18.36	19.51	18.80	19.95	20.41	19.26	20.41	19.70	20.85	21.31
	4H	19.05	20.10	19.51	20.55	21.05	20.31	21.36	20.78	21.82	22.31
	6H	19.57	20.49	20.06	20.98	21.49	21.36	22.29	21.85	22.77	23.28
	8H	19.74	20.61	20.24	21.09	21.61	21.88	22.74	22.37	23.23	23.75
	12H	19.87	20.65	20.38	21.17	21.69	22.42	23.21	22.94	23.73	24.25
8H	4H	19.47	20.34	19.97	20.83	21.35	20.58	21.45	21.08	21.94	22.46
	6H	20.14	20.87	20.67	21.40	21.93	21.80	22.53	22.33	23.06	23.59
	8H	20.40	21.06	20.94	21.60	22.14	22.45	23.11	22.99	23.65	24.19
	12H	20.61	21.19	21.15	21.73	22.34	23.16	23.75	23.70	24.28	24.89
12H	4H	19.57	20.35	20.08	20.87	21.39	20.60	21.39	21.12	21.91	22.43
	6H	20.30	20.96	20.84	21.50	22.04	21.86	22.52	22.40	23.07	23.61
	8H	20.63	21.22	21.18	21.75	22.36	22.58	23.17	23.12	23.70	24.31

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L850-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K): 4966
 CIE u' : 0.2093
 CIE v' : 0.4890
 Duv: 0.0036
 CIE x: 0.3468
 CIE y: 0.3601
 CIE z: 0.2931
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 570
 Purity: 12.1135
 R_f: 84
 R_g: 96.2

CRI (Ra): 83.1
 R1: 81.0
 R2: 87.8
 R3: 92.7
 R4: 82.4
 R5: 81.0
 R6: 82.6
 R7: 88.5
 R8: 68.6
 R9: 10.3
 R10: 70.9
 R11: 81.3
 R12: 55.9
 R13: 82.8
 R14: 96.1
 R15: 75.1



Test Conditions

Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.94

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.11

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7



TM-30-18

Summary

$R_f = 84$
 $R_g = 96.2$
 $\text{CIE } R_a = 83.1$
 $R_9 = 10.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)