

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217187

Luminaire Tested: 14-ID2-30-CNV-L840-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1217187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 14-ID2-30-CNV-L840-U  
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP LENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3239.7 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.33  
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')  
CIE Type: Direct  
  
Input Watts (W): 26.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1217187  
CATALOG NUMBER: 14-ID2-30-CNV-L840-U

### Luminous Intensity Polar Plot





TEST NUMBER: P1217187  
 CATALOG NUMBER: 14-ID2-30-CNV-L840-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	118	118	118	118	115	115	115	115	110	110	110	105	105	105	100	100	100
1	107	102	98	94	104	100	96	92	95	92	88	91	88	85	87	84	82
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69
3	89	78	70	63	86	76	69	62	73	66	61	70	64	60	67	62	58
4	81	69	60	54	79	68	59	53	65	58	52	62	56	51	60	54	50
5	75	62	53	46	73	61	52	46	58	51	45	56	49	44	54	48	44
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	49	43	38
7	64	51	42	36	62	50	41	35	48	40	35	46	40	35	45	39	34
8	60	46	38	32	58	45	37	32	44	37	31	42	36	31	41	35	31
9	56	42	34	29	54	42	34	29	40	33	28	39	33	28	38	32	28
10	52	39	31	26	51	39	31	26	37	30	26	36	30	25	35	29	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3063	3063	3063
5°	3057	3018	3024
10°	3029	2969	2976
15°	2990	2909	2918
20°	2939	2839	2845
25°	2881	2757	2758
30°	2804	2666	2665
35°	2722	2566	2565
40°	2630	2458	2454
45°	2541	2343	2335
50°	2438	2217	2210
55°	2328	2079	2084
60°	2201	1942	1955
65°	2067	1799	1838
70°	1911	1664	1741
75°	1730	1560	1667
80°	1493	1485	1633
85°	1303	1459	1670

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2541 cd/sqm



TEST NUMBER: P1217187  
 CATALOG NUMBER: 14-ID2-30-CNV-L840-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.6	3.3
10°-20°	306.2	9.5
20°-30°	456.4	14.1
30°-40°	537.0	16.6
40°-50°	541.9	16.7
50°-60°	477.7	14.7
60°-70°	366.0	11.3
70°-80°	239.7	7.4
80°-90°	128.1	4.0
90°-100°	54.4	1.7
100°-110°	17.4	0.5
110°-120°	4.1	0.1
120°-130°	1.9	0.1
130°-140°	0.9	0.0
140°-150°	0.3	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.2	26.9
0°-40°	1407.3	43.4
0°-60°	2426.9	74.9
0°-90°	3160.6	97.6
90°-120°	75.9	2.3
90°-150°	79.0	2.4
90°-180°	79.0	2.4
0°-180°	3239.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1138	1138	1138	1138	1138	
5°	1136	1134	1131	1132	1135	108
15°	1085	1084	1084	1088	1092	306
25°	988	987	990	994	998	455
35°	852	852	858	865	868	532
45°	694	695	703	711	712	535
55°	524	524	533	544	546	469
65°	352	354	368	382	388	349
75°	191	199	229	250	256	203
85°	62	84	124	147	153	62
90°	22	48	83	105	112	14
95°	18	24	51	71	77	14
105°	12	10	11	22	26	13
115°	8	6	3	0	0	8
125°	5	4	2	0	0	5
135°	3	2	1	0	0	2
145°	2	1	0	0	0	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1217187  
 CATALOG NUMBER: 14-ID2-30-CNV-L840-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1138.3	1138.3	1138.3	1138.3	1138.3
2.5°	1140.5	1138.8	1135.0	1136.1	1137.7
5°	1135.6	1133.9	1131.2	1131.8	1135.0
7.5°	1128.5	1126.3	1124.1	1125.8	1129.6
10°	1116.5	1115.4	1113.8	1116.0	1119.8
12.5°	1102.3	1101.3	1100.7	1103.4	1107.8
15°	1084.9	1083.8	1083.8	1088.2	1092.5
17.5°	1064.8	1064.2	1065.3	1070.2	1073.5
20°	1041.3	1040.8	1042.4	1047.3	1051.2
22.5°	1016.8	1015.8	1017.4	1021.7	1025.6
25°	988.5	986.9	989.6	994.5	998.3
27.5°	958.0	955.3	959.7	965.1	968.4
30°	923.2	923.7	928.1	933.5	936.8
32.5°	888.8	888.3	893.8	900.3	903.6
35°	851.8	851.8	858.4	865.4	868.2
37.5°	813.1	814.8	821.3	827.9	831.1
40°	773.9	776.1	782.6	789.7	792.4
42.5°	733.6	735.8	742.9	750.5	752.7
45°	694.4	695.0	702.6	710.8	711.8
47.5°	651.9	652.5	660.6	668.8	670.4
50°	610.0	610.5	618.7	627.4	628.5
52.5°	567.5	568.1	575.1	585.5	587.7
55°	524.5	524.5	532.7	543.5	545.7
57.5°	481.5	481.5	490.2	501.6	504.3
60°	437.3	438.4	449.3	460.2	464.0
62.5°	394.9	396.0	407.9	419.4	424.3
65°	352.4	354.0	368.2	381.8	387.8
67.5°	311.0	313.2	329.5	346.9	352.4
70°	269.6	274.0	293.6	312.6	318.6
72.5°	229.8	234.7	260.9	281.0	286.5
75°	191.2	198.8	229.3	250.0	256.0
77.5°	153.6	165.0	199.9	222.2	227.7
80°	118.2	135.1	172.7	195.0	201.0
82.5°	88.2	107.3	147.6	170.5	175.9
85°	61.5	84.4	123.6	147.1	153.0
87.5°	39.8	64.8	102.4	125.3	131.8
90°	21.8	47.9	83.3	105.1	111.7
92.5°	19.6	34.9	66.4	87.1	93.7
95°	18.0	24.5	51.2	70.8	77.3
97.5°	16.3	16.3	38.1	56.1	62.1
100°	15.2	12.0	27.2	43.0	49.0
102.5°	13.6	10.9	18.0	31.6	37.0
105°	12.5	9.8	10.9	21.8	26.1
107.5°	11.4	8.7	5.4	13.6	17.4
110°	10.3	8.2	4.4	6.5	10.3



TEST NUMBER: P1217187  
 CATALOG NUMBER: 14-ID2-30-CNV-L840-U

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	9.3	7.1	3.8	1.6	3.8
115°	8.2	6.5	3.3	0.0	0.0
117.5°	7.1	6.0	2.7	0.0	0.0
120°	6.5	4.9	2.7	0.0	0.0
122.5°	6.0	4.4	2.2	0.0	0.0
125°	4.9	3.8	1.6	0.0	0.0
127.5°	4.4	3.3	1.6	0.0	0.0
130°	3.8	3.3	1.1	0.0	0.0
132.5°	3.3	2.7	1.1	0.0	0.0
135°	2.7	2.2	1.1	0.0	0.0
137.5°	2.7	2.2	0.5	0.0	0.0
140°	2.2	1.6	0.5	0.0	0.0
142.5°	1.6	1.1	0.5	0.0	0.0
145°	1.6	1.1	0.0	0.0	0.0
147.5°	1.1	1.1	0.0	0.0	0.0
150°	1.1	0.5	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217187  
 CATALOG NUMBER: 14-ID2-30-CNV-L840-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.95	15.55	14.36	15.91	16.29	14.60	16.19	15.00	16.55	16.93
	3H	15.55	17.00	15.97	17.38	17.80	16.57	18.02	16.99	18.40	18.82
	4H	16.12	17.49	16.56	17.89	18.32	17.47	18.83	17.90	19.23	19.66
	6H	16.52	17.79	16.97	18.20	18.65	18.34	19.61	18.79	20.02	20.47
	8H	16.64	17.85	17.10	18.29	18.75	18.76	19.98	19.23	20.41	20.87
	12H	16.72	17.88	17.19	18.32	18.80	19.20	20.37	19.67	20.80	21.29
4H	2H	14.60	15.96	15.03	16.36	16.79	15.11	16.47	15.55	16.87	17.31
	3H	16.42	17.57	16.87	18.02	18.47	17.32	18.47	17.76	18.92	19.37
	4H	17.11	18.16	17.58	18.62	19.11	18.37	19.42	18.84	19.88	20.37
	6H	17.63	18.55	18.12	19.04	19.55	19.42	20.35	19.91	20.83	21.34
	8H	17.80	18.67	18.30	19.16	19.68	19.94	20.81	20.43	21.29	21.81
	12H	17.93	18.71	18.45	19.23	19.76	20.48	21.27	21.00	21.79	22.31
8H	4H	17.53	18.40	18.03	18.89	19.41	18.64	19.51	19.14	20.00	20.52
	6H	18.21	18.94	18.74	19.47	20.00	19.86	20.60	20.39	21.13	21.65
	8H	18.46	19.12	19.00	19.66	20.20	20.51	21.17	21.05	21.71	22.25
	12H	18.67	19.26	19.21	19.79	20.40	21.22	21.81	21.77	22.34	22.95
12H	4H	17.63	18.41	18.14	18.93	19.46	18.67	19.45	19.18	19.97	20.49
	6H	18.36	19.02	18.90	19.57	20.11	19.92	20.58	20.47	21.13	21.67
	8H	18.69	19.28	19.24	19.81	20.42	20.64	21.23	21.19	21.76	22.37



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-5

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L840-U

Data in this report applies to families of products including 22ID2-55-CFR1-L840-U


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L840-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 80CRI

**Spectral Parameters**

CCT (K): 3915  
 CIE u': 0.2259  
 CIE v': 0.5051  
 Duv: 0.0015  
 CIE x: 0.3854  
 CIE y: 0.3830  
 CIE z: 0.2316  
 Peak Wavelength (nm): 453  
 Dominant Wavelength (nm): 578  
 Purity: 30.6207  
 Rf: 83.2  
 Rg: 94.6

CRI (Ra):	82.3		
R1:	80.6	R9:	7.6
R2:	88.9	R10:	72.9
R3:	94.6	R11:	78.7
R4:	80.5	R12:	57.3
R5:	80.0	R13:	82.7
R6:	84.0	R14:	97.1
R7:	86.1	R15:	74.3
R8:	64.0		



**Test Conditions**


Stabilization Time: 34M  
 Operation Time: 1H 34M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-5

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-5

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR S/P: 1.65**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-5

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 3.36**





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

**Summary**

$R_f = 83.2$   
 $R_g = 94.6$   
 CIE  $R_a = 82.3$   
 $R_9 = 7.6$




**Color Vector Graphics**








**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 86	CES26 = 83	CES51 = 92	CES76 = 75
CES02 = 61	CES27 = 91	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 88	CES78 = 74
CES04 = 70	CES29 = 90	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 90	CES55 = 85	CES80 = 89
CES06 = 50	CES31 = 91	CES56 = 83	CES81 = 81
CES07 = 41	CES32 = 83	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 90	CES84 = 90
CES10 = 74	CES35 = 92	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 78	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 91	CES62 = 79	CES87 = 84
CES13 = 42	CES38 = 84	CES63 = 82	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 77
CES15 = 71	CES40 = 96	CES65 = 74	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 70	CES91 = 67
CES17 = 49	CES42 = 93	CES67 = 69	CES92 = 64
CES18 = 56	CES43 = 91	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 63
CES20 = 65	CES45 = 94	CES70 = 72	CES95 = 72
CES21 = 86	CES46 = 91	CES71 = 64	CES96 = 84
CES22 = 78	CES47 = 95	CES72 = 88	CES97 = 91
CES23 = 91	CES48 = 83	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 90	CES99 = 77
CES25 = 71	CES50 = 93	CES75 = 68	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)