

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216798

Luminaire Tested: 14-ID2-60-CFR1-L830-U

Issue Date: 12/5/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1216798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/5/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: 14-ID2-60-CFR1-L830-U  
Description: 1X4 IN DEPTH TROFFER WITH 1INCH CUBE REGRESS LENS  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5816.9 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.17 / 1.28  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 53.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P1216798  
CATALOG NUMBER: 14-ID2-60-CFR1-L830-U

### Luminous Intensity Polar Plot





TEST NUMBER: P1216798  
 CATALOG NUMBER: 14-ID2-60-CFR1-L830-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	65	72	67	63	61
4	84	73	64	58	82	71	63	57	69	62	56	66	61	56	64	59	55	53
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48	46
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43	41
7	67	53	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38	36
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34	32
9	58	45	37	32	57	44	37	31	43	36	31	42	36	31	41	35	31	29
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6370	6370	6370
5°	6378	6352	6373
10°	6353	6318	6340
15°	6296	6253	6258
20°	6216	6146	6123
25°	6113	6005	5950
30°	5982	5842	5753
35°	5818	5640	5518
40°	5635	5410	5265
45°	5420	5173	4994
50°	5189	4898	4700
55°	4931	4604	4392
60°	4626	4293	4060
65°	4328	3947	3690
70°	3957	3570	3308
75°	3503	3105	2839
80°	2862	2512	2253
85°	2032	1667	1365

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5420 cd/sqm



TEST NUMBER: P1216798  
 CATALOG NUMBER: 14-ID2-60-CFR1-L830-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.6	3.8
10°-20°	633.3	10.9
20°-30°	932.7	16.0
30°-40°	1075.9	18.5
40°-50°	1052.1	18.1
50°-60°	884.6	15.2
60°-70°	621.5	10.7
70°-80°	321.9	5.5
80°-90°	71.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1789.7	30.8
0°-40°	2865.5	49.3
0°-60°	4802.2	82.6
0°-90°	5816.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5816.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2367	2367	2367	2367	2367	
5°	2361	2358	2352	2352	2359	224
15°	2260	2255	2244	2240	2246	637
25°	2059	2050	2022	2002	2004	948
35°	1771	1756	1717	1686	1680	1107
45°	1424	1407	1359	1322	1312	1099
55°	1051	1031	981	949	936	939
65°	680	662	620	592	580	674
75°	337	325	299	279	273	358
85°	66	68	54	46	44	82
90°	0	0	0	0	0	



TEST NUMBER: P1216798  
 CATALOG NUMBER: 14-ID2-60-CFR1-L830-U

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2367.2	2367.2	2367.2	2367.2	2367.2
2.5°	2372.1	2367.2	2361.3	2363.3	2366.2
5°	2361.3	2358.4	2351.5	2352.5	2359.3
7.5°	2346.6	2342.7	2334.8	2336.8	2344.6
10°	2325.0	2319.1	2312.2	2313.2	2320.1
12.5°	2295.5	2290.6	2281.8	2280.8	2287.6
15°	2260.1	2255.2	2244.4	2240.5	2246.4
17.5°	2218.9	2213.0	2199.2	2192.4	2196.3
20°	2170.8	2164.9	2146.2	2133.4	2138.3
22.5°	2117.7	2110.8	2087.3	2072.5	2074.5
25°	2058.8	2049.9	2022.4	2001.8	2003.8
27.5°	1994.9	1983.1	1952.7	1930.1	1929.1
30°	1925.2	1912.4	1880.0	1853.5	1851.5
32.5°	1849.6	1836.8	1799.5	1771.0	1769.0
35°	1771.0	1756.3	1717.0	1685.5	1679.6
37.5°	1689.5	1672.8	1630.5	1600.1	1595.2
40°	1604.0	1586.3	1540.2	1507.7	1498.9
42.5°	1515.6	1498.9	1449.8	1418.4	1406.6
45°	1424.3	1406.6	1359.4	1322.1	1312.3
47.5°	1336.8	1313.3	1263.2	1231.7	1217.0
50°	1239.6	1219.9	1169.9	1137.4	1122.7
52.5°	1146.3	1126.6	1074.6	1042.2	1029.4
55°	1051.0	1031.4	981.3	948.8	936.1
57.5°	952.8	937.1	888.9	858.5	844.7
60°	859.5	843.7	797.6	769.1	754.4
62.5°	772.0	752.4	707.2	680.7	666.0
65°	679.7	662.0	619.8	592.3	579.5
67.5°	590.3	573.6	534.3	510.8	500.9
70°	502.9	488.2	453.8	430.2	420.4
72.5°	417.5	404.7	374.2	351.6	344.8
75°	336.9	325.1	298.6	279.0	273.1
77.5°	258.3	251.5	226.9	210.2	205.3
80°	184.7	181.7	162.1	148.3	145.4
82.5°	119.8	118.9	106.1	94.3	90.4
85°	65.8	67.8	54.0	46.2	44.2
87.5°	23.6	23.6	16.7	14.7	13.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216798  
 CATALOG NUMBER: 14-ID2-60-CFR1-L830-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.54	19.12	17.91	19.44	19.75	16.89	18.47	17.25	18.78	19.10
	3H	19.16	20.59	19.54	20.91	21.27	18.37	19.80	18.75	20.12	20.49
	4H	19.73	21.07	20.13	21.42	21.79	18.87	20.20	19.27	20.55	20.93
	6H	20.11	21.34	20.52	21.71	22.10	19.17	20.41	19.58	20.77	21.16
	8H	20.21	21.38	20.63	21.77	22.17	19.24	20.42	19.66	20.81	21.21
	12H	20.26	21.38	20.69	21.77	22.20	19.26	20.39	19.69	20.77	21.20
4H	2H	18.02	19.36	18.42	19.70	20.08	17.49	18.83	17.89	19.18	19.55
	3H	19.86	20.97	20.27	21.37	21.77	19.18	20.29	19.59	20.69	21.09
	4H	20.55	21.55	20.98	21.97	22.40	19.78	20.78	20.21	21.19	21.63
	6H	21.04	21.91	21.50	22.36	22.81	20.18	21.05	20.63	21.49	21.95
	8H	21.18	21.99	21.64	22.44	22.90	20.27	21.09	20.73	21.53	22.00
	12H	21.26	21.99	21.74	22.47	22.94	20.32	21.05	20.80	21.53	22.00
8H	4H	20.74	21.56	21.20	22.00	22.47	20.05	20.86	20.51	21.31	21.77
	6H	21.33	22.01	21.82	22.49	22.97	20.53	21.21	21.03	21.70	22.17
	8H	21.52	22.13	22.03	22.63	23.12	20.67	21.28	21.18	21.78	22.27
	12H	21.65	22.19	22.16	22.68	23.24	20.75	21.29	21.26	21.78	22.34
12H	4H	20.75	21.48	21.23	21.96	22.43	20.07	20.80	20.55	21.28	21.75
	6H	21.34	21.95	21.85	22.46	22.94	20.57	21.17	21.08	21.68	22.17
	8H	21.58	22.11	22.08	22.60	23.16	20.75	21.29	21.26	21.78	22.34

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U




**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-458-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/27/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Corelite  
 Catalog Number: **22ID2-55-CFR1-L830-U**  
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

**Spectral Parameters**

CCT (K): 3031  
 CIE u': 0.2493  
 CIE v': 0.5215  
 Duv: 0.0005  
 CIE x: 0.4355  
 CIE y: 0.4049  
 CIE z: 0.1596  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 582  
 Purity: 52.24762  
 Rf: 84.8  
 Rg: 95.8

CRI (Ra):	82.5		
R1:	80.7	R9:	5.8
R2:	90.5	R10:	78.6
R3:	96.7	R11:	80.2
R4:	80.7	R12:	69.8
R5:	80.9	R13:	83.0
R6:	88.5	R14:	98.8
R7:	83.0	R15:	73.0
R8:	58.8		



**Test Conditions**


Stabilization Time: 38M  
 Operation Time: 1H 38M  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR S/P: 1.35

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.59





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

**Summary**

$R_f = 84.8$   
 $R_g = 95.8$   
 $CIE R_a = 82.5$   
 $R_9 = 5.8$




**Color Vector Graphics**






Individual Sample Fidelity Index ( $R_{f,i}$ )

CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	







Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)