

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217198

Luminaire Tested: 14-ID2-35-CNV-L935-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-35-CNV-L935-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3099.2 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.33
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 30.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217198
CATALOG NUMBER: 14-ID2-35-CNV-L935-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217198

CATALOG NUMBER: 14-ID2-35-CNV-L935-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	118	118	118	118	115	115	115	115		110	110	110			105	105	105			98
1	107	102	98	94	104	100	96	92		95	92	88			91	88	85			80
2	98	89	82	76	95	87	80	75		83	77	73			79	75	71			66
3	89	78	70	63	86	76	69	62		73	66	61			70	64	60			56
4	81	69	60	54	79	68	59	53		65	58	52			62	56	51			48
5	75	62	53	46	73	61	52	46		58	51	45			56	49	44			41
6	69	56	47	40	67	55	46	40		53	45	39			51	44	39			36
7	64	51	42	36	62	50	41	35		48	40	35			46	40	35			32
8	60	46	38	32	58	45	37	32		44	37	31			42	36	31			29
9	56	42	34	29	54	42	34	29		40	33	28			39	33	28			26
10	52	39	31	26	51	39	31	26		37	30	26			36	30	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2930	2930	2930
5°	2924	2887	2893
10°	2898	2841	2847
15°	2861	2783	2792
20°	2812	2716	2721
25°	2756	2637	2639
30°	2682	2550	2549
35°	2604	2454	2453
40°	2516	2351	2348
45°	2431	2241	2234
50°	2332	2121	2114
55°	2227	1989	1994
60°	2106	1858	1871
65°	1977	1721	1759
70°	1828	1591	1666
75°	1655	1492	1594
80°	1429	1421	1562
85°	1248	1396	1598

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2431 cd/sqm

TEST NUMBER: P1217198
 CATALOG NUMBER: 14-ID2-35-CNV-L935-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	3.3
10°-20°	293.0	9.5
20°-30°	436.6	14.1
30°-40°	513.7	16.6
40°-50°	518.4	16.7
50°-60°	457.0	14.7
60°-70°	350.1	11.3
70°-80°	229.3	7.4
80°-90°	122.6	4.0
90°-100°	52.1	1.7
100°-110°	16.6	0.5
110°-120°	3.9	0.1
120°-130°	1.8	0.1
130°-140°	0.9	0.0
140°-150°	0.3	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	832.5	26.9
0°-40°	1346.2	43.4
0°-60°	2321.6	74.9
0°-90°	3023.6	97.6
90°-120°	72.6	2.3
90°-150°	75.6	2.4
90°-180°	76.0	2.5
0°-180°	3099.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1086	1085	1082	1083	1086	103
15°	1038	1037	1037	1041	1045	293
25°	946	944	947	951	955	435
35°	815	815	821	828	830	509
45°	664	665	672	680	681	512
55°	502	502	510	520	522	449
65°	337	339	352	365	371	334
75°	183	190	219	239	245	194
85°	59	81	118	141	146	60
90°	21	46	80	101	107	13
95°	17	23	49	68	74	13
105°	12	9	10	21	25	13
115°	8	6	3	0	0	8
125°	5	4	2	0	0	4
135°	3	2	1	0	0	2
145°	2	1	0	0	0	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217198

CATALOG NUMBER: 14-ID2-35-CNV-L935-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1088.9	1088.9	1088.9	1088.9	1088.9
2.5°	1091.0	1089.4	1085.8	1086.8	1088.4
5°	1086.3	1084.8	1082.1	1082.7	1085.8
7.5°	1079.5	1077.5	1075.4	1076.9	1080.6
10°	1068.1	1067.0	1065.5	1067.6	1071.2
12.5°	1054.5	1053.5	1053.0	1055.6	1059.7
15°	1037.9	1036.8	1036.8	1041.0	1045.2
17.5°	1018.6	1018.1	1019.1	1023.8	1026.9
20°	996.2	995.7	997.2	1001.9	1005.6
22.5°	972.7	971.7	973.3	977.4	981.1
25°	945.6	944.1	946.7	951.4	955.0
27.5°	916.5	913.9	918.0	923.2	926.4
30°	883.1	883.6	887.8	893.0	896.1
32.5°	850.3	849.8	855.0	861.2	864.4
35°	814.9	814.9	821.1	827.9	830.5
37.5°	777.9	779.4	785.7	791.9	795.1
40°	740.4	742.4	748.7	755.5	758.1
42.5°	701.8	703.9	710.7	718.0	720.0
45°	664.3	664.8	672.1	679.9	681.0
47.5°	623.7	624.2	632.0	639.8	641.4
50°	583.5	584.1	591.9	600.2	601.3
52.5°	542.9	543.4	550.2	560.1	562.2
55°	501.7	501.7	509.6	520.0	522.1
57.5°	460.6	460.6	468.9	479.9	482.5
60°	418.4	419.4	429.8	440.3	443.9
62.5°	377.7	378.8	390.2	401.2	405.9
65°	337.1	338.7	352.2	365.2	371.0
67.5°	297.5	299.6	315.2	331.9	337.1
70°	257.9	262.1	280.8	299.1	304.8
72.5°	219.9	224.6	249.6	268.8	274.1
75°	182.9	190.2	219.3	239.1	244.9
77.5°	146.9	157.9	191.2	212.6	217.8
80°	113.1	129.2	165.2	186.5	192.3
82.5°	84.4	102.6	141.2	163.1	168.3
85°	58.9	80.8	118.3	140.7	146.4
87.5°	38.0	62.0	98.0	119.8	126.1
90°	20.8	45.8	79.7	100.6	106.8
92.5°	18.8	33.3	63.6	83.4	89.6
95°	17.2	23.4	49.0	67.7	74.0
97.5°	15.6	15.6	36.5	53.7	59.4
100°	14.6	11.5	26.1	41.2	46.9
102.5°	13.0	10.4	17.2	30.2	35.4
105°	12.0	9.4	10.4	20.8	25.0
107.5°	10.9	8.3	5.2	13.0	16.7
110°	9.9	7.8	4.2	6.3	9.9

TEST NUMBER: P1217198

CATALOG NUMBER: 14-ID2-35-CNV-L935-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	8.9	6.8	3.6	1.6	3.6
115°	7.8	6.3	3.1	0.0	0.0
117.5°	6.8	5.7	2.6	0.0	0.0
120°	6.3	4.7	2.6	0.0	0.0
122.5°	5.7	4.2	2.1	0.0	0.0
125°	4.7	3.6	1.6	0.0	0.0
127.5°	4.2	3.1	1.6	0.0	0.0
130°	3.6	3.1	1.0	0.0	0.0
132.5°	3.1	2.6	1.0	0.0	0.0
135°	2.6	2.1	1.0	0.0	0.0
137.5°	2.6	2.1	0.5	0.0	0.0
140°	2.1	1.6	0.5	0.0	0.0
142.5°	1.6	1.0	0.5	0.0	0.0
145°	1.6	1.0	0.0	0.0	0.0
147.5°	1.0	1.0	0.0	0.0	0.0
150°	1.0	0.5	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217198

CATALOG NUMBER: 14-ID2-35-CNV-L935-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	15.39	14.20	15.76	16.13	14.44	16.03	14.85	16.40	16.78
	3H	15.40	16.84	15.81	17.22	17.64	16.42	17.86	16.83	18.24	18.66
	4H	15.97	17.33	16.40	17.73	18.17	17.31	18.68	17.75	19.08	19.51
	6H	16.36	17.63	16.81	18.05	18.50	18.19	19.46	18.64	19.87	20.32
	8H	16.49	17.70	16.95	18.14	18.59	18.61	19.82	19.07	20.26	20.72
	12H	16.57	17.73	17.03	18.16	18.65	19.05	20.21	19.52	20.65	21.13
4H	2H	14.44	15.81	14.88	16.20	16.64	14.96	16.32	15.39	16.72	17.15
	3H	16.26	17.42	16.71	17.86	18.32	17.16	18.32	17.61	18.76	19.22
	4H	16.95	18.00	17.42	18.46	18.96	18.22	19.27	18.69	19.72	20.22
	6H	17.48	18.40	17.97	18.89	19.40	19.27	20.19	19.76	20.68	21.19
	8H	17.65	18.51	18.14	19.00	19.52	19.78	20.65	20.28	21.14	21.66
	12H	17.77	18.56	18.29	19.08	19.60	20.33	21.11	20.85	21.63	22.16
8H	4H	17.38	18.25	17.88	18.73	19.26	18.49	19.36	18.99	19.84	20.36
	6H	18.05	18.78	18.58	19.31	19.84	19.71	20.44	20.24	20.97	21.50
	8H	18.30	18.96	18.85	19.51	20.05	20.35	21.01	20.90	21.56	22.10
	12H	18.51	19.10	19.06	19.63	20.25	21.07	21.66	21.61	22.19	22.80
12H	4H	17.47	18.26	17.99	18.78	19.30	18.51	19.30	19.03	19.81	20.34
	6H	18.21	18.87	18.75	19.41	19.95	19.77	20.43	20.31	20.97	21.51
	8H	18.54	19.13	19.08	19.66	20.27	20.49	21.08	21.03	21.61	22.22

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-10

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L935-U

Data in this report applies to families of products including 22ID2-55-CFR1-L935-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-10
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L935-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 90CRI

Spectral Parameters

CCT (K): 3377
 CIE u' : 0.2392
 CIE v' : 0.5128
 Duv: -0.0007
 CIE x: 0.4116
 CIE y: 0.3922
 CIE z: 0.1962
 Peak Wavelength (nm): 618
 Dominant Wavelength (nm): 581
 Purity: 41.24368
 R_f: 91.8
 R_g: 99.6

CRI (Ra): 93.6
 R1: 94.1
 R2: 96.6
 R3: 97.5
 R4: 94.0
 R5: 93.6
 R6: 94.8
 R7: 93.4
 R8: 84.8
 R9: 64.2
 R10: 91.1
 R11: 94.7
 R12: 78.5
 R13: 95.0
 R14: 98.1
 R15: 91.0



Test Conditions

Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-10

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-10

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-10

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.19

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10


TM-30-18

Summary

$R_f = 91.8$
 $R_g = 99.6$
 $CIE R_a = 93.6$
 $R_9 = 64.2$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 92	CES52 = 99	CES77 = 89
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 96	CES54 = 93	CES79 = 95
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 86
CES07 = 43	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 94
CES10 = 75	CES35 = 96	CES60 = 92	CES85 = 83
CES11 = 58	CES36 = 82	CES61 = 92	CES86 = 86
CES12 = 64	CES37 = 95	CES62 = 87	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 93	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 97	CES66 = 88	CES91 = 75
CES17 = 50	CES42 = 95	CES67 = 87	CES92 = 80
CES18 = 56	CES43 = 94	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 81
CES20 = 67	CES45 = 97	CES70 = 86	CES95 = 84
CES21 = 86	CES46 = 97	CES71 = 82	CES96 = 92
CES22 = 78	CES47 = 96	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 92	CES73 = 82	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 92	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)