

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217074

Luminaire Tested: 14-ID2-70-CFD2-L950-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-70-CFD2-L950-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5842.1 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217074
CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217074

CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	109	109	109		103	103	103		98
1	107	102	98	94	104	100	95	92	94	91	88		90	87	85		85
2	97	89	82	76	94	87	80	75	82	77	72		78	74	70		75
3	89	78	70	63	86	76	69	62	73	66	61		69	64	59		66
4	81	69	60	54	79	68	59	53	65	57	52		62	56	51		59
5	75	62	53	46	72	61	52	46	58	51	45		56	49	44		53
6	69	56	47	40	67	55	46	40	52	45	39		50	44	39		48
7	64	51	42	36	62	50	41	35	48	40	35		46	39	34		44
8	60	46	38	32	58	45	37	32	44	36	31		42	36	31		41
9	56	42	34	29	54	42	34	29	40	33	28		39	32	28		38
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5501	5501	5501
5°	5493	5422	5429
10°	5445	5332	5338
15°	5372	5224	5222
20°	5280	5087	5067
25°	5169	4927	4889
30°	5030	4747	4709
35°	4852	4547	4519
40°	4666	4338	4325
45°	4440	4128	4120
50°	4211	3914	3934
55°	3965	3693	3761
60°	3717	3486	3589
65°	3450	3271	3407
70°	3173	3034	3174
75°	2861	2751	2858
80°	2505	2396	2485
85°	2161	2050	2134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4440 cd/sqm

TEST NUMBER: P1217074
 CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.3	3.3
10°-20°	549.2	9.4
20°-30°	815.4	14.0
30°-40°	954.4	16.3
40°-50°	958.6	16.4
50°-60°	849.0	14.5
60°-70°	660.3	11.3
70°-80°	419.4	7.2
80°-90°	187.4	3.2
90°-100°	89.5	1.5
100°-110°	68.4	1.2
110°-120°	48.2	0.8
120°-130°	28.8	0.5
130°-140°	14.1	0.2
140°-150°	5.1	0.1
150°-160°	0.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.0	26.7
0°-40°	2512.4	43.0
0°-60°	4320.0	73.9
0°-90°	5587.2	95.6
90°-120°	206.0	3.5
90°-150°	254.0	4.3
90°-180°	255.0	4.4
0°-180°	5842.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2044	2044	2044	2044	2044	
5°	2041	2039	2032	2033	2038	194
15°	1949	1950	1946	1949	1955	549
25°	1773	1775	1769	1768	1770	816
35°	1518	1531	1521	1529	1530	950
45°	1213	1238	1238	1257	1256	937
55°	893	929	946	979	985	800
65°	588	631	670	714	719	584
75°	316	361	404	441	439	337
85°	102	138	174	198	196	104
90°	44	76	109	125	123	27
95°	38	61	90	101	100	30
105°	27	44	72	85	88	29
115°	18	27	53	68	73	18
125°	11	14	34	47	52	10
135°	7	6	18	28	33	5
145°	4	3	6	13	17	2
155°	2	1	1	2	3	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217074

CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2044.4	2044.4	2044.4	2044.4	2044.4
2.5°	2049.1	2047.2	2039.7	2040.6	2044.4
5°	2040.6	2038.7	2032.1	2033.1	2037.8
7.5°	2026.4	2025.5	2018.9	2020.8	2027.4
10°	2006.6	2005.7	2000.0	2002.8	2008.5
12.5°	1981.1	1980.2	1975.5	1978.3	1984.0
15°	1949.0	1950.0	1946.2	1949.0	1954.7
17.5°	1912.2	1914.1	1908.4	1912.2	1916.9
20°	1870.6	1872.5	1867.8	1867.8	1872.5
22.5°	1824.4	1826.3	1820.6	1820.6	1824.4
25°	1773.4	1775.3	1768.7	1767.7	1769.6
27.5°	1715.8	1720.5	1712.0	1712.9	1713.9
30°	1656.3	1661.0	1652.5	1654.4	1655.3
32.5°	1588.3	1597.7	1588.3	1592.1	1594.0
35°	1518.4	1530.7	1521.3	1528.8	1529.7
37.5°	1447.6	1460.8	1452.3	1462.7	1463.6
40°	1373.0	1388.1	1381.5	1394.7	1396.6
42.5°	1295.6	1314.5	1310.7	1326.7	1324.8
45°	1213.4	1238.0	1238.0	1256.8	1255.9
47.5°	1134.1	1161.5	1165.3	1187.0	1187.0
50°	1053.8	1084.0	1092.5	1118.0	1119.0
52.5°	973.6	1006.6	1020.8	1047.2	1051.0
55°	893.3	929.2	946.2	979.2	984.9
57.5°	814.9	850.8	876.3	910.3	917.8
60°	738.4	776.2	806.4	845.1	851.7
62.5°	661.9	702.6	739.4	777.2	784.7
65°	588.3	630.8	669.5	713.9	718.6
67.5°	517.5	560.0	602.5	644.0	650.6
70°	447.6	492.0	535.4	578.8	580.7
72.5°	380.5	424.9	469.3	509.9	509.9
75°	316.3	360.7	404.2	441.0	439.1
77.5°	258.7	298.4	339.9	373.0	370.2
80°	198.3	238.9	278.6	308.8	305.9
82.5°	146.4	183.2	222.9	251.2	248.3
85°	102.0	137.9	173.7	198.3	195.5
87.5°	67.0	102.0	135.0	155.8	153.0
90°	44.4	76.5	108.6	124.6	122.8
92.5°	39.7	67.0	96.3	109.5	107.6
95°	37.8	61.4	89.7	101.0	100.1
97.5°	35.9	56.7	84.0	96.3	96.3
100°	33.1	52.9	80.3	92.5	93.5
102.5°	30.2	48.2	75.5	88.8	90.7
105°	27.4	44.4	71.8	85.0	87.8
107.5°	25.5	39.7	67.0	81.2	85.0
110°	22.7	35.9	62.3	77.4	81.2

TEST NUMBER: P1217074

CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	19.8	31.2	57.6	72.7	77.4
115°	17.9	27.4	52.9	68.0	72.7
117.5°	16.1	23.6	48.2	63.3	67.0
120°	14.2	20.8	43.4	58.5	62.3
122.5°	12.3	17.0	38.7	52.9	57.6
125°	11.3	14.2	34.0	47.2	51.9
127.5°	9.4	11.3	29.3	42.5	47.2
130°	8.5	8.5	24.6	37.8	42.5
132.5°	7.6	6.6	20.8	33.1	36.8
135°	6.6	5.7	17.9	28.3	33.1
137.5°	5.7	4.7	14.2	24.6	28.3
140°	4.7	3.8	11.3	20.8	23.6
142.5°	3.8	2.8	8.5	17.0	19.8
145°	3.8	2.8	5.7	13.2	17.0
147.5°	2.8	1.9	2.8	10.4	13.2
150°	1.9	1.9	0.9	7.6	9.4
152.5°	1.9	0.9	0.9	4.7	6.6
155°	1.9	0.9	0.9	1.9	2.8
157.5°	0.9	0.9	0.9	0.0	0.0
160°	0.9	0.9	0.9	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217074

CATALOG NUMBER: 14-ID2-70-CFD2-L950-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.75	17.29	16.19	17.70	18.12	16.64	18.18	17.08	18.59	19.01
	3H	17.31	18.71	17.76	19.12	19.59	18.67	20.06	19.11	20.48	20.95
	4H	17.86	19.18	18.32	19.61	20.09	19.49	20.81	19.96	21.24	21.72
	6H	18.24	19.46	18.72	19.92	20.41	20.18	21.40	20.66	21.85	22.35
	8H	18.35	19.52	18.84	20.00	20.50	20.46	21.63	20.95	22.10	22.61
	12H	18.42	19.54	18.92	20.01	20.54	20.72	21.84	21.22	22.31	22.84
4H	2H	16.45	17.77	16.92	18.20	18.68	17.15	18.47	17.62	18.91	19.39
	3H	18.24	19.36	18.72	19.84	20.34	19.40	20.51	19.88	21.00	21.50
	4H	18.93	19.94	19.43	20.43	20.97	20.38	21.39	20.88	21.88	22.42
	6H	19.43	20.32	19.95	20.84	21.39	21.22	22.11	21.74	22.63	23.18
	8H	19.59	20.42	20.12	20.94	21.51	21.57	22.40	22.10	22.93	23.49
	12H	19.70	20.45	20.25	21.00	21.57	21.91	22.66	22.46	23.21	23.78
8H	4H	19.35	20.18	19.87	20.70	21.26	20.62	21.45	21.15	21.97	22.54
	6H	19.99	20.69	20.55	21.26	21.83	21.61	22.30	22.17	22.87	23.44
	8H	20.23	20.85	20.80	21.43	22.02	22.06	22.69	22.64	23.27	23.85
	12H	20.41	20.97	20.98	21.53	22.19	22.52	23.08	23.10	23.65	24.30
12H	4H	19.42	20.17	19.97	20.72	21.29	20.64	21.39	21.18	21.94	22.51
	6H	20.11	20.74	20.68	21.32	21.90	21.65	22.28	22.22	22.85	23.44
	8H	20.41	20.97	20.98	21.53	22.19	22.17	22.72	22.74	23.29	23.94

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-13
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L950-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

Spectral Parameters

CCT (K): 4919
 CIE u' : 0.2096
 CIE v' : 0.4901
 Duv: 0.0038
 CIE x: 0.3483
 CIE y: 0.3619
 CIE z: 0.2898
 Peak Wavelength (nm): 453
 Dominant Wavelength (nm): 570
 Purity: 13.10873
 R_f: 90.8
 R_g: 97.4

CRI (Ra): 94.0
 R1: 94.8
 R2: 97.7
 R3: 98.4
 R4: 90.8
 R5: 92.2
 R6: 94.3
 R7: 94.0
 R8: 90.0
 R9: 77.7
 R10: 93.1
 R11: 92.0
 R12: 65.9
 R13: 95.9
 R14: 99.0
 R15: 91.4



Test Conditions

Stabilization Time: M
 Operation Time: 1H 0M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-13

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.09

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.55

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13


TM-30-18

Summary

$R_f = 90.8$
 $R_g = 97.4$
 $CIE R_a = 94.0$
 $R_9 = 77.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 98	CES51 = 93	CES76 = 91
CES02 = 61	CES27 = 86	CES52 = 96	CES77 = 89
CES03 = 31	CES28 = 98	CES53 = 93	CES78 = 87
CES04 = 68	CES29 = 90	CES54 = 89	CES79 = 97
CES05 = 48	CES30 = 80	CES55 = 86	CES80 = 94
CES06 = 50	CES31 = 92	CES56 = 89	CES81 = 89
CES07 = 41	CES32 = 97	CES57 = 87	CES82 = 97
CES08 = 40	CES33 = 89	CES58 = 87	CES83 = 96
CES09 = 29	CES34 = 98	CES59 = 96	CES84 = 94
CES10 = 73	CES35 = 98	CES60 = 89	CES85 = 84
CES11 = 56	CES36 = 74	CES61 = 90	CES86 = 90
CES12 = 62	CES37 = 97	CES62 = 78	CES87 = 92
CES13 = 42	CES38 = 75	CES63 = 89	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 90
CES15 = 71	CES40 = 97	CES65 = 87	CES90 = 92
CES16 = 47	CES41 = 91	CES66 = 82	CES91 = 69
CES17 = 48	CES42 = 99	CES67 = 82	CES92 = 81
CES18 = 56	CES43 = 97	CES68 = 86	CES93 = 88
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 86
CES20 = 65	CES45 = 97	CES70 = 86	CES95 = 83
CES21 = 84	CES46 = 94	CES71 = 77	CES96 = 94
CES22 = 77	CES47 = 90	CES72 = 93	CES97 = 97
CES23 = 91	CES48 = 83	CES73 = 82	CES98 = 94
CES24 = 89	CES49 = 95	CES74 = 89	CES99 = 92
CES25 = 70	CES50 = 94	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)