

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216812

Luminaire Tested: 14-ID2-70-CFR1-L940-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-13)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-70-CFR1-L940-U
Description: 1X4 IN DEPTH TROFFER WITH 1INCH CUBE REGRESS LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5773.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.17 / 1.28
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216812
CATALOG NUMBER: 14-ID2-70-CFR1-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216812

CATALOG NUMBER: 14-ID2-70-CFR1-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	101	97	107	103	99	96	99	96	93		95	92	90		85
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		72
3	92	81	74	67	89	80	73	67	77	71	66		74	69	65		61
4	84	73	64	58	82	71	63	57	69	62	56		66	61	56		53
5	78	65	56	50	75	64	56	50	62	55	49		60	54	49		46
6	72	59	50	44	70	58	50	44	56	49	43		54	48	43		41
7	67	53	45	39	65	53	45	39	51	44	39		50	43	38		36
8	62	49	41	35	61	48	40	35	47	40	35		46	39	34		32
9	58	45	37	32	57	44	37	31	43	36	31		42	36	31		29
10	55	42	34	29	53	41	34	29	40	33	29		39	33	28		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6322	6322	6322
5°	6331	6304	6326
10°	6305	6271	6292
15°	6249	6206	6211
20°	6170	6100	6078
25°	6067	5960	5905
30°	5937	5798	5710
35°	5774	5598	5476
40°	5592	5370	5226
45°	5380	5135	4956
50°	5151	4861	4665
55°	4894	4569	4359
60°	4591	4260	4029
65°	4295	3917	3663
70°	3927	3544	3282
75°	3477	3082	2818
80°	2841	2493	2236
85°	2016	1655	1355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5380 cd/sqm

TEST NUMBER: P1216812
 CATALOG NUMBER: 14-ID2-70-CFR1-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.0	3.8
10°-20°	628.6	10.9
20°-30°	925.7	16.0
30°-40°	1067.8	18.5
40°-50°	1044.2	18.1
50°-60°	877.9	15.2
60°-70°	616.8	10.7
70°-80°	319.5	5.5
80°-90°	70.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1776.3	30.8
0°-40°	2844.0	49.3
0°-60°	4766.1	82.6
0°-90°	5773.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5773.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2350	2350	2350	2350	2350	
5°	2344	2341	2334	2335	2342	223
15°	2243	2238	2228	2224	2230	632
25°	2043	2035	2007	1987	1989	941
35°	1758	1743	1704	1673	1667	1099
45°	1414	1396	1349	1312	1302	1091
55°	1043	1024	974	942	929	932
65°	675	657	615	588	575	668
75°	334	323	296	277	271	355
85°	65	67	54	46	44	81
90°	0	0	0	0	0	

TEST NUMBER: P1216812

CATALOG NUMBER: 14-ID2-70-CFR1-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2349.5	2349.5	2349.5	2349.5	2349.5
2.5°	2354.3	2349.5	2343.6	2345.6	2348.5
5°	2343.6	2340.7	2333.9	2334.8	2341.7
7.5°	2329.0	2325.1	2317.3	2319.2	2327.0
10°	2307.5	2301.7	2294.9	2295.8	2302.7
12.5°	2278.3	2273.4	2264.6	2263.7	2270.5
15°	2243.2	2238.3	2227.6	2223.7	2229.5
17.5°	2202.3	2196.4	2182.8	2175.9	2179.8
20°	2154.5	2148.6	2130.1	2117.4	2122.3
22.5°	2101.8	2095.0	2071.6	2057.0	2058.9
25°	2043.3	2034.6	2007.3	1986.8	1988.8
27.5°	1980.0	1968.3	1938.1	1915.6	1914.7
30°	1910.8	1898.1	1865.9	1839.6	1837.6
32.5°	1835.7	1823.0	1786.0	1757.7	1755.8
35°	1757.7	1743.1	1704.1	1672.9	1667.0
37.5°	1676.8	1660.2	1618.3	1588.1	1583.2
40°	1592.0	1574.4	1528.6	1496.4	1487.7
42.5°	1504.2	1487.7	1438.9	1407.7	1396.0
45°	1413.6	1396.0	1349.2	1312.2	1302.4
47.5°	1326.8	1303.4	1253.7	1222.5	1207.9
50°	1230.3	1210.8	1161.1	1128.9	1114.3
52.5°	1137.7	1118.2	1066.5	1034.3	1021.7
55°	1043.1	1023.6	973.9	941.7	929.1
57.5°	945.6	930.0	882.3	852.0	838.4
60°	853.0	837.4	791.6	763.3	748.7
62.5°	766.3	746.8	701.9	675.6	661.0
65°	674.6	657.1	615.1	587.9	575.2
67.5°	585.9	569.3	530.3	506.9	497.2
70°	499.1	484.5	450.4	427.0	417.2
72.5°	414.3	401.7	371.4	349.0	342.2
75°	334.4	322.7	296.4	276.9	271.0
77.5°	256.4	249.6	225.2	208.6	203.7
80°	183.3	180.4	160.9	147.2	144.3
82.5°	118.9	118.0	105.3	93.6	89.7
85°	65.3	67.3	53.6	45.8	43.9
87.5°	23.4	23.4	16.6	14.6	13.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216812

CATALOG NUMBER: 14-ID2-70-CFR1-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.51	19.10	17.88	19.41	19.72	16.86	18.44	17.23	18.76	19.07
	3H	19.14	20.56	19.51	20.89	21.25	18.35	19.77	18.73	20.10	20.46
	4H	19.71	21.04	20.10	21.39	21.77	18.84	20.18	19.24	20.53	20.90
	6H	20.08	21.32	20.49	21.68	22.07	19.14	20.38	19.55	20.75	21.14
	8H	20.18	21.36	20.60	21.75	22.15	19.21	20.39	19.64	20.78	21.18
	12H	20.23	21.36	20.66	21.74	22.17	19.24	20.37	19.67	20.75	21.18
4H	2H	17.99	19.33	18.39	19.68	20.05	17.46	18.80	17.86	19.15	19.53
	3H	19.83	20.94	20.24	21.34	21.74	19.15	20.27	19.56	20.67	21.07
	4H	20.52	21.52	20.95	21.94	22.38	19.75	20.75	20.18	21.17	21.61
	6H	21.01	21.89	21.47	22.33	22.79	20.15	21.02	20.60	21.46	21.92
	8H	21.15	21.97	21.61	22.41	22.88	20.25	21.06	20.71	21.51	21.97
	12H	21.23	21.96	21.71	22.44	22.91	20.29	21.02	20.77	21.50	21.97
8H	4H	20.72	21.53	21.18	21.98	22.44	20.02	20.84	20.48	21.28	21.75
	6H	21.30	21.98	21.80	22.47	22.94	20.50	21.18	21.00	21.67	22.15
	8H	21.49	22.10	22.00	22.61	23.09	20.64	21.25	21.16	21.76	22.25
	12H	21.63	22.16	22.14	22.66	23.22	20.73	21.26	21.23	21.75	22.32
12H	4H	20.72	21.45	21.20	21.93	22.40	20.04	20.78	20.52	21.25	21.72
	6H	21.31	21.92	21.83	22.43	22.92	20.54	21.15	21.05	21.66	22.14
	8H	21.55	22.08	22.06	22.58	23.14	20.72	21.26	21.23	21.75	22.31

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions

Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)