

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216771

Luminaire Tested: 14-ID2-40-CFR1-L935-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-13)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-40-CFR1-L935-U
Description: 1X4 IN DEPTH TROFFER WITH 1INCH CUBE REGRESS LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3498.2 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.17 / 1.28
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216771
CATALOG NUMBER: 14-ID2-40-CFR1-L935-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216771

CATALOG NUMBER: 14-ID2-40-CFR1-L935-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74
3	92	81	74	67	89	80	73	67	77	71	66	74	69	65	72	67	63
4	84	73	64	58	82	71	63	57	69	62	56	66	61	56	64	59	55
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43
7	67	53	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34
9	58	45	37	32	57	44	37	31	43	36	31	42	36	31	41	35	31
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3831	3831	3831
5°	3836	3820	3833
10°	3821	3800	3812
15°	3787	3760	3763
20°	3739	3696	3683
25°	3676	3611	3578
30°	3598	3513	3460
35°	3499	3392	3318
40°	3388	3254	3166
45°	3260	3111	3003
50°	3121	2945	2827
55°	2966	2769	2641
60°	2782	2582	2442
65°	2603	2373	2219
70°	2379	2147	1989
75°	2106	1867	1707
80°	1722	1511	1354
85°	1223	1003	821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3260 cd/sqm

TEST NUMBER: P1216771
 CATALOG NUMBER: 14-ID2-40-CFR1-L935-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	3.8
10°-20°	380.9	10.9
20°-30°	560.9	16.0
30°-40°	647.0	18.5
40°-50°	632.7	18.1
50°-60°	532.0	15.2
60°-70°	373.8	10.7
70°-80°	193.6	5.5
80°-90°	42.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.3	30.8
0°-40°	1723.3	49.3
0°-60°	2887.9	82.6
0°-90°	3498.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3498.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1424	1424	1424	1424	1424	
5°	1420	1418	1414	1415	1419	135
15°	1359	1356	1350	1347	1351	383
25°	1238	1233	1216	1204	1205	570
35°	1065	1056	1033	1014	1010	666
45°	856	846	818	795	789	661
55°	632	620	590	571	563	565
65°	409	398	373	356	348	405
75°	203	196	180	168	164	215
85°	40	41	32	28	27	49
90°	0	0	0	0	0	

TEST NUMBER: P1216771

CATALOG NUMBER: 14-ID2-40-CFR1-L935-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.6	1423.6	1423.6	1423.6	1423.6
2.5°	1426.6	1423.6	1420.1	1421.2	1423.0
5°	1420.1	1418.3	1414.1	1414.7	1418.9
7.5°	1411.2	1408.8	1404.1	1405.3	1410.0
10°	1398.2	1394.7	1390.5	1391.1	1395.2
12.5°	1380.5	1377.5	1372.2	1371.6	1375.8
15°	1359.2	1356.3	1349.8	1347.4	1350.9
17.5°	1334.4	1330.9	1322.6	1318.5	1320.8
20°	1305.5	1301.9	1290.7	1283.0	1286.0
22.5°	1273.6	1269.4	1255.2	1246.4	1247.6
25°	1238.1	1232.8	1216.3	1203.9	1205.0
27.5°	1199.7	1192.6	1174.3	1160.7	1160.1
30°	1157.8	1150.1	1130.6	1114.7	1113.5
32.5°	1112.3	1104.6	1082.2	1065.0	1063.9
35°	1065.0	1056.2	1032.6	1013.6	1010.1
37.5°	1016.0	1006.0	980.6	962.3	959.3
40°	964.6	954.0	926.2	906.7	901.4
42.5°	911.5	901.4	871.9	853.0	845.9
45°	856.5	845.9	817.5	795.1	789.2
47.5°	803.9	789.8	759.6	740.7	731.9
50°	745.5	733.7	703.5	684.0	675.2
52.5°	689.4	677.5	646.2	626.7	619.1
55°	632.1	620.2	590.1	570.6	562.9
57.5°	573.0	563.5	534.6	516.3	508.0
60°	516.9	507.4	479.7	462.5	453.7
62.5°	464.3	452.5	425.3	409.4	400.5
65°	408.8	398.1	372.7	356.2	348.5
67.5°	355.0	345.0	321.3	307.2	301.3
70°	302.4	293.6	272.9	258.7	252.8
72.5°	251.0	243.4	225.1	211.5	207.3
75°	202.6	195.5	179.6	167.8	164.2
77.5°	155.4	151.2	136.5	126.4	123.5
80°	111.1	109.3	97.5	89.2	87.4
82.5°	72.1	71.5	63.8	56.7	54.3
85°	39.6	40.8	32.5	27.8	26.6
87.5°	14.2	14.2	10.0	8.9	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216771

CATALOG NUMBER: 14-ID2-40-CFR1-L935-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.77	17.35	16.14	17.67	17.98	15.12	16.70	15.49	17.02	17.33
	3H	17.40	18.82	17.77	19.15	19.51	16.61	18.03	16.99	18.36	18.72
	4H	17.97	19.30	18.36	19.65	20.03	17.10	18.44	17.50	18.78	19.16
	6H	18.34	19.58	18.75	19.94	20.33	17.40	18.64	17.81	19.00	19.40
	8H	18.44	19.62	18.86	20.01	20.41	17.47	18.65	17.90	19.04	19.44
	12H	18.49	19.62	18.92	20.00	20.43	17.50	18.63	17.93	19.01	19.44
4H	2H	16.25	17.59	16.65	17.94	18.31	15.72	17.06	16.12	17.41	17.79
	3H	18.09	19.20	18.50	19.60	20.00	17.41	18.53	17.82	18.93	19.33
	4H	18.78	19.78	19.21	20.20	20.64	18.01	19.01	18.44	19.43	19.87
	6H	19.27	20.15	19.73	20.59	21.05	18.41	19.28	18.86	19.72	20.18
	8H	19.41	20.23	19.87	20.67	21.14	18.50	19.32	18.97	19.77	20.23
	12H	19.49	20.22	19.97	20.70	21.17	18.55	19.28	19.03	19.76	20.23
8H	4H	18.98	19.79	19.44	20.24	20.70	18.28	19.10	18.74	19.54	20.01
	6H	19.56	20.24	20.06	20.73	21.20	18.76	19.44	19.26	19.93	20.41
	8H	19.75	20.36	20.26	20.87	21.35	18.90	19.51	19.42	20.02	20.51
	12H	19.89	20.42	20.40	20.92	21.48	18.99	19.52	19.49	20.01	20.58
12H	4H	18.98	19.71	19.46	20.19	20.66	18.30	19.04	18.78	19.51	19.98
	6H	19.57	20.18	20.09	20.69	21.18	18.80	19.41	19.31	19.92	20.40
	8H	19.81	20.34	20.32	20.84	21.40	18.98	19.52	19.49	20.01	20.57

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-10

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L935-U

Data in this report applies to families of products including 22ID2-55-CFR1-L935-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-10
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L935-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 90CRI

Spectral Parameters

CCT (K): 3377
 CIE u' : 0.2392
 CIE v' : 0.5128
 Duv: -0.0007
 CIE x: 0.4116
 CIE y: 0.3922
 CIE z: 0.1962
 Peak Wavelength (nm): 618
 Dominant Wavelength (nm): 581
 Purity: 41.24368
 R_f: 91.8
 R_g: 99.6

CRI (Ra): 93.6
 R1: 94.1
 R2: 96.6
 R3: 97.5
 R4: 94.0
 R5: 93.6
 R6: 94.8
 R7: 93.4
 R8: 84.8
 R9: 64.2
 R10: 91.1
 R11: 94.7
 R12: 78.5
 R13: 95.0
 R14: 98.1
 R15: 91.0



Test Conditions

Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-10

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-10

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.19

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

TM-30-18

Summary

$R_f = 91.8$
 $R_g = 99.6$
 $CIE R_a = 93.6$
 $R_9 = 64.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 92	CES52 = 99	CES77 = 89
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 96	CES54 = 93	CES79 = 95
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 86
CES07 = 43	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 94
CES10 = 75	CES35 = 96	CES60 = 92	CES85 = 83
CES11 = 58	CES36 = 82	CES61 = 92	CES86 = 86
CES12 = 64	CES37 = 95	CES62 = 87	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 93	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 97	CES66 = 88	CES91 = 75
CES17 = 50	CES42 = 95	CES67 = 87	CES92 = 80
CES18 = 56	CES43 = 94	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 81
CES20 = 67	CES45 = 97	CES70 = 86	CES95 = 84
CES21 = 86	CES46 = 97	CES71 = 82	CES96 = 92
CES22 = 78	CES47 = 96	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 92	CES73 = 82	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 92	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)