

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217122

Luminaire Tested: 14-ID2-45-CNC-L830-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1217122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-17)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-45-CNC-L830-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESS LENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4474.2 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.3
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217122
CATALOG NUMBER: 14-ID2-45-CNC-L830-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217122

CATALOG NUMBER: 14-ID2-45-CNC-L830-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	104	100	97	106	102	98	95	98	95	92		94	92	89		84
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		71
3	91	81	73	66	88	79	72	66	76	70	64		73	68	63		60
4	83	72	63	56	81	70	62	56	68	61	55		65	59	54		52
5	77	64	55	49	75	63	55	48	61	54	48		59	53	47		45
6	71	58	49	43	69	57	49	43	55	48	42		53	47	42		39
7	66	53	44	38	64	52	44	38	50	43	37		49	42	37		35
8	61	48	40	34	60	47	39	34	46	39	34		45	38	33		31
9	57	44	36	31	56	44	36	31	42	35	30		41	35	30		28
10	54	41	33	28	53	40	33	28	39	32	28		38	32	27		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4712	4687	4698
10°	4685	4658	4669
15°	4637	4608	4616
20°	4577	4533	4531
25°	4491	4441	4425
30°	4390	4321	4316
35°	4268	4201	4196
40°	4134	4073	4067
45°	3986	3934	3926
50°	3828	3790	3784
55°	3658	3633	3615
60°	3468	3468	3456
65°	3236	3284	3255
70°	2998	3065	3017
75°	2649	2816	2705
80°	2252	2428	2252
85°	1692	1831	1763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3986 cd/sqm

TEST NUMBER: P1217122
 CATALOG NUMBER: 14-ID2-45-CNC-L830-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.0	3.7
10°-20°	466.9	10.4
20°-30°	689.1	15.4
30°-40°	801.9	17.9
40°-50°	799.1	17.9
50°-60°	692.9	15.5
60°-70°	508.2	11.4
70°-80°	281.1	6.3
80°-90°	70.0	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1321.0	29.5
0°-40°	2122.9	47.4
0°-60°	3614.9	80.8
0°-90°	4474.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4474.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1748	1748	1748	1748	1748	
5°	1744	1742	1735	1735	1739	166
15°	1664	1662	1654	1652	1657	469
25°	1512	1504	1496	1487	1490	696
35°	1299	1291	1279	1273	1277	812
45°	1048	1042	1034	1028	1032	808
55°	780	778	774	770	771	697
65°	508	516	516	509	511	506
75°	255	272	271	261	260	273
85°	55	62	59	55	57	66
90°	0	0	0	0	0	

TEST NUMBER: P1217122

CATALOG NUMBER: 14-ID2-45-CNC-L830-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1748.2	1748.2	1748.2	1748.2	1748.2
2.5°	1751.2	1748.9	1742.9	1742.9	1745.9
5°	1744.4	1742.1	1735.3	1735.3	1739.1
7.5°	1731.4	1729.9	1722.3	1722.3	1727.6
10°	1714.7	1711.7	1704.8	1704.1	1708.6
12.5°	1692.6	1689.6	1682.0	1680.5	1685.0
15°	1664.5	1661.5	1653.9	1651.6	1656.9
17.5°	1634.8	1628.7	1621.9	1617.3	1621.9
20°	1598.3	1592.2	1583.1	1577.8	1582.3
22.5°	1557.2	1550.4	1541.3	1532.9	1538.2
25°	1512.4	1504.0	1495.6	1487.2	1490.3
27.5°	1464.4	1454.5	1444.6	1437.0	1440.1
30°	1412.7	1402.0	1390.6	1384.5	1389.1
32.5°	1354.9	1348.8	1336.6	1329.8	1333.6
35°	1299.3	1291.0	1278.8	1272.7	1277.3
37.5°	1239.2	1230.9	1220.2	1213.4	1217.9
40°	1176.9	1169.3	1159.4	1152.5	1157.8
42.5°	1113.0	1108.4	1097.7	1090.1	1095.5
45°	1047.5	1042.2	1033.8	1027.8	1031.6
47.5°	981.4	976.8	969.9	963.1	968.4
50°	914.4	912.9	905.3	899.2	903.8
52.5°	846.7	846.7	839.9	834.5	839.1
55°	779.8	778.2	774.4	769.9	770.6
57.5°	712.1	712.1	709.0	704.4	708.2
60°	644.3	647.4	644.3	639.0	642.1
62.5°	577.4	581.2	579.7	573.6	576.6
65°	508.2	516.5	515.8	508.9	511.2
67.5°	445.8	452.6	451.9	445.8	447.3
70°	381.1	390.3	389.5	382.7	383.4
72.5°	315.7	329.4	328.6	321.0	321.0
75°	254.8	271.6	270.8	260.9	260.2
77.5°	200.1	214.5	213.0	202.4	202.4
80°	145.3	158.2	156.7	145.3	145.3
82.5°	96.6	108.0	105.0	95.9	97.4
85°	54.8	62.4	59.3	54.8	57.1
87.5°	19.8	24.3	23.6	19.8	22.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217122

CATALOG NUMBER: 14-ID2-45-CNC-L830-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.49	18.10	16.86	18.42	18.73	16.43	18.03	16.79	18.35	18.66
	3H	18.18	19.63	18.55	19.95	20.31	18.12	19.57	18.49	19.89	20.25
	4H	18.77	20.14	19.17	20.48	20.86	18.72	20.09	19.12	20.43	20.81
	6H	19.18	20.45	19.59	20.81	21.20	19.13	20.39	19.54	20.76	21.15
	8H	19.30	20.50	19.72	20.89	21.29	19.24	20.45	19.67	20.84	21.23
	12H	19.36	20.52	19.79	20.90	21.33	19.31	20.46	19.74	20.84	21.27
4H	2H	17.09	18.46	17.49	18.81	19.18	17.04	18.40	17.44	18.75	19.13
	3H	19.00	20.14	19.41	20.54	20.94	18.95	20.09	19.35	20.48	20.88
	4H	19.74	20.77	20.17	21.18	21.62	19.67	20.70	20.10	21.11	21.55
	6H	20.28	21.18	20.73	21.62	22.07	20.19	21.09	20.64	21.53	21.98
	8H	20.43	21.27	20.89	21.72	22.18	20.33	21.17	20.79	21.62	22.08
	12H	20.53	21.29	21.01	21.76	22.23	20.43	21.19	20.91	21.66	22.13
8H	4H	20.03	20.87	20.49	21.31	21.78	19.97	20.81	20.43	21.25	21.72
	6H	20.69	21.38	21.18	21.87	22.35	20.59	21.29	21.08	21.77	22.25
	8H	20.91	21.54	21.42	22.04	22.53	20.79	21.42	21.30	21.92	22.41
	12H	21.07	21.62	21.58	22.12	22.68	20.94	21.49	21.45	21.99	22.55
12H	4H	20.05	20.81	20.53	21.28	21.75	19.99	20.75	20.48	21.23	21.70
	6H	20.73	21.35	21.24	21.86	22.35	20.63	21.26	21.14	21.77	22.25
	8H	21.00	21.56	21.51	22.05	22.61	20.89	21.44	21.40	21.93	22.49

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L830-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

Spectral Parameters

CCT (K): 3031
 CIE u' : 0.2493
 CIE v' : 0.5215
 Duv: 0.0005
 CIE x: 0.4355
 CIE y: 0.4049
 CIE z: 0.1596
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 582
 Purity: 52.24762
 Rf: 84.8
 Rg: 95.8

CRI (Ra): 82.5
 R1: 80.7
 R2: 90.5
 R3: 96.7
 R4: 80.7
 R5: 80.9
 R6: 88.5
 R7: 83.0
 R8: 58.8
 R9: 5.8
 R10: 78.6
 R11: 80.2
 R12: 69.8
 R13: 83.0
 R14: 98.8
 R15: 73.0



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.59


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3


TM-30-18

Summary

$R_f = 84.8$
 $R_g = 95.8$
 $CIE R_a = 82.5$
 $R_9 = 5.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)