

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217076

Luminaire Tested: 14-ID2-80-CFD2-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-80-CFD2-L835-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7405.9 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217076
CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217076

CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	96
1	107	102	98	94	104	100	95	92	94	91	88	90	87	85	85	83	81	81	81	79
2	97	89	82	76	94	87	80	75	82	77	72	78	74	70	75	71	68	68	68	66
3	89	78	70	63	86	76	69	62	73	66	61	69	64	59	66	62	58	58	58	55
4	81	69	60	54	79	68	59	53	65	57	52	62	56	51	59	54	50	50	50	47
5	75	62	53	46	72	61	52	46	58	51	45	56	49	44	53	48	43	43	43	41
6	69	56	47	40	67	55	46	40	52	45	39	50	44	39	48	43	38	38	38	36
7	64	51	42	36	62	50	41	35	48	40	35	46	39	34	44	38	34	34	34	32
8	60	46	38	32	58	45	37	32	44	36	31	42	36	31	41	35	30	30	30	28
9	56	42	34	29	54	42	34	29	40	33	28	39	32	28	38	32	27	27	27	26
10	52	39	31	26	51	39	31	26	37	30	26	36	30	25	35	29	25	25	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6974	6974	6974
5°	6963	6874	6882
10°	6902	6759	6766
15°	6810	6622	6619
20°	6693	6449	6424
25°	6553	6245	6198
30°	6377	6018	5969
35°	6151	5764	5729
40°	5916	5499	5483
45°	5629	5232	5223
50°	5338	4962	4987
55°	5026	4682	4768
60°	4712	4419	4550
65°	4374	4146	4319
70°	4022	3846	4024
75°	3628	3486	3623
80°	3176	3036	3151
85°	2740	2600	2705

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5629 cd/sqm

TEST NUMBER: P1217076
 CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.1	3.3
10°-20°	696.3	9.4
20°-30°	1033.7	14.0
30°-40°	1209.9	16.3
40°-50°	1215.2	16.4
50°-60°	1076.3	14.5
60°-70°	837.1	11.3
70°-80°	531.6	7.2
80°-90°	237.6	3.2
90°-100°	113.4	1.5
100°-110°	86.7	1.2
110°-120°	61.0	0.8
120°-130°	36.5	0.5
130°-140°	17.8	0.2
140°-150°	6.5	0.1
150°-160°	1.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1975.0	26.7
0°-40°	3184.9	43.0
0°-60°	5476.4	73.9
0°-90°	7082.8	95.6
90°-120°	261.1	3.5
90°-150°	322.0	4.3
90°-180°	323.0	4.4
0°-180°	7405.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2592	2592	2592	2592	2592	
5°	2587	2584	2576	2577	2583	246
15°	2471	2472	2467	2471	2478	697
25°	2248	2250	2242	2241	2243	1034
35°	1925	1940	1928	1938	1939	1204
45°	1538	1569	1569	1593	1592	1188
55°	1132	1178	1200	1241	1248	1014
65°	746	800	849	905	911	740
75°	401	457	512	559	557	427
85°	129	175	220	251	248	131
90°	56	97	138	158	156	34
95°	48	78	114	128	127	38
105°	35	56	91	108	111	37
115°	23	35	67	86	92	23
125°	14	18	43	60	66	13
135°	8	7	23	36	42	7
145°	5	4	7	17	22	3
155°	2	1	1	2	4	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217076

CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2591.6	2591.6	2591.6	2591.6	2591.6
2.5°	2597.6	2595.2	2585.6	2586.8	2591.6
5°	2586.8	2584.4	2576.1	2577.3	2583.2
7.5°	2568.9	2567.7	2559.3	2561.7	2570.1
10°	2543.7	2542.5	2535.4	2539.0	2546.1
12.5°	2511.4	2510.2	2504.2	2507.8	2515.0
15°	2470.7	2471.9	2467.1	2470.7	2477.9
17.5°	2424.0	2426.4	2419.3	2424.0	2430.0
20°	2371.4	2373.8	2367.8	2367.8	2373.8
22.5°	2312.7	2315.1	2307.9	2307.9	2312.7
25°	2248.1	2250.5	2242.1	2240.9	2243.3
27.5°	2175.1	2181.0	2170.3	2171.5	2172.7
30°	2099.6	2105.6	2094.8	2097.2	2098.4
32.5°	2013.4	2025.4	2013.4	2018.2	2020.6
35°	1924.9	1940.4	1928.5	1938.0	1939.2
37.5°	1835.1	1851.8	1841.1	1854.2	1855.4
40°	1740.5	1759.7	1751.3	1768.1	1770.4
42.5°	1642.4	1666.3	1661.5	1681.9	1679.5
45°	1538.2	1569.3	1569.3	1593.3	1592.1
47.5°	1437.7	1472.4	1477.2	1504.7	1504.7
50°	1335.9	1374.2	1385.0	1417.3	1418.5
52.5°	1234.2	1276.1	1294.0	1327.5	1332.3
55°	1132.4	1177.9	1199.5	1241.3	1248.5
57.5°	1033.1	1078.5	1110.9	1154.0	1163.5
60°	936.1	984.0	1022.3	1071.4	1079.7
62.5°	839.1	890.6	937.3	985.2	994.8
65°	745.8	799.6	848.7	905.0	911.0
67.5°	656.0	709.9	763.7	816.4	824.8
70°	567.4	623.7	678.7	733.8	736.2
72.5°	482.4	538.7	594.9	646.4	646.4
75°	401.0	457.3	512.3	559.0	556.6
77.5°	328.0	378.3	430.9	472.8	469.2
80°	251.4	302.9	353.1	391.4	387.8
82.5°	185.5	232.2	282.5	318.4	314.8
85°	129.3	174.8	220.3	251.4	247.8
87.5°	85.0	129.3	171.2	197.5	193.9
90°	56.3	97.0	137.7	158.0	155.6
92.5°	50.3	85.0	122.1	138.9	136.5
95°	47.9	77.8	113.7	128.1	126.9
97.5°	45.5	71.8	106.5	122.1	122.1
100°	41.9	67.0	101.7	117.3	118.5
102.5°	38.3	61.0	95.8	112.5	114.9
105°	34.7	56.3	91.0	107.7	111.3
107.5°	32.3	50.3	85.0	102.9	107.7
110°	28.7	45.5	79.0	98.2	102.9

TEST NUMBER: P1217076

CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	25.1	39.5	73.0	92.2	98.2
115°	22.7	34.7	67.0	86.2	92.2
117.5°	20.3	29.9	61.0	80.2	85.0
120°	18.0	26.3	55.1	74.2	79.0
122.5°	15.6	21.5	49.1	67.0	73.0
125°	14.4	18.0	43.1	59.9	65.8
127.5°	12.0	14.4	37.1	53.9	59.9
130°	10.8	10.8	31.1	47.9	53.9
132.5°	9.6	8.4	26.3	41.9	46.7
135°	8.4	7.2	22.7	35.9	41.9
137.5°	7.2	6.0	18.0	31.1	35.9
140°	6.0	4.8	14.4	26.3	29.9
142.5°	4.8	3.6	10.8	21.5	25.1
145°	4.8	3.6	7.2	16.8	21.5
147.5°	3.6	2.4	3.6	13.2	16.8
150°	2.4	2.4	1.2	9.6	12.0
152.5°	2.4	1.2	1.2	6.0	8.4
155°	2.4	1.2	1.2	2.4	3.6
157.5°	1.2	1.2	1.2	0.0	0.0
160°	1.2	1.2	1.2	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217076

CATALOG NUMBER: 14-ID2-80-CFD2-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.58	18.12	17.01	18.52	18.95	17.47	19.01	17.90	19.41	19.84
	3H	18.13	19.53	18.58	19.95	20.41	19.49	20.89	19.94	21.30	21.77
	4H	18.68	20.00	19.15	20.44	20.92	20.31	21.63	20.78	22.07	22.55
	6H	19.07	20.29	19.55	20.74	21.24	21.00	22.22	21.48	22.67	23.17
	8H	19.18	20.34	19.67	20.82	21.32	21.28	22.45	21.78	22.93	23.43
	12H	19.25	20.37	19.74	20.83	21.37	21.54	22.66	22.04	23.13	23.66
4H	2H	17.27	18.59	17.74	19.03	19.51	17.98	19.30	18.45	19.73	20.21
	3H	19.07	20.18	19.55	20.66	21.16	20.23	21.34	20.71	21.82	22.32
	4H	19.75	20.76	20.25	21.25	21.79	21.20	22.21	21.70	22.70	23.24
	6H	20.26	21.14	20.78	21.66	22.22	22.04	22.93	22.56	23.45	24.00
	8H	20.41	21.24	20.94	21.76	22.33	22.40	23.23	22.92	23.75	24.31
	12H	20.52	21.27	21.07	21.82	22.39	22.73	23.48	23.28	24.03	24.60
8H	4H	20.17	21.00	20.70	21.52	22.09	21.45	22.28	21.97	22.80	23.36
	6H	20.82	21.51	21.38	22.08	22.65	22.43	23.13	22.99	23.69	24.26
	8H	21.05	21.68	21.62	22.26	22.84	22.89	23.52	23.46	24.09	24.68
	12H	21.24	21.79	21.81	22.36	23.01	23.35	23.91	23.92	24.47	25.12
12H	4H	20.24	20.99	20.79	21.54	22.11	21.46	22.21	22.01	22.76	23.33
	6H	20.93	21.56	21.51	22.14	22.72	22.47	23.10	23.05	23.68	24.26
	8H	21.23	21.79	21.81	22.36	23.01	22.99	23.55	23.57	24.11	24.77

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 R_f: 84.9
 R_g: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions

Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.07

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1



TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $\text{CIE } R_a = 84.2$
 $R_9 = 13.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)