

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216957

Luminaire Tested: 14-ID2-50-CFD1-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-15)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-50-CFD1-L835-U
Description: 1X4 IN DEPTH TROFFER WITH 1INCH CUBE DROP LENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5059.3 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.08')
CIE Type: Direct

Input Watts (W): 44.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216957
CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216957

CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		99
1	108	104	99	95	106	101	97	94	97	93	90		93	90	88		83
2	99	90	84	78	96	88	82	77	85	79	75		81	77	73		69
3	90	80	71	65	88	78	70	64	75	68	63		72	66	62		58
4	83	71	62	55	80	69	61	55	67	60	54		64	58	53		50
5	76	63	54	48	74	62	54	47	60	52	47		58	51	46		44
6	70	57	48	42	68	56	48	42	54	47	41		52	46	41		38
7	65	52	43	37	64	51	43	37	49	42	37		48	41	36		34
8	61	47	39	33	59	47	39	33	45	38	33		44	37	32		30
9	57	44	35	30	55	43	35	30	42	35	30		41	34	29		27
10	53	40	32	27	52	40	32	27	39	32	27		38	31	27		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5148	5148	5148
5°	5148	5100	5111
10°	5114	5037	5043
15°	5061	4954	4958
20°	4986	4847	4835
25°	4889	4716	4674
30°	4762	4565	4516
35°	4617	4397	4343
40°	4464	4217	4153
45°	4284	4024	3959
50°	4089	3835	3770
55°	3878	3637	3572
60°	3656	3414	3402
65°	3412	3198	3208
70°	3145	2963	2989
75°	2827	2698	2701
80°	2406	2402	2397
85°	1970	2124	2143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4284 cd/sqm

TEST NUMBER: P1216957
 CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	3.6
10°-20°	511.8	10.1
20°-30°	756.3	14.9
30°-40°	879.3	17.4
40°-50°	874.5	17.3
50°-60°	760.8	15.0
60°-70°	571.1	11.3
70°-80°	341.4	6.7
80°-90°	132.6	2.6
90°-100°	40.9	0.8
100°-110°	10.0	0.2
110°-120°	0.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1448.7	28.6
0°-40°	2328.0	46.0
0°-60°	3963.3	78.3
0°-90°	5008.4	99.0
90°-120°	51.0	1.0
90°-150°	51.0	1.0
90°-180°	51.0	1.0
0°-180°	5059.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1913	1913	1913	1913	1913	
5°	1909	1906	1900	1900	1906	181
15°	1826	1820	1812	1812	1818	515
25°	1662	1652	1641	1630	1633	765
35°	1425	1419	1405	1391	1396	892
45°	1148	1142	1132	1122	1124	886
55°	850	850	854	848	848	760
65°	559	566	578	584	590	554
75°	292	308	328	336	337	310
85°	78	100	124	132	133	84
90°	21	39	62	72	73	15
95°	14	20	40	53	57	10
105°	3	2	3	17	21	3
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1216957

CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1913.2	1913.2	1913.2	1913.2	1913.2
2.5°	1915.8	1914.1	1907.2	1909.0	1911.5
5°	1909.0	1906.4	1899.6	1900.4	1905.5
7.5°	1897.0	1891.9	1886.0	1886.8	1891.9
10°	1878.3	1874.0	1866.4	1867.2	1871.5
12.5°	1854.4	1849.3	1841.7	1842.5	1847.6
15°	1826.3	1819.5	1811.8	1811.8	1817.8
17.5°	1793.1	1785.4	1776.9	1774.4	1780.3
20°	1753.9	1746.3	1736.0	1730.9	1737.7
22.5°	1710.5	1702.0	1690.0	1682.4	1690.0
25°	1661.9	1652.5	1640.6	1629.6	1633.0
27.5°	1609.1	1599.7	1586.1	1575.0	1579.3
30°	1550.3	1542.7	1529.0	1517.1	1520.5
32.5°	1489.8	1482.2	1468.6	1454.9	1459.2
35°	1425.1	1419.1	1404.7	1391.0	1396.1
37.5°	1362.1	1352.7	1339.1	1324.6	1329.7
40°	1292.2	1284.6	1271.8	1256.4	1261.6
42.5°	1221.5	1214.7	1204.5	1190.0	1193.4
45°	1148.3	1142.3	1132.1	1121.9	1123.6
47.5°	1074.2	1069.9	1063.9	1052.9	1054.6
50°	1000.0	997.5	993.2	983.9	986.4
52.5°	924.2	922.5	922.5	914.9	919.1
55°	850.1	850.1	853.5	847.6	848.4
57.5°	775.2	778.6	783.7	780.3	785.4
60°	702.8	705.3	712.1	714.7	719.8
62.5°	630.4	636.3	644.8	649.1	654.2
65°	558.8	566.5	578.4	584.4	590.3
67.5°	489.8	498.3	515.4	521.3	526.4
70°	421.7	433.6	449.8	458.3	463.4
72.5°	355.2	369.7	388.4	397.0	397.8
75°	292.2	308.4	328.0	336.5	337.3
77.5°	231.7	247.0	270.0	278.5	278.5
80°	172.9	190.8	217.2	224.0	224.9
82.5°	121.8	141.4	166.1	173.8	173.8
85°	78.4	100.5	124.4	132.0	132.9
87.5°	46.0	67.3	90.3	98.8	99.7
90°	21.3	39.2	62.2	72.4	73.3
92.5°	17.9	29.8	51.1	62.2	64.7
95°	14.5	19.6	40.0	52.8	57.1
97.5°	11.1	11.1	29.8	43.4	47.7
100°	7.7	6.0	19.6	34.1	39.2
102.5°	5.1	3.4	10.2	24.7	29.8
105°	2.6	1.7	3.4	17.0	21.3
107.5°	0.9	0.0	0.0	8.5	13.6
110°	0.0	0.0	0.0	1.7	6.0

TEST NUMBER: P1216957

CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216957

CATALOG NUMBER: 14-ID2-50-CFD1-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.20	17.80	16.58	18.13	18.47	16.42	18.02	16.81	18.36	18.70
	3H	17.81	19.26	18.20	19.61	19.99	18.28	19.73	18.67	20.07	20.46
	4H	18.38	19.75	18.80	20.12	20.52	19.01	20.37	19.42	20.74	21.14
	6H	18.77	20.03	19.20	20.42	20.84	19.60	20.87	20.03	21.25	21.67
	8H	18.88	20.09	19.32	20.50	20.92	19.83	21.04	20.27	21.45	21.87
	12H	18.94	20.10	19.39	20.50	20.96	20.04	21.20	20.49	21.60	22.05
4H	2H	16.82	18.18	17.23	18.55	18.95	17.00	18.36	17.41	18.73	19.13
	3H	18.66	19.80	19.08	20.22	20.64	19.07	20.21	19.49	20.63	21.06
	4H	19.36	20.39	19.80	20.83	21.29	19.93	20.97	20.38	21.40	21.86
	6H	19.86	20.77	20.33	21.23	21.71	20.67	21.58	21.14	22.04	22.52
	8H	20.01	20.87	20.49	21.33	21.82	20.96	21.81	21.44	22.27	22.76
	12H	20.12	20.88	20.61	21.38	21.87	21.24	22.00	21.73	22.50	22.99
8H	4H	19.70	20.55	20.18	21.01	21.50	20.21	21.06	20.69	21.52	22.01
	6H	20.33	21.04	20.84	21.55	22.05	21.08	21.79	21.59	22.30	22.80
	8H	20.55	21.19	21.08	21.72	22.23	21.46	22.10	21.99	22.63	23.14
	12H	20.73	21.30	21.25	21.80	22.39	21.85	22.42	22.37	22.93	23.51
12H	4H	19.75	20.52	20.24	21.01	21.50	20.23	21.00	20.73	21.49	21.99
	6H	20.42	21.06	20.94	21.58	22.09	21.13	21.77	21.65	22.29	22.80
	8H	20.70	21.27	21.22	21.78	22.36	21.58	22.14	22.10	22.65	23.24

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 R_f: 84.9
 R_g: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions


Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.07

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1



TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $CIE R_a = 84.2$
 $R_9 = 13.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)