

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217255

Luminaire Tested: 14-ID2-80-CNV-L940-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-80-CNV-L940-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE DROP LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6389.8 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.33
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217255
CATALOG NUMBER: 14-ID2-80-CNV-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217255

CATALOG NUMBER: 14-ID2-80-CNV-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	110	110	110		105	105	105		98
1	107	102	98	94	104	100	96	92	95	92	88		91	88	85		80
2	98	89	82	76	95	87	80	75	83	77	73		79	75	71		66
3	89	78	70	63	86	76	69	62	73	66	61		70	64	60		56
4	81	69	60	54	79	68	59	53	65	58	52		62	56	51		48
5	75	62	53	46	73	61	52	46	58	51	45		56	49	44		41
6	69	56	47	40	67	55	46	40	53	45	39		51	44	39		36
7	64	51	42	36	62	50	41	35	48	40	35		46	40	35		32
8	60	46	38	32	58	45	37	32	44	37	31		42	36	31		29
9	56	42	34	29	54	42	34	29	40	33	28		39	33	28		26
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6042	6042	6042
5°	6029	5953	5964
10°	5975	5857	5869
15°	5898	5738	5757
20°	5797	5600	5611
25°	5683	5437	5441
30°	5530	5259	5256
35°	5369	5061	5058
40°	5188	4848	4841
45°	5012	4620	4606
50°	4808	4372	4359
55°	4591	4101	4111
60°	4342	3831	3857
65°	4076	3548	3626
70°	3769	3281	3434
75°	3411	3077	3287
80°	2944	2928	3221
85°	2572	2877	3295

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5012 cd/sqm

TEST NUMBER: P1217255
 CATALOG NUMBER: 14-ID2-80-CNV-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.3	3.3
10°-20°	604.0	9.5
20°-30°	900.1	14.1
30°-40°	1059.2	16.6
40°-50°	1068.8	16.7
50°-60°	942.2	14.7
60°-70°	721.8	11.3
70°-80°	472.7	7.4
80°-90°	252.7	4.0
90°-100°	107.4	1.7
100°-110°	34.3	0.5
110°-120°	8.0	0.1
120°-130°	3.7	0.1
130°-140°	1.8	0.0
140°-150°	0.6	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1716.4	26.9
0°-40°	2775.7	43.4
0°-60°	4786.7	74.9
0°-90°	6233.9	97.6
90°-120°	149.8	2.3
90°-150°	155.9	2.4
90°-180°	156.0	2.4
0°-180°	6389.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2245	2245	2245	2245	2245	
5°	2240	2236	2231	2232	2239	213
15°	2140	2138	2138	2146	2155	603
25°	1950	1946	1952	1962	1969	897
35°	1680	1680	1693	1707	1712	1050
45°	1370	1371	1386	1402	1404	1055
55°	1034	1034	1051	1072	1076	925
65°	695	698	726	753	765	689
75°	377	392	452	493	505	400
85°	121	166	244	290	302	123
90°	43	94	164	207	220	28
95°	35	48	101	140	152	28
105°	25	19	22	43	52	26
115°	16	13	6	0	0	16
125°	10	8	3	0	0	9
135°	5	4	2	0	0	5
145°	3	2	0	0	0	2
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217255

CATALOG NUMBER: 14-ID2-80-CNV-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2245.1	2245.1	2245.1	2245.1	2245.1
2.5°	2249.4	2246.2	2238.7	2240.8	2244.1
5°	2239.8	2236.5	2231.2	2232.2	2238.7
7.5°	2225.8	2221.5	2217.2	2220.4	2227.9
10°	2202.2	2200.0	2196.8	2201.1	2208.6
12.5°	2174.2	2172.1	2171.0	2176.4	2185.0
15°	2139.9	2137.7	2137.7	2146.3	2154.9
17.5°	2100.1	2099.0	2101.2	2110.9	2117.3
20°	2053.9	2052.8	2056.1	2065.7	2073.3
22.5°	2005.6	2003.4	2006.7	2015.2	2022.8
25°	1949.7	1946.5	1951.9	1961.5	1969.1
27.5°	1889.6	1884.2	1892.8	1903.5	1910.0
30°	1820.8	1821.9	1830.5	1841.2	1847.7
32.5°	1753.1	1752.1	1762.8	1775.7	1782.1
35°	1680.1	1680.1	1693.0	1706.9	1712.3
37.5°	1603.8	1607.0	1619.9	1632.8	1639.3
40°	1526.5	1530.8	1543.7	1557.6	1563.0
42.5°	1447.0	1451.3	1465.2	1480.3	1484.6
45°	1369.6	1370.7	1385.8	1401.9	1404.0
47.5°	1285.8	1286.9	1303.0	1319.1	1322.4
50°	1203.1	1204.2	1220.3	1237.5	1239.7
52.5°	1119.3	1120.4	1134.4	1154.8	1159.1
55°	1034.5	1034.5	1050.6	1072.1	1076.4
57.5°	949.6	949.6	966.8	989.4	994.7
60°	862.6	864.8	886.2	907.7	915.2
62.5°	778.8	781.0	804.6	827.2	836.8
65°	695.0	698.2	726.2	753.0	764.8
67.5°	613.4	617.7	649.9	684.3	695.0
70°	531.7	540.3	579.0	616.6	628.4
72.5°	453.3	463.0	514.6	554.3	565.0
75°	377.1	392.1	452.2	493.1	504.9
77.5°	302.9	325.5	394.2	438.3	449.0
80°	233.1	266.4	340.5	384.6	396.4
82.5°	174.0	211.6	291.1	336.2	347.0
85°	121.4	166.5	243.8	290.0	301.9
87.5°	78.4	127.8	202.0	247.1	260.0
90°	43.0	94.5	164.4	207.3	220.2
92.5°	38.7	68.8	131.1	171.9	184.8
95°	35.4	48.3	101.0	139.6	152.5
97.5°	32.2	32.2	75.2	110.6	122.5
100°	30.1	23.6	53.7	84.9	96.7
102.5°	26.9	21.5	35.4	62.3	73.0
105°	24.7	19.3	21.5	43.0	51.6
107.5°	22.6	17.2	10.7	26.9	34.4
110°	20.4	16.1	8.6	12.9	20.4

TEST NUMBER: P1217255

CATALOG NUMBER: 14-ID2-80-CNV-L940-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	18.3	14.0	7.5	3.2	7.5
115°	16.1	12.9	6.4	0.0	0.0
117.5°	14.0	11.8	5.4	0.0	0.0
120°	12.9	9.7	5.4	0.0	0.0
122.5°	11.8	8.6	4.3	0.0	0.0
125°	9.7	7.5	3.2	0.0	0.0
127.5°	8.6	6.4	3.2	0.0	0.0
130°	7.5	6.4	2.1	0.0	0.0
132.5°	6.4	5.4	2.1	0.0	0.0
135°	5.4	4.3	2.1	0.0	0.0
137.5°	5.4	4.3	1.1	0.0	0.0
140°	4.3	3.2	1.1	0.0	0.0
142.5°	3.2	2.1	1.1	0.0	0.0
145°	3.2	2.1	0.0	0.0	0.0
147.5°	2.1	2.1	0.0	0.0	0.0
150°	2.1	1.1	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217255

CATALOG NUMBER: 14-ID2-80-CNV-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.31	17.90	16.72	18.27	18.65	16.96	18.55	17.36	18.92	19.29
	3H	17.91	19.36	18.33	19.73	20.15	18.93	20.38	19.35	20.76	21.18
	4H	18.48	19.85	18.92	20.24	20.68	19.83	21.19	20.26	21.59	22.02
	6H	18.88	20.15	19.33	20.56	21.01	20.70	21.97	21.15	22.38	22.83
	8H	19.00	20.21	19.46	20.65	21.11	21.12	22.34	21.59	22.77	23.23
	12H	19.08	20.24	19.55	20.67	21.16	21.56	22.73	22.03	23.16	23.65
4H	2H	16.96	18.32	17.39	18.72	19.15	17.47	18.83	17.91	19.23	19.67
	3H	18.78	19.93	19.23	20.38	20.83	19.68	20.83	20.13	21.28	21.73
	4H	19.47	20.52	19.94	20.98	21.47	20.73	21.78	21.20	22.24	22.73
	6H	19.99	20.91	20.48	21.40	21.91	21.78	22.71	22.27	23.19	23.70
	8H	20.16	21.03	20.66	21.51	22.04	22.30	23.16	22.79	23.65	24.17
	12H	20.29	21.07	20.80	21.59	22.12	22.84	23.63	23.36	24.15	24.67
8H	4H	19.89	20.76	20.39	21.25	21.77	21.00	21.87	21.50	22.36	22.88
	6H	20.56	21.30	21.09	21.83	22.36	22.22	22.95	22.75	23.49	24.01
	8H	20.82	21.48	21.36	22.02	22.56	22.87	23.53	23.41	24.07	24.61
	12H	21.03	21.61	21.57	22.15	22.76	23.58	24.17	24.12	24.70	25.31
12H	4H	19.99	20.77	20.50	21.29	21.81	21.03	21.81	21.54	22.33	22.85
	6H	20.72	21.38	21.26	21.93	22.47	22.28	22.94	22.83	23.49	24.03
	8H	21.05	21.64	21.60	22.17	22.78	23.00	23.59	23.55	24.12	24.73

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions

Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.61


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11


TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)