

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217062

Luminaire Tested: 14-ID2-60-CFD2-L850-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-60-CFD2-L850-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6346.4 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 53.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217062
CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217062

CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	109	109	109		103	103	103		98
1	107	102	98	94	104	100	95	92	94	91	88		90	87	85		85
2	97	89	82	76	94	87	80	75	82	77	72		78	74	70		75
3	89	78	70	63	86	76	69	62	73	66	61		69	64	59		66
4	81	69	60	54	79	68	59	53	65	57	52		62	56	51		59
5	75	62	53	46	72	61	52	46	58	51	45		56	49	44		53
6	69	56	47	40	67	55	46	40	52	45	39		50	44	39		48
7	64	51	42	36	62	50	41	35	48	40	35		46	39	34		44
8	60	46	38	32	58	45	37	32	44	36	31		42	36	31		41
9	56	42	34	29	54	42	34	29	40	33	28		39	32	28		38
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5976	5976	5976
5°	5967	5890	5897
10°	5915	5792	5798
15°	5836	5675	5672
20°	5736	5526	5505
25°	5615	5352	5312
30°	5465	5157	5115
35°	5271	4940	4909
40°	5069	4713	4699
45°	4824	4484	4476
50°	4575	4252	4274
55°	4307	4012	4086
60°	4038	3787	3899
65°	3748	3553	3701
70°	3447	3295	3448
75°	3108	2988	3105
80°	2721	2602	2701
85°	2348	2227	2317

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1217062
 CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.0	3.3
10°-20°	596.7	9.4
20°-30°	885.8	14.0
30°-40°	1036.8	16.3
40°-50°	1041.4	16.4
50°-60°	922.3	14.5
60°-70°	717.3	11.3
70°-80°	455.6	7.2
80°-90°	203.6	3.2
90°-100°	97.2	1.5
100°-110°	74.3	1.2
110°-120°	52.3	0.8
120°-130°	31.3	0.5
130°-140°	15.3	0.2
140°-150°	5.6	0.1
150°-160°	1.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1692.5	26.7
0°-40°	2729.3	43.0
0°-60°	4693.0	73.9
0°-90°	6069.5	95.6
90°-120°	223.8	3.5
90°-150°	275.9	4.3
90°-180°	277.0	4.4
0°-180°	6346.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2217	2215	2208	2209	2214	210
15°	2117	2118	2114	2117	2123	597
25°	1926	1928	1921	1920	1922	886
35°	1650	1663	1653	1661	1662	1032
45°	1318	1345	1345	1365	1364	1018
55°	970	1009	1028	1064	1070	869
65°	639	685	727	776	781	634
75°	344	392	439	479	477	366
85°	111	150	189	215	212	113
90°	48	83	118	135	133	29
95°	41	67	98	110	109	33
105°	30	48	78	92	95	32
115°	20	30	57	74	79	20
125°	12	15	37	51	56	11
135°	7	6	20	31	36	6
145°	4	3	6	14	18	2
155°	2	1	1	2	3	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217062

CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2220.9	2220.9	2220.9	2220.9	2220.9
2.5°	2226.0	2223.9	2215.7	2216.8	2220.9
5°	2216.8	2214.7	2207.5	2208.6	2213.7
7.5°	2201.4	2200.3	2193.2	2195.2	2202.4
10°	2179.8	2178.8	2172.7	2175.7	2181.9
12.5°	2152.1	2151.1	2146.0	2149.1	2155.2
15°	2117.3	2118.3	2114.2	2117.3	2123.4
17.5°	2077.3	2079.3	2073.2	2077.3	2082.4
20°	2032.1	2034.2	2029.0	2029.0	2034.2
22.5°	1981.9	1983.9	1977.8	1977.8	1981.9
25°	1926.5	1928.5	1921.3	1920.3	1922.4
27.5°	1863.9	1869.0	1859.8	1860.8	1861.8
30°	1799.3	1804.4	1795.2	1797.2	1798.2
32.5°	1725.4	1735.7	1725.4	1729.5	1731.6
35°	1649.5	1662.8	1652.6	1660.8	1661.8
37.5°	1572.6	1586.9	1577.7	1589.0	1590.0
40°	1491.5	1507.9	1500.8	1515.1	1517.2
42.5°	1407.4	1427.9	1423.8	1441.3	1439.2
45°	1318.2	1344.8	1344.8	1365.3	1364.3
47.5°	1232.0	1261.7	1265.8	1289.4	1289.4
50°	1144.8	1177.6	1186.9	1214.6	1215.6
52.5°	1057.6	1093.5	1108.9	1137.6	1141.7
55°	970.4	1009.4	1027.9	1063.8	1069.9
57.5°	885.3	924.2	951.9	988.9	997.1
60°	802.2	843.2	876.0	918.1	925.3
62.5°	719.1	763.2	803.2	844.2	852.4
65°	639.1	685.2	727.3	775.5	780.6
67.5°	562.1	608.3	654.5	699.6	706.8
70°	486.2	534.4	581.6	628.8	630.9
72.5°	413.4	461.6	509.8	553.9	553.9
75°	343.6	391.9	439.0	479.1	477.0
77.5°	281.1	324.2	369.3	405.2	402.1
80°	215.4	259.5	302.6	335.4	332.4
82.5°	159.0	199.0	242.1	272.9	269.8
85°	110.8	149.8	188.7	215.4	212.3
87.5°	72.8	110.8	146.7	169.3	166.2
90°	48.2	83.1	118.0	135.4	133.4
92.5°	43.1	72.8	104.6	119.0	116.9
95°	41.0	66.7	97.5	109.8	108.7
97.5°	39.0	61.5	91.3	104.6	104.6
100°	35.9	57.4	87.2	100.5	101.6
102.5°	32.8	52.3	82.1	96.4	98.5
105°	29.7	48.2	78.0	92.3	95.4
107.5°	27.7	43.1	72.8	88.2	92.3
110°	24.6	39.0	67.7	84.1	88.2

TEST NUMBER: P1217062

CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	21.5	33.9	62.6	79.0	84.1
115°	19.5	29.7	57.4	73.9	79.0
117.5°	17.4	25.6	52.3	68.7	72.8
120°	15.4	22.6	47.2	63.6	67.7
122.5°	13.3	18.5	42.1	57.4	62.6
125°	12.3	15.4	36.9	51.3	56.4
127.5°	10.3	12.3	31.8	46.2	51.3
130°	9.2	9.2	26.7	41.0	46.2
132.5°	8.2	7.2	22.6	35.9	40.0
135°	7.2	6.2	19.5	30.8	35.9
137.5°	6.2	5.1	15.4	26.7	30.8
140°	5.1	4.1	12.3	22.6	25.6
142.5°	4.1	3.1	9.2	18.5	21.5
145°	4.1	3.1	6.2	14.4	18.5
147.5°	3.1	2.1	3.1	11.3	14.4
150°	2.1	2.1	1.0	8.2	10.3
152.5°	2.1	1.0	1.0	5.1	7.2
155°	2.1	1.0	1.0	2.1	3.1
157.5°	1.0	1.0	1.0	0.0	0.0
160°	1.0	1.0	1.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217062

CATALOG NUMBER: 14-ID2-60-CFD2-L850-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.04	17.58	16.47	17.99	18.41	16.93	18.47	17.36	18.88	19.30
	3H	17.60	18.99	18.04	19.41	19.88	18.96	20.35	19.40	20.77	21.23
	4H	18.15	19.46	18.61	19.90	20.38	19.78	21.10	20.24	21.53	22.01
	6H	18.53	19.75	19.01	20.20	20.70	20.46	21.69	20.94	22.14	22.63
	8H	18.64	19.81	19.13	20.28	20.79	20.75	21.92	21.24	22.39	22.89
	12H	18.71	19.83	19.21	20.30	20.83	21.00	22.13	21.50	22.59	23.13
4H	2H	16.74	18.05	17.20	18.49	18.97	17.44	18.76	17.91	19.19	19.68
	3H	18.53	19.64	19.01	20.12	20.63	19.69	20.80	20.17	21.28	21.79
	4H	19.21	20.22	19.71	20.72	21.26	20.66	21.67	21.16	22.17	22.71
	6H	19.72	20.61	20.24	21.13	21.68	21.51	22.39	22.03	22.91	23.47
	8H	19.88	20.71	20.40	21.23	21.79	21.86	22.69	22.39	23.21	23.78
	12H	19.99	20.74	20.53	21.29	21.86	22.20	22.95	22.74	23.50	24.07
8H	4H	19.63	20.47	20.16	20.99	21.55	20.91	21.74	21.44	22.26	22.83
	6H	20.28	20.98	20.84	21.54	22.12	21.89	22.59	22.45	23.16	23.73
	8H	20.51	21.14	21.09	21.72	22.30	22.35	22.98	22.93	23.56	24.14
	12H	20.70	21.26	21.27	21.82	22.47	22.81	23.37	23.39	23.93	24.59
12H	4H	19.71	20.46	20.25	21.01	21.58	20.92	21.68	21.47	22.23	22.80
	6H	20.40	21.03	20.97	21.60	22.19	21.94	22.56	22.51	23.14	23.73
	8H	20.70	21.25	21.27	21.82	22.47	22.46	23.01	23.03	23.58	24.23

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-7

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L850-U

Data in this report applies to families of products including 22ID2-55-CFR1-L850-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L850-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 80CRI

Spectral Parameters

CCT (K): 4966
 CIE u' : 0.2093
 CIE v' : 0.4890
 Duv: 0.0036
 CIE x: 0.3468
 CIE y: 0.3601
 CIE z: 0.2931
 Peak Wavelength (nm): 450
 Dominant Wavelength (nm): 570
 Purity: 12.1135
 R_f: 84
 R_g: 96.2

CRI (Ra): 83.1
 R1: 81.0
 R2: 87.8
 R3: 92.7
 R4: 82.4
 R5: 81.0
 R6: 82.6
 R7: 88.5
 R8: 68.6
 R9: 10.3
 R10: 70.9
 R11: 81.3
 R12: 55.9
 R13: 82.8
 R14: 96.1
 R15: 75.1



Test Conditions

Stabilization Time: 37M
 Operation Time: 1H 37M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.94

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.11

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	262	NR	620	472	NR	750	15	NR	880	0	NR
365	0	NR	495	307	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	358	NR	630	412	NR	760	11	NR	890	0	NR
375	0	NR	505	403	NR	635	379	NR	765	9	NR	895	0	NR
380	0	NR	510	440	NR	640	346	NR	770	8	NR	900	0	NR
385	1	NR	515	471	NR	645	313	NR	775	7	NR	905	0	NR
390	3	NR	520	490	NR	650	282	NR	780	6	NR	910	0	NR
395	4	NR	525	504	NR	655	252	NR	785	5	NR	915	0	NR
400	6	NR	530	515	NR	660	223	NR	790	4	NR	920	0	NR
405	9	NR	535	524	NR	665	197	NR	795	4	NR	925	0	NR
410	12	NR	540	530	NR	670	171	NR	800	3	NR	930	0	NR
415	20	NR	545	539	NR	675	149	NR	805	3	NR	935	0	NR
420	36	NR	550	545	NR	680	130	NR	810	2	NR	940	0	NR
425	64	NR	555	554	NR	685	112	NR	815	2	NR	945	0	NR
430	117	NR	560	562	NR	690	97	NR	820	2	NR	950	0	NR
435	212	NR	565	567	NR	695	83	NR	825	2	NR	955	0	NR
440	378	NR	570	571	NR	700	71	NR	830	1	NR	960	0	NR
445	709	NR	575	574	NR	705	61	NR	835	1	NR	965	0	NR
450	1000	NR	580	579	NR	710	52	NR	840	1	NR	970	0	NR
455	789	NR	585	578	NR	715	44	NR	845	1	NR	975	0	NR
460	519	NR	590	578	NR	720	38	NR	850	1	NR	980	0	NR
465	429	NR	595	571	NR	725	32	NR	855	1	NR	985	0	NR
470	316	NR	600	560	NR	730	28	NR	860	1	NR	990	0	NR
475	236	NR	605	545	NR	735	24	NR	865	1	NR	995	0	NR
480	224	NR	610	524	NR	740	20	NR	870	0	NR	1000	0	NR
485	235	NR	615	501	NR	745	17	NR	875	0	NR			

REPORT NUMBER: SP1-2506-458-7


TM-30-18

Summary

$R_f = 84$
 $R_g = 96.2$
 $\text{CIE } R_a = 83.1$
 $R_9 = 10.3$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 80	CES51 = 95	CES76 = 72
CES02 = 60	CES27 = 93	CES52 = 95	CES77 = 81
CES03 = 30	CES28 = 90	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 85	CES54 = 90	CES79 = 91
CES05 = 47	CES30 = 97	CES55 = 89	CES80 = 87
CES06 = 50	CES31 = 87	CES56 = 86	CES81 = 84
CES07 = 40	CES32 = 79	CES57 = 85	CES82 = 95
CES08 = 39	CES33 = 92	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 84	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 91	CES60 = 91	CES85 = 81
CES11 = 56	CES36 = 83	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 90	CES62 = 85	CES87 = 84
CES13 = 42	CES38 = 93	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 79	CES89 = 79
CES15 = 71	CES40 = 94	CES65 = 76	CES90 = 89
CES16 = 46	CES41 = 99	CES66 = 75	CES91 = 72
CES17 = 48	CES42 = 89	CES67 = 73	CES92 = 67
CES18 = 55	CES43 = 88	CES68 = 78	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 82	CES94 = 65
CES20 = 64	CES45 = 93	CES70 = 73	CES95 = 73
CES21 = 85	CES46 = 91	CES71 = 67	CES96 = 84
CES22 = 77	CES47 = 96	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 87	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 71	CES50 = 95	CES75 = 68	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)