

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1214648

Luminaire Tested: 22-ID2-25-CFR2-L950-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1214648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-11)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-25-CFR2-L950-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH CUBE REGRESS LENS
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2445.5 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.17 / 1.27
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1214648
CATALOG NUMBER: 22-ID2-25-CFR2-L950-U

Luminous Intensity Polar Plot



TEST NUMBER: P1214648

CATALOG NUMBER: 22-ID2-25-CFR2-L950-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	110	105	101	98	107	103	99	96		99	96	93			95	92	90			91
2	100	92	86	81	98	91	85	80		87	82	78			84	80	76			81
3	92	82	74	68	89	80	73	67		77	71	66			75	69	65			72
4	84	73	64	58	82	72	64	58		69	62	57			67	61	56			65
5	78	65	57	50	76	64	56	50		62	55	50			60	54	49			58
6	72	59	50	44	70	58	50	44		56	49	44			55	48	43			53
7	67	54	45	39	65	53	45	39		51	44	39			50	44	39			49
8	62	49	41	35	61	49	41	35		47	40	35			46	40	35			45
9	58	45	37	32	57	45	37	32		44	37	32			43	36	31			42
10	55	42	34	29	54	41	34	29		40	34	29			39	33	29			39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2734	2734	2734
5°	2736	2728	2733
10°	2724	2716	2717
15°	2687	2686	2681
20°	2632	2633	2624
25°	2563	2559	2555
30°	2485	2472	2473
35°	2395	2378	2385
40°	2297	2280	2286
45°	2191	2165	2173
50°	2078	2048	2070
55°	1956	1927	1943
60°	1824	1790	1826
65°	1677	1645	1671
70°	1495	1478	1502
75°	1286	1264	1299
80°	979	979	1018
85°	537	574	565

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2191 cd/sqm

TEST NUMBER: P1214648
 CATALOG NUMBER: 22-ID2-25-CFR2-L950-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	3.9
10°-20°	271.3	11.1
20°-30°	396.9	16.2
30°-40°	454.4	18.6
40°-50°	441.3	18.0
50°-60°	369.9	15.1
60°-70°	258.5	10.6
70°-80°	131.1	5.4
80°-90°	26.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.1	31.2
0°-40°	1218.5	49.8
0°-60°	2029.7	83.0
0°-90°	2445.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2445.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1016	1016	1016	1016	1016	
5°	1013	1011	1010	1010	1012	96
15°	964	964	964	962	962	272
25°	863	865	862	862	860	397
35°	729	729	724	727	726	456
45°	576	574	569	572	571	444
55°	417	413	411	414	414	373
65°	263	260	258	260	262	262
75°	124	122	122	123	125	132
85°	17	18	19	19	18	26
90°	0	0	0	0	0	

TEST NUMBER: P1214648

CATALOG NUMBER: 22-ID2-25-CFR2-L950-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1015.9	1015.9	1015.9	1015.9	1015.9
2.5°	1016.2	1015.2	1013.7	1014.3	1015.2
5°	1012.8	1011.3	1010.0	1010.4	1011.9
7.5°	1006.4	1004.6	1003.0	1003.6	1004.9
10°	996.9	995.1	993.9	993.9	994.2
12.5°	983.5	981.6	981.0	980.1	980.7
15°	964.5	964.2	964.2	962.1	962.4
17.5°	944.4	943.5	943.5	941.0	940.7
20°	919.0	919.0	919.3	917.8	916.3
22.5°	892.8	893.1	892.5	890.9	887.9
25°	863.1	864.7	861.9	862.5	860.4
27.5°	832.0	832.3	830.2	831.1	830.2
30°	799.6	799.6	795.6	799.0	795.9
32.5°	764.5	765.7	760.5	763.3	763.0
35°	729.1	728.8	723.9	726.9	726.0
37.5°	692.7	691.2	687.5	689.4	689.4
40°	653.9	652.1	649.0	651.8	650.9
42.5°	615.7	613.3	609.3	611.2	613.0
45°	575.7	573.6	569.0	571.5	571.1
47.5°	536.0	533.9	528.7	531.4	532.7
50°	496.3	494.2	489.3	492.0	494.5
52.5°	457.2	453.6	450.5	453.9	453.9
55°	416.9	412.9	410.8	413.9	414.2
57.5°	377.8	374.5	371.7	374.5	374.8
60°	339.0	336.3	332.6	335.7	339.3
62.5°	301.8	298.4	295.3	297.8	299.6
65°	263.3	259.6	258.4	260.2	262.4
67.5°	228.2	224.5	222.4	223.3	227.2
70°	190.0	189.7	187.8	188.1	190.9
72.5°	155.8	154.9	154.5	155.8	158.2
75°	123.7	122.2	121.6	123.4	124.9
77.5°	94.1	93.2	91.6	92.5	93.2
80°	63.2	62.9	63.2	65.4	65.7
82.5°	38.5	38.5	38.8	40.6	39.4
85°	17.4	17.7	18.6	18.9	18.3
87.5°	6.4	6.7	6.4	7.3	6.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1214648

CATALOG NUMBER: 22-ID2-25-CFR2-L950-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.18	15.75	14.54	16.06	16.38	14.17	15.74	14.53	16.05	16.37
	3H	15.71	17.13	16.09	17.46	17.82	15.70	17.11	16.08	17.44	17.80
	4H	16.22	17.55	16.62	17.90	18.27	16.22	17.55	16.62	17.90	18.27
	6H	16.53	17.76	16.94	18.13	18.52	16.53	17.76	16.94	18.13	18.52
	8H	16.59	17.76	17.02	18.15	18.55	16.60	17.77	17.03	18.16	18.56
	12H	16.61	17.73	17.04	18.11	18.54	16.62	17.74	17.05	18.12	18.55
4H	2H	14.71	16.04	15.11	16.39	16.77	14.70	16.03	15.10	16.38	16.76
	3H	16.45	17.56	16.86	17.96	18.36	16.44	17.54	16.85	17.94	18.34
	4H	17.07	18.06	17.50	18.48	18.91	17.07	18.06	17.50	18.48	18.91
	6H	17.47	18.34	17.93	18.78	19.24	17.48	18.35	17.94	18.79	19.25
	8H	17.56	18.37	18.02	18.81	19.28	17.58	18.39	18.04	18.83	19.30
	12H	17.60	18.32	18.08	18.80	19.27	17.62	18.34	18.10	18.82	19.29
8H	4H	17.28	18.09	17.75	18.54	19.00	17.28	18.09	17.75	18.54	19.00
	6H	17.77	18.44	18.26	18.93	19.40	17.78	18.45	18.27	18.94	19.42
	8H	17.89	18.49	18.40	19.00	19.49	17.92	18.52	18.43	19.03	19.51
	12H	17.96	18.49	18.47	18.98	19.54	17.99	18.52	18.50	19.01	19.58
12H	4H	17.29	18.02	17.77	18.49	18.96	17.29	18.02	17.77	18.49	18.96
	6H	17.78	18.38	18.29	18.89	19.38	17.79	18.39	18.30	18.90	19.39
	8H	17.94	18.47	18.45	18.97	19.53	17.97	18.50	18.48	18.99	19.55

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-13

Test Date: 08/27/2025

Luminaire Tested: 22ID2-55-CFR1-L950-U

Data in this report applies to families of products including 22ID2-55-CFR1-L950-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-13
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L950-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 5000K 90CRI

Spectral Parameters

CCT (K): 4919
 CIE u' : 0.2096
 CIE v' : 0.4901
 Duv: 0.0038
 CIE x: 0.3483
 CIE y: 0.3619
 CIE z: 0.2898
 Peak Wavelength (nm): 453
 Dominant Wavelength (nm): 570
 Purity: 13.10873
 R_f: 90.8
 R_g: 97.4

CRI (Ra): 94.0
 R1: 94.8
 R2: 97.7
 R3: 98.4
 R4: 90.8
 R5: 92.2
 R6: 94.3
 R7: 94.0
 R8: 90.0
 R9: 77.7
 R10: 93.1
 R11: 92.0
 R12: 65.9
 R13: 95.9
 R14: 99.0
 R15: 91.4



Test Conditions


Stabilization Time: M
 Operation Time: 1H 0M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-458-13


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-13

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-13

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.09

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.55


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	419	NR	620	583	NR	750	44	NR	880	1	NR
365	0	NR	495	441	NR	625	580	NR	755	37	NR	885	1	NR
370	0	NR	500	472	NR	630	572	NR	760	32	NR	890	1	NR
375	0	NR	505	501	NR	635	559	NR	765	27	NR	895	0	NR
380	0	NR	510	524	NR	640	543	NR	770	23	NR	900	0	NR
385	0	NR	515	545	NR	645	522	NR	775	20	NR	905	0	NR
390	1	NR	520	559	NR	650	496	NR	780	17	NR	910	0	NR
395	3	NR	525	572	NR	655	468	NR	785	14	NR	915	0	NR
400	4	NR	530	581	NR	660	435	NR	790	12	NR	920	0	NR
405	7	NR	535	590	NR	665	403	NR	795	10	NR	925	0	NR
410	9	NR	540	595	NR	670	368	NR	800	9	NR	930	0	NR
415	14	NR	545	599	NR	675	335	NR	805	8	NR	935	0	NR
420	23	NR	550	599	NR	680	304	NR	810	6	NR	940	0	NR
425	40	NR	555	599	NR	685	271	NR	815	6	NR	945	0	NR
430	72	NR	560	595	NR	690	243	NR	820	5	NR	950	0	NR
435	132	NR	565	589	NR	695	215	NR	825	4	NR	955	0	NR
440	243	NR	570	581	NR	700	189	NR	830	3	NR	960	0	NR
445	488	NR	575	575	NR	705	165	NR	835	3	NR	965	0	NR
450	879	NR	580	573	NR	710	144	NR	840	3	NR	970	0	NR
455	974	NR	585	570	NR	715	124	NR	845	2	NR	975	0	NR
460	726	NR	590	572	NR	720	108	NR	850	2	NR	980	0	NR
465	627	NR	595	574	NR	725	93	NR	855	2	NR	985	0	NR
470	546	NR	600	576	NR	730	80	NR	860	1	NR	990	0	NR
475	434	NR	605	581	NR	735	69	NR	865	1	NR	995	0	NR
480	395	NR	610	582	NR	740	59	NR	870	1	NR	1000	0	NR
485	403	NR	615	586	NR	745	51	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-13





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 97.4$
 $CIE R_a = 94.0$
 $R_9 = 77.7$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 98	CES51 = 93	CES76 = 91
CES02 = 61	CES27 = 86	CES52 = 96	CES77 = 89
CES03 = 31	CES28 = 98	CES53 = 93	CES78 = 87
CES04 = 68	CES29 = 90	CES54 = 89	CES79 = 97
CES05 = 48	CES30 = 80	CES55 = 86	CES80 = 94
CES06 = 50	CES31 = 92	CES56 = 89	CES81 = 89
CES07 = 41	CES32 = 97	CES57 = 87	CES82 = 97
CES08 = 40	CES33 = 89	CES58 = 87	CES83 = 96
CES09 = 29	CES34 = 98	CES59 = 96	CES84 = 94
CES10 = 73	CES35 = 98	CES60 = 89	CES85 = 84
CES11 = 56	CES36 = 74	CES61 = 90	CES86 = 90
CES12 = 62	CES37 = 97	CES62 = 78	CES87 = 92
CES13 = 42	CES38 = 75	CES63 = 89	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 90
CES15 = 71	CES40 = 97	CES65 = 87	CES90 = 92
CES16 = 47	CES41 = 91	CES66 = 82	CES91 = 69
CES17 = 48	CES42 = 99	CES67 = 82	CES92 = 81
CES18 = 56	CES43 = 97	CES68 = 86	CES93 = 88
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 86
CES20 = 65	CES45 = 97	CES70 = 86	CES95 = 83
CES21 = 84	CES46 = 94	CES71 = 77	CES96 = 94
CES22 = 77	CES47 = 90	CES72 = 93	CES97 = 97
CES23 = 91	CES48 = 83	CES73 = 82	CES98 = 94
CES24 = 89	CES49 = 95	CES74 = 89	CES99 = 92
CES25 = 70	CES50 = 94	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)