

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1214843

Luminaire Tested: 22-ID2-40-CFD2-L840-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1214843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-13)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-40-CFD2-L840-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4599.9 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 2' x H: 0.16')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1214843
CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

Luminous Intensity Polar Plot



TEST NUMBER: P1214843

CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	109	109	109		103	103	103		98
1	107	102	98	94	104	100	95	92	95	91	88		90	87	85		86
2	97	89	82	76	94	87	80	75	83	77	73		79	74	70		75
3	89	78	70	63	86	76	69	62	73	66	61		69	64	59		66
4	81	69	60	54	79	68	59	53	65	58	52		62	56	51		59
5	75	62	53	46	72	61	52	46	58	51	45		56	49	44		53
6	69	56	47	40	67	55	46	40	52	45	39		50	44	39		48
7	64	51	42	36	62	50	41	36	48	40	35		46	39	34		44
8	60	46	38	32	58	45	37	32	44	37	31		42	36	31		41
9	56	43	34	29	54	42	34	29	40	33	28		39	33	28		38
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4385	4385	4385
5°	4352	4335	4352
10°	4296	4267	4296
15°	4221	4175	4219
20°	4120	4071	4115
25°	4011	3946	3998
30°	3876	3803	3856
35°	3735	3657	3719
40°	3593	3496	3565
45°	3440	3344	3422
50°	3301	3180	3264
55°	3159	3028	3130
60°	3021	2869	2978
65°	2885	2709	2824
70°	2708	2523	2665
75°	2513	2299	2464
80°	2290	2032	2247
85°	2093	1816	2029

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3440 cd/sqm

TEST NUMBER: P1214843
 CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	3.3
10°-20°	435.6	9.5
20°-30°	643.6	14.0
30°-40°	750.1	16.3
40°-50°	753.6	16.4
50°-60°	670.9	14.6
60°-70°	522.9	11.4
70°-80°	333.4	7.2
80°-90°	149.9	3.3
90°-100°	69.5	1.5
100°-110°	50.2	1.1
110°-120°	33.5	0.7
120°-130°	19.4	0.4
130°-140°	9.5	0.2
140°-150°	3.4	0.1
150°-160°	0.6	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.0	26.8
0°-40°	1983.1	43.1
0°-60°	3407.5	74.1
0°-90°	4413.8	96.0
90°-120°	153.2	3.3
90°-150°	185.5	4.0
90°-180°	186.0	4.0
0°-180°	4599.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1630	1630	1630	1630	1630	
5°	1622	1621	1621	1621	1622	154
15°	1548	1546	1544	1545	1547	436
25°	1401	1400	1399	1396	1397	645
35°	1201	1202	1201	1196	1196	752
45°	976	981	978	974	971	754
55°	750	753	750	747	743	672
65°	531	533	529	526	520	524
75°	314	318	314	313	308	333
85°	130	135	135	133	126	124
90°	70	76	79	77	71	41
95°	59	64	65	64	60	47
105°	46	47	49	48	46	49
115°	34	33	35	33	33	34
125°	23	21	22	20	22	21
135°	14	12	11	11	14	11
145°	7	6	3	5	7	5
155°	2	1	1	1	2	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P1214843

CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1629.7	1629.7	1629.7	1629.7	1629.7
2.5°	1628.5	1627.4	1626.8	1628.0	1629.7
5°	1622.3	1620.6	1620.6	1621.2	1622.3
7.5°	1610.4	1609.3	1608.1	1609.8	1611.0
10°	1594.5	1593.4	1592.8	1593.4	1594.5
12.5°	1574.1	1571.3	1571.3	1572.4	1574.1
15°	1547.5	1546.4	1544.1	1545.2	1546.9
17.5°	1515.2	1516.3	1513.5	1514.1	1514.6
20°	1480.6	1480.1	1480.1	1479.5	1478.9
22.5°	1443.8	1441.5	1441.0	1438.7	1440.4
25°	1401.3	1399.6	1399.0	1396.2	1396.8
27.5°	1355.4	1353.1	1351.4	1350.3	1349.2
30°	1305.0	1305.0	1303.8	1301.6	1298.2
32.5°	1255.1	1254.5	1252.8	1250.0	1248.9
35°	1200.7	1201.9	1201.3	1195.6	1195.6
37.5°	1148.6	1148.6	1146.3	1142.9	1138.4
40°	1091.4	1092.5	1089.7	1085.7	1082.9
42.5°	1034.7	1035.8	1034.1	1031.3	1026.2
45°	976.3	980.9	978.0	974.1	971.2
47.5°	920.2	924.2	920.2	917.4	913.4
50°	863.6	866.4	861.9	859.6	853.9
52.5°	807.5	810.3	806.9	804.6	799.0
55°	750.2	753.1	749.7	746.8	743.4
57.5°	695.8	698.1	695.3	693.6	687.3
60°	639.2	642.6	637.5	635.8	630.1
62.5°	582.5	589.3	583.1	580.8	575.7
65°	530.9	532.6	528.7	525.8	519.6
67.5°	474.3	477.7	473.1	470.9	465.2
70°	419.9	423.8	420.4	418.2	413.1
72.5°	366.6	372.3	366.6	364.9	359.8
75°	313.9	318.5	314.5	313.4	307.7
77.5°	263.5	268.6	263.5	265.2	259.5
80°	214.8	220.4	215.3	216.5	210.8
82.5°	171.7	175.1	173.4	172.3	166.6
85°	129.8	134.9	134.9	133.2	125.8
87.5°	95.2	99.7	101.4	100.9	94.1
90°	70.3	76.5	78.8	77.1	71.4
92.5°	63.5	68.6	70.8	69.1	64.0
95°	58.9	63.5	65.2	64.0	59.5
97.5°	55.5	58.9	60.6	58.9	55.5
100°	52.7	55.0	56.7	55.0	52.1
102.5°	49.3	51.0	52.7	51.0	48.7
105°	46.5	47.0	48.7	47.6	45.9
107.5°	43.6	43.6	44.8	43.6	42.5
110°	40.2	40.2	41.4	40.2	39.1

TEST NUMBER: P1214843

CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	36.8	36.8	38.0	36.3	36.3
115°	34.0	33.4	34.6	32.9	33.4
117.5°	30.6	30.0	31.2	29.5	30.0
120°	27.8	26.6	27.8	26.1	27.2
122.5°	25.5	23.8	24.9	23.2	24.4
125°	22.7	21.0	22.1	20.4	22.1
127.5°	20.4	18.1	19.3	17.6	19.3
130°	18.1	15.9	16.4	14.7	17.6
132.5°	15.9	13.6	14.2	13.0	15.3
135°	13.6	11.9	11.3	11.3	13.6
137.5°	11.9	10.2	9.1	9.6	11.3
140°	10.2	8.5	6.8	7.9	9.6
142.5°	8.5	6.8	5.1	6.8	8.5
145°	7.4	5.7	3.4	5.1	6.8
147.5°	5.7	4.5	1.7	4.0	5.1
150°	4.5	2.8	0.6	2.8	3.4
152.5°	2.8	2.3	0.6	1.7	2.3
155°	1.7	1.1	0.6	1.1	1.7
157.5°	0.6	0.6	0.6	0.6	0.6
160°	0.6	0.6	0.6	0.6	0.6
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1214843

CATALOG NUMBER: 22-ID2-40-CFD2-L840-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.56	17.11	15.99	17.51	17.92	15.51	17.05	15.93	17.45	17.87
	3H	17.40	18.80	17.84	19.21	19.67	17.32	18.72	17.76	19.13	19.59
	4H	18.12	19.45	18.59	19.88	20.35	18.03	19.36	18.50	19.79	20.26
	6H	18.71	19.94	19.18	20.38	20.87	18.61	19.84	19.09	20.29	20.78
	8H	18.93	20.11	19.42	20.57	21.07	18.83	20.01	19.32	20.48	20.97
	12H	19.11	20.24	19.61	20.70	21.23	19.01	20.14	19.50	20.60	21.12
4H	2H	16.16	17.48	16.62	17.91	18.39	16.12	17.44	16.58	17.87	18.34
	3H	18.22	19.34	18.70	19.82	20.31	18.15	19.27	18.63	19.75	20.24
	4H	19.09	20.10	19.58	20.59	21.12	19.00	20.02	19.50	20.51	21.04
	6H	19.81	20.71	20.33	21.22	21.77	19.73	20.62	20.24	21.13	21.68
	8H	20.10	20.93	20.62	21.45	22.01	20.00	20.84	20.53	21.36	21.91
	12H	20.34	21.10	20.89	21.64	22.21	20.24	21.00	20.79	21.54	22.11
8H	4H	19.40	20.24	19.92	20.75	21.31	19.33	20.17	19.85	20.68	21.24
	6H	20.27	20.97	20.83	21.53	22.10	20.19	20.90	20.75	21.45	22.02
	8H	20.65	21.28	21.22	21.85	22.43	20.56	21.20	21.13	21.77	22.35
	12H	21.00	21.56	21.57	22.12	22.77	20.91	21.47	21.48	22.03	22.68
12H	4H	19.44	20.20	19.98	20.74	21.31	19.37	20.13	19.92	20.67	21.24
	6H	20.34	20.98	20.91	21.55	22.13	20.27	20.90	20.84	21.47	22.05
	8H	20.79	21.35	21.36	21.91	22.56	20.71	21.27	21.28	21.83	22.47

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-5

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L840-U

Data in this report applies to families of products including 22ID2-55-CFR1-L840-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L840-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 80CRI

Spectral Parameters

CCT (K): 3915
 CIE u' : 0.2259
 CIE v' : 0.5051
 Duv: 0.0015
 CIE x: 0.3854
 CIE y: 0.3830
 CIE z: 0.2316
 Peak Wavelength (nm): 453
 Dominant Wavelength (nm): 578
 Purity: 30.6207
 R_f: 83.2
 R_g: 94.6

CRI (Ra): 82.3
 R1: 80.6
 R2: 88.9
 R3: 94.6
 R4: 80.5
 R5: 80.0
 R6: 84.0
 R7: 86.1
 R8: 64.0
 R9: 7.6
 R10: 72.9
 R11: 78.7
 R12: 57.3
 R13: 82.7
 R14: 97.1
 R15: 74.3



Test Conditions


Stabilization Time: 34M
 Operation Time: 1H 34M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.65

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-5

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.36

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	266	NR	620	755	NR	750	24	NR	880	1	NR
365	0	NR	495	307	NR	625	710	NR	755	21	NR	885	0	NR
370	0	NR	500	366	NR	630	663	NR	760	18	NR	890	0	NR
375	0	NR	505	430	NR	635	612	NR	765	15	NR	895	0	NR
380	0	NR	510	486	NR	640	561	NR	770	13	NR	900	0	NR
385	0	NR	515	536	NR	645	509	NR	775	11	NR	905	0	NR
390	1	NR	520	571	NR	650	458	NR	780	10	NR	910	0	NR
395	3	NR	525	600	NR	655	410	NR	785	8	NR	915	0	NR
400	5	NR	530	624	NR	660	363	NR	790	7	NR	920	0	NR
405	7	NR	535	645	NR	665	321	NR	795	6	NR	925	0	NR
410	10	NR	540	661	NR	670	280	NR	800	5	NR	930	0	NR
415	16	NR	545	681	NR	675	244	NR	805	5	NR	935	0	NR
420	30	NR	550	701	NR	680	213	NR	810	4	NR	940	0	NR
425	53	NR	555	724	NR	685	183	NR	815	3	NR	945	0	NR
430	95	NR	560	747	NR	690	159	NR	820	3	NR	950	0	NR
435	170	NR	565	772	NR	695	136	NR	825	3	NR	955	0	NR
440	289	NR	570	795	NR	700	117	NR	830	2	NR	960	0	NR
445	522	NR	575	817	NR	705	100	NR	835	2	NR	965	0	NR
450	895	NR	580	841	NR	710	85	NR	840	2	NR	970	0	NR
455	957	NR	585	857	NR	715	72	NR	845	1	NR	975	0	NR
460	642	NR	590	871	NR	720	62	NR	850	1	NR	980	0	NR
465	487	NR	595	875	NR	725	53	NR	855	1	NR	985	0	NR
470	397	NR	600	866	NR	730	45	NR	860	1	NR	990	0	NR
475	289	NR	605	852	NR	735	39	NR	865	1	NR	995	0	NR
480	241	NR	610	827	NR	740	33	NR	870	1	NR	1000	0	NR
485	245	NR	615	796	NR	745	28	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-5

TM-30-18

Summary

$R_f = 83.2$
 $R_g = 94.6$
 $CIE R_a = 82.3$
 $R_9 = 7.6$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 83	CES51 = 92	CES76 = 75
CES02 = 61	CES27 = 91	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 88	CES78 = 74
CES04 = 70	CES29 = 90	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 90	CES55 = 85	CES80 = 89
CES06 = 50	CES31 = 91	CES56 = 83	CES81 = 81
CES07 = 41	CES32 = 83	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 90	CES84 = 90
CES10 = 74	CES35 = 92	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 78	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 91	CES62 = 79	CES87 = 84
CES13 = 42	CES38 = 84	CES63 = 82	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 77
CES15 = 71	CES40 = 96	CES65 = 74	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 70	CES91 = 67
CES17 = 49	CES42 = 93	CES67 = 69	CES92 = 64
CES18 = 56	CES43 = 91	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 63
CES20 = 65	CES45 = 94	CES70 = 72	CES95 = 72
CES21 = 86	CES46 = 91	CES71 = 64	CES96 = 84
CES22 = 78	CES47 = 95	CES72 = 88	CES97 = 91
CES23 = 91	CES48 = 83	CES73 = 66	CES98 = 86
CES24 = 90	CES49 = 90	CES74 = 90	CES99 = 77
CES25 = 71	CES50 = 93	CES75 = 68	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)