

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217067

Luminaire Tested: 14-ID2-70-CFD2-L830-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1217067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-16)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-70-CFD2-L830-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6601.3 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.16')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217067
CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217067

CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	96
1	107	102	98	94	104	100	95	92	94	91	88	90	87	85	85	83	81	81	81	79
2	97	89	82	76	94	87	80	75	82	77	72	78	74	70	75	71	68	68	68	66
3	89	78	70	63	86	76	69	62	73	66	61	69	64	59	66	62	58	58	58	55
4	81	69	60	54	79	68	59	53	65	57	52	62	56	51	59	54	50	50	50	47
5	75	62	53	46	72	61	52	46	58	51	45	56	49	44	53	48	43	43	43	41
6	69	56	47	40	67	55	46	40	52	45	39	50	44	39	48	43	38	38	38	36
7	64	51	42	36	62	50	41	35	48	40	35	46	39	34	44	38	34	34	34	32
8	60	46	38	32	58	45	37	32	44	36	31	42	36	31	41	35	30	30	30	28
9	56	42	34	29	54	42	34	29	40	33	28	39	32	28	38	32	27	27	27	26
10	52	39	31	26	51	39	31	26	37	30	26	36	30	25	35	29	25	25	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6216	6216	6216
5°	6207	6127	6134
10°	6152	6025	6031
15°	6070	5903	5900
20°	5966	5748	5726
25°	5841	5567	5525
30°	5684	5364	5321
35°	5483	5138	5106
40°	5273	4902	4887
45°	5017	4664	4656
50°	4758	4423	4446
55°	4480	4173	4250
60°	4200	3939	4056
65°	3898	3696	3849
70°	3586	3428	3586
75°	3233	3108	3230
80°	2831	2707	2809
85°	2441	2316	2411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5017 cd/sqm

TEST NUMBER: P1217067
 CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.5	3.3
10°-20°	620.6	9.4
20°-30°	921.4	14.0
30°-40°	1078.4	16.3
40°-50°	1083.2	16.4
50°-60°	959.4	14.5
60°-70°	746.2	11.3
70°-80°	473.9	7.2
80°-90°	211.8	3.2
90°-100°	101.1	1.5
100°-110°	77.2	1.2
110°-120°	54.4	0.8
120°-130°	32.5	0.5
130°-140°	15.9	0.2
140°-150°	5.8	0.1
150°-160°	1.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1760.4	26.7
0°-40°	2838.9	43.0
0°-60°	4881.4	73.9
0°-90°	6313.3	95.6
90°-120°	232.8	3.5
90°-150°	287.0	4.3
90°-180°	288.0	4.4
0°-180°	6601.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2310	2310	2310	2310	2310	
5°	2306	2304	2296	2297	2303	219
15°	2202	2203	2199	2202	2209	621
25°	2004	2006	1998	1997	2000	922
35°	1716	1730	1719	1728	1728	1073
45°	1371	1399	1399	1420	1419	1059
55°	1009	1050	1069	1106	1113	904
65°	665	713	756	807	812	660
75°	357	408	457	498	496	381
85°	115	156	196	224	221	117
90°	50	86	123	141	139	30
95°	43	69	101	114	113	34
105°	31	50	81	96	99	33
115°	20	31	60	77	82	20
125°	13	16	38	53	59	11
135°	8	6	20	32	37	6
145°	4	3	6	15	19	2
155°	2	1	1	2	3	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1217067

CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2310.1	2310.1	2310.1	2310.1	2310.1
2.5°	2315.4	2313.3	2304.7	2305.8	2310.1
5°	2305.8	2303.7	2296.2	2297.3	2302.6
7.5°	2289.8	2288.7	2281.3	2283.4	2290.9
10°	2267.4	2266.3	2259.9	2263.1	2269.5
12.5°	2238.6	2237.5	2232.2	2235.4	2241.8
15°	2202.3	2203.4	2199.1	2202.3	2208.7
17.5°	2160.7	2162.8	2156.4	2160.7	2166.0
20°	2113.7	2115.9	2110.5	2110.5	2115.9
22.5°	2061.5	2063.6	2057.2	2057.2	2061.5
25°	2003.8	2006.0	1998.5	1997.4	1999.6
27.5°	1938.7	1944.1	1934.5	1935.5	1936.6
30°	1871.5	1876.9	1867.3	1869.4	1870.5
32.5°	1794.7	1805.4	1794.7	1799.0	1801.1
35°	1715.7	1729.6	1718.9	1727.5	1728.5
37.5°	1635.7	1650.7	1641.1	1652.8	1653.9
40°	1551.4	1568.5	1561.0	1576.0	1578.1
42.5°	1463.9	1485.3	1481.0	1499.1	1497.0
45°	1371.1	1398.8	1398.8	1420.2	1419.1
47.5°	1281.5	1312.4	1316.7	1341.2	1341.2
50°	1190.8	1224.9	1234.5	1263.3	1264.4
52.5°	1100.1	1137.4	1153.4	1183.3	1187.6
55°	1009.4	1049.9	1069.1	1106.5	1112.9
57.5°	920.8	961.4	990.2	1028.6	1037.1
60°	834.4	877.1	911.2	955.0	962.4
62.5°	748.0	793.9	835.5	878.1	886.7
65°	664.7	712.8	756.5	806.7	812.0
67.5°	584.7	632.7	680.7	727.7	735.2
70°	505.8	555.9	605.0	654.1	656.2
72.5°	430.0	480.2	530.3	576.2	576.2
75°	357.4	407.6	456.7	498.3	496.2
77.5°	292.4	337.2	384.1	421.5	418.3
80°	224.1	270.0	314.8	348.9	345.7
82.5°	165.4	207.0	251.8	283.8	280.6
85°	115.2	155.8	196.3	224.1	220.9
87.5°	75.8	115.2	152.6	176.1	172.9
90°	50.1	86.4	122.7	140.8	138.7
92.5°	44.8	75.8	108.8	123.8	121.6
95°	42.7	69.4	101.4	114.2	113.1
97.5°	40.5	64.0	95.0	108.8	108.8
100°	37.3	59.8	90.7	104.6	105.6
102.5°	34.1	54.4	85.4	100.3	102.4
105°	30.9	50.1	81.1	96.0	99.2
107.5°	28.8	44.8	75.8	91.8	96.0
110°	25.6	40.5	70.4	87.5	91.8

TEST NUMBER: P1217067

CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	22.4	35.2	65.1	82.2	87.5
115°	20.3	30.9	59.8	76.8	82.2
117.5°	18.1	26.7	54.4	71.5	75.8
120°	16.0	23.5	49.1	66.2	70.4
122.5°	13.9	19.2	43.7	59.8	65.1
125°	12.8	16.0	38.4	53.4	58.7
127.5°	10.7	12.8	33.1	48.0	53.4
130°	9.6	9.6	27.7	42.7	48.0
132.5°	8.5	7.5	23.5	37.3	41.6
135°	7.5	6.4	20.3	32.0	37.3
137.5°	6.4	5.3	16.0	27.7	32.0
140°	5.3	4.3	12.8	23.5	26.7
142.5°	4.3	3.2	9.6	19.2	22.4
145°	4.3	3.2	6.4	14.9	19.2
147.5°	3.2	2.1	3.2	11.7	14.9
150°	2.1	2.1	1.1	8.5	10.7
152.5°	2.1	1.1	1.1	5.3	7.5
155°	2.1	1.1	1.1	2.1	3.2
157.5°	1.1	1.1	1.1	0.0	0.0
160°	1.1	1.1	1.1	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217067

CATALOG NUMBER: 14-ID2-70-CFD2-L830-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.18	17.72	16.61	18.12	18.55	17.07	18.61	17.50	19.01	19.44
	3H	17.73	19.13	18.18	19.55	20.01	19.09	20.49	19.54	20.90	21.37
	4H	18.28	19.60	18.75	20.04	20.52	19.92	21.23	20.38	21.67	22.15
	6H	18.67	19.89	19.15	20.34	20.84	20.60	21.83	21.08	22.28	22.77
	8H	18.78	19.95	19.27	20.42	20.92	20.88	22.05	21.38	22.53	23.03
	12H	18.85	19.97	19.34	20.43	20.97	21.14	22.26	21.64	22.73	23.26
4H	2H	16.87	18.19	17.34	18.63	19.11	17.58	18.90	18.05	19.33	19.81
	3H	18.67	19.78	19.15	20.26	20.76	19.83	20.94	20.31	21.42	21.92
	4H	19.35	20.36	19.85	20.86	21.39	20.80	21.81	21.30	22.31	22.84
	6H	19.86	20.74	20.38	21.27	21.82	21.64	22.53	22.17	23.05	23.61
	8H	20.01	20.84	20.54	21.37	21.93	22.00	22.83	22.53	23.35	23.92
	12H	20.12	20.87	20.67	21.42	21.99	22.33	23.08	22.88	23.63	24.20
8H	4H	19.77	20.60	20.30	21.12	21.69	21.05	21.88	21.57	22.40	22.96
	6H	20.42	21.12	20.98	21.68	22.25	22.03	22.73	22.59	23.29	23.87
	8H	20.65	21.28	21.22	21.86	22.44	22.49	23.12	23.06	23.69	24.28
	12H	20.84	21.39	21.41	21.96	22.61	22.95	23.51	23.52	24.07	24.73
12H	4H	19.84	20.59	20.39	21.14	21.71	21.06	21.81	21.61	22.36	22.93
	6H	20.53	21.16	21.11	21.74	22.33	22.07	22.70	22.65	23.28	23.86
	8H	20.83	21.39	21.41	21.96	22.61	22.59	23.15	23.17	23.71	24.37

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L830-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

Spectral Parameters

CCT (K): 3031
 CIE u' : 0.2493
 CIE v' : 0.5215
 Duv: 0.0005
 CIE x: 0.4355
 CIE y: 0.4049
 CIE z: 0.1596
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 582
 Purity: 52.24762
 Rf: 84.8
 Rg: 95.8

CRI (Ra): 82.5
 R1: 80.7
 R2: 90.5
 R3: 96.7
 R4: 80.7
 R5: 80.9
 R6: 88.5
 R7: 83.0
 R8: 58.8
 R9: 5.8
 R10: 78.6
 R11: 80.2
 R12: 69.8
 R13: 83.0
 R14: 98.8
 R15: 73.0



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.59

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3


TM-30-18

Summary

$R_f = 84.8$
 $R_g = 95.8$
 $CIE R_a = 82.5$
 $R_9 = 5.8$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)