

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1217159

Luminaire Tested: 14-ID2-70-CNC-L935-U

Issue Date: 12/5/2025


Test Information

Test Method: LM-79-2019
Report Number: P1217159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-17)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-70-CNC-L935-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CURVE REGRESS LENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5424.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.19 / 1.3
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1217159
CATALOG NUMBER: 14-ID2-70-CNC-L935-U

Luminous Intensity Polar Plot



TEST NUMBER: P1217159

CATALOG NUMBER: 14-ID2-70-CNC-L935-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	104	100	97	106	102	98	95	98	95	92		94	92	89		84
2	99	91	85	79	97	90	83	78	86	81	76		83	78	75		71
3	91	81	73	66	88	79	72	66	76	70	64		73	68	63		60
4	83	72	63	56	81	70	62	56	68	61	55		65	59	54		52
5	77	64	55	49	75	63	55	48	61	54	48		59	53	47		45
6	71	58	49	43	69	57	49	43	55	48	42		53	47	42		39
7	66	53	44	38	64	52	44	38	50	43	37		49	42	37		35
8	61	48	40	34	60	47	39	34	46	39	34		45	38	33		31
9	57	44	36	31	56	44	36	31	42	35	30		41	35	30		28
10	54	41	33	28	53	40	33	28	39	32	28		38	32	27		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5703	5703	5703
5°	5712	5683	5695
10°	5680	5648	5660
15°	5622	5586	5596
20°	5549	5496	5493
25°	5444	5383	5364
30°	5322	5239	5233
35°	5175	5093	5087
40°	5012	4937	4931
45°	4833	4770	4759
50°	4641	4595	4587
55°	4435	4405	4383
60°	4204	4204	4189
65°	3923	3982	3947
70°	3635	3715	3657
75°	3213	3413	3279
80°	2731	2944	2731
85°	2050	2220	2137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4833 cd/sqm

TEST NUMBER: P1217159
 CATALOG NUMBER: 14-ID2-70-CNC-L935-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.0	3.7
10°-20°	566.0	10.4
20°-30°	835.4	15.4
30°-40°	972.2	17.9
40°-50°	968.8	17.9
50°-60°	840.0	15.5
60°-70°	616.2	11.4
70°-80°	340.7	6.3
80°-90°	84.9	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.4	29.5
0°-40°	2573.6	47.4
0°-60°	4382.4	80.8
0°-90°	5424.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5424.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2119	2119	2119	2119	2119	
5°	2115	2112	2104	2104	2108	201
15°	2018	2014	2005	2002	2009	569
25°	1833	1823	1813	1803	1807	844
35°	1575	1565	1550	1543	1548	984
45°	1270	1264	1253	1246	1251	980
55°	945	944	939	933	934	845
65°	616	626	625	617	620	613
75°	309	329	328	316	315	330
85°	66	76	72	66	69	80
90°	0	0	0	0	0	

TEST NUMBER: P1217159

CATALOG NUMBER: 14-ID2-70-CNC-L935-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2119.3	2119.3	2119.3	2119.3	2119.3
2.5°	2123.0	2120.3	2112.9	2112.9	2116.6
5°	2114.7	2112.0	2103.7	2103.7	2108.3
7.5°	2099.0	2097.2	2088.0	2088.0	2094.4
10°	2078.8	2075.1	2066.8	2065.8	2071.4
12.5°	2052.0	2048.3	2039.1	2037.3	2042.8
15°	2017.9	2014.2	2005.0	2002.2	2008.7
17.5°	1981.9	1974.5	1966.2	1960.7	1966.2
20°	1937.7	1930.3	1919.2	1912.8	1918.3
22.5°	1887.9	1879.6	1868.5	1858.3	1864.8
25°	1833.4	1823.3	1813.1	1803.0	1806.7
27.5°	1775.3	1763.3	1751.4	1742.1	1745.8
30°	1712.6	1699.7	1685.9	1678.5	1684.0
32.5°	1642.5	1635.2	1620.4	1612.1	1616.7
35°	1575.2	1565.1	1550.3	1542.9	1548.5
37.5°	1502.4	1492.2	1479.3	1471.0	1476.5
40°	1426.7	1417.5	1405.5	1397.2	1403.7
42.5°	1349.3	1343.7	1330.8	1321.6	1328.0
45°	1269.9	1263.5	1253.3	1246.0	1250.6
47.5°	1189.7	1184.2	1175.9	1167.6	1174.0
50°	1108.5	1106.7	1097.5	1090.1	1095.6
52.5°	1026.5	1026.5	1018.2	1011.7	1017.2
55°	945.3	943.5	938.9	933.3	934.2
57.5°	863.2	863.2	859.5	854.0	858.6
60°	781.1	784.8	781.1	774.7	778.4
62.5°	700.0	704.6	702.8	695.4	699.1
65°	616.1	626.2	625.3	617.0	619.8
67.5°	540.4	548.7	547.8	540.4	542.3
70°	462.0	473.1	472.2	463.9	464.8
72.5°	382.7	399.3	398.4	389.2	389.2
75°	309.0	329.2	328.3	316.3	315.4
77.5°	242.6	260.1	258.2	245.3	245.3
80°	176.2	191.8	190.0	176.2	176.2
82.5°	117.1	131.0	127.3	116.2	118.0
85°	66.4	75.6	71.9	66.4	69.2
87.5°	24.0	29.5	28.6	24.0	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1217159

CATALOG NUMBER: 14-ID2-70-CNC-L935-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.77	17.53	19.08	19.40	17.09	18.70	17.46	19.02	19.33
	3H	18.85	20.29	19.22	20.62	20.98	18.79	20.24	19.16	20.56	20.92
	4H	19.44	20.80	19.84	21.15	21.53	19.39	20.76	19.79	21.10	21.48
	6H	19.85	21.12	20.26	21.48	21.87	19.80	21.06	20.21	21.43	21.82
	8H	19.97	21.17	20.39	21.56	21.96	19.91	21.11	20.33	21.50	21.90
	12H	20.03	21.18	20.46	21.57	21.99	19.98	21.13	20.40	21.51	21.94
4H	2H	17.76	19.13	18.16	19.47	19.85	17.71	19.07	18.11	19.42	19.80
	3H	19.67	20.81	20.08	21.21	21.61	19.61	20.75	20.02	21.15	21.55
	4H	20.41	21.44	20.84	21.85	22.29	20.34	21.37	20.77	21.78	22.22
	6H	20.95	21.84	21.40	22.29	22.74	20.86	21.75	21.31	22.20	22.65
	8H	21.10	21.94	21.56	22.38	22.85	21.00	21.84	21.46	22.29	22.75
	12H	21.20	21.95	21.68	22.43	22.90	21.10	21.86	21.58	22.33	22.80
8H	4H	20.70	21.54	21.16	21.98	22.45	20.64	21.48	21.10	21.92	22.38
	6H	21.35	22.05	21.85	22.54	23.02	21.26	21.95	21.75	22.44	22.92
	8H	21.58	22.20	22.09	22.71	23.20	21.46	22.08	21.97	22.59	23.08
	12H	21.74	22.29	22.25	22.78	23.35	21.61	22.16	22.12	22.65	23.22
12H	4H	20.72	21.47	21.20	21.95	22.42	20.66	21.42	21.14	21.89	22.36
	6H	21.40	22.02	21.91	22.53	23.02	21.30	21.93	21.81	22.44	22.92
	8H	21.67	22.23	22.18	22.72	23.28	21.56	22.11	22.06	22.60	23.16

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-10

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L935-U

Data in this report applies to families of products including 22ID2-55-CFR1-L935-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-10
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L935-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 90CRI

Spectral Parameters

CCT (K): 3377
 CIE u' : 0.2392
 CIE v' : 0.5128
 Duv: -0.0007
 CIE x: 0.4116
 CIE y: 0.3922
 CIE z: 0.1962
 Peak Wavelength (nm): 618
 Dominant Wavelength (nm): 581
 Purity: 41.24368
 R_f: 91.8
 R_g: 99.6

CRI (Ra): 93.6
 R1: 94.1
 R2: 96.6
 R3: 97.5
 R4: 94.0
 R5: 93.6
 R6: 94.8
 R7: 93.4
 R8: 84.8
 R9: 64.2
 R10: 91.1
 R11: 94.7
 R12: 78.5
 R13: 95.0
 R14: 98.1
 R15: 91.0



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2506-458-10

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-10

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.19


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	362	NR	620	996	NR	750	68	NR	880	1	NR
365	0	NR	495	412	NR	625	989	NR	755	58	NR	885	1	NR
370	0	NR	500	463	NR	630	973	NR	760	49	NR	890	1	NR
375	0	NR	505	509	NR	635	947	NR	765	42	NR	895	1	NR
380	0	NR	510	548	NR	640	914	NR	770	36	NR	900	1	NR
385	0	NR	515	582	NR	645	872	NR	775	31	NR	905	1	NR
390	1	NR	520	605	NR	650	822	NR	780	26	NR	910	1	NR
395	2	NR	525	626	NR	655	770	NR	785	22	NR	915	1	NR
400	4	NR	530	646	NR	660	712	NR	790	19	NR	920	0	NR
405	6	NR	535	666	NR	665	656	NR	795	16	NR	925	0	NR
410	9	NR	540	683	NR	670	596	NR	800	14	NR	930	0	NR
415	15	NR	545	702	NR	675	538	NR	805	12	NR	935	0	NR
420	27	NR	550	720	NR	680	486	NR	810	10	NR	940	0	NR
425	48	NR	555	740	NR	685	432	NR	815	9	NR	945	0	NR
430	85	NR	560	757	NR	690	385	NR	820	7	NR	950	0	NR
435	152	NR	565	776	NR	695	339	NR	825	6	NR	955	0	NR
440	274	NR	570	794	NR	700	297	NR	830	5	NR	960	0	NR
445	536	NR	575	816	NR	705	260	NR	835	5	NR	965	0	NR
450	793	NR	580	842	NR	710	225	NR	840	4	NR	970	0	NR
455	659	NR	585	867	NR	715	194	NR	845	3	NR	975	0	NR
460	484	NR	590	899	NR	720	169	NR	850	3	NR	980	0	NR
465	441	NR	595	927	NR	725	146	NR	855	2	NR	985	0	NR
470	353	NR	600	950	NR	730	125	NR	860	2	NR	990	0	NR
475	293	NR	605	974	NR	735	107	NR	865	2	NR	995	0	NR
480	300	NR	610	986	NR	740	92	NR	870	2	NR	1000	0	NR
485	325	NR	615	998	NR	745	79	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-10





TM-30-18

Summary

$R_f = 91.8$
 $R_g = 99.6$
 $CIE R_a = 93.6$
 $R_9 = 64.2$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 92	CES52 = 99	CES77 = 89
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 96	CES54 = 93	CES79 = 95
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 86
CES07 = 43	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 42	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 94
CES10 = 75	CES35 = 96	CES60 = 92	CES85 = 83
CES11 = 58	CES36 = 82	CES61 = 92	CES86 = 86
CES12 = 64	CES37 = 95	CES62 = 87	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 93	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 87
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 97	CES66 = 88	CES91 = 75
CES17 = 50	CES42 = 95	CES67 = 87	CES92 = 80
CES18 = 56	CES43 = 94	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 81
CES20 = 67	CES45 = 97	CES70 = 86	CES95 = 84
CES21 = 86	CES46 = 97	CES71 = 82	CES96 = 92
CES22 = 78	CES47 = 96	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 92	CES73 = 82	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 92	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 84	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)