

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1216902

Luminaire Tested: 14-ID2-80-CFR2-L835-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1216902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2508-507-14)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 14-ID2-80-CFR2-L835-U
Description: 1X4 IN DEPTH TROFFER WITH 2INCH CUBE REGRESS LENS
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7367.6 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.16 / 1.28
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1216902
CATALOG NUMBER: 14-ID2-80-CFR2-L835-U

Luminous Intensity Polar Plot



TEST NUMBER: P1216902

CATALOG NUMBER: 14-ID2-80-CFR2-L835-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	110	105	101	98	107	103	99	96	99	96	93		95	93	90		86
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		72
3	92	82	74	68	89	80	73	67	77	71	66		75	70	65		62
4	84	73	65	58	82	72	64	58	69	62	57		67	61	56		53
5	78	66	57	51	76	64	56	50	62	55	50		60	54	49		47
6	72	59	51	44	70	58	50	44	57	49	44		55	48	44		41
7	67	54	45	40	65	53	45	39	52	44	39		50	44	39		37
8	62	49	41	35	61	49	41	35	47	40	35		46	40	35		33
9	58	45	37	32	57	45	37	32	44	37	32		43	36	32		30
10	55	42	34	29	54	41	34	29	40	34	29		40	33	29		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8171	8171	8171
5°	8190	8161	8196
10°	8163	8157	8193
15°	8106	8096	8063
20°	8014	7952	7860
25°	7893	7744	7609
30°	7736	7509	7331
35°	7530	7227	7030
40°	7304	6917	6681
45°	7042	6573	6300
50°	6740	6183	5878
55°	6390	5767	5430
60°	6029	5308	4941
65°	5624	4802	4390
70°	5113	4247	3777
75°	4480	3609	2975
80°	3617	2672	2078
85°	2439	1958	1738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7042 cd/sqm

TEST NUMBER: P1216902
 CATALOG NUMBER: 14-ID2-80-CFR2-L835-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.8	3.9
10°-20°	817.7	11.1
20°-30°	1202.5	16.3
30°-40°	1382.8	18.8
40°-50°	1344.2	18.2
50°-60°	1115.0	15.1
60°-70°	764.2	10.4
70°-80°	374.4	5.1
80°-90°	79.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2308.0	31.3
0°-40°	3690.8	50.1
0°-60°	6149.9	83.5
0°-90°	7367.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7367.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3037	3037	3037	3037	3037	
5°	3032	3028	3021	3026	3034	288
15°	2910	2912	2906	2894	2894	820
25°	2658	2662	2608	2573	2563	1224
35°	2292	2280	2200	2156	2140	1433
45°	1850	1819	1727	1674	1655	1426
55°	1362	1318	1229	1179	1157	1220
65°	883	828	754	711	689	875
75°	431	395	347	303	286	459
85°	79	69	63	59	56	101
90°	0	0	0	0	0	

TEST NUMBER: P1216902

CATALOG NUMBER: 14-ID2-80-CFR2-L835-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3036.6	3036.6	3036.6	3036.6	3036.6
2.5°	3041.4	3036.6	3029.4	3031.8	3036.6
5°	3031.8	3028.2	3021.1	3025.8	3034.2
7.5°	3013.9	3011.5	3006.7	3013.9	3024.6
10°	2987.5	2986.3	2985.1	2989.9	2998.3
12.5°	2952.8	2952.8	2952.8	2949.2	2952.8
15°	2909.7	2912.1	2906.1	2894.2	2894.2
17.5°	2858.3	2863.1	2847.5	2828.3	2823.6
20°	2798.4	2804.4	2776.9	2749.4	2744.6
22.5°	2731.4	2737.4	2695.5	2663.2	2657.2
25°	2658.4	2662.0	2608.1	2573.4	2562.6
27.5°	2575.8	2575.8	2515.9	2476.5	2462.1
30°	2489.6	2484.8	2416.6	2374.7	2359.2
32.5°	2391.5	2385.5	2310.1	2267.0	2251.4
35°	2292.1	2280.2	2200.0	2155.7	2140.1
37.5°	2188.0	2171.2	2086.3	2039.6	2021.6
40°	2079.1	2056.3	1969.0	1919.9	1901.9
42.5°	1966.6	1940.2	1849.3	1801.4	1778.6
45°	1850.5	1819.3	1727.2	1674.5	1655.4
47.5°	1730.8	1696.1	1602.7	1552.4	1529.7
50°	1609.9	1570.4	1477.0	1426.7	1404.0
52.5°	1486.6	1441.1	1352.5	1302.3	1280.7
55°	1362.1	1317.8	1229.2	1179.0	1157.4
57.5°	1243.6	1192.1	1106.0	1059.3	1035.3
60°	1120.3	1068.9	986.3	939.6	918.0
62.5°	1004.2	946.8	869.0	823.5	801.9
65°	883.3	828.3	754.1	711.0	689.4
67.5°	764.8	713.4	645.1	600.9	582.9
70°	649.9	600.9	539.8	497.9	480.0
72.5°	538.6	496.7	442.9	397.4	381.8
75°	430.9	395.0	347.1	302.8	286.1
77.5°	329.2	300.4	254.9	211.9	195.1
80°	233.4	211.9	172.4	136.5	134.1
82.5°	150.8	135.3	102.9	98.1	95.8
85°	79.0	69.4	63.4	58.6	56.3
87.5°	25.1	25.1	25.1	20.3	19.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1216902

CATALOG NUMBER: 14-ID2-80-CFR2-L835-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.44	20.01	18.80	20.32	20.64	17.53	19.10	17.90	19.41	19.73
	3H	20.04	21.45	20.42	21.78	22.14	18.87	20.28	19.25	20.61	20.97
	4H	20.60	21.92	20.99	22.27	22.64	19.26	20.59	19.66	20.93	21.31
	6H	20.96	22.18	21.37	22.55	22.94	19.44	20.66	19.85	21.03	21.42
	8H	21.05	22.21	21.47	22.60	23.00	19.48	20.65	19.91	21.04	21.44
	12H	21.09	22.21	21.52	22.59	23.02	19.50	20.62	19.93	21.00	21.43
4H	2H	18.86	20.19	19.26	20.53	20.91	18.12	19.44	18.52	19.79	20.17
	3H	20.66	21.76	21.07	22.16	22.56	19.66	20.76	20.07	21.16	21.56
	4H	21.33	22.32	21.76	22.74	23.18	20.13	21.12	20.56	21.54	21.98
	6H	21.80	22.67	22.26	23.11	23.57	20.38	21.24	20.84	21.68	22.14
	8H	21.93	22.73	22.39	23.18	23.64	20.44	21.25	20.91	21.69	22.16
	12H	22.00	22.72	22.48	23.20	23.67	20.49	21.21	20.97	21.69	22.16
8H	4H	21.48	22.29	21.94	22.73	23.20	20.39	21.19	20.85	21.63	22.10
	6H	22.03	22.69	22.52	23.18	23.66	20.69	21.36	21.19	21.85	22.33
	8H	22.20	22.79	22.71	23.30	23.79	20.79	21.39	21.30	21.90	22.38
	12H	22.31	22.84	22.82	23.33	23.89	20.88	21.40	21.39	21.90	22.46
12H	4H	21.47	22.19	21.95	22.67	23.14	20.40	21.12	20.89	21.60	22.07
	6H	22.02	22.61	22.53	23.12	23.61	20.72	21.32	21.23	21.83	22.31
	8H	22.23	22.75	22.73	23.24	23.81	20.86	21.38	21.37	21.88	22.44

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-1

Test Date: 07/23/2025

Luminaire Tested: 22ID2-55-CFR1-L835-U

Data in this report applies to families of products including 22ID2-55-CFR1-L835-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L835-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3500K 80CRI

Spectral Parameters

CCT (K): 3440
 CIE u' : 0.2370
 CIE v' : 0.5132
 Duv: 0.0005
 CIE x: 0.4093
 CIE y: 0.3940
 CIE z: 0.1967
 Peak Wavelength (nm): 599
 Dominant Wavelength (nm): 580
 Purity: 41.09375
 R_f: 84.9
 R_g: 94.6

CRI (Ra): 84.2
 R1: 82.8
 R2: 91.7
 R3: 96.7
 R4: 81.9
 R5: 82.6
 R6: 88.8
 R7: 85.0
 R8: 63.7
 R9: 13.6
 R10: 80.1
 R11: 81.1
 R12: 65.8
 R13: 85.2
 R14: 98.7
 R15: 76.2



Test Conditions

Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.53

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.07

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	295	NR	620	910	NR	750	30	NR	880	1	NR
365	0	NR	495	335	NR	625	862	NR	755	25	NR	885	1	NR
370	0	NR	500	390	NR	630	809	NR	760	21	NR	890	1	NR
375	0	NR	505	445	NR	635	752	NR	765	18	NR	895	0	NR
380	0	NR	510	490	NR	640	694	NR	770	16	NR	900	0	NR
385	0	NR	515	532	NR	645	630	NR	775	13	NR	905	0	NR
390	0	NR	520	563	NR	650	571	NR	780	12	NR	910	0	NR
395	2	NR	525	588	NR	655	512	NR	785	10	NR	915	0	NR
400	3	NR	530	609	NR	660	453	NR	790	8	NR	920	0	NR
405	5	NR	535	631	NR	665	401	NR	795	7	NR	925	0	NR
410	8	NR	540	654	NR	670	351	NR	800	6	NR	930	0	NR
415	13	NR	545	677	NR	675	306	NR	805	5	NR	935	0	NR
420	23	NR	550	702	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	734	NR	685	230	NR	815	4	NR	945	0	NR
430	70	NR	560	767	NR	690	199	NR	820	4	NR	950	0	NR
435	126	NR	565	802	NR	695	171	NR	825	3	NR	955	0	NR
440	221	NR	570	838	NR	700	146	NR	830	3	NR	960	0	NR
445	418	NR	575	875	NR	705	125	NR	835	2	NR	965	0	NR
450	729	NR	580	913	NR	710	107	NR	840	2	NR	970	0	NR
455	816	NR	585	946	NR	715	90	NR	845	2	NR	975	0	NR
460	578	NR	590	976	NR	720	77	NR	850	1	NR	980	0	NR
465	458	NR	595	992	NR	725	66	NR	855	1	NR	985	0	NR
470	390	NR	600	999	NR	730	56	NR	860	1	NR	990	0	NR
475	299	NR	605	995	NR	735	47	NR	865	1	NR	995	0	NR
480	260	NR	610	975	NR	740	40	NR	870	1	NR	1000	0	NR
485	271	NR	615	948	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-1


TM-30-18

Summary

$R_f = 84.9$
 $R_g = 94.6$
 $CIE R_a = 84.2$
 $R_9 = 13.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 87	CES51 = 92	CES76 = 81
CES02 = 62	CES27 = 91	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 94	CES53 = 90	CES78 = 80
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 92
CES05 = 49	CES30 = 89	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 94	CES56 = 85	CES81 = 77
CES07 = 41	CES32 = 86	CES57 = 83	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 84	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 76
CES11 = 58	CES36 = 79	CES61 = 87	CES86 = 73
CES12 = 64	CES37 = 95	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 84	CES63 = 85	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 78	CES89 = 78
CES15 = 71	CES40 = 97	CES65 = 78	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 75	CES91 = 71
CES17 = 50	CES42 = 96	CES67 = 74	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 95	CES70 = 77	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 71	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 72	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 90	CES99 = 79
CES25 = 72	CES50 = 93	CES75 = 75	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)