

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1214863

Luminaire Tested: 22-ID2-50-CFD2-L940-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1214863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-13)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-50-CFD2-L940-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4912.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 2' x H: 0.16')
CIE Type: Direct

Input Watts (W): 44.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1214863
CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1214863
 CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	109	109	109		103	103	103		98
1	107	102	98	94	104	100	95	92	95	91	88		90	87	85		86
2	97	89	82	76	94	87	80	75	83	77	73		79	74	70		75
3	89	78	70	63	86	76	69	62	73	66	61		69	64	59		66
4	81	69	60	54	79	68	59	53	65	58	52		62	56	51		59
5	75	62	53	46	72	61	52	46	58	51	45		56	49	44		53
6	69	56	47	40	67	55	46	40	52	45	39		50	44	39		48
7	64	51	42	36	62	50	41	36	48	40	35		46	39	34		44
8	60	46	38	32	58	45	37	32	44	37	31		42	36	31		41
9	56	43	34	29	54	42	34	29	40	33	28		39	33	28		38
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4683	4683	4683
5°	4647	4629	4647
10°	4588	4557	4588
15°	4507	4459	4505
20°	4400	4347	4395
25°	4283	4214	4270
30°	4139	4061	4117
35°	3989	3905	3972
40°	3836	3733	3807
45°	3674	3571	3655
50°	3525	3395	3485
55°	3373	3234	3343
60°	3227	3063	3181
65°	3082	2893	3016
70°	2892	2695	2845
75°	2684	2455	2631
80°	2444	2170	2400
85°	2235	1939	2166

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3674 cd/sqm

TEST NUMBER: P1214863
 CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.3	3.3
10°-20°	465.1	9.5
20°-30°	687.3	14.0
30°-40°	801.0	16.3
40°-50°	804.7	16.4
50°-60°	716.4	14.6
60°-70°	558.4	11.4
70°-80°	356.1	7.2
80°-90°	160.1	3.3
90°-100°	74.2	1.5
100°-110°	53.6	1.1
110°-120°	35.7	0.7
120°-130°	20.7	0.4
130°-140°	10.1	0.2
140°-150°	3.7	0.1
150°-160°	0.6	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1316.7	26.8
0°-40°	2117.7	43.1
0°-60°	3638.8	74.1
0°-90°	4713.4	96.0
90°-120°	163.6	3.3
90°-150°	198.1	4.0
90°-180°	199.0	4.1
0°-180°	4912.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1740	1740	1740	1740	1740	
5°	1732	1731	1731	1731	1732	164
15°	1652	1651	1649	1650	1652	465
25°	1496	1495	1494	1491	1492	689
35°	1282	1283	1283	1277	1277	803
45°	1043	1047	1044	1040	1037	806
55°	801	804	801	798	794	718
65°	567	569	565	562	555	560
75°	335	340	336	335	329	355
85°	139	144	144	142	134	133
90°	75	82	84	82	76	44
95°	63	68	70	68	64	50
105°	50	50	52	51	49	53
115°	36	36	37	35	36	36
125°	24	22	24	22	24	22
135°	14	13	12	12	14	12
145°	8	6	4	5	7	5
155°	2	1	1	1	2	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P1214863

CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1740.3	1740.3	1740.3	1740.3	1740.3
2.5°	1739.1	1737.9	1737.3	1738.5	1740.3
5°	1732.4	1730.6	1730.6	1731.2	1732.4
7.5°	1719.7	1718.5	1717.3	1719.1	1720.3
10°	1702.8	1701.6	1701.0	1701.6	1702.8
12.5°	1681.0	1678.0	1678.0	1679.2	1681.0
15°	1652.5	1651.3	1648.9	1650.1	1651.9
17.5°	1618.1	1619.3	1616.2	1616.8	1617.5
20°	1581.1	1580.5	1580.5	1579.9	1579.3
22.5°	1541.8	1539.4	1538.8	1536.4	1538.2
25°	1496.4	1494.6	1494.0	1491.0	1491.6
27.5°	1447.4	1445.0	1443.2	1442.0	1440.8
30°	1393.6	1393.6	1392.4	1389.9	1386.3
32.5°	1340.3	1339.7	1337.9	1334.9	1333.7
35°	1282.2	1283.4	1282.8	1276.8	1276.8
37.5°	1226.6	1226.6	1224.1	1220.5	1215.7
40°	1165.4	1166.6	1163.6	1159.4	1156.4
42.5°	1104.9	1106.1	1104.3	1101.3	1095.8
45°	1042.6	1047.4	1044.4	1040.2	1037.2
47.5°	982.7	986.9	982.7	979.7	975.4
50°	922.2	925.2	920.4	917.9	911.9
52.5°	862.3	865.3	861.7	859.3	853.2
55°	801.2	804.2	800.6	797.5	793.9
57.5°	743.1	745.5	742.5	740.7	734.0
60°	682.6	686.2	680.7	678.9	672.9
62.5°	622.1	629.3	622.7	620.2	614.8
65°	567.0	568.8	564.6	561.5	554.9
67.5°	506.5	510.1	505.3	502.8	496.8
70°	448.4	452.6	449.0	446.6	441.1
72.5°	391.5	397.6	391.5	389.7	384.2
75°	335.2	340.1	335.8	334.6	328.6
77.5°	281.4	286.8	281.4	283.2	277.1
80°	229.3	235.4	229.9	231.2	225.1
82.5°	183.3	187.0	185.2	184.0	177.9
85°	138.6	144.0	144.0	142.2	134.3
87.5°	101.7	106.5	108.3	107.7	100.4
90°	75.0	81.7	84.1	82.3	76.2
92.5°	67.8	73.2	75.6	73.8	68.4
95°	62.9	67.8	69.6	68.4	63.5
97.5°	59.3	62.9	64.7	62.9	59.3
100°	56.3	58.7	60.5	58.7	55.7
102.5°	52.6	54.5	56.3	54.5	52.0
105°	49.6	50.2	52.0	50.8	49.0
107.5°	46.6	46.6	47.8	46.6	45.4
110°	43.0	43.0	44.2	43.0	41.8

TEST NUMBER: P1214863

CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	39.3	39.3	40.5	38.7	38.7
115°	36.3	35.7	36.9	35.1	35.7
117.5°	32.7	32.1	33.3	31.5	32.1
120°	29.7	28.4	29.7	27.8	29.0
122.5°	27.2	25.4	26.6	24.8	26.0
125°	24.2	22.4	23.6	21.8	23.6
127.5°	21.8	19.4	20.6	18.8	20.6
130°	19.4	16.9	17.5	15.7	18.8
132.5°	16.9	14.5	15.1	13.9	16.3
135°	14.5	12.7	12.1	12.1	14.5
137.5°	12.7	10.9	9.7	10.3	12.1
140°	10.9	9.1	7.3	8.5	10.3
142.5°	9.1	7.3	5.4	7.3	9.1
145°	7.9	6.1	3.6	5.4	7.3
147.5°	6.1	4.8	1.8	4.2	5.4
150°	4.8	3.0	0.6	3.0	3.6
152.5°	3.0	2.4	0.6	1.8	2.4
155°	1.8	1.2	0.6	1.2	1.8
157.5°	0.6	0.6	0.6	0.6	0.6
160°	0.6	0.6	0.6	0.6	0.6
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1214863

CATALOG NUMBER: 22-ID2-50-CFD2-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.79	17.34	16.22	17.74	18.15	15.73	17.28	16.16	17.68	18.10
	3H	17.63	19.03	18.07	19.44	19.90	17.55	18.95	17.99	19.36	19.82
	4H	18.35	19.68	18.81	20.11	20.58	18.26	19.59	18.72	20.02	20.49
	6H	18.94	20.17	19.41	20.61	21.10	18.84	20.07	19.32	20.52	21.01
	8H	19.16	20.33	19.65	20.80	21.30	19.06	20.24	19.55	20.70	21.20
	12H	19.34	20.47	19.83	20.93	21.45	19.24	20.36	19.73	20.83	21.35
4H	2H	16.39	17.71	16.85	18.14	18.61	16.34	17.67	16.81	18.10	18.57
	3H	18.45	19.57	18.92	20.04	20.54	18.38	19.50	18.86	19.98	20.47
	4H	19.31	20.33	19.81	20.82	21.35	19.23	20.25	19.73	20.74	21.27
	6H	20.04	20.93	20.56	21.45	22.00	19.95	20.85	20.47	21.36	21.91
	8H	20.33	21.16	20.85	21.68	22.24	20.23	21.07	20.75	21.58	22.14
	12H	20.57	21.33	21.11	21.87	22.43	20.47	21.23	21.01	21.77	22.33
8H	4H	19.63	20.47	20.15	20.98	21.54	19.56	20.40	20.08	20.91	21.47
	6H	20.50	21.20	21.05	21.76	22.33	20.42	21.12	20.98	21.68	22.25
	8H	20.88	21.51	21.45	22.08	22.66	20.79	21.42	21.36	22.00	22.57
	12H	21.23	21.79	21.80	22.35	23.00	21.14	21.70	21.71	22.26	22.91
12H	4H	19.67	20.43	20.21	20.97	21.53	19.60	20.36	20.14	20.90	21.47
	6H	20.57	21.20	21.14	21.78	22.35	20.50	21.13	21.07	21.70	22.28
	8H	21.02	21.58	21.58	22.14	22.78	20.93	21.50	21.50	22.05	22.70

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)