

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1214601

Luminaire Tested: 22-ID2-55-CFR1-L830-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1214601
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2506-458-3)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-55-CFR1-L830-U
Description: 2X2 IN DEPTH TROFFER WITH 1INCH CUBE REGRESS LENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5643.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1214601
CATALOG NUMBER: 22-ID2-55-CFR1-L830-U

Luminous Intensity Polar Plot



TEST NUMBER: P1214601

CATALOG NUMBER: 22-ID2-55-CFR1-L830-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	101	97	107	103	99	96	98	95	93		94	92	90		85
2	100	92	85	80	97	90	84	79	87	82	77		83	79	75		72
3	91	81	73	67	89	80	72	67	77	70	65		74	69	64		61
4	84	72	64	57	82	71	63	57	68	62	56		66	60	55		53
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		46
6	72	59	50	44	70	58	49	43	56	48	43		54	48	43		40
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		36
8	62	49	40	35	60	48	40	35	47	39	34		45	39	34		32
9	58	45	37	31	57	44	36	31	43	36	31		42	36	31		29
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6114	6114	6114
5°	6096	6105	6099
10°	6072	6074	6071
15°	6006	6014	6006
20°	5909	5917	5907
25°	5773	5782	5769
30°	5623	5620	5614
35°	5441	5448	5436
40°	5245	5242	5237
45°	5046	5024	5021
50°	4812	4785	4785
55°	4564	4527	4527
60°	4294	4251	4251
65°	3994	3947	3947
70°	3644	3610	3621
75°	3215	3185	3193
80°	2633	2611	2633
85°	1868	1846	1914

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5046 cd/sqm

TEST NUMBER: P1214601
 CATALOG NUMBER: 22-ID2-55-CFR1-L830-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.5	3.8
10°-20°	607.9	10.8
20°-30°	895.4	15.9
30°-40°	1034.7	18.3
40°-50°	1016.7	18.0
50°-60°	862.5	15.3
60°-70°	614.1	10.9
70°-80°	323.6	5.7
80°-90°	73.5	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1717.7	30.4
0°-40°	2752.4	48.8
0°-60°	4631.7	82.1
0°-90°	5643.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5643.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2272	2272	2272	2272	2272	
5°	2257	2260	2260	2260	2258	214
15°	2156	2159	2159	2157	2156	608
25°	1944	1947	1947	1944	1943	895
35°	1656	1658	1658	1651	1655	1035
45°	1326	1319	1320	1312	1319	1022
55°	973	964	965	959	965	870
65°	627	619	620	615	620	622
75°	309	303	306	300	307	329
85°	60	57	60	58	62	75
90°	0	0	0	0	0	

TEST NUMBER: P1214601

CATALOG NUMBER: 22-ID2-55-CFR1-L830-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2271.9	2271.9	2271.9	2271.9	2271.9
2.5°	2268.2	2269.7	2269.0	2269.7	2267.5
5°	2256.6	2260.2	2260.2	2259.5	2258.0
7.5°	2241.3	2244.9	2244.2	2244.2	2241.3
10°	2222.3	2223.8	2223.0	2223.0	2221.6
12.5°	2193.9	2195.3	2194.6	2194.6	2193.1
15°	2155.9	2158.8	2158.8	2157.4	2155.9
17.5°	2112.9	2115.1	2115.8	2112.9	2112.2
20°	2063.3	2065.5	2066.2	2062.6	2062.6
22.5°	2006.4	2009.3	2009.3	2005.7	2006.4
25°	1944.4	1947.3	1947.3	1943.7	1943.0
27.5°	1878.8	1881.0	1880.2	1876.6	1876.6
30°	1809.5	1810.2	1808.8	1802.2	1806.6
32.5°	1734.4	1735.8	1736.6	1729.3	1732.2
35°	1656.3	1658.5	1658.5	1651.2	1654.9
37.5°	1576.1	1576.8	1576.8	1569.5	1573.9
40°	1493.0	1493.0	1492.2	1484.9	1490.8
42.5°	1412.7	1405.4	1406.9	1399.6	1406.2
45°	1325.9	1318.6	1320.1	1312.1	1319.4
47.5°	1237.7	1230.4	1231.1	1226.0	1231.1
50°	1149.4	1142.1	1142.9	1137.0	1142.9
52.5°	1061.2	1053.2	1053.2	1048.1	1053.2
55°	972.9	964.2	964.9	959.1	964.9
57.5°	884.7	875.9	876.7	871.6	876.7
60°	797.9	789.1	789.9	784.8	789.9
62.5°	711.8	703.1	703.8	698.7	708.2
65°	627.2	619.2	619.9	614.8	619.9
67.5°	544.8	536.8	537.5	530.2	541.2
70°	463.1	455.8	458.8	450.0	460.2
72.5°	385.1	377.8	380.7	372.7	382.2
75°	309.2	302.7	306.3	299.8	307.1
77.5°	237.0	231.9	234.8	229.7	235.6
80°	169.9	165.6	168.5	163.4	169.9
82.5°	110.1	106.5	110.1	107.2	110.9
85°	60.5	56.9	59.8	58.3	62.0
87.5°	20.4	18.2	20.4	18.2	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1214601

CATALOG NUMBER: 22-ID2-55-CFR1-L830-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.75	17.53	19.06	19.38	17.12	18.71	17.49	19.02	19.34
	3H	18.77	20.20	19.14	20.52	20.88	18.72	20.15	19.09	20.47	20.83
	4H	19.33	20.67	19.73	21.02	21.40	19.28	20.62	19.67	20.97	21.34
	6H	19.69	20.94	20.10	21.30	21.69	19.64	20.89	20.05	21.25	21.64
	8H	19.79	20.97	20.21	21.36	21.76	19.74	20.93	20.16	21.31	21.71
	12H	19.83	20.97	20.26	21.35	21.78	19.79	20.93	20.22	21.31	21.74
4H	2H	17.73	19.07	18.13	19.42	19.80	17.70	19.04	18.09	19.39	19.76
	3H	19.54	20.66	19.95	21.06	21.46	19.49	20.62	19.90	21.01	21.41
	4H	20.21	21.22	20.64	21.63	22.07	20.16	21.17	20.59	21.59	22.02
	6H	20.68	21.56	21.14	22.00	22.46	20.63	21.51	21.09	21.96	22.41
	8H	20.81	21.63	21.27	22.07	22.54	20.76	21.59	21.22	22.03	22.50
	12H	20.88	21.62	21.36	22.10	22.57	20.84	21.58	21.32	22.06	22.53
8H	4H	20.46	21.28	20.92	21.72	22.19	20.41	21.24	20.87	21.68	22.15
	6H	21.02	21.70	21.51	22.19	22.67	20.97	21.66	21.47	22.15	22.62
	8H	21.19	21.81	21.71	22.31	22.80	21.15	21.77	21.67	22.27	22.76
	12H	21.31	21.85	21.82	22.35	22.91	21.28	21.82	21.79	22.31	22.88
12H	4H	20.47	21.21	20.95	21.69	22.16	20.43	21.17	20.91	21.64	22.11
	6H	21.04	21.66	21.56	22.17	22.65	21.00	21.61	21.51	22.12	22.61
	8H	21.27	21.81	21.77	22.30	22.86	21.23	21.77	21.74	22.26	22.82

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L830-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

Spectral Parameters

CCT (K): 3031
 CIE u' : 0.2493
 CIE v' : 0.5215
 Duv: 0.0005
 CIE x: 0.4355
 CIE y: 0.4049
 CIE z: 0.1596
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 582
 Purity: 52.24762
 Rf: 84.8
 Rg: 95.8

CRI (Ra): 82.5
 R1: 80.7
 R2: 90.5
 R3: 96.7
 R4: 80.7
 R5: 80.9
 R6: 88.5
 R7: 83.0
 R8: 58.8
 R9: 5.8
 R10: 78.6
 R11: 80.2
 R12: 69.8
 R13: 83.0
 R14: 98.8
 R15: 73.0



Test Conditions


Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.59


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3





TM-30-18

Summary

$R_f = 84.8$
 $R_g = 95.8$
 $CIE R_a = 82.5$
 $R_9 = 5.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)