

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1215545

Luminaire Tested: 24-ID2-35-CFR1-L830-U

Issue Date: 12/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1215545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2508-510-6)
Test Lab: INNOVATION CENTER
Issue Date: 12/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 24-ID2-35-CFR1-L830-U
Description: 2X4 IN DEPTH TROFFER WITH 1INCH CUBE REGRESS LENS
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3674.1 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.19 / 1.3
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1215545
CATALOG NUMBER: 24-ID2-35-CFR1-L830-U

Luminous Intensity Polar Plot



TEST NUMBER: P1215545

CATALOG NUMBER: 24-ID2-35-CFR1-L830-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	109	105	101	97	107	103	99	95	98	95	92		94	92	90		85
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		71
3	91	81	73	67	89	79	72	66	77	70	65		74	68	64		61
4	84	72	64	57	81	71	63	57	68	61	56		66	60	55		52
5	77	65	56	49	75	64	55	49	61	54	49		59	53	48		45
6	71	58	50	43	70	57	49	43	56	48	43		54	47	42		40
7	66	53	44	38	65	52	44	38	51	43	38		49	43	38		36
8	62	49	40	34	60	48	40	34	47	39	34		45	39	34		32
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		29
10	54	41	33	28	53	41	33	28	40	33	28		39	32	28		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1964	1964	1964
5°	1970	1961	1963
10°	1959	1950	1952
15°	1942	1931	1930
20°	1914	1902	1899
25°	1881	1863	1860
30°	1837	1816	1807
35°	1786	1759	1750
40°	1725	1698	1678
45°	1668	1630	1609
50°	1597	1559	1533
55°	1520	1478	1445
60°	1439	1393	1359
65°	1352	1296	1253
70°	1244	1187	1139
75°	1109	1044	1007
80°	907	855	813
85°	636	621	573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1668 cd/sqm

TEST NUMBER: P1215545
 CATALOG NUMBER: 24-ID2-35-CFR1-L830-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.9	3.8
10°-20°	390.9	10.6
20°-30°	578.2	15.7
30°-40°	670.9	18.3
40°-50°	662.2	18.0
50°-60°	565.1	15.4
60°-70°	405.1	11.0
70°-80°	214.7	5.8
80°-90°	49.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1107.0	30.1
0°-40°	1777.8	48.4
0°-60°	3005.1	81.8
0°-90°	3674.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3674.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1460	1460	1460	1460	1460	
5°	1458	1454	1452	1450	1453	138
15°	1394	1388	1386	1384	1386	393
25°	1267	1261	1255	1251	1253	583
35°	1087	1081	1071	1066	1066	679
45°	876	868	856	848	846	675
55°	648	641	630	621	616	580
65°	425	419	407	400	394	420
75°	213	208	201	196	194	226
85°	41	42	40	38	37	52
90°	0	0	0	0	0	

TEST NUMBER: P1215545

CATALOG NUMBER: 24-ID2-35-CFR1-L830-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1459.8	1459.8	1459.8	1459.8	1459.8
2.5°	1464.8	1459.3	1457.3	1455.7	1458.8
5°	1458.3	1453.7	1451.7	1449.7	1453.2
7.5°	1448.7	1443.7	1441.2	1439.7	1442.7
10°	1434.2	1429.6	1427.1	1425.6	1428.6
12.5°	1416.1	1411.6	1408.6	1407.1	1410.1
15°	1394.0	1388.5	1386.0	1383.5	1385.5
17.5°	1366.9	1362.9	1359.9	1355.9	1357.9
20°	1336.8	1331.8	1328.7	1325.2	1326.2
22.5°	1303.1	1299.1	1293.6	1290.6	1290.6
25°	1267.0	1261.0	1255.0	1250.9	1252.9
27.5°	1224.3	1219.3	1212.8	1207.3	1207.8
30°	1182.2	1175.6	1168.6	1163.6	1163.1
32.5°	1135.5	1131.0	1120.9	1115.9	1114.4
35°	1087.3	1080.8	1071.2	1065.7	1065.7
37.5°	1036.1	1030.6	1021.0	1013.0	1009.5
40°	982.4	976.9	966.8	958.3	955.3
42.5°	929.2	926.2	911.6	904.6	900.1
45°	876.5	867.9	856.4	848.3	845.8
47.5°	821.2	813.7	800.7	791.6	787.6
50°	763.0	758.0	744.9	733.9	732.4
52.5°	707.8	699.3	689.2	677.2	675.2
55°	648.1	641.0	630.0	621.0	615.9
57.5°	591.8	586.3	575.3	563.2	560.7
60°	534.6	529.1	517.5	508.5	505.0
62.5°	480.9	472.9	463.8	452.3	448.8
65°	424.7	418.7	407.1	399.6	393.6
67.5°	368.5	363.9	354.4	347.4	343.4
70°	316.2	310.7	301.7	293.2	289.6
72.5°	265.0	258.0	249.5	243.5	242.0
75°	213.3	207.8	200.8	195.8	193.8
77.5°	162.6	160.6	154.6	149.1	147.1
80°	117.0	115.5	110.4	106.9	104.9
82.5°	75.8	74.8	72.8	69.8	69.3
85°	41.2	42.2	40.2	38.2	37.1
87.5°	14.6	14.1	13.6	13.1	12.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1215545

CATALOG NUMBER: 24-ID2-35-CFR1-L830-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.45	15.04	13.81	15.35	15.67	13.15	14.74	13.52	15.06	15.37
	3H	15.09	16.53	15.47	16.86	17.22	14.74	16.17	15.12	16.50	16.86
	4H	15.68	17.03	16.08	17.38	17.75	15.29	16.64	15.69	16.99	17.36
	6H	16.06	17.31	16.47	17.67	18.07	15.64	16.89	16.05	17.25	17.64
	8H	16.16	17.35	16.58	17.74	18.14	15.73	16.92	16.15	17.31	17.71
	12H	16.21	17.35	16.64	17.73	18.16	15.77	16.92	16.20	17.30	17.73
4H	2H	13.99	15.34	14.39	15.69	16.06	13.75	15.10	14.15	15.45	15.82
	3H	15.85	16.97	16.26	17.37	17.77	15.55	16.67	15.96	17.07	17.47
	4H	16.55	17.56	16.98	17.98	18.42	16.21	17.22	16.64	17.64	18.07
	6H	17.04	17.93	17.50	18.37	18.83	16.66	17.55	17.12	17.99	18.45
	8H	17.18	18.01	17.64	18.45	18.92	16.79	17.61	17.25	18.06	18.52
	12H	17.26	18.00	17.74	18.48	18.95	16.86	17.60	17.34	18.08	18.55
8H	4H	16.78	17.61	17.24	18.05	18.52	16.48	17.30	16.94	17.75	18.21
	6H	17.37	18.06	17.87	18.55	19.02	17.02	17.71	17.52	18.20	18.67
	8H	17.56	18.18	18.07	18.68	19.17	17.20	17.81	17.71	18.32	18.81
	12H	17.69	18.24	18.20	18.73	19.29	17.32	17.86	17.83	18.35	18.92
12H	4H	16.80	17.54	17.28	18.01	18.48	16.50	17.24	16.98	17.71	18.18
	6H	17.40	18.01	17.91	18.52	19.01	17.06	17.67	17.57	18.18	18.67
	8H	17.63	18.17	18.14	18.66	19.23	17.28	17.82	17.79	18.31	18.88

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-3

Test Date: 07/24/2025

Luminaire Tested: 22ID2-55-CFR1-L830-U

Data in this report applies to families of products including 22ID2-55-CFR1-L830-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L830-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 3000K 80CRI

Spectral Parameters

CCT (K): 3031
 CIE u' : 0.2493
 CIE v' : 0.5215
 Duv: 0.0005
 CIE x: 0.4355
 CIE y: 0.4049
 CIE z: 0.1596
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 582
 Purity: 52.24762
 Rf: 84.8
 Rg: 95.8

CRI (Ra): 82.5
 R1: 80.7
 R2: 90.5
 R3: 96.7
 R4: 80.7
 R5: 80.9
 R6: 88.5
 R7: 83.0
 R8: 58.8
 R9: 5.8
 R10: 78.6
 R11: 80.2
 R12: 69.8
 R13: 83.0
 R14: 98.8
 R15: 73.0



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-458-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.59

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	229	NR	620	922	NR	750	29	NR	880	1	NR
365	0	NR	495	275	NR	625	875	NR	755	25	NR	885	1	NR
370	0	NR	500	326	NR	630	822	NR	760	21	NR	890	1	NR
375	0	NR	505	372	NR	635	764	NR	765	18	NR	895	0	NR
380	0	NR	510	411	NR	640	704	NR	770	15	NR	900	0	NR
385	0	NR	515	447	NR	645	638	NR	775	13	NR	905	0	NR
390	0	NR	520	473	NR	650	577	NR	780	11	NR	910	0	NR
395	1	NR	525	495	NR	655	517	NR	785	10	NR	915	0	NR
400	3	NR	530	515	NR	660	457	NR	790	8	NR	920	0	NR
405	4	NR	535	537	NR	665	404	NR	795	7	NR	925	0	NR
410	7	NR	540	559	NR	670	353	NR	800	6	NR	930	0	NR
415	12	NR	545	584	NR	675	307	NR	805	5	NR	935	0	NR
420	22	NR	550	612	NR	680	267	NR	810	5	NR	940	0	NR
425	40	NR	555	648	NR	685	230	NR	815	4	NR	945	0	NR
430	69	NR	560	688	NR	690	199	NR	820	3	NR	950	0	NR
435	120	NR	565	730	NR	695	170	NR	825	3	NR	955	0	NR
440	212	NR	570	777	NR	700	145	NR	830	3	NR	960	0	NR
445	400	NR	575	824	NR	705	124	NR	835	2	NR	965	0	NR
450	578	NR	580	873	NR	710	106	NR	840	2	NR	970	0	NR
455	478	NR	585	918	NR	715	90	NR	845	2	NR	975	0	NR
460	332	NR	590	958	NR	720	76	NR	850	1	NR	980	0	NR
465	295	NR	595	983	NR	725	65	NR	855	1	NR	985	0	NR
470	231	NR	600	997	NR	730	55	NR	860	1	NR	990	0	NR
475	183	NR	605	998	NR	735	47	NR	865	1	NR	995	0	NR
480	184	NR	610	982	NR	740	40	NR	870	1	NR	1000	0	NR
485	201	NR	615	958	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-3


TM-30-18

Summary

$R_f = 84.8$
 $R_g = 95.8$
 $CIE\ R_a = 82.5$
 $R_9 = 5.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 84	CES51 = 94	CES76 = 80
CES02 = 63	CES27 = 94	CES52 = 94	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 89	CES78 = 79
CES04 = 70	CES29 = 87	CES54 = 91	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 90	CES80 = 90
CES06 = 51	CES31 = 89	CES56 = 87	CES81 = 74
CES07 = 42	CES32 = 82	CES57 = 86	CES82 = 95
CES08 = 41	CES33 = 92	CES58 = 87	CES83 = 94
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 92
CES10 = 76	CES35 = 94	CES60 = 92	CES85 = 77
CES11 = 59	CES36 = 86	CES61 = 88	CES86 = 69
CES12 = 65	CES37 = 94	CES62 = 90	CES87 = 84
CES13 = 43	CES38 = 95	CES63 = 87	CES88 = 88
CES14 = 74	CES39 = 98	CES64 = 81	CES89 = 75
CES15 = 72	CES40 = 95	CES65 = 79	CES90 = 89
CES16 = 47	CES41 = 97	CES66 = 79	CES91 = 77
CES17 = 50	CES42 = 95	CES67 = 78	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 81	CES93 = 79
CES19 = 72	CES44 = 99	CES69 = 86	CES94 = 62
CES20 = 67	CES45 = 93	CES70 = 78	CES95 = 74
CES21 = 87	CES46 = 90	CES71 = 75	CES96 = 84
CES22 = 79	CES47 = 94	CES72 = 91	CES97 = 89
CES23 = 92	CES48 = 85	CES73 = 73	CES98 = 85
CES24 = 91	CES49 = 90	CES74 = 92	CES99 = 77
CES25 = 72	CES50 = 94	CES75 = 78	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)